

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331365-830

Luminaire Tested: **SA2XXDIP-C675D925U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331365-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5954.1 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331365-830
CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331365-830

CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	69	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35	30
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30	26
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26	22
5	67	55	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331365-830

CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	1.6
10°-20°	264.8	4.4
20°-30°	389.2	6.5
30°-40°	452.1	7.6
40°-50°	451.6	7.6
50°-60°	393.8	6.6
60°-70°	291.2	4.9
70°-80°	164.9	2.8
80°-90°	48.7	0.8
90°-100°	195.6	3.3
100°-110°	663.7	11.1
110°-120°	705.1	11.8
120°-130°	580.4	9.7
130°-140°	466.1	7.8
140°-150°	352.2	5.9
150°-160°	247.5	4.2
160°-170°	145.7	2.4
170°-180°	47.4	0.8
0°-30°	748.0	12.6
0°-40°	1200.1	20.2
0°-60°	2045.4	34.4
0°-90°	2550.3	42.8
90°-120°	1564.4	26.3
90°-150°	2963.2	49.8
90°-180°	3404.0	57.2
0°-180°	5954.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	13	32	31	31	4
95°	33	81	369	139	107	35
105°	115	173	697	1246	1060	122
115°	202	255	583	1204	1395	200
125°	282	334	561	975	1132	251
135°	331	395	554	819	938	256
145°	378	435	551	684	749	237
155°	430	464	535	605	629	198
165°	468	483	513	544	552	132
175°	488	489	493	499	498	46
180°	489	489	489	489	489	



TEST NUMBER: P331365-830

CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.0	14.2	14.7	14.7	14.7	15.0	15.6	16.5	17.3	17.2	16.5
90°	0.9	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0
92.5°	11.5	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3
95°	32.9	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6
97.5°	53.6	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3
100°	72.4	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6
102.5°	89.7	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9
105°	114.8	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3
107.5°	141.9	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7
110°	159.9	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8



TEST NUMBER: P331365-830

CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.4	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7
115°	202.3	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9
117.5°	228.9	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6
120°	245.5	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6
122.5°	261.4	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8
125°	282.2	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5
127.5°	298.8	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6
130°	308.6	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3
132.5°	317.5	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3
135°	331.1	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7
137.5°	343.9	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8
140°	353.7	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6
142.5°	363.4	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3
145°	378.1	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4
147.5°	394.0	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2
150°	404.5	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2
152.5°	415.0	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9
155°	429.9	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1
157.5°	442.3	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9
160°	450.6	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2
162.5°	458.8	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1
165°	468.4	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1
167.5°	476.4	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3
170°	481.6	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1
172.5°	484.7	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9
175°	488.2	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9
177.5°	489.9	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331365-830

CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	15.7	14.9	14.7	14.6	14.4	14.2	14.0	13.9
90°	30.1	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	82.0	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	246.5	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	575.1	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	858.8	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1044.7	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1142.9	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1072.2	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1011.3	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0



TEST NUMBER: P331365-830

CATALOG NUMBER: SA2XXDIP-C675D925U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	955.5	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	887.0	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	835.5	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	809.9	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	789.6	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	760.1	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	730.9	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	712.1	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	694.0	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	668.8	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	648.7	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	635.9	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	625.4	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	610.5	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	599.0	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	590.8	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	582.5	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	571.0	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	557.6	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	549.3	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	541.1	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	528.7	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	516.8	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	510.8	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	504.0	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	496.7	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)