

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331390-830

Luminaire Tested: **SA2XXDIP-C865D530U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331390-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5303.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331390-830
CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331390-830

CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	62
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	37
4	77	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331390-830

CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	2.3
10°-20°	344.2	6.5
20°-30°	505.9	9.5
30°-40°	587.6	11.1
40°-50°	587.0	11.1
50°-60°	511.9	9.7
60°-70°	378.5	7.1
70°-80°	214.4	4.0
80°-90°	59.3	1.1
90°-100°	22.7	0.4
100°-110°	83.2	1.6
110°-120°	222.3	4.2
120°-130°	366.9	6.9
130°-140°	390.2	7.4
140°-150°	362.7	6.8
150°-160°	291.6	5.5
160°-170°	187.9	3.5
170°-180°	64.7	1.2
0°-30°	972.3	18.3
0°-40°	1559.9	29.4
0°-60°	2658.7	50.1
0°-90°	3310.9	62.4
90°-120°	328.1	6.2
90°-150°	1447.9	27.3
90°-180°	1992.0	37.6
0°-180°	5303.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	6	10	12	13	4
95°	32	17	19	22	21	39
105°	150	156	30	35	37	160
115°	283	291	304	86	40	278
125°	400	406	416	419	421	356
135°	495	502	507	512	511	382
145°	574	574	582	585	583	359
155°	632	628	634	636	632	291
165°	666	663	664	668	664	188
175°	681	678	679	682	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331390-830

CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.1	17.9	17.7	17.5	17.2	17.1	16.8	16.5	16.2	15.9	15.5
90°	0.5	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4
92.5°	9.9	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7
95°	32.0	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7
97.5°	63.4	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1
100°	87.1	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9
102.5°	113.0	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0
105°	149.5	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2
107.5°	191.1	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8
110°	217.9	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1



TEST NUMBER: P331390-830

CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	243.1	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2
115°	282.9	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9
117.5°	318.4	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0
120°	344.3	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8
122.5°	366.4	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6
125°	399.9	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4
127.5°	430.3	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4
130°	449.6	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1
132.5°	469.3	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4
135°	494.8	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2
137.5°	520.8	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3
140°	537.6	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0
142.5°	551.8	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4
145°	574.0	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7
147.5°	593.4	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4
150°	606.0	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1
152.5°	616.6	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9
155°	632.1	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2
157.5°	644.1	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3
160°	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0
162.5°	657.5	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9
165°	666.0	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3
167.5°	672.3	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5
170°	675.8	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7
172.5°	678.3	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0
175°	681.3	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6
177.5°	681.7	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331390-830

CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	14.9	14.3	13.8	13.4	13.2	13.0	12.8	12.6
90°	10.9	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.0	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.3	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	26.6	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	29.8	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	31.1	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	32.4	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	39.6	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	64.2	53.3	42.3	37.1	37.5	38.0	38.5	38.8



TEST NUMBER: P331390-830

CATALOG NUMBER: SA2XXDIP-C865D530U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.3	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	202.3	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	311.7	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	363.2	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	385.3	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.2	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	446.6	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	465.2	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	483.4	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	509.3	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	533.4	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	548.9	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	563.4	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	583.4	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.0	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	611.7	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	621.6	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	634.9	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.0	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	652.5	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	658.6	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	672.2	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	675.4	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	677.8	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	680.3	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	680.6	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)