

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331713

Luminaire Tested: **SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331713
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5366.4 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331713
CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20													
RC	80					70					50					30					10					0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																
1	101	97	94	90	95	91	88	85	80	78	76	70	68	67	60	59	58	54																
2	93	86	80	76	87	81	76	72	71	68	64	63	60	57	54	52	51	47																
3	86	77	70	64	80	72	66	61	64	59	55	56	53	50	49	47	44	41																
4	79	69	61	55	74	65	58	53	58	52	48	51	47	44	45	42	39	36																
5	73	62	54	48	68	59	52	46	52	47	42	46	42	39	41	38	35	32																
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	38	34	31	29																
7	63	51	43	38	59	49	42	37	44	38	34	39	34	31	35	31	28	26																
8	59	47	39	34	55	45	38	33	40	35	31	36	32	28	32	29	26	24																
9	55	43	36	31	52	41	34	30	37	32	28	33	29	26	30	26	24	22																
10	52	40	33	28	49	38	32	27	34	29	25	31	27	24	28	24	22	20																

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	3.4
10°-20°	504.4	9.4
20°-30°	650.0	12.1
30°-40°	617.7	11.5
40°-50°	529.1	9.9
50°-60°	402.9	7.5
60°-70°	254.7	4.7
70°-80°	127.2	2.4
80°-90°	35.8	0.7
90°-100°	118.6	2.2
100°-110°	402.4	7.5
110°-120°	427.5	8.0
120°-130°	351.9	6.6
130°-140°	282.6	5.3
140°-150°	213.5	4.0
150°-160°	150.1	2.8
160°-170°	88.3	1.6
170°-180°	28.8	0.5
0°-30°	1335.4	24.9
0°-40°	1953.1	36.4
0°-60°	2885.1	53.8
0°-90°	3302.8	61.5
90°-120°	948.4	17.7
90°-150°	1796.4	33.5
90°-180°	2064.0	38.5
0°-180°	5366.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	26
90°	19	1	19	1	19	11
95°	65	20	65	20	65	85
105°	643	70	643	70	643	622
115°	846	123	846	123	846	828
125°	686	171	686	171	686	620
135°	569	201	569	201	569	442
145°	454	229	454	229	454	288
155°	382	261	382	261	382	178
165°	335	284	335	284	335	96
175°	302	296	302	296	302	29
180°	296	296	296	296	296	



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	12.3	12.8	12.8	12.8	12.8	12.7	12.4	13.2	12.8	13.4	12.8
90°	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2	18.8	19.4	18.8
92.5°	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7	62.6	74.1	73.1
95°	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4	195.6	223.6	197.9
97.5°	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7	400.3	381.6	287.4
100°	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7	532.6	450.5	310.2
102.5°	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4	581.9	452.8	301.6
105°	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9	574.3	422.6	284.6
107.5°	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0	524.2	390.2	276.1
110°	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1	492.7	374.7	274.3



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3	470.8	364.6	274.8
115°	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8	443.7	353.6	277.2
117.5°	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5	426.6	348.2	281.3
120°	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0	417.5	345.0	284.0
122.5°	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7	409.7	343.2	287.2
125°	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8	398.6	339.9	292.0
127.5°	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1	388.4	338.0	296.9
130°	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7	381.5	337.0	300.5
132.5°	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8	376.0	336.6	304.2
135°	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5	368.4	335.9	308.5
137.5°	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3	363.0	335.8	312.4
140°	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5	359.9	335.3	314.2
142.5°	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1	356.7	335.3	315.6
145°	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1	352.4	334.2	317.1
147.5°	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2	348.1	332.1	317.5
150°	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1	344.5	330.8	317.1
152.5°	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1	341.3	328.5	316.2
155°	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2	335.3	324.5	314.8
157.5°	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1	329.7	320.4	312.2
160°	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0	325.6	317.7	310.8
162.5°	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0	322.0	315.4	309.4
165°	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5	315.9	310.8	306.8
167.5°	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3	310.0	306.8	304.2
170°	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7	306.8	304.5	302.8
172.5°	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6	303.6	301.8	301.0
175°	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1	299.4	298.8	298.3
177.5°	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	12.1	11.8	11.3	10.4	10.7	11.0	13.2	15.5	13.7	12.6	11.8
90°	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6	2.3	4.6	5.7
92.5°	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0	10.0	14.1	16.7
95°	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0	22.2	27.9	33.1
97.5°	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5	35.6	41.6	49.4
100°	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9	45.6	50.8	59.9
102.5°	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4	55.7	60.8	69.9
105°	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6	71.9	75.8	84.4
107.5°	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0	87.8	91.7	99.6
110°	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9	99.2	102.7	110.1



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0	109.3	113.1	120.1
115°	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6	125.5	128.9	135.7
117.5°	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8	141.1	144.5	150.6
120°	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8	151.1	154.5	159.7
122.5°	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4	160.3	163.7	169.3
125°	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1	172.8	176.2	183.1
127.5°	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1	183.4	188.2	195.7
130°	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1	189.3	195.0	203.0
132.5°	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5	195.3	201.4	209.9
135°	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7	203.0	209.9	218.4
137.5°	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5	211.2	218.1	227.2
140°	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4	216.7	223.6	232.7
142.5°	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4	222.2	228.6	237.7
145°	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3	231.5	237.2	245.8
147.5°	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8	240.5	246.0	253.9
150°	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2	246.9	251.5	258.9
152.5°	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6	252.4	257.0	263.5
155°	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6	261.2	264.6	270.9
157.5°	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1	268.7	271.5	276.9
160°	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2	273.7	276.0	280.6
162.5°	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2	277.8	280.1	283.8
165°	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0	283.4	284.6	288.0
167.5°	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8	288.1	289.1	291.3
170°	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0	290.8	291.4	293.1
172.5°	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8	293.1	292.8	294.5
175°	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0	295.4	294.8	296.0
177.5°	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0	296.1	295.6	296.5
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	11.5	11.3	10.8	11.6	12.3	11.8	11.7	11.1	10.9	11.1	10.7
90°	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2	17.1	18.2	18.8
92.5°	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7	42.7	37.9	34.3
95°	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4	114.6	90.7	78.1
97.5°	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7	285.3	223.6	182.4
100°	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7	450.0	371.8	302.8
102.5°	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4	617.4	560.3	487.1
105°	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9	757.3	764.8	745.9
107.5°	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0	747.1	806.4	834.0
110°	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1	715.1	788.1	834.9



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3	677.3	755.3	808.9
115°	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8	625.6	700.3	759.1
117.5°	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5	583.6	651.4	706.5
120°	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0	561.7	622.2	674.1
122.5°	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7	543.5	600.7	647.6
125°	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8	519.5	569.7	612.5
127.5°	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1	496.3	543.6	583.1
130°	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7	480.8	525.8	563.4
132.5°	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8	466.2	507.6	542.9
135°	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5	443.1	480.8	512.7
137.5°	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3	424.8	454.6	482.5
140°	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5	412.9	439.1	464.2
142.5°	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1	402.4	425.0	446.0
145°	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1	388.9	406.6	423.2
147.5°	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2	378.0	391.8	403.9
150°	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1	370.7	382.7	392.9
152.5°	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1	364.8	374.9	383.8
155°	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2	355.3	363.8	370.1
157.5°	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1	345.7	352.9	357.8
160°	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0	339.3	345.6	349.6
162.5°	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0	333.4	338.8	341.8
165°	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5	324.5	328.5	330.8
167.5°	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3	316.4	319.1	321.2
170°	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7	311.4	313.7	314.8
172.5°	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6	306.8	308.6	309.3
175°	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1	301.7	302.3	302.8
177.5°	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9	297.9	298.4	298.4
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	10.7	10.1	10.7	10.1	10.7	10.1	10.7	10.7	11.1	10.9	11.1
90°	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.2	17.1	18.2
92.5°	33.9	32.1	32.5	31.6	32.5	32.1	33.9	34.3	37.9	42.7	49.7
95°	70.7	66.2	64.4	65.0	64.4	66.2	70.7	78.1	90.7	114.6	149.4
97.5°	155.1	141.1	132.8	128.0	132.8	141.1	155.1	182.4	223.6	285.3	348.7
100°	255.5	231.0	214.4	204.2	214.4	231.0	255.5	302.8	371.8	450.0	520.7
102.5°	435.7	393.8	373.2	359.3	373.2	393.8	435.7	487.1	560.3	617.4	633.4
105°	710.6	675.2	650.7	642.7	650.7	675.2	710.6	745.9	764.8	757.3	692.9
107.5°	838.4	836.5	831.6	821.0	831.6	836.5	838.4	834.0	806.4	747.1	650.0
110°	859.4	870.3	875.4	874.8	875.4	870.3	859.4	834.9	788.1	715.1	613.1



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	843.0	861.1	870.8	873.9	870.8	861.1	843.0	808.9	755.3	677.3	579.3
115°	799.5	825.8	840.6	845.7	840.6	825.8	799.5	759.1	700.3	625.6	537.8
117.5°	747.8	775.5	791.1	795.4	791.1	775.5	747.8	706.5	651.4	583.6	506.5
120°	714.0	740.8	757.3	763.0	757.3	740.8	714.0	674.1	622.2	561.7	491.0
122.5°	683.4	709.8	724.5	729.3	724.5	709.8	683.4	647.6	600.7	543.5	478.7
125°	645.6	667.2	681.5	686.1	681.5	667.2	645.6	612.5	569.7	519.5	460.8
127.5°	611.9	632.2	644.5	648.2	644.5	632.2	611.9	583.1	543.6	496.3	443.1
130°	591.4	610.8	622.2	626.7	622.2	610.8	591.4	563.4	525.8	480.8	431.7
132.5°	570.4	589.8	600.3	604.4	600.3	589.8	570.4	542.9	507.6	466.2	420.8
135°	537.2	556.0	566.3	568.6	566.3	556.0	537.2	512.7	480.8	443.1	405.5
137.5°	504.8	521.0	530.0	533.4	530.0	521.0	504.8	482.5	454.6	424.8	393.3
140°	482.5	497.3	505.8	509.3	505.8	497.3	482.5	464.2	439.1	412.9	385.5
142.5°	463.3	476.8	484.4	485.1	484.4	476.8	463.3	446.0	425.0	402.4	379.1
145°	436.8	446.5	452.2	453.9	452.2	446.5	436.8	423.2	406.6	388.9	370.1
147.5°	415.2	422.9	426.8	427.8	426.8	422.9	415.2	403.9	391.8	378.0	363.2
150°	401.5	408.3	411.7	412.3	411.7	408.3	401.5	392.9	382.7	370.7	358.1
152.5°	390.5	396.5	399.0	399.1	399.0	396.5	390.5	383.8	374.9	364.8	353.1
155°	376.4	380.4	382.7	381.5	382.7	380.4	376.4	370.1	363.8	355.3	346.2
157.5°	362.2	365.6	366.6	366.6	366.6	365.6	362.2	357.8	352.9	345.7	338.1
160°	353.6	356.4	357.0	357.0	357.0	356.4	353.6	349.6	345.6	339.3	333.0
162.5°	345.8	347.8	348.3	347.9	348.3	347.8	345.8	341.8	338.8	333.4	328.0
165°	333.0	335.3	335.3	334.8	335.3	335.3	333.0	330.8	328.5	324.5	320.5
167.5°	322.2	323.5	323.4	322.7	323.4	323.5	322.2	321.2	319.1	316.4	313.3
170°	315.4	317.1	316.5	315.4	316.5	317.1	315.4	314.8	313.7	311.4	309.7
172.5°	309.9	310.7	310.1	309.4	310.1	310.7	309.9	309.3	308.6	306.8	305.6
175°	302.8	303.4	302.8	301.7	302.8	303.4	302.8	302.8	302.3	301.7	301.1
177.5°	298.4	298.4	297.9	297.0	297.9	298.4	298.4	298.4	298.4	297.9	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	11.7	11.8	12.3	11.6	10.8	11.3	11.5	11.8	12.6	13.7	15.5
90°	18.8	19.4	18.8	15.4	11.4	8.6	6.8	5.7	4.6	2.3	0.6
92.5°	62.6	74.1	73.1	56.9	38.8	25.9	20.5	16.7	14.1	10.0	7.0
95°	195.6	223.6	197.9	131.7	82.1	55.9	42.2	33.1	27.9	22.2	20.0
97.5°	400.3	381.6	287.4	177.5	108.4	75.4	59.9	49.4	41.6	35.6	32.5
100°	532.6	450.5	310.2	187.1	117.5	87.3	71.3	59.9	50.8	45.6	43.9
102.5°	581.9	452.8	301.6	187.5	125.7	97.7	81.8	69.9	60.8	55.7	54.4
105°	574.3	422.6	284.6	190.5	139.7	112.9	96.9	84.4	75.8	71.9	69.6
107.5°	524.2	390.2	276.1	198.3	154.1	128.1	112.0	99.6	91.7	87.8	86.0
110°	492.7	374.7	274.3	204.7	163.7	138.6	122.0	110.1	102.7	99.2	96.9



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	470.8	364.6	274.8	211.6	172.8	148.6	131.6	120.1	113.1	109.3	107.0
115°	443.7	353.6	277.2	221.8	187.1	162.5	147.1	135.7	128.9	125.5	122.6
117.5°	426.6	348.2	281.3	232.8	200.2	177.5	161.5	150.6	144.5	141.1	138.8
120°	417.5	345.0	284.0	240.1	209.3	187.1	171.1	159.7	154.5	151.1	148.8
122.5°	409.7	343.2	287.2	246.5	218.0	197.1	180.7	169.3	163.7	160.3	158.4
125°	398.6	339.9	292.0	256.6	231.0	210.4	194.5	183.1	176.2	172.8	171.1
127.5°	388.4	338.0	296.9	266.1	243.1	223.1	206.7	195.7	188.2	183.4	181.1
130°	381.5	337.0	300.5	272.0	250.4	230.4	214.4	203.0	195.0	189.3	187.1
132.5°	376.0	336.6	304.2	278.0	256.7	237.7	221.7	209.9	201.4	195.3	192.5
135°	368.4	335.9	308.5	285.7	265.8	247.5	231.5	218.4	209.9	203.0	200.7
137.5°	363.0	335.8	312.4	291.6	273.1	255.0	240.2	227.2	218.1	211.2	208.5
140°	359.9	335.3	314.2	294.8	277.2	260.1	245.2	232.7	223.6	216.7	214.4
142.5°	356.7	335.3	315.6	297.6	280.4	263.7	249.8	237.7	228.6	222.2	220.4
145°	352.4	334.2	317.1	301.1	285.1	269.7	257.2	245.8	237.2	231.5	229.3
147.5°	348.1	332.1	317.5	303.1	289.0	274.5	263.4	253.9	246.0	240.5	238.8
150°	344.5	330.8	317.1	304.0	290.8	277.7	267.5	258.9	251.5	246.9	245.2
152.5°	341.3	328.5	316.2	304.4	292.7	280.9	271.6	263.5	257.0	252.4	251.6
155°	335.3	324.5	314.8	305.1	295.4	285.7	277.2	270.9	264.6	261.2	260.6
157.5°	329.7	320.4	312.2	305.1	297.3	289.1	282.0	276.9	271.5	268.7	268.1
160°	325.6	317.7	310.8	305.1	298.3	291.4	285.1	280.6	276.0	273.7	273.2
162.5°	322.0	315.4	309.4	304.6	298.7	292.8	287.9	283.8	280.1	277.8	278.2
165°	315.9	310.8	306.8	303.4	299.4	294.3	290.8	288.0	284.6	283.4	284.0
167.5°	310.0	306.8	304.2	302.6	299.3	295.5	293.4	291.3	289.1	288.1	288.8
170°	306.8	304.5	302.8	301.7	298.8	296.0	294.3	293.1	291.4	290.8	292.0
172.5°	303.6	301.8	301.0	300.3	298.4	296.4	295.2	294.5	292.8	293.1	293.8
175°	299.4	298.8	298.3	298.8	297.7	296.5	296.0	296.0	294.8	295.4	296.0
177.5°	297.0	296.5	297.0	297.9	297.0	296.5	296.5	296.5	295.6	296.1	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.2	11.0	10.7	10.4	11.3	11.8	12.1	12.8	13.4	12.8	13.2
90°	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8	18.2
92.5°	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6	49.7
95°	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6	149.4
97.5°	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3	348.7
100°	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6	520.7
102.5°	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9	633.4
105°	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3	692.9
107.5°	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2	650.0
110°	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7	613.1



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8	579.3
115°	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7	537.8
117.5°	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6	506.5
120°	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5	491.0
122.5°	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7	478.7
125°	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6	460.8
127.5°	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4	443.1
130°	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5	431.7
132.5°	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0	420.8
135°	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4	405.5
137.5°	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0	393.3
140°	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9	385.5
142.5°	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7	379.1
145°	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4	370.1
147.5°	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1	363.2
150°	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5	358.1
152.5°	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3	353.1
155°	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3	346.2
157.5°	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7	338.1
160°	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6	333.0
162.5°	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0	328.0
165°	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9	320.5
167.5°	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0	313.3
170°	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8	309.7
172.5°	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6	305.6
175°	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4	301.1
177.5°	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0	297.9
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	12.4	12.7	12.8	12.8	12.8	12.8	12.3
90°	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	715.1	788.1	834.9	859.4	870.3	875.4	874.8



TEST NUMBER: P331713

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)