

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331716

Luminaire Tested: **SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331716  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5082.0 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331716  
CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331716

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	79	74	70	69	66	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	31	38	32	28	33	29	25	29	26	23	21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23675	23675	23675
5°	23765	23378	23506
10°	23582	22996	22799
15°	23311	22313	21670
20°	22936	21340	20270
25°	22552	20236	18912
30°	22018	19099	17169
35°	21498	17864	15640
40°	20976	16585	13873
45°	20361	15150	12271
50°	19733	13700	10698
55°	19088	12141	9188
60°	18338	10498	7627
65°	17490	8821	6946
70°	16475	7265	6387
75°	15234	6625	5958
80°	13445	5923	5430
85°	10578	4668	4668



TEST NUMBER: P331716

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.2	2.7
10°-20°	376.8	7.4
20°-30°	529.2	10.4
30°-40°	577.1	11.4
40°-50°	530.6	10.4
50°-60°	416.7	8.2
60°-70°	271.7	5.3
70°-80°	140.1	2.8
80°-90°	39.0	0.8
90°-100°	118.6	2.3
100°-110°	402.4	7.9
110°-120°	427.5	8.4
120°-130°	351.9	6.9
130°-140°	282.6	5.6
140°-150°	213.5	4.2
150°-160°	150.1	3.0
160°-170°	88.3	1.7
170°-180°	28.8	0.6
0°-30°	1043.3	20.5
0°-40°	1620.3	31.9
0°-60°	2567.6	50.5
0°-90°	3018.4	59.4
90°-120°	948.4	18.7
90°-150°	1796.4	35.3
90°-180°	2064.0	40.6
0°-180°	5082.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1459	1442	1453	1450	139
15°	1395	1378	1335	1310	1296	393
25°	1266	1221	1136	1083	1062	582
35°	1091	1020	906	826	794	682
45°	892	800	664	573	537	688
55°	678	572	431	355	326	606
65°	458	350	231	188	182	454
75°	244	154	106	97	96	258
85°	57	31	25	25	25	67
90°	1	8	19	18	19	3
95°	20	49	224	84	65	21
105°	70	105	423	755	643	74
115°	123	155	354	730	846	122
125°	171	202	340	591	686	152
135°	201	240	336	497	569	155
145°	229	263	334	415	454	144
155°	261	281	324	367	382	120
165°	284	293	311	330	335	80
175°	296	296	299	303	302	28
180°	296	296	296	296	296	



TEST NUMBER: P331716

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1471.6	1470.4	1469.2	1468.0	1466.9	1465.0	1462.4	1459.8	1457.2	1454.6	1457.0
5°	1466.3	1464.8	1463.3	1461.8	1460.4	1457.7	1453.9	1450.1	1446.2	1442.4	1445.0
7.5°	1451.1	1449.3	1447.5	1445.7	1443.8	1440.7	1436.2	1431.7	1427.2	1422.7	1423.5
10°	1438.4	1436.3	1434.3	1432.2	1430.1	1426.2	1420.3	1414.4	1408.5	1402.6	1401.7
12.5°	1422.5	1419.9	1417.4	1414.9	1412.3	1407.3	1399.7	1392.2	1384.6	1377.1	1375.5
15°	1394.6	1391.4	1388.1	1384.9	1381.6	1375.0	1365.0	1355.0	1344.9	1334.9	1329.3
17.5°	1360.4	1355.4	1350.5	1345.5	1340.6	1331.7	1318.8	1305.9	1293.1	1280.2	1273.6
20°	1334.9	1329.0	1323.1	1317.2	1311.3	1301.0	1286.2	1271.5	1256.8	1242.0	1234.6
22.5°	1307.3	1300.7	1294.1	1287.5	1280.9	1269.3	1252.6	1236.0	1219.4	1202.7	1193.2
25°	1265.9	1256.5	1247.0	1237.6	1228.2	1213.7	1194.2	1174.8	1155.3	1135.9	1123.8
27.5°	1216.0	1205.7	1195.5	1185.2	1175.0	1158.9	1136.9	1115.0	1093.0	1071.1	1057.0
30°	1181.0	1169.8	1158.6	1147.4	1136.2	1118.8	1095.2	1071.6	1048.0	1024.4	1009.4
32.5°	1147.0	1133.9	1120.8	1107.7	1094.6	1076.1	1052.0	1027.9	1003.9	979.8	962.7
35°	1090.7	1075.7	1060.7	1045.6	1030.6	1010.1	984.1	958.2	932.3	906.3	887.7
37.5°	1034.5	1018.0	1001.5	984.9	968.4	946.3	918.7	891.0	863.4	835.7	815.2
40°	995.2	977.5	959.8	942.1	924.4	901.3	872.7	844.1	815.5	786.9	765.9
42.5°	954.9	936.2	917.6	899.0	880.3	856.2	826.7	797.1	767.6	738.0	716.4
45°	891.7	871.9	852.2	832.4	812.7	787.3	756.4	725.4	694.4	663.5	642.5
47.5°	830.1	809.2	788.3	767.3	746.4	719.9	688.0	656.0	624.0	592.1	571.3
50°	785.6	764.6	743.7	722.7	701.8	675.1	642.7	610.2	577.8	545.4	525.0
52.5°	742.0	720.1	698.3	676.4	654.5	627.7	596.0	564.2	532.5	500.8	481.1
55°	678.1	655.1	632.1	609.1	586.1	558.6	526.8	494.9	463.1	431.3	413.6
57.5°	612.5	588.9	565.3	541.7	518.2	491.1	460.4	429.8	399.2	368.6	352.4
60°	567.9	544.3	520.8	497.2	473.6	446.6	416.2	385.8	355.5	325.1	310.1
62.5°	524.4	500.8	477.2	453.6	430.0	403.8	374.8	345.9	316.9	287.9	273.6
65°	457.8	433.9	410.0	386.1	362.3	337.0	310.5	284.0	257.4	230.9	220.9
67.5°	393.6	369.9	346.2	322.4	298.7	274.9	251.1	227.2	203.3	179.4	174.8
70°	349.0	326.0	303.0	280.0	257.0	235.3	215.0	194.6	174.3	153.9	151.0
72.5°	306.5	284.5	262.4	240.4	218.3	199.1	182.8	166.4	150.1	133.8	131.3
75°	244.2	223.5	202.9	182.2	161.6	146.3	136.2	126.2	116.2	106.2	104.1
77.5°	182.9	164.7	146.6	128.5	110.4	99.0	94.1	89.3	84.5	79.6	78.4
80°	144.6	129.6	114.6	99.5	84.5	75.5	72.5	69.6	66.6	63.7	62.5
82.5°	109.6	97.9	86.1	74.4	62.7	55.8	53.8	51.8	49.8	47.8	47.1
85°	57.1	50.9	44.7	38.5	32.3	28.8	27.9	27.0	26.1	25.2	25.2
87.5°	17.1	15.6	14.1	12.5	10.8	10.2	10.8	11.6	12.3	12.4	12.0
90°	0.6	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8
92.5°	7.0	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6
95°	20.0	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6
97.5°	32.5	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3
100°	43.9	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6
102.5°	54.4	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9
105°	69.6	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3
107.5°	86.0	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2
110°	96.9	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7



TEST NUMBER: P331716

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8
115°	122.6	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7
117.5°	138.8	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6
120°	148.8	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5
122.5°	158.4	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7
125°	171.1	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6
127.5°	181.1	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4
130°	187.1	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5
132.5°	192.5	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0
135°	200.7	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4
137.5°	208.5	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0
140°	214.4	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9
142.5°	220.4	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7
145°	229.3	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4
147.5°	238.8	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1
150°	245.2	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5
152.5°	251.6	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3
155°	260.6	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3
157.5°	268.1	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7
160°	273.2	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6
162.5°	278.2	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0
165°	284.0	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9
167.5°	288.8	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0
170°	292.0	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8
172.5°	293.8	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6
175°	296.0	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4
177.5°	297.0	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331716

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1459.3	1461.7	1464.0	1465.0	1464.5	1464.0	1463.6	1463.1
5°	1447.7	1450.3	1453.0	1453.9	1453.0	1452.1	1451.2	1450.3
7.5°	1424.3	1425.0	1425.8	1425.4	1423.9	1422.4	1420.8	1419.3
10°	1400.8	1399.9	1399.0	1397.7	1395.9	1394.2	1392.4	1390.6
12.5°	1373.9	1372.3	1370.7	1368.5	1365.5	1362.6	1359.6	1356.7
15°	1323.7	1318.1	1312.5	1308.2	1305.3	1302.3	1299.4	1296.4
17.5°	1266.9	1260.2	1253.6	1247.7	1242.6	1237.6	1232.5	1227.4
20°	1227.3	1219.9	1212.5	1205.6	1199.1	1192.6	1186.1	1179.7
22.5°	1183.8	1174.3	1164.8	1157.6	1152.8	1147.9	1143.1	1138.3
25°	1111.7	1099.6	1087.5	1079.2	1074.8	1070.4	1066.0	1061.6
27.5°	1042.9	1028.8	1014.7	1004.2	997.2	990.1	983.1	976.1
30°	994.3	979.3	964.2	952.7	944.8	936.8	928.9	920.9
32.5°	945.5	928.3	911.2	898.8	891.4	883.9	876.4	868.9
35°	869.1	850.6	832.0	819.5	813.0	806.5	800.0	793.5
37.5°	794.8	774.3	753.9	739.9	732.5	725.0	717.6	710.2
40°	745.0	724.1	703.1	688.8	681.2	673.5	665.8	658.2
42.5°	694.8	673.1	651.5	636.9	629.5	622.1	614.6	607.2
45°	621.6	600.7	579.7	565.7	558.6	551.6	544.5	537.4
47.5°	550.4	529.6	508.8	495.2	488.8	482.3	475.9	469.5
50°	504.7	484.3	464.0	450.7	444.5	438.3	432.1	425.9
52.5°	461.5	441.9	422.2	409.6	403.8	398.1	392.4	386.7
55°	395.9	378.2	360.5	348.8	343.2	337.6	332.0	326.4
57.5°	336.2	320.0	303.8	293.3	288.6	283.8	279.1	274.4
60°	295.0	280.0	264.9	255.1	250.3	245.6	240.9	236.2
62.5°	259.3	245.0	230.6	222.0	219.2	216.4	213.5	210.7
65°	210.8	200.8	190.8	185.3	184.4	183.6	182.7	181.8
67.5°	170.2	165.6	161.0	158.2	157.3	156.3	155.4	154.5
70°	148.0	145.1	142.1	140.1	138.9	137.7	136.5	135.3
72.5°	128.8	126.3	123.8	122.3	121.5	120.8	120.1	119.4
75°	102.0	100.0	97.9	96.7	96.4	96.1	95.8	95.5
77.5°	77.3	76.1	74.9	74.1	73.6	73.1	72.7	72.2
80°	61.3	60.2	59.0	58.4	58.4	58.4	58.4	58.4
82.5°	46.4	45.6	44.9	44.6	44.6	44.6	44.6	44.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2
87.5°	11.7	11.2	11.2	11.2	11.2	11.2	11.2	11.2
90°	18.2	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	49.7	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	149.4	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	348.7	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	520.7	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	633.4	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	692.9	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	650.0	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	613.1	715.1	788.1	834.9	859.4	870.3	875.4	874.8





TEST NUMBER: P331716

CATALOG NUMBER: SA2XXRDIP-C865D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	579.3	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	537.8	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	506.5	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	491.0	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	478.7	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	460.8	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	443.1	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	431.7	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	420.8	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	405.5	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	393.3	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	385.5	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	379.1	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	370.1	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	363.2	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	358.1	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	353.1	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	346.2	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	338.1	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	333.0	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	328.0	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	320.5	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	313.3	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	309.7	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	305.6	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.1	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)