

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331748-830

Luminaire Tested: **SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331748-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6037.1 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60				
1	101	97	93	90	94	91	88	85	79	77	75	69	67	65	59	58	57	52				
2	93	86	80	75	86	80	75	71	70	67	63	61	59	56	53	51	49	45				
3	85	76	69	64	79	72	66	61	63	58	55	55	52	49	48	45	43	39				
4	79	68	61	55	73	64	58	52	57	52	48	50	46	43	43	41	38	35				
5	73	61	54	48	68	58	51	46	51	46	42	45	41	38	40	37	34	31				
6	67	56	48	42	63	53	46	41	47	41	37	42	37	34	37	33	30	28				
7	63	51	43	38	59	48	41	36	43	37	33	38	34	30	34	30	28	25				
8	58	46	39	34	55	44	37	33	40	34	30	35	31	28	31	28	25	23				
9	55	43	35	31	51	41	34	29	37	31	27	33	28	25	29	26	23	21				
10	51	39	32	28	48	38	31	27	34	29	25	30	26	23	27	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	3.3
10°-20°	549.1	9.1
20°-30°	707.5	11.7
30°-40°	672.4	11.1
40°-50°	576.0	9.5
50°-60°	438.6	7.3
60°-70°	277.3	4.6
70°-80°	138.5	2.3
80°-90°	39.5	0.7
90°-100°	55.3	0.9
100°-110°	171.8	2.8
110°-120°	293.7	4.9
120°-130°	386.2	6.4
130°-140°	433.5	7.2
140°-150°	425.0	7.0
150°-160°	356.5	5.9
160°-170°	236.5	3.9
170°-180°	82.6	1.4
0°-30°	1453.7	24.1
0°-40°	2126.0	35.2
0°-60°	3140.7	52.0
0°-90°	3596.0	59.6
90°-120°	520.8	8.6
90°-150°	1765.5	29.2
90°-180°	2441.0	40.4
0°-180°	6037.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	29
90°	25	1	25	1	25	12
95°	46	38	46	38	46	51
105°	164	158	164	158	164	172
115°	295	295	295	295	295	291
125°	430	429	430	429	430	384
135°	561	555	561	555	561	432
145°	681	673	681	673	681	425
155°	776	770	776	770	776	357
165°	838	838	838	838	838	236
175°	869	872	869	872	869	83
180°	873	873	873	873	873	



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	14.2	14.8	14.8	14.7	14.7	14.7	14.8	15.5	14.9	15.6	14.2
90°	25.1	24.9	24.7	24.6	24.4	24.5	24.8	25.2	25.4	25.8	22.1
92.5°	23.8	23.8	23.8	23.8	23.8	23.7	23.7	23.6	23.5	23.5	22.6
95°	45.7	46.0	46.4	46.7	47.0	47.1	47.1	47.1	47.1	47.1	46.8
97.5°	79.1	79.2	79.2	79.3	79.3	79.3	79.3	79.3	79.3	79.3	78.6
100°	100.9	101.1	101.2	101.4	101.6	101.7	101.7	101.7	101.7	101.7	101.1
102.5°	125.6	125.8	126.0	126.2	126.3	126.4	126.2	126.1	125.9	125.8	125.2
105°	163.5	163.5	163.5	163.5	163.5	163.4	163.1	162.8	162.4	162.1	161.7
107.5°	199.3	200.0	200.8	201.5	202.3	202.6	202.4	202.3	202.2	202.0	202.0
110°	226.9	227.4	227.9	228.4	228.8	229.1	229.1	229.1	229.1	229.1	229.1



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.4	253.8	254.1	254.5	254.9	255.2	255.6	256.0	256.5	256.8	256.9
115°	294.7	295.2	295.7	296.1	296.6	297.0	297.2	297.3	297.5	297.7	297.9
117.5°	334.0	334.5	335.0	335.5	336.0	336.4	336.9	337.2	337.6	338.0	338.9
120°	361.7	362.2	362.7	363.2	363.7	363.9	363.9	363.9	363.9	363.9	365.2
122.5°	388.9	389.2	389.6	389.9	390.3	390.7	391.1	391.4	391.8	392.2	393.1
125°	430.3	430.5	430.6	430.7	430.9	431.2	431.7	432.3	432.7	433.2	433.7
127.5°	468.0	468.5	469.0	469.6	470.0	470.6	471.2	471.8	472.4	473.0	473.5
130°	495.1	495.8	496.4	497.0	497.7	498.2	498.5	498.9	499.2	499.5	499.8
132.5°	521.0	521.5	522.1	522.5	523.1	523.8	524.4	525.2	525.9	526.6	526.5
135°	561.4	561.8	562.4	562.9	563.4	563.6	563.8	564.0	564.2	564.3	564.0
137.5°	597.9	598.6	599.3	599.9	600.6	601.0	601.1	601.2	601.3	601.4	601.1
140°	623.3	624.0	624.6	625.3	625.8	626.2	626.2	626.2	626.2	626.2	625.4
142.5°	646.3	647.0	647.5	648.2	648.8	649.1	649.0	648.8	648.8	648.7	648.1
145°	680.7	681.4	682.0	682.7	683.3	683.6	683.4	683.2	683.2	683.0	681.9
147.5°	711.5	712.2	712.8	713.4	714.1	714.2	713.8	713.4	713.0	712.8	712.1
150°	731.6	732.1	732.5	733.0	733.6	733.6	733.0	732.5	732.1	731.6	730.9
152.5°	750.5	751.0	751.7	752.3	752.9	752.9	752.3	751.7	751.0	750.5	749.6
155°	775.8	776.3	776.7	777.2	777.8	777.6	776.7	775.9	775.1	774.3	773.8
157.5°	797.6	798.3	799.2	799.9	800.7	800.6	799.5	798.3	797.2	796.1	795.8
160°	811.2	811.8	812.5	813.1	813.8	813.6	812.7	811.6	810.7	809.6	809.5
162.5°	822.9	823.7	824.5	825.3	826.0	826.0	824.8	823.7	822.6	821.4	821.3
165°	838.4	839.2	840.0	840.8	841.7	841.5	840.4	839.2	838.1	836.9	836.9
167.5°	851.1	852.0	852.8	853.7	854.5	854.3	853.2	852.1	850.9	849.7	849.8
170°	857.5	858.6	859.5	860.5	861.5	861.4	860.3	859.1	858.0	856.8	857.0
172.5°	862.9	863.8	864.8	865.8	866.8	866.7	865.5	864.4	863.3	862.1	862.3
175°	868.6	869.6	870.5	871.6	872.5	872.4	871.3	870.2	869.0	867.9	868.2
177.5°	871.3	872.0	872.8	873.6	874.4	874.4	873.6	872.8	872.0	871.3	871.5
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	13.6	13.4	12.6	11.5	11.7	11.9	14.4	16.9	15.0	13.7	12.9
90°	18.6	15.0	11.4	8.6	6.6	4.7	2.7	0.8	2.7	4.7	6.6
92.5°	21.7	20.8	20.0	18.9	17.4	16.0	14.5	13.1	14.5	16.0	17.4
95°	46.5	46.2	45.8	44.9	43.3	41.6	40.0	38.3	40.0	41.6	43.3
97.5°	78.0	77.4	76.8	75.8	74.3	72.9	71.4	70.0	71.4	72.9	74.3
100°	100.7	100.2	99.7	98.8	97.5	96.1	94.9	93.6	94.9	96.1	97.5
102.5°	124.6	123.9	123.4	122.5	121.5	120.5	119.3	118.3	119.3	120.5	121.5
105°	161.5	161.1	160.8	160.3	159.9	159.4	158.9	158.4	158.9	159.4	159.9
107.5°	202.0	202.0	202.0	201.6	201.0	200.2	199.5	198.8	199.5	200.2	201.0
110°	229.1	229.1	229.1	228.7	227.6	226.7	225.6	224.7	225.6	226.7	227.6



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	257.1	257.2	257.3	256.9	255.9	255.0	254.0	253.0	254.0	255.0	255.9
115°	298.3	298.6	299.0	298.6	297.7	296.6	295.7	294.7	295.7	296.6	297.7
117.5°	339.9	340.7	341.7	341.5	340.2	338.8	337.5	336.2	337.5	338.8	340.2
120°	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	365.2	366.6	367.9
122.5°	394.1	395.0	395.9	395.6	394.0	392.5	390.9	389.3	390.9	392.5	394.0
125°	434.1	434.7	435.2	434.7	433.2	431.7	430.3	428.8	430.3	431.7	433.2
127.5°	474.2	474.8	475.3	474.7	472.9	471.0	469.1	467.2	469.1	471.0	472.9
130°	500.1	500.5	500.8	499.9	497.8	495.7	493.5	491.4	493.5	495.7	497.8
132.5°	526.5	526.4	526.3	525.5	523.7	522.0	520.3	518.5	520.3	522.0	523.7
135°	563.6	563.4	563.0	561.9	560.2	558.4	556.6	554.8	556.6	558.4	560.2
137.5°	600.6	600.2	599.7	598.8	597.4	595.9	594.4	593.0	594.4	595.9	597.4
140°	624.6	623.8	622.9	621.8	620.3	618.9	617.4	616.0	617.4	618.9	620.3
142.5°	647.5	647.0	646.4	645.4	643.9	642.4	640.9	639.5	640.9	642.4	643.9
145°	681.0	680.0	679.0	678.0	676.8	675.7	674.5	673.4	674.5	675.7	676.8
147.5°	711.4	710.8	710.1	709.1	707.7	706.3	704.9	703.6	704.9	706.3	707.7
150°	730.3	729.6	729.0	728.1	727.2	726.1	725.2	724.2	725.2	726.1	727.2
152.5°	748.9	748.1	747.2	746.4	745.5	744.4	743.5	742.4	743.5	744.4	745.5
155°	773.4	772.8	772.3	771.8	771.4	770.9	770.3	769.9	770.3	770.9	771.4
157.5°	795.5	795.2	794.9	794.7	794.3	794.0	793.6	793.3	793.6	794.0	794.3
160°	809.4	809.2	809.0	808.8	808.4	808.1	807.8	807.5	807.8	808.1	808.4
162.5°	821.1	821.0	820.8	820.7	820.6	820.6	820.5	820.4	820.5	820.6	820.6
165°	836.9	836.9	836.9	837.0	837.2	837.4	837.5	837.6	837.5	837.4	837.2
167.5°	849.8	849.9	849.9	850.2	850.6	851.1	851.6	852.1	851.6	851.1	850.6
170°	857.1	857.3	857.4	857.8	858.3	858.8	859.3	859.8	859.3	858.8	858.3
172.5°	862.4	862.6	862.8	863.1	863.6	864.1	864.6	865.1	864.6	864.1	863.6
175°	868.6	868.8	869.2	869.6	870.1	870.5	871.1	871.6	871.1	870.5	870.1
177.5°	871.8	872.0	872.3	872.6	873.0	873.5	873.8	874.2	873.8	873.5	873.0
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	12.7	12.6	12.3	13.0	13.7	13.9	13.8	13.1	13.0	13.0	12.3
90°	8.6	11.4	15.0	18.6	22.1	25.8	25.4	25.2	24.8	24.5	24.4
92.5°	18.9	20.0	20.8	21.7	22.6	23.5	23.5	23.6	23.7	23.7	23.8
95°	44.9	45.8	46.2	46.5	46.8	47.1	47.1	47.1	47.1	47.1	47.0
97.5°	75.8	76.8	77.4	78.0	78.6	79.3	79.3	79.3	79.3	79.3	79.3
100°	98.8	99.7	100.2	100.7	101.1	101.7	101.7	101.7	101.7	101.7	101.6
102.5°	122.5	123.4	123.9	124.6	125.2	125.8	125.9	126.1	126.2	126.4	126.3
105°	160.3	160.8	161.1	161.5	161.7	162.1	162.4	162.8	163.1	163.4	163.5
107.5°	201.6	202.0	202.0	202.0	202.0	202.0	202.2	202.3	202.4	202.6	202.3
110°	228.7	229.1	229.1	229.1	229.1	229.1	229.1	229.1	229.1	229.1	228.8



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	256.9	257.3	257.2	257.1	256.9	256.8	256.5	256.0	255.6	255.2	254.9
115°	298.6	299.0	298.6	298.3	297.9	297.7	297.5	297.3	297.2	297.0	296.6
117.5°	341.5	341.7	340.7	339.9	338.9	338.0	337.6	337.2	336.9	336.4	336.0
120°	369.2	369.2	367.9	366.6	365.2	363.9	363.9	363.9	363.9	363.9	363.7
122.5°	395.6	395.9	395.0	394.1	393.1	392.2	391.8	391.4	391.1	390.7	390.3
125°	434.7	435.2	434.7	434.1	433.7	433.2	432.7	432.3	431.7	431.2	430.9
127.5°	474.7	475.3	474.8	474.2	473.5	473.0	472.4	471.8	471.2	470.6	470.0
130°	499.9	500.8	500.5	500.1	499.8	499.5	499.2	498.9	498.5	498.2	497.7
132.5°	525.5	526.3	526.4	526.5	526.5	526.6	525.9	525.2	524.4	523.8	523.1
135°	561.9	563.0	563.4	563.6	564.0	564.3	564.2	564.0	563.8	563.6	563.4
137.5°	598.8	599.7	600.2	600.6	601.1	601.4	601.3	601.2	601.1	601.0	600.6
140°	621.8	622.9	623.8	624.6	625.4	626.2	626.2	626.2	626.2	626.2	625.8
142.5°	645.4	646.4	647.0	647.5	648.1	648.7	648.8	648.8	649.0	649.1	648.8
145°	678.0	679.0	680.0	681.0	681.9	683.0	683.2	683.2	683.4	683.6	683.3
147.5°	709.1	710.1	710.8	711.4	712.1	712.8	713.0	713.4	713.8	714.2	714.1
150°	728.1	729.0	729.6	730.3	730.9	731.6	732.1	732.5	733.0	733.6	733.6
152.5°	746.4	747.2	748.1	748.9	749.6	750.5	751.0	751.7	752.3	752.9	752.9
155°	771.8	772.3	772.8	773.4	773.8	774.3	775.1	775.9	776.7	777.6	777.8
157.5°	794.7	794.9	795.2	795.5	795.8	796.1	797.2	798.3	799.5	800.6	800.7
160°	808.8	809.0	809.2	809.4	809.5	809.6	810.7	811.6	812.7	813.6	813.8
162.5°	820.7	820.8	821.0	821.1	821.3	821.4	822.6	823.7	824.8	826.0	826.0
165°	837.0	836.9	836.9	836.9	836.9	836.9	838.1	839.2	840.4	841.5	841.7
167.5°	850.2	849.9	849.9	849.8	849.8	849.7	850.9	852.1	853.2	854.3	854.5
170°	857.8	857.4	857.3	857.1	857.0	856.8	858.0	859.1	860.3	861.4	861.5
172.5°	863.1	862.8	862.6	862.4	862.3	862.1	863.3	864.4	865.5	866.7	866.8
175°	869.6	869.2	868.8	868.6	868.2	867.9	869.0	870.2	871.3	872.4	872.5
177.5°	872.6	872.3	872.0	871.8	871.5	871.3	872.0	872.8	873.6	874.4	874.4
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	12.4	11.9	12.5	12.0	12.5	11.9	12.4	12.3	13.0	13.0	13.1
90°	24.6	24.7	24.9	25.1	24.9	24.7	24.6	24.4	24.5	24.8	25.2
92.5°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.7	23.7	23.6
95°	46.7	46.4	46.0	45.7	46.0	46.4	46.7	47.0	47.1	47.1	47.1
97.5°	79.3	79.2	79.2	79.1	79.2	79.2	79.3	79.3	79.3	79.3	79.3
100°	101.4	101.2	101.1	100.9	101.1	101.2	101.4	101.6	101.7	101.7	101.7
102.5°	126.2	126.0	125.8	125.6	125.8	126.0	126.2	126.3	126.4	126.2	126.1
105°	163.5	163.5	163.5	163.5	163.5	163.5	163.5	163.5	163.4	163.1	162.8
107.5°	201.5	200.8	200.0	199.3	200.0	200.8	201.5	202.3	202.6	202.4	202.3
110°	228.4	227.9	227.4	226.9	227.4	227.9	228.4	228.8	229.1	229.1	229.1



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	254.5	254.1	253.8	253.4	253.8	254.1	254.5	254.9	255.2	255.6	256.0
115°	296.1	295.7	295.2	294.7	295.2	295.7	296.1	296.6	297.0	297.2	297.3
117.5°	335.5	335.0	334.5	334.0	334.5	335.0	335.5	336.0	336.4	336.9	337.2
120°	363.2	362.7	362.2	361.7	362.2	362.7	363.2	363.7	363.9	363.9	363.9
122.5°	389.9	389.6	389.2	388.9	389.2	389.6	389.9	390.3	390.7	391.1	391.4
125°	430.7	430.6	430.5	430.3	430.5	430.6	430.7	430.9	431.2	431.7	432.3
127.5°	469.6	469.0	468.5	468.0	468.5	469.0	469.6	470.0	470.6	471.2	471.8
130°	497.0	496.4	495.8	495.1	495.8	496.4	497.0	497.7	498.2	498.5	498.9
132.5°	522.5	522.1	521.5	521.0	521.5	522.1	522.5	523.1	523.8	524.4	525.2
135°	562.9	562.4	561.8	561.4	561.8	562.4	562.9	563.4	563.6	563.8	564.0
137.5°	599.9	599.3	598.6	597.9	598.6	599.3	599.9	600.6	601.0	601.1	601.2
140°	625.3	624.6	624.0	623.3	624.0	624.6	625.3	625.8	626.2	626.2	626.2
142.5°	648.2	647.5	647.0	646.3	647.0	647.5	648.2	648.8	649.1	649.0	648.8
145°	682.7	682.0	681.4	680.7	681.4	682.0	682.7	683.3	683.6	683.4	683.2
147.5°	713.4	712.8	712.2	711.5	712.2	712.8	713.4	714.1	714.2	713.8	713.4
150°	733.0	732.5	732.1	731.6	732.1	732.5	733.0	733.6	733.6	733.0	732.5
152.5°	752.3	751.7	751.0	750.5	751.0	751.7	752.3	752.9	752.9	752.3	751.7
155°	777.2	776.7	776.3	775.8	776.3	776.7	777.2	777.8	777.6	776.7	775.9
157.5°	799.9	799.2	798.3	797.6	798.3	799.2	799.9	800.7	800.6	799.5	798.3
160°	813.1	812.5	811.8	811.2	811.8	812.5	813.1	813.8	813.6	812.7	811.6
162.5°	825.3	824.5	823.7	822.9	823.7	824.5	825.3	826.0	826.0	824.8	823.7
165°	840.8	840.0	839.2	838.4	839.2	840.0	840.8	841.7	841.5	840.4	839.2
167.5°	853.7	852.8	852.0	851.1	852.0	852.8	853.7	854.5	854.3	853.2	852.1
170°	860.5	859.5	858.6	857.5	858.6	859.5	860.5	861.5	861.4	860.3	859.1
172.5°	865.8	864.8	863.8	862.9	863.8	864.8	865.8	866.8	866.7	865.5	864.4
175°	871.6	870.5	869.6	868.6	869.6	870.5	871.6	872.5	872.4	871.3	870.2
177.5°	873.6	872.8	872.0	871.3	872.0	872.8	873.6	874.4	874.4	873.6	872.8
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	13.8	13.9	13.7	13.0	12.3	12.6	12.7	12.9	13.7	15.0	16.9
90°	25.4	25.8	22.1	18.6	15.0	11.4	8.6	6.6	4.7	2.7	0.8
92.5°	23.5	23.5	22.6	21.7	20.8	20.0	18.9	17.4	16.0	14.5	13.1
95°	47.1	47.1	46.8	46.5	46.2	45.8	44.9	43.3	41.6	40.0	38.3
97.5°	79.3	79.3	78.6	78.0	77.4	76.8	75.8	74.3	72.9	71.4	70.0
100°	101.7	101.7	101.1	100.7	100.2	99.7	98.8	97.5	96.1	94.9	93.6
102.5°	125.9	125.8	125.2	124.6	123.9	123.4	122.5	121.5	120.5	119.3	118.3
105°	162.4	162.1	161.7	161.5	161.1	160.8	160.3	159.9	159.4	158.9	158.4
107.5°	202.2	202.0	202.0	202.0	202.0	202.0	201.6	201.0	200.2	199.5	198.8
110°	229.1	229.1	229.1	229.1	229.1	229.1	228.7	227.6	226.7	225.6	224.7



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	256.5	256.8	256.9	257.1	257.2	257.3	256.9	255.9	255.0	254.0	253.0
115°	297.5	297.7	297.9	298.3	298.6	299.0	298.6	297.7	296.6	295.7	294.7
117.5°	337.6	338.0	338.9	339.9	340.7	341.7	341.5	340.2	338.8	337.5	336.2
120°	363.9	363.9	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9
122.5°	391.8	392.2	393.1	394.1	395.0	395.9	395.6	394.0	392.5	390.9	389.3
125°	432.7	433.2	433.7	434.1	434.7	435.2	434.7	433.2	431.7	430.3	428.8
127.5°	472.4	473.0	473.5	474.2	474.8	475.3	474.7	472.9	471.0	469.1	467.2
130°	499.2	499.5	499.8	500.1	500.5	500.8	499.9	497.8	495.7	493.5	491.4
132.5°	525.9	526.6	526.5	526.5	526.4	526.3	525.5	523.7	522.0	520.3	518.5
135°	564.2	564.3	564.0	563.6	563.4	563.0	561.9	560.2	558.4	556.6	554.8
137.5°	601.3	601.4	601.1	600.6	600.2	599.7	598.8	597.4	595.9	594.4	593.0
140°	626.2	626.2	625.4	624.6	623.8	622.9	621.8	620.3	618.9	617.4	616.0
142.5°	648.8	648.7	648.1	647.5	647.0	646.4	645.4	643.9	642.4	640.9	639.5
145°	683.2	683.0	681.9	681.0	680.0	679.0	678.0	676.8	675.7	674.5	673.4
147.5°	713.0	712.8	712.1	711.4	710.8	710.1	709.1	707.7	706.3	704.9	703.6
150°	732.1	731.6	730.9	730.3	729.6	729.0	728.1	727.2	726.1	725.2	724.2
152.5°	751.0	750.5	749.6	748.9	748.1	747.2	746.4	745.5	744.4	743.5	742.4
155°	775.1	774.3	773.8	773.4	772.8	772.3	771.8	771.4	770.9	770.3	769.9
157.5°	797.2	796.1	795.8	795.5	795.2	794.9	794.7	794.3	794.0	793.6	793.3
160°	810.7	809.6	809.5	809.4	809.2	809.0	808.8	808.4	808.1	807.8	807.5
162.5°	822.6	821.4	821.3	821.1	821.0	820.8	820.7	820.6	820.6	820.5	820.4
165°	838.1	836.9	836.9	836.9	836.9	836.9	837.0	837.2	837.4	837.5	837.6
167.5°	850.9	849.7	849.8	849.8	849.9	849.9	850.2	850.6	851.1	851.6	852.1
170°	858.0	856.8	857.0	857.1	857.3	857.4	857.8	858.3	858.8	859.3	859.8
172.5°	863.3	862.1	862.3	862.4	862.6	862.8	863.1	863.6	864.1	864.6	865.1
175°	869.0	867.9	868.2	868.6	868.8	869.2	869.6	870.1	870.5	871.1	871.6
177.5°	872.0	871.3	871.5	871.8	872.0	872.3	872.6	873.0	873.5	873.8	874.2
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.4	11.9	11.7	11.5	12.6	13.4	13.6	14.2	15.6	14.9	15.5
90°	2.7	4.7	6.6	8.6	11.4	15.0	18.6	22.1	25.8	25.4	25.2
92.5°	14.5	16.0	17.4	18.9	20.0	20.8	21.7	22.6	23.5	23.5	23.6
95°	40.0	41.6	43.3	44.9	45.8	46.2	46.5	46.8	47.1	47.1	47.1
97.5°	71.4	72.9	74.3	75.8	76.8	77.4	78.0	78.6	79.3	79.3	79.3
100°	94.9	96.1	97.5	98.8	99.7	100.2	100.7	101.1	101.7	101.7	101.7
102.5°	119.3	120.5	121.5	122.5	123.4	123.9	124.6	125.2	125.8	125.9	126.1
105°	158.9	159.4	159.9	160.3	160.8	161.1	161.5	161.7	162.1	162.4	162.8
107.5°	199.5	200.2	201.0	201.6	202.0	202.0	202.0	202.0	202.0	202.2	202.3
110°	225.6	226.7	227.6	228.7	229.1	229.1	229.1	229.1	229.1	229.1	229.1



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	254.0	255.0	255.9	256.9	257.3	257.2	257.1	256.9	256.8	256.5	256.0
115°	295.7	296.6	297.7	298.6	299.0	298.6	298.3	297.9	297.7	297.5	297.3
117.5°	337.5	338.8	340.2	341.5	341.7	340.7	339.9	338.9	338.0	337.6	337.2
120°	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	363.9	363.9
122.5°	390.9	392.5	394.0	395.6	395.9	395.0	394.1	393.1	392.2	391.8	391.4
125°	430.3	431.7	433.2	434.7	435.2	434.7	434.1	433.7	433.2	432.7	432.3
127.5°	469.1	471.0	472.9	474.7	475.3	474.8	474.2	473.5	473.0	472.4	471.8
130°	493.5	495.7	497.8	499.9	500.8	500.5	500.1	499.8	499.5	499.2	498.9
132.5°	520.3	522.0	523.7	525.5	526.3	526.4	526.5	526.5	526.6	525.9	525.2
135°	556.6	558.4	560.2	561.9	563.0	563.4	563.6	564.0	564.3	564.2	564.0
137.5°	594.4	595.9	597.4	598.8	599.7	600.2	600.6	601.1	601.4	601.3	601.2
140°	617.4	618.9	620.3	621.8	622.9	623.8	624.6	625.4	626.2	626.2	626.2
142.5°	640.9	642.4	643.9	645.4	646.4	647.0	647.5	648.1	648.7	648.8	648.8
145°	674.5	675.7	676.8	678.0	679.0	680.0	681.0	681.9	683.0	683.2	683.2
147.5°	704.9	706.3	707.7	709.1	710.1	710.8	711.4	712.1	712.8	713.0	713.4
150°	725.2	726.1	727.2	728.1	729.0	729.6	730.3	730.9	731.6	732.1	732.5
152.5°	743.5	744.4	745.5	746.4	747.2	748.1	748.9	749.6	750.5	751.0	751.7
155°	770.3	770.9	771.4	771.8	772.3	772.8	773.4	773.8	774.3	775.1	775.9
157.5°	793.6	794.0	794.3	794.7	794.9	795.2	795.5	795.8	796.1	797.2	798.3
160°	807.8	808.1	808.4	808.8	809.0	809.2	809.4	809.5	809.6	810.7	811.6
162.5°	820.5	820.6	820.6	820.7	820.8	821.0	821.1	821.3	821.4	822.6	823.7
165°	837.5	837.4	837.2	837.0	836.9	836.9	836.9	836.9	836.9	838.1	839.2
167.5°	851.6	851.1	850.6	850.2	849.9	849.9	849.8	849.8	849.7	850.9	852.1
170°	859.3	858.8	858.3	857.8	857.4	857.3	857.1	857.0	856.8	858.0	859.1
172.5°	864.6	864.1	863.6	863.1	862.8	862.6	862.4	862.3	862.1	863.3	864.4
175°	871.1	870.5	870.1	869.6	869.2	868.8	868.6	868.2	867.9	869.0	870.2
177.5°	873.8	873.5	873.0	872.6	872.3	872.0	871.8	871.5	871.3	872.0	872.8
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	14.8	14.7	14.7	14.7	14.8	14.8	14.2
90°	24.8	24.5	24.4	24.6	24.7	24.9	25.1
92.5°	23.7	23.7	23.8	23.8	23.8	23.8	23.8
95°	47.1	47.1	47.0	46.7	46.4	46.0	45.7
97.5°	79.3	79.3	79.3	79.3	79.2	79.2	79.1
100°	101.7	101.7	101.6	101.4	101.2	101.1	100.9
102.5°	126.2	126.4	126.3	126.2	126.0	125.8	125.6
105°	163.1	163.4	163.5	163.5	163.5	163.5	163.5
107.5°	202.4	202.6	202.3	201.5	200.8	200.0	199.3
110°	229.1	229.1	228.8	228.4	227.9	227.4	226.9



TEST NUMBER: P331748-830

CATALOG NUMBER: SA2XXRDIP-C1005D725U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	255.6	255.2	254.9	254.5	254.1	253.8	253.4
115°	297.2	297.0	296.6	296.1	295.7	295.2	294.7
117.5°	336.9	336.4	336.0	335.5	335.0	334.5	334.0
120°	363.9	363.9	363.7	363.2	362.7	362.2	361.7
122.5°	391.1	390.7	390.3	389.9	389.6	389.2	388.9
125°	431.7	431.2	430.9	430.7	430.6	430.5	430.3
127.5°	471.2	470.6	470.0	469.6	469.0	468.5	468.0
130°	498.5	498.2	497.7	497.0	496.4	495.8	495.1
132.5°	524.4	523.8	523.1	522.5	522.1	521.5	521.0
135°	563.8	563.6	563.4	562.9	562.4	561.8	561.4
137.5°	601.1	601.0	600.6	599.9	599.3	598.6	597.9
140°	626.2	626.2	625.8	625.3	624.6	624.0	623.3
142.5°	649.0	649.1	648.8	648.2	647.5	647.0	646.3
145°	683.4	683.6	683.3	682.7	682.0	681.4	680.7
147.5°	713.8	714.2	714.1	713.4	712.8	712.2	711.5
150°	733.0	733.6	733.6	733.0	732.5	732.1	731.6
152.5°	752.3	752.9	752.9	752.3	751.7	751.0	750.5
155°	776.7	777.6	777.8	777.2	776.7	776.3	775.8
157.5°	799.5	800.6	800.7	799.9	799.2	798.3	797.6
160°	812.7	813.6	813.8	813.1	812.5	811.8	811.2
162.5°	824.8	826.0	826.0	825.3	824.5	823.7	822.9
165°	840.4	841.5	841.7	840.8	840.0	839.2	838.4
167.5°	853.2	854.3	854.5	853.7	852.8	852.0	851.1
170°	860.3	861.4	861.5	860.5	859.5	858.6	857.5
172.5°	865.5	866.7	866.8	865.8	864.8	863.8	862.9
175°	871.3	872.4	872.5	871.6	870.5	869.6	868.6
177.5°	873.6	874.4	874.4	873.6	872.8	872.0	871.3
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0

(END OF REPORT)