

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331420-935

Luminaire Tested: **SA2XXDIP-C1005D330U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331420-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4916.2 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	71	70	66
2	96	89	83	77	91	85	79	75	78	73	70	71	68	65	65	62	60	57
3	88	79	71	65	84	75	69	63	69	64	59	64	59	56	58	55	52	49
4	81	70	62	56	77	67	60	55	62	56	51	57	52	48	53	49	45	43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	44	40	38
6	69	57	49	43	66	55	47	42	51	45	40	47	42	38	44	39	36	33
7	64	52	44	38	61	50	43	37	47	40	36	43	38	34	40	36	32	30
8	60	48	40	34	57	46	39	34	43	37	32	40	34	31	37	32	29	27
9	56	44	36	31	54	42	35	30	39	33	29	37	32	28	34	30	26	25
10	53	40	33	28	50	39	32	28	37	31	26	34	29	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.5	3.3
10°-20°	475.3	9.7
20°-30°	689.9	14.0
30°-40°	728.0	14.8
40°-50°	644.6	13.1
50°-60°	514.4	10.5
60°-70°	349.6	7.1
70°-80°	179.3	3.6
80°-90°	44.2	0.9
90°-100°	12.8	0.3
100°-110°	47.1	1.0
110°-120°	125.8	2.6
120°-130°	207.7	4.2
130°-140°	220.8	4.5
140°-150°	205.3	4.2
150°-160°	165.0	3.4
160°-170°	106.3	2.2
170°-180°	36.6	0.7
0°-30°	1328.7	27.0
0°-40°	2056.7	41.8
0°-60°	3215.7	65.4
0°-90°	3788.7	77.1
90°-120°	185.7	3.8
90°-150°	819.5	16.7
90°-180°	1127.0	22.9
0°-180°	4916.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	39
90°	8	0	8	0	8	5
95°	12	18	12	18	12	11
105°	21	85	21	85	21	22
115°	23	160	23	160	23	57
125°	238	226	238	226	238	206
135°	289	280	289	280	289	223
145°	330	325	330	325	330	206
155°	358	358	358	358	358	165
165°	376	377	376	377	376	106
175°	383	386	383	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	15.2	15.2	15.7	15.2	15.2	15.6	15.6	15.0	15.4	15.9	16.4
90°	7.5	7.4	7.2	7.1	7.1	6.8	6.5	6.2	5.9	5.6	5.1
92.5°	7.5	7.4	7.4	7.3	7.2	7.1	7.0	6.8	6.6	6.5	6.2
95°	12.0	12.1	12.1	12.1	12.2	12.1	11.8	11.5	11.2	10.8	10.4
97.5°	16.0	15.9	15.8	15.8	15.7	15.5	15.2	15.1	14.8	14.6	13.5
100°	18.7	18.5	18.4	18.3	18.2	17.8	17.4	16.9	16.4	15.8	14.8
102.5°	20.0	19.8	19.6	19.5	19.3	18.9	18.3	17.6	17.0	16.3	25.1
105°	21.2	20.9	20.7	20.4	20.1	19.7	19.0	18.3	17.7	17.0	33.8
107.5°	21.8	21.5	21.3	21.0	20.8	21.0	21.7	22.4	23.1	23.8	44.0
110°	22.0	21.8	21.5	21.3	21.0	23.9	30.1	36.3	42.5	48.7	66.6



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	22.2	22.0	21.8	21.6	21.4	32.6	55.2	77.7	100.3	122.9	127.3
115°	22.8	27.3	31.8	36.2	40.6	57.2	85.8	114.5	143.1	171.8	170.2
117.5°	93.2	107.9	122.5	137.2	151.8	162.6	169.4	176.4	183.3	190.3	189.2
120°	169.8	178.1	186.5	194.8	203.2	207.0	206.3	205.5	204.8	204.1	202.9
122.5°	211.9	213.5	215.2	216.8	218.3	219.0	218.5	218.1	217.7	217.2	216.0
125°	238.0	237.8	237.6	237.5	237.3	236.9	236.5	236.1	235.7	235.2	234.0
127.5°	254.5	254.4	254.4	254.4	254.3	254.0	253.4	252.8	252.1	251.5	250.6
130°	264.8	264.8	264.8	264.9	265.0	264.7	264.0	263.3	262.6	262.0	261.3
132.5°	274.7	274.8	274.9	274.9	275.0	274.7	274.1	273.6	273.0	272.4	271.7
135°	289.2	289.4	289.5	289.6	289.7	289.5	288.9	288.3	287.7	287.1	286.5
137.5°	302.5	302.6	302.9	303.1	303.2	303.1	302.5	301.9	301.3	300.7	300.1
140°	310.6	311.0	311.3	311.6	311.9	311.8	311.3	310.6	310.1	309.5	308.9
142.5°	318.7	319.0	319.3	319.6	319.9	319.9	319.3	318.8	318.3	317.8	317.0
145°	329.8	330.2	330.5	330.8	331.1	331.1	330.6	330.2	329.8	329.3	328.3
147.5°	339.8	340.0	340.3	340.5	340.8	340.8	340.4	340.1	339.8	339.5	338.5
150°	345.8	346.0	346.4	346.7	347.0	347.0	346.6	346.2	345.9	345.5	344.5
152.5°	350.9	351.3	351.7	352.1	352.5	352.5	352.1	351.8	351.4	351.0	350.1
155°	358.0	358.5	359.0	359.5	360.0	360.1	359.6	359.3	359.0	358.5	357.8
157.5°	364.5	365.0	365.5	365.9	366.4	366.4	366.1	365.7	365.2	364.8	364.3
160°	368.3	368.8	369.2	369.6	370.1	370.1	369.7	369.4	368.9	368.6	368.2
162.5°	371.4	372.0	372.5	373.0	373.6	373.6	373.2	372.7	372.4	372.0	371.6
165°	376.1	376.5	376.9	377.4	377.8	377.8	377.4	376.9	376.5	376.1	375.9
167.5°	379.0	379.6	380.1	380.7	381.3	381.3	380.9	380.5	380.0	379.6	379.4
170°	380.8	381.4	381.9	382.5	383.1	383.1	382.7	382.3	381.9	381.4	381.3
172.5°	382.2	382.7	383.3	383.8	384.4	384.4	384.0	383.6	383.1	382.7	382.6
175°	383.3	383.9	384.6	385.2	385.8	385.9	385.5	385.0	384.6	384.2	384.1
177.5°	384.1	384.5	385.0	385.4	385.8	385.9	385.6	385.2	384.9	384.5	384.4
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	16.8	16.6	16.5	17.5	15.8	15.7	13.3	11.7	11.3	10.8	10.0
90°	4.6	4.0	3.6	3.0	2.3	1.6	0.9	0.3	0.9	1.6	2.3
92.5°	5.9	5.7	5.5	5.3	5.4	5.5	5.6	5.6	5.6	5.5	5.4
95°	10.0	9.6	9.1	9.9	12.0	14.0	16.0	18.1	16.0	14.0	12.0
97.5°	12.5	11.5	10.5	12.9	18.7	24.4	30.1	35.9	30.1	24.4	18.7
100°	13.8	12.7	11.6	15.4	23.8	32.3	40.8	49.2	40.8	32.3	23.8
102.5°	33.9	42.7	51.5	56.8	58.6	60.4	62.2	64.0	62.2	60.4	58.6
105°	50.8	67.7	84.6	92.0	90.2	88.3	86.4	84.6	86.4	88.3	90.2
107.5°	64.3	84.6	104.8	114.2	112.7	111.2	109.7	108.1	109.7	111.2	112.7
110°	84.5	102.4	120.2	128.5	127.3	126.0	124.6	123.3	124.6	126.0	127.3



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.7	136.1	140.5	142.2	141.0	139.9	138.7	137.6	138.7	139.9	141.0
115°	168.7	167.1	165.6	164.3	163.2	162.2	161.1	160.1	161.1	162.2	163.2
117.5°	188.1	187.1	186.0	184.9	183.7	182.5	181.3	180.2	181.3	182.5	183.7
120°	201.8	200.7	199.6	198.5	197.7	196.7	195.8	194.8	195.8	196.7	197.7
122.5°	214.7	213.5	212.3	211.3	210.3	209.3	208.4	207.3	208.4	209.3	210.3
125°	232.9	231.7	230.6	229.5	228.8	227.9	227.1	226.4	227.1	227.9	228.8
127.5°	249.8	248.8	248.0	247.1	246.2	245.3	244.4	243.5	244.4	245.3	246.2
130°	260.6	259.9	259.2	258.4	257.4	256.4	255.5	254.4	255.5	256.4	257.4
132.5°	271.0	270.4	269.7	269.0	268.1	267.3	266.4	265.6	266.4	267.3	268.1
135°	285.9	285.3	284.8	284.0	283.0	282.1	281.0	280.1	281.0	282.1	283.0
137.5°	299.4	298.8	298.2	297.5	296.8	296.1	295.4	294.7	295.4	296.1	296.8
140°	308.2	307.5	306.9	306.3	305.7	305.2	304.8	304.3	304.8	305.2	305.7
142.5°	316.2	315.5	314.7	314.1	313.7	313.1	312.7	312.3	312.7	313.1	313.7
145°	327.3	326.1	325.1	324.6	324.7	324.8	324.9	324.9	324.9	324.8	324.7
147.5°	337.4	336.3	335.3	334.9	335.1	335.4	335.6	335.9	335.6	335.4	335.1
150°	343.5	342.5	341.6	341.2	341.6	342.1	342.5	342.9	342.5	342.1	341.6
152.5°	349.1	348.2	347.2	347.1	347.5	348.0	348.5	349.0	348.5	348.0	347.5
155°	357.1	356.4	355.6	355.5	356.0	356.6	357.1	357.7	357.1	356.6	356.0
157.5°	363.8	363.3	362.7	362.7	363.2	363.6	364.1	364.5	364.1	363.6	363.2
160°	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.2	367.8	367.5
162.5°	371.3	370.9	370.7	370.7	371.0	371.4	371.8	372.1	371.8	371.4	371.0
165°	375.7	375.6	375.4	375.5	375.8	376.2	376.6	376.9	376.6	376.2	375.8
167.5°	379.3	379.1	378.9	379.0	379.4	379.8	380.1	380.5	380.1	379.8	379.4
170°	381.2	381.0	380.9	381.0	381.4	381.8	382.1	382.5	382.1	381.8	381.4
172.5°	382.5	382.4	382.2	382.4	382.7	383.1	383.5	383.8	383.5	383.1	382.7
175°	383.9	383.8	383.7	383.8	384.3	384.7	385.1	385.6	385.1	384.7	384.3
177.5°	384.4	384.4	384.4	384.4	384.8	385.1	385.5	385.8	385.5	385.1	384.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	9.6	9.1	8.7	8.9	8.4	8.0	7.5	7.6	7.7	6.6	6.7
90°	3.0	3.6	4.0	4.6	5.1	5.6	5.9	6.2	6.5	6.8	7.1
92.5°	5.3	5.5	5.7	5.9	6.2	6.5	6.6	6.8	7.0	7.1	7.2
95°	9.9	9.1	9.6	10.0	10.4	10.8	11.2	11.5	11.8	12.1	12.2
97.5°	12.9	10.5	11.5	12.5	13.5	14.6	14.8	15.1	15.2	15.5	15.7
100°	15.4	11.6	12.7	13.8	14.8	15.8	16.4	16.9	17.4	17.8	18.2
102.5°	56.8	51.5	42.7	33.9	25.1	16.3	17.0	17.6	18.3	18.9	19.3
105°	92.0	84.6	67.7	50.8	33.8	17.0	17.7	18.3	19.0	19.7	20.1
107.5°	114.2	104.8	84.6	64.3	44.0	23.8	23.1	22.4	21.7	21.0	20.8
110°	128.5	120.2	102.4	84.5	66.6	48.7	42.5	36.3	30.1	23.9	21.0



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.2	140.5	136.1	131.7	127.3	122.9	100.3	77.7	55.2	32.6	21.4
115°	164.3	165.6	167.1	168.7	170.2	171.8	143.1	114.5	85.8	57.2	40.6
117.5°	184.9	186.0	187.1	188.1	189.2	190.3	183.3	176.4	169.4	162.6	151.8
120°	198.5	199.6	200.7	201.8	202.9	204.1	204.8	205.5	206.3	207.0	203.2
122.5°	211.3	212.3	213.5	214.7	216.0	217.2	217.7	218.1	218.5	219.0	218.3
125°	229.5	230.6	231.7	232.9	234.0	235.2	235.7	236.1	236.5	236.9	237.3
127.5°	247.1	248.0	248.8	249.8	250.6	251.5	252.1	252.8	253.4	254.0	254.3
130°	258.4	259.2	259.9	260.6	261.3	262.0	262.6	263.3	264.0	264.7	265.0
132.5°	269.0	269.7	270.4	271.0	271.7	272.4	273.0	273.6	274.1	274.7	275.0
135°	284.0	284.8	285.3	285.9	286.5	287.1	287.7	288.3	288.9	289.5	289.7
137.5°	297.5	298.2	298.8	299.4	300.1	300.7	301.3	301.9	302.5	303.1	303.2
140°	306.3	306.9	307.5	308.2	308.9	309.5	310.1	310.6	311.3	311.8	311.9
142.5°	314.1	314.7	315.5	316.2	317.0	317.8	318.3	318.8	319.3	319.9	319.9
145°	324.6	325.1	326.1	327.3	328.3	329.3	329.8	330.2	330.6	331.1	331.1
147.5°	334.9	335.3	336.3	337.4	338.5	339.5	339.8	340.1	340.4	340.8	340.8
150°	341.2	341.6	342.5	343.5	344.5	345.5	345.9	346.2	346.6	347.0	347.0
152.5°	347.1	347.2	348.2	349.1	350.1	351.0	351.4	351.8	352.1	352.5	352.5
155°	355.5	355.6	356.4	357.1	357.8	358.5	359.0	359.3	359.6	360.1	360.0
157.5°	362.7	362.7	363.3	363.8	364.3	364.8	365.2	365.7	366.1	366.4	366.4
160°	367.1	367.1	367.5	367.8	368.2	368.6	368.9	369.4	369.7	370.1	370.1
162.5°	370.7	370.7	370.9	371.3	371.6	372.0	372.4	372.7	373.2	373.6	373.6
165°	375.5	375.4	375.6	375.7	375.9	376.1	376.5	376.9	377.4	377.8	377.8
167.5°	379.0	378.9	379.1	379.3	379.4	379.6	380.0	380.5	380.9	381.3	381.3
170°	381.0	380.9	381.0	381.2	381.3	381.4	381.9	382.3	382.7	383.1	383.1
172.5°	382.4	382.2	382.4	382.5	382.6	382.7	383.1	383.6	384.0	384.4	384.4
175°	383.8	383.7	383.8	383.9	384.1	384.2	384.6	385.0	385.5	385.9	385.8
177.5°	384.4	384.4	384.4	384.4	384.4	384.5	384.9	385.2	385.6	385.9	385.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	6.7	6.2	6.2	5.8	6.2	6.2	6.7	6.7	6.6	7.7	7.6
90°	7.1	7.2	7.4	7.5	7.4	7.2	7.1	7.1	6.8	6.5	6.2
92.5°	7.3	7.4	7.4	7.5	7.4	7.4	7.3	7.2	7.1	7.0	6.8
95°	12.1	12.1	12.1	12.0	12.1	12.1	12.1	12.2	12.1	11.8	11.5
97.5°	15.8	15.8	15.9	16.0	15.9	15.8	15.8	15.7	15.5	15.2	15.1
100°	18.3	18.4	18.5	18.7	18.5	18.4	18.3	18.2	17.8	17.4	16.9
102.5°	19.5	19.6	19.8	20.0	19.8	19.6	19.5	19.3	18.9	18.3	17.6
105°	20.4	20.7	20.9	21.2	20.9	20.7	20.4	20.1	19.7	19.0	18.3
107.5°	21.0	21.3	21.5	21.8	21.5	21.3	21.0	20.8	21.0	21.7	22.4
110°	21.3	21.5	21.8	22.0	21.8	21.5	21.3	21.0	23.9	30.1	36.3



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	21.6	21.8	22.0	22.2	22.0	21.8	21.6	21.4	32.6	55.2	77.7
115°	36.2	31.8	27.3	22.8	27.3	31.8	36.2	40.6	57.2	85.8	114.5
117.5°	137.2	122.5	107.9	93.2	107.9	122.5	137.2	151.8	162.6	169.4	176.4
120°	194.8	186.5	178.1	169.8	178.1	186.5	194.8	203.2	207.0	206.3	205.5
122.5°	216.8	215.2	213.5	211.9	213.5	215.2	216.8	218.3	219.0	218.5	218.1
125°	237.5	237.6	237.8	238.0	237.8	237.6	237.5	237.3	236.9	236.5	236.1
127.5°	254.4	254.4	254.4	254.5	254.4	254.4	254.4	254.3	254.0	253.4	252.8
130°	264.9	264.8	264.8	264.8	264.8	264.8	264.9	265.0	264.7	264.0	263.3
132.5°	274.9	274.9	274.8	274.7	274.8	274.9	274.9	275.0	274.7	274.1	273.6
135°	289.6	289.5	289.4	289.2	289.4	289.5	289.6	289.7	289.5	288.9	288.3
137.5°	303.1	302.9	302.6	302.5	302.6	302.9	303.1	303.2	303.1	302.5	301.9
140°	311.6	311.3	311.0	310.6	311.0	311.3	311.6	311.9	311.8	311.3	310.6
142.5°	319.6	319.3	319.0	318.7	319.0	319.3	319.6	319.9	319.9	319.3	318.8
145°	330.8	330.5	330.2	329.8	330.2	330.5	330.8	331.1	331.1	330.6	330.2
147.5°	340.5	340.3	340.0	339.8	340.0	340.3	340.5	340.8	340.8	340.4	340.1
150°	346.7	346.4	346.0	345.8	346.0	346.4	346.7	347.0	347.0	346.6	346.2
152.5°	352.1	351.7	351.3	350.9	351.3	351.7	352.1	352.5	352.5	352.1	351.8
155°	359.5	359.0	358.5	358.0	358.5	359.0	359.5	360.0	360.1	359.6	359.3
157.5°	365.9	365.5	365.0	364.5	365.0	365.5	365.9	366.4	366.4	366.1	365.7
160°	369.6	369.2	368.8	368.3	368.8	369.2	369.6	370.1	370.1	369.7	369.4
162.5°	373.0	372.5	372.0	371.4	372.0	372.5	373.0	373.6	373.6	373.2	372.7
165°	377.4	376.9	376.5	376.1	376.5	376.9	377.4	377.8	377.8	377.4	376.9
167.5°	380.7	380.1	379.6	379.0	379.6	380.1	380.7	381.3	381.3	380.9	380.5
170°	382.5	381.9	381.4	380.8	381.4	381.9	382.5	383.1	383.1	382.7	382.3
172.5°	383.8	383.3	382.7	382.2	382.7	383.3	383.8	384.4	384.4	384.0	383.6
175°	385.2	384.6	383.9	383.3	383.9	384.6	385.2	385.8	385.9	385.5	385.0
177.5°	385.4	385.0	384.5	384.1	384.5	385.0	385.4	385.8	385.9	385.6	385.2
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	7.5	8.0	8.4	8.9	8.7	9.1	9.6	10.0	10.8	11.3	11.7
90°	5.9	5.6	5.1	4.6	4.0	3.6	3.0	2.3	1.6	0.9	0.3
92.5°	6.6	6.5	6.2	5.9	5.7	5.5	5.3	5.4	5.5	5.6	5.6
95°	11.2	10.8	10.4	10.0	9.6	9.1	9.9	12.0	14.0	16.0	18.1
97.5°	14.8	14.6	13.5	12.5	11.5	10.5	12.9	18.7	24.4	30.1	35.9
100°	16.4	15.8	14.8	13.8	12.7	11.6	15.4	23.8	32.3	40.8	49.2
102.5°	17.0	16.3	25.1	33.9	42.7	51.5	56.8	58.6	60.4	62.2	64.0
105°	17.7	17.0	33.8	50.8	67.7	84.6	92.0	90.2	88.3	86.4	84.6
107.5°	23.1	23.8	44.0	64.3	84.6	104.8	114.2	112.7	111.2	109.7	108.1
110°	42.5	48.7	66.6	84.5	102.4	120.2	128.5	127.3	126.0	124.6	123.3



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	100.3	122.9	127.3	131.7	136.1	140.5	142.2	141.0	139.9	138.7	137.6
115°	143.1	171.8	170.2	168.7	167.1	165.6	164.3	163.2	162.2	161.1	160.1
117.5°	183.3	190.3	189.2	188.1	187.1	186.0	184.9	183.7	182.5	181.3	180.2
120°	204.8	204.1	202.9	201.8	200.7	199.6	198.5	197.7	196.7	195.8	194.8
122.5°	217.7	217.2	216.0	214.7	213.5	212.3	211.3	210.3	209.3	208.4	207.3
125°	235.7	235.2	234.0	232.9	231.7	230.6	229.5	228.8	227.9	227.1	226.4
127.5°	252.1	251.5	250.6	249.8	248.8	248.0	247.1	246.2	245.3	244.4	243.5
130°	262.6	262.0	261.3	260.6	259.9	259.2	258.4	257.4	256.4	255.5	254.4
132.5°	273.0	272.4	271.7	271.0	270.4	269.7	269.0	268.1	267.3	266.4	265.6
135°	287.7	287.1	286.5	285.9	285.3	284.8	284.0	283.0	282.1	281.0	280.1
137.5°	301.3	300.7	300.1	299.4	298.8	298.2	297.5	296.8	296.1	295.4	294.7
140°	310.1	309.5	308.9	308.2	307.5	306.9	306.3	305.7	305.2	304.8	304.3
142.5°	318.3	317.8	317.0	316.2	315.5	314.7	314.1	313.7	313.1	312.7	312.3
145°	329.8	329.3	328.3	327.3	326.1	325.1	324.6	324.7	324.8	324.9	324.9
147.5°	339.8	339.5	338.5	337.4	336.3	335.3	334.9	335.1	335.4	335.6	335.9
150°	345.9	345.5	344.5	343.5	342.5	341.6	341.2	341.6	342.1	342.5	342.9
152.5°	351.4	351.0	350.1	349.1	348.2	347.2	347.1	347.5	348.0	348.5	349.0
155°	359.0	358.5	357.8	357.1	356.4	355.6	355.5	356.0	356.6	357.1	357.7
157.5°	365.2	364.8	364.3	363.8	363.3	362.7	362.7	363.2	363.6	364.1	364.5
160°	368.9	368.6	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6
162.5°	372.4	372.0	371.6	371.3	370.9	370.7	370.7	371.0	371.4	371.8	372.1
165°	376.5	376.1	375.9	375.7	375.6	375.4	375.5	375.8	376.2	376.6	376.9
167.5°	380.0	379.6	379.4	379.3	379.1	378.9	379.0	379.4	379.8	380.1	380.5
170°	381.9	381.4	381.3	381.2	381.0	380.9	381.0	381.4	381.8	382.1	382.5
172.5°	383.1	382.7	382.6	382.5	382.4	382.2	382.4	382.7	383.1	383.5	383.8
175°	384.6	384.2	384.1	383.9	383.8	383.7	383.8	384.3	384.7	385.1	385.6
177.5°	384.9	384.5	384.4	384.4	384.4	384.4	384.4	384.8	385.1	385.5	385.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.3	15.7	15.8	17.5	16.5	16.6	16.8	16.4	15.9	15.4	15.0
90°	0.9	1.6	2.3	3.0	3.6	4.0	4.6	5.1	5.6	5.9	6.2
92.5°	5.6	5.5	5.4	5.3	5.5	5.7	5.9	6.2	6.5	6.6	6.8
95°	16.0	14.0	12.0	9.9	9.1	9.6	10.0	10.4	10.8	11.2	11.5
97.5°	30.1	24.4	18.7	12.9	10.5	11.5	12.5	13.5	14.6	14.8	15.1
100°	40.8	32.3	23.8	15.4	11.6	12.7	13.8	14.8	15.8	16.4	16.9
102.5°	62.2	60.4	58.6	56.8	51.5	42.7	33.9	25.1	16.3	17.0	17.6
105°	86.4	88.3	90.2	92.0	84.6	67.7	50.8	33.8	17.0	17.7	18.3
107.5°	109.7	111.2	112.7	114.2	104.8	84.6	64.3	44.0	23.8	23.1	22.4
110°	124.6	126.0	127.3	128.5	120.2	102.4	84.5	66.6	48.7	42.5	36.3



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	139.9	141.0	142.2	140.5	136.1	131.7	127.3	122.9	100.3	77.7
115°	161.1	162.2	163.2	164.3	165.6	167.1	168.7	170.2	171.8	143.1	114.5
117.5°	181.3	182.5	183.7	184.9	186.0	187.1	188.1	189.2	190.3	183.3	176.4
120°	195.8	196.7	197.7	198.5	199.6	200.7	201.8	202.9	204.1	204.8	205.5
122.5°	208.4	209.3	210.3	211.3	212.3	213.5	214.7	216.0	217.2	217.7	218.1
125°	227.1	227.9	228.8	229.5	230.6	231.7	232.9	234.0	235.2	235.7	236.1
127.5°	244.4	245.3	246.2	247.1	248.0	248.8	249.8	250.6	251.5	252.1	252.8
130°	255.5	256.4	257.4	258.4	259.2	259.9	260.6	261.3	262.0	262.6	263.3
132.5°	266.4	267.3	268.1	269.0	269.7	270.4	271.0	271.7	272.4	273.0	273.6
135°	281.0	282.1	283.0	284.0	284.8	285.3	285.9	286.5	287.1	287.7	288.3
137.5°	295.4	296.1	296.8	297.5	298.2	298.8	299.4	300.1	300.7	301.3	301.9
140°	304.8	305.2	305.7	306.3	306.9	307.5	308.2	308.9	309.5	310.1	310.6
142.5°	312.7	313.1	313.7	314.1	314.7	315.5	316.2	317.0	317.8	318.3	318.8
145°	324.9	324.8	324.7	324.6	325.1	326.1	327.3	328.3	329.3	329.8	330.2
147.5°	335.6	335.4	335.1	334.9	335.3	336.3	337.4	338.5	339.5	339.8	340.1
150°	342.5	342.1	341.6	341.2	341.6	342.5	343.5	344.5	345.5	345.9	346.2
152.5°	348.5	348.0	347.5	347.1	347.2	348.2	349.1	350.1	351.0	351.4	351.8
155°	357.1	356.6	356.0	355.5	355.6	356.4	357.1	357.8	358.5	359.0	359.3
157.5°	364.1	363.6	363.2	362.7	362.7	363.3	363.8	364.3	364.8	365.2	365.7
160°	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.9	369.4
162.5°	371.8	371.4	371.0	370.7	370.7	370.9	371.3	371.6	372.0	372.4	372.7
165°	376.6	376.2	375.8	375.5	375.4	375.6	375.7	375.9	376.1	376.5	376.9
167.5°	380.1	379.8	379.4	379.0	378.9	379.1	379.3	379.4	379.6	380.0	380.5
170°	382.1	381.8	381.4	381.0	380.9	381.0	381.2	381.3	381.4	381.9	382.3
172.5°	383.5	383.1	382.7	382.4	382.2	382.4	382.5	382.6	382.7	383.1	383.6
175°	385.1	384.7	384.3	383.8	383.7	383.8	383.9	384.1	384.2	384.6	385.0
177.5°	385.5	385.1	384.8	384.4	384.4	384.4	384.4	384.4	384.5	384.9	385.2
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	15.6	15.6	15.2	15.2	15.7	15.2	15.2
90°	6.5	6.8	7.1	7.1	7.2	7.4	7.5
92.5°	7.0	7.1	7.2	7.3	7.4	7.4	7.5
95°	11.8	12.1	12.2	12.1	12.1	12.1	12.0
97.5°	15.2	15.5	15.7	15.8	15.8	15.9	16.0
100°	17.4	17.8	18.2	18.3	18.4	18.5	18.7
102.5°	18.3	18.9	19.3	19.5	19.6	19.8	20.0
105°	19.0	19.7	20.1	20.4	20.7	20.9	21.2
107.5°	21.7	21.0	20.8	21.0	21.3	21.5	21.8
110°	30.1	23.9	21.0	21.3	21.5	21.8	22.0



TEST NUMBER: P331420-935

CATALOG NUMBER: SA2XXDIP-C1005D330U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	55.2	32.6	21.4	21.6	21.8	22.0	22.2
115°	85.8	57.2	40.6	36.2	31.8	27.3	22.8
117.5°	169.4	162.6	151.8	137.2	122.5	107.9	93.2
120°	206.3	207.0	203.2	194.8	186.5	178.1	169.8
122.5°	218.5	219.0	218.3	216.8	215.2	213.5	211.9
125°	236.5	236.9	237.3	237.5	237.6	237.8	238.0
127.5°	253.4	254.0	254.3	254.4	254.4	254.4	254.5
130°	264.0	264.7	265.0	264.9	264.8	264.8	264.8
132.5°	274.1	274.7	275.0	274.9	274.9	274.8	274.7
135°	288.9	289.5	289.7	289.6	289.5	289.4	289.2
137.5°	302.5	303.1	303.2	303.1	302.9	302.6	302.5
140°	311.3	311.8	311.9	311.6	311.3	311.0	310.6
142.5°	319.3	319.9	319.9	319.6	319.3	319.0	318.7
145°	330.6	331.1	331.1	330.8	330.5	330.2	329.8
147.5°	340.4	340.8	340.8	340.5	340.3	340.0	339.8
150°	346.6	347.0	347.0	346.7	346.4	346.0	345.8
152.5°	352.1	352.5	352.5	352.1	351.7	351.3	350.9
155°	359.6	360.1	360.0	359.5	359.0	358.5	358.0
157.5°	366.1	366.4	366.4	365.9	365.5	365.0	364.5
160°	369.7	370.1	370.1	369.6	369.2	368.8	368.3
162.5°	373.2	373.6	373.6	373.0	372.5	372.0	371.4
165°	377.4	377.8	377.8	377.4	376.9	376.5	376.1
167.5°	380.9	381.3	381.3	380.7	380.1	379.6	379.0
170°	382.7	383.1	383.1	382.5	381.9	381.4	380.8
172.5°	384.0	384.4	384.4	383.8	383.3	382.7	382.2
175°	385.5	385.9	385.8	385.2	384.6	383.9	383.3
177.5°	385.6	385.9	385.8	385.4	385.0	384.5	384.1
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7

(END OF REPORT)