

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331438-935

Luminaire Tested: **SA2XXDIP-C1005D725U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331438-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6284.3 lumens  
Efficiency: N/A  
Efficacy: 103.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331438-935  
CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	55	53	50	49	44
3	84	75	68	62	79	71	64	59	62	57	53	54	51	48	47	44	42	38
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37	33
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	32	29
6	66	54	46	40	62	51	44	39	46	40	35	40	36	32	35	32	29	26
7	61	49	41	36	57	47	39	34	41	36	31	37	32	29	32	29	26	23
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23	21
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	2.6
10°-20°	475.3	7.6
20°-30°	689.9	11.0
30°-40°	728.0	11.6
40°-50°	644.6	10.3
50°-60°	514.4	8.2
60°-70°	349.6	5.6
70°-80°	179.3	2.9
80°-90°	45.3	0.7
90°-100°	28.4	0.5
100°-110°	104.1	1.7
110°-120°	278.3	4.4
120°-130°	459.4	7.3
130°-140°	488.6	7.8
140°-150°	454.1	7.2
150°-160°	365.1	5.8
160°-170°	235.3	3.7
170°-180°	81.0	1.3
0°-30°	1328.7	21.1
0°-40°	2056.7	32.7
0°-60°	3215.7	51.2
0°-90°	3789.9	60.3
90°-120°	410.8	6.5
90°-150°	1813.0	28.8
90°-180°	2494.0	39.7
0°-180°	6284.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	39
90°	17	1	17	1	17	9
95°	26	40	26	40	26	25
105°	47	187	47	187	47	49
115°	50	354	50	354	50	126
125°	527	501	527	501	527	456
135°	640	620	640	620	640	493
145°	730	719	730	719	730	456
155°	792	791	792	791	792	365
165°	832	834	832	834	832	235
175°	848	853	848	853	848	81
180°	851	851	851	851	851	



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	17.0	17.0	17.5	16.9	16.8	17.3	17.1	16.4	16.9	17.2	17.6
90°	16.6	16.4	16.1	15.8	15.5	15.1	14.4	13.7	13.0	12.3	11.2
92.5°	16.6	16.4	16.3	16.1	16.0	15.7	15.3	15.0	14.6	14.3	13.8
95°	26.5	26.6	26.8	26.9	27.0	26.8	26.1	25.4	24.7	24.0	23.1
97.5°	35.4	35.2	35.0	34.9	34.7	34.4	33.8	33.2	32.7	32.1	30.0
100°	41.2	41.0	40.7	40.5	40.2	39.5	38.4	37.3	36.2	35.1	32.8
102.5°	44.3	43.8	43.5	43.0	42.7	41.8	40.4	38.9	37.5	36.1	55.5
105°	46.8	46.2	45.7	45.2	44.6	43.6	42.1	40.6	39.1	37.5	74.9
107.5°	48.1	47.6	47.1	46.5	46.0	46.5	48.0	49.5	51.1	52.6	97.4
110°	48.6	48.1	47.5	47.0	46.5	53.0	66.7	80.4	94.1	107.8	147.3



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.2	48.7	48.3	47.9	47.4	72.2	122.1	172.0	222.0	271.8	281.6
115°	50.5	60.4	70.2	80.1	89.9	126.6	189.9	253.3	316.7	380.0	376.6
117.5°	206.2	238.6	271.0	303.3	335.7	359.6	374.9	390.3	405.6	420.9	418.5
120°	375.7	394.2	412.7	431.1	449.6	458.1	456.4	454.8	453.1	451.4	449.0
122.5°	468.8	472.4	476.0	479.6	483.2	484.5	483.5	482.5	481.5	480.5	477.9
125°	526.6	526.2	525.8	525.4	525.0	524.3	523.3	522.4	521.4	520.5	517.8
127.5°	563.1	563.0	562.9	562.8	562.7	562.0	560.6	559.2	557.8	556.4	554.5
130°	585.7	585.8	586.0	586.2	586.3	585.6	584.1	582.6	581.1	579.5	578.1
132.5°	607.9	608.0	608.2	608.3	608.5	607.9	606.6	605.3	604.0	602.7	601.2
135°	639.9	640.2	640.5	640.8	641.0	640.5	639.1	637.7	636.4	635.0	633.8
137.5°	669.1	669.6	670.0	670.5	671.0	670.5	669.2	667.9	666.5	665.2	663.7
140°	687.3	688.0	688.7	689.4	690.1	689.8	688.5	687.3	686.1	684.9	683.4
142.5°	705.1	705.8	706.5	707.1	707.8	707.6	706.5	705.3	704.2	703.1	701.4
145°	729.9	730.6	731.2	731.9	732.5	732.5	731.5	730.6	729.6	728.6	726.3
147.5°	751.7	752.3	752.8	753.4	754.0	753.9	753.2	752.4	751.7	751.1	748.7
150°	764.9	765.6	766.3	767.0	767.7	767.6	766.8	765.9	765.2	764.3	762.2
152.5°	776.3	777.2	778.1	779.0	779.9	780.0	779.1	778.3	777.5	776.6	774.6
155°	792.0	793.2	794.3	795.3	796.4	796.6	795.7	795.0	794.1	793.2	791.6
157.5°	806.5	807.5	808.6	809.7	810.7	810.8	809.9	808.9	808.0	807.1	805.9
160°	814.9	815.8	816.7	817.7	818.6	818.7	817.9	817.1	816.3	815.5	814.6
162.5°	821.7	822.9	824.1	825.3	826.5	826.6	825.6	824.7	823.8	822.9	822.2
165°	832.1	833.0	834.0	835.0	835.9	835.9	835.0	834.0	833.0	832.1	831.6
167.5°	838.6	839.8	841.1	842.3	843.5	843.7	842.7	841.8	840.8	839.8	839.5
170°	842.6	843.8	845.0	846.3	847.5	847.7	846.6	845.7	844.7	843.8	843.5
172.5°	845.5	846.7	848.0	849.2	850.4	850.6	849.6	848.7	847.7	846.7	846.4
175°	848.1	849.5	850.8	852.2	853.6	853.8	852.8	851.9	850.9	850.0	849.6
177.5°	849.7	850.7	851.7	852.6	853.7	853.8	853.0	852.2	851.4	850.7	850.6
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	17.8	17.7	17.4	18.3	16.4	16.0	13.6	11.7	11.5	11.3	10.5
90°	10.2	9.0	7.9	6.6	5.2	3.6	2.2	0.6	2.2	3.6	5.2
92.5°	13.2	12.7	12.1	11.9	12.1	12.1	12.3	12.4	12.3	12.1	12.1
95°	22.1	21.2	20.1	22.0	26.5	31.0	35.6	40.0	35.6	31.0	26.5
97.5°	27.7	25.5	23.2	28.5	41.2	54.0	66.7	79.5	66.7	54.0	41.2
100°	30.5	28.2	25.8	34.0	52.8	71.5	90.2	109.0	90.2	71.5	52.8
102.5°	75.0	94.5	113.9	125.6	129.7	133.6	137.6	141.5	137.6	133.6	129.7
105°	112.3	149.6	187.0	203.6	199.6	195.4	191.3	187.3	191.3	195.4	199.6
107.5°	142.2	187.0	231.9	252.6	249.3	246.0	242.6	239.4	242.6	246.0	249.3
110°	186.9	226.4	266.0	284.3	281.5	278.6	275.7	272.9	275.7	278.6	281.5





TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	291.4	301.2	310.9	314.5	312.0	309.4	306.9	304.4	306.9	309.4	312.0
115°	373.2	369.7	366.4	363.4	361.1	358.8	356.5	354.1	356.5	358.8	361.1
117.5°	416.2	413.9	411.5	409.0	406.4	403.8	401.2	398.6	401.2	403.8	406.4
120°	446.5	444.1	441.6	439.4	437.3	435.2	433.2	431.1	433.2	435.2	437.3
122.5°	475.2	472.5	469.8	467.4	465.2	463.0	460.9	458.7	460.9	463.0	465.2
125°	515.2	512.6	510.1	507.8	506.1	504.3	502.5	500.8	502.5	504.3	506.1
127.5°	552.5	550.6	548.6	546.6	544.7	542.8	540.8	538.8	540.8	542.8	544.7
130°	576.5	575.1	573.5	571.7	569.5	567.3	565.2	562.9	565.2	567.3	569.5
132.5°	599.7	598.2	596.7	595.0	593.1	591.3	589.4	587.5	589.4	591.3	593.1
135°	632.5	631.3	630.1	628.4	626.2	624.0	621.8	619.6	621.8	624.0	626.2
137.5°	662.4	661.0	659.6	658.1	656.6	655.0	653.5	652.0	653.5	655.0	656.6
140°	681.9	680.4	678.9	677.5	676.5	675.4	674.2	673.2	674.2	675.4	676.5
142.5°	699.6	697.9	696.2	694.8	693.9	692.9	691.9	691.0	691.9	692.9	693.9
145°	723.9	721.6	719.3	718.2	718.3	718.5	718.6	718.8	718.6	718.5	718.3
147.5°	746.4	744.2	741.8	741.0	741.5	742.0	742.5	743.0	742.5	742.0	741.5
150°	759.9	757.8	755.6	754.9	756.0	756.9	757.9	758.8	757.9	756.9	756.0
152.5°	772.5	770.4	768.4	767.8	768.9	770.0	771.0	772.1	771.0	770.0	768.9
155°	790.0	788.3	786.7	786.5	787.7	788.9	790.2	791.4	790.2	788.9	787.7
157.5°	804.8	803.7	802.5	802.5	803.5	804.5	805.6	806.6	805.6	804.5	803.5
160°	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	814.6	813.8	813.0
162.5°	821.4	820.7	820.0	820.0	820.9	821.7	822.5	823.4	822.5	821.7	820.9
165°	831.3	830.9	830.4	830.6	831.5	832.3	833.1	834.0	833.1	832.3	831.5
167.5°	839.0	838.7	838.3	838.5	839.4	840.2	841.0	841.8	841.0	840.2	839.4
170°	843.3	843.0	842.7	843.0	843.8	844.6	845.4	846.3	845.4	844.6	843.8
172.5°	846.2	845.9	845.7	845.9	846.7	847.6	848.3	849.2	848.3	847.6	846.7
175°	849.4	849.1	848.9	849.2	850.2	851.1	852.0	853.0	852.0	851.1	850.2
177.5°	850.5	850.3	850.2	850.6	851.4	852.1	852.9	853.7	852.9	852.1	851.4
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	10.3	10.1	9.7	9.9	9.6	9.3	9.0	9.0	9.2	8.3	8.4
90°	6.6	7.9	9.0	10.2	11.2	12.3	13.0	13.7	14.4	15.1	15.5
92.5°	11.9	12.1	12.7	13.2	13.8	14.3	14.6	15.0	15.3	15.7	16.0
95°	22.0	20.1	21.2	22.1	23.1	24.0	24.7	25.4	26.1	26.8	27.0
97.5°	28.5	23.2	25.5	27.7	30.0	32.1	32.7	33.2	33.8	34.4	34.7
100°	34.0	25.8	28.2	30.5	32.8	35.1	36.2	37.3	38.4	39.5	40.2
102.5°	125.6	113.9	94.5	75.0	55.5	36.1	37.5	38.9	40.4	41.8	42.7
105°	203.6	187.0	149.6	112.3	74.9	37.5	39.1	40.6	42.1	43.6	44.6
107.5°	252.6	231.9	187.0	142.2	97.4	52.6	51.1	49.5	48.0	46.5	46.0
110°	284.3	266.0	226.4	186.9	147.3	107.8	94.1	80.4	66.7	53.0	46.5



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	314.5	310.9	301.2	291.4	281.6	271.8	222.0	172.0	122.1	72.2	47.4
115°	363.4	366.4	369.7	373.2	376.6	380.0	316.7	253.3	189.9	126.6	89.9
117.5°	409.0	411.5	413.9	416.2	418.5	420.9	405.6	390.3	374.9	359.6	335.7
120°	439.4	441.6	444.1	446.5	449.0	451.4	453.1	454.8	456.4	458.1	449.6
122.5°	467.4	469.8	472.5	475.2	477.9	480.5	481.5	482.5	483.5	484.5	483.2
125°	507.8	510.1	512.6	515.2	517.8	520.5	521.4	522.4	523.3	524.3	525.0
127.5°	546.6	548.6	550.6	552.5	554.5	556.4	557.8	559.2	560.6	562.0	562.7
130°	571.7	573.5	575.1	576.5	578.1	579.5	581.1	582.6	584.1	585.6	586.3
132.5°	595.0	596.7	598.2	599.7	601.2	602.7	604.0	605.3	606.6	607.9	608.5
135°	628.4	630.1	631.3	632.5	633.8	635.0	636.4	637.7	639.1	640.5	641.0
137.5°	658.1	659.6	661.0	662.4	663.7	665.2	666.5	667.9	669.2	670.5	671.0
140°	677.5	678.9	680.4	681.9	683.4	684.9	686.1	687.3	688.5	689.8	690.1
142.5°	694.8	696.2	697.9	699.6	701.4	703.1	704.2	705.3	706.5	707.6	707.8
145°	718.2	719.3	721.6	723.9	726.3	728.6	729.6	730.6	731.5	732.5	732.5
147.5°	741.0	741.8	744.2	746.4	748.7	751.1	751.7	752.4	753.2	753.9	754.0
150°	754.9	755.6	757.8	759.9	762.2	764.3	765.2	765.9	766.8	767.6	767.7
152.5°	767.8	768.4	770.4	772.5	774.6	776.6	777.5	778.3	779.1	780.0	779.9
155°	786.5	786.7	788.3	790.0	791.6	793.2	794.1	795.0	795.7	796.6	796.4
157.5°	802.5	802.5	803.7	804.8	805.9	807.1	808.0	808.9	809.9	810.8	810.7
160°	812.2	812.2	813.0	813.8	814.6	815.5	816.3	817.1	817.9	818.7	818.6
162.5°	820.0	820.0	820.7	821.4	822.2	822.9	823.8	824.7	825.6	826.6	826.5
165°	830.6	830.4	830.9	831.3	831.6	832.1	833.0	834.0	835.0	835.9	835.9
167.5°	838.5	838.3	838.7	839.0	839.5	839.8	840.8	841.8	842.7	843.7	843.5
170°	843.0	842.7	843.0	843.3	843.5	843.8	844.7	845.7	846.6	847.7	847.5
172.5°	845.9	845.7	845.9	846.2	846.4	846.7	847.7	848.7	849.6	850.6	850.4
175°	849.2	848.9	849.1	849.4	849.6	850.0	850.9	851.9	852.8	853.8	853.6
177.5°	850.6	850.2	850.3	850.5	850.6	850.7	851.4	852.2	853.0	853.8	853.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	8.4	8.0	8.0	7.6	8.0	8.0	8.4	8.4	8.3	9.2	9.0
90°	15.8	16.1	16.4	16.6	16.4	16.1	15.8	15.5	15.1	14.4	13.7
92.5°	16.1	16.3	16.4	16.6	16.4	16.3	16.1	16.0	15.7	15.3	15.0
95°	26.9	26.8	26.6	26.5	26.6	26.8	26.9	27.0	26.8	26.1	25.4
97.5°	34.9	35.0	35.2	35.4	35.2	35.0	34.9	34.7	34.4	33.8	33.2
100°	40.5	40.7	41.0	41.2	41.0	40.7	40.5	40.2	39.5	38.4	37.3
102.5°	43.0	43.5	43.8	44.3	43.8	43.5	43.0	42.7	41.8	40.4	38.9
105°	45.2	45.7	46.2	46.8	46.2	45.7	45.2	44.6	43.6	42.1	40.6
107.5°	46.5	47.1	47.6	48.1	47.6	47.1	46.5	46.0	46.5	48.0	49.5
110°	47.0	47.5	48.1	48.6	48.1	47.5	47.0	46.5	53.0	66.7	80.4



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	47.9	48.3	48.7	49.2	48.7	48.3	47.9	47.4	72.2	122.1	172.0
115°	80.1	70.2	60.4	50.5	60.4	70.2	80.1	89.9	126.6	189.9	253.3
117.5°	303.3	271.0	238.6	206.2	238.6	271.0	303.3	335.7	359.6	374.9	390.3
120°	431.1	412.7	394.2	375.7	394.2	412.7	431.1	449.6	458.1	456.4	454.8
122.5°	479.6	476.0	472.4	468.8	472.4	476.0	479.6	483.2	484.5	483.5	482.5
125°	525.4	525.8	526.2	526.6	526.2	525.8	525.4	525.0	524.3	523.3	522.4
127.5°	562.8	562.9	563.0	563.1	563.0	562.9	562.8	562.7	562.0	560.6	559.2
130°	586.2	586.0	585.8	585.7	585.8	586.0	586.2	586.3	585.6	584.1	582.6
132.5°	608.3	608.2	608.0	607.9	608.0	608.2	608.3	608.5	607.9	606.6	605.3
135°	640.8	640.5	640.2	639.9	640.2	640.5	640.8	641.0	640.5	639.1	637.7
137.5°	670.5	670.0	669.6	669.1	669.6	670.0	670.5	671.0	670.5	669.2	667.9
140°	689.4	688.7	688.0	687.3	688.0	688.7	689.4	690.1	689.8	688.5	687.3
142.5°	707.1	706.5	705.8	705.1	705.8	706.5	707.1	707.8	707.6	706.5	705.3
145°	731.9	731.2	730.6	729.9	730.6	731.2	731.9	732.5	732.5	731.5	730.6
147.5°	753.4	752.8	752.3	751.7	752.3	752.8	753.4	754.0	753.9	753.2	752.4
150°	767.0	766.3	765.6	764.9	765.6	766.3	767.0	767.7	767.6	766.8	765.9
152.5°	779.0	778.1	777.2	776.3	777.2	778.1	779.0	779.9	780.0	779.1	778.3
155°	795.3	794.3	793.2	792.0	793.2	794.3	795.3	796.4	796.6	795.7	795.0
157.5°	809.7	808.6	807.5	806.5	807.5	808.6	809.7	810.7	810.8	809.9	808.9
160°	817.7	816.7	815.8	814.9	815.8	816.7	817.7	818.6	818.7	817.9	817.1
162.5°	825.3	824.1	822.9	821.7	822.9	824.1	825.3	826.5	826.6	825.6	824.7
165°	835.0	834.0	833.0	832.1	833.0	834.0	835.0	835.9	835.9	835.0	834.0
167.5°	842.3	841.1	839.8	838.6	839.8	841.1	842.3	843.5	843.7	842.7	841.8
170°	846.3	845.0	843.8	842.6	843.8	845.0	846.3	847.5	847.7	846.6	845.7
172.5°	849.2	848.0	846.7	845.5	846.7	848.0	849.2	850.4	850.6	849.6	848.7
175°	852.2	850.8	849.5	848.1	849.5	850.8	852.2	853.6	853.8	852.8	851.9
177.5°	852.6	851.7	850.7	849.7	850.7	851.7	852.6	853.7	853.8	853.0	852.2
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	9.0	9.3	9.6	9.9	9.7	10.1	10.3	10.5	11.3	11.5	11.7
90°	13.0	12.3	11.2	10.2	9.0	7.9	6.6	5.2	3.6	2.2	0.6
92.5°	14.6	14.3	13.8	13.2	12.7	12.1	11.9	12.1	12.1	12.3	12.4
95°	24.7	24.0	23.1	22.1	21.2	20.1	22.0	26.5	31.0	35.6	40.0
97.5°	32.7	32.1	30.0	27.7	25.5	23.2	28.5	41.2	54.0	66.7	79.5
100°	36.2	35.1	32.8	30.5	28.2	25.8	34.0	52.8	71.5	90.2	109.0
102.5°	37.5	36.1	55.5	75.0	94.5	113.9	125.6	129.7	133.6	137.6	141.5
105°	39.1	37.5	74.9	112.3	149.6	187.0	203.6	199.6	195.4	191.3	187.3
107.5°	51.1	52.6	97.4	142.2	187.0	231.9	252.6	249.3	246.0	242.6	239.4
110°	94.1	107.8	147.3	186.9	226.4	266.0	284.3	281.5	278.6	275.7	272.9



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.0	271.8	281.6	291.4	301.2	310.9	314.5	312.0	309.4	306.9	304.4
115°	316.7	380.0	376.6	373.2	369.7	366.4	363.4	361.1	358.8	356.5	354.1
117.5°	405.6	420.9	418.5	416.2	413.9	411.5	409.0	406.4	403.8	401.2	398.6
120°	453.1	451.4	449.0	446.5	444.1	441.6	439.4	437.3	435.2	433.2	431.1
122.5°	481.5	480.5	477.9	475.2	472.5	469.8	467.4	465.2	463.0	460.9	458.7
125°	521.4	520.5	517.8	515.2	512.6	510.1	507.8	506.1	504.3	502.5	500.8
127.5°	557.8	556.4	554.5	552.5	550.6	548.6	546.6	544.7	542.8	540.8	538.8
130°	581.1	579.5	578.1	576.5	575.1	573.5	571.7	569.5	567.3	565.2	562.9
132.5°	604.0	602.7	601.2	599.7	598.2	596.7	595.0	593.1	591.3	589.4	587.5
135°	636.4	635.0	633.8	632.5	631.3	630.1	628.4	626.2	624.0	621.8	619.6
137.5°	666.5	665.2	663.7	662.4	661.0	659.6	658.1	656.6	655.0	653.5	652.0
140°	686.1	684.9	683.4	681.9	680.4	678.9	677.5	676.5	675.4	674.2	673.2
142.5°	704.2	703.1	701.4	699.6	697.9	696.2	694.8	693.9	692.9	691.9	691.0
145°	729.6	728.6	726.3	723.9	721.6	719.3	718.2	718.3	718.5	718.6	718.8
147.5°	751.7	751.1	748.7	746.4	744.2	741.8	741.0	741.5	742.0	742.5	743.0
150°	765.2	764.3	762.2	759.9	757.8	755.6	754.9	756.0	756.9	757.9	758.8
152.5°	777.5	776.6	774.6	772.5	770.4	768.4	767.8	768.9	770.0	771.0	772.1
155°	794.1	793.2	791.6	790.0	788.3	786.7	786.5	787.7	788.9	790.2	791.4
157.5°	808.0	807.1	805.9	804.8	803.7	802.5	802.5	803.5	804.5	805.6	806.6
160°	816.3	815.5	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5
162.5°	823.8	822.9	822.2	821.4	820.7	820.0	820.0	820.9	821.7	822.5	823.4
165°	833.0	832.1	831.6	831.3	830.9	830.4	830.6	831.5	832.3	833.1	834.0
167.5°	840.8	839.8	839.5	839.0	838.7	838.3	838.5	839.4	840.2	841.0	841.8
170°	844.7	843.8	843.5	843.3	843.0	842.7	843.0	843.8	844.6	845.4	846.3
172.5°	847.7	846.7	846.4	846.2	845.9	845.7	845.9	846.7	847.6	848.3	849.2
175°	850.9	850.0	849.6	849.4	849.1	848.9	849.2	850.2	851.1	852.0	853.0
177.5°	851.4	850.7	850.6	850.5	850.3	850.2	850.6	851.4	852.1	852.9	853.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.6	16.0	16.4	18.3	17.4	17.7	17.8	17.6	17.2	16.9	16.4
90°	2.2	3.6	5.2	6.6	7.9	9.0	10.2	11.2	12.3	13.0	13.7
92.5°	12.3	12.1	12.1	11.9	12.1	12.7	13.2	13.8	14.3	14.6	15.0
95°	35.6	31.0	26.5	22.0	20.1	21.2	22.1	23.1	24.0	24.7	25.4
97.5°	66.7	54.0	41.2	28.5	23.2	25.5	27.7	30.0	32.1	32.7	33.2
100°	90.2	71.5	52.8	34.0	25.8	28.2	30.5	32.8	35.1	36.2	37.3
102.5°	137.6	133.6	129.7	125.6	113.9	94.5	75.0	55.5	36.1	37.5	38.9
105°	191.3	195.4	199.6	203.6	187.0	149.6	112.3	74.9	37.5	39.1	40.6
107.5°	242.6	246.0	249.3	252.6	231.9	187.0	142.2	97.4	52.6	51.1	49.5
110°	275.7	278.6	281.5	284.3	266.0	226.4	186.9	147.3	107.8	94.1	80.4





TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	306.9	309.4	312.0	314.5	310.9	301.2	291.4	281.6	271.8	222.0	172.0
115°	356.5	358.8	361.1	363.4	366.4	369.7	373.2	376.6	380.0	316.7	253.3
117.5°	401.2	403.8	406.4	409.0	411.5	413.9	416.2	418.5	420.9	405.6	390.3
120°	433.2	435.2	437.3	439.4	441.6	444.1	446.5	449.0	451.4	453.1	454.8
122.5°	460.9	463.0	465.2	467.4	469.8	472.5	475.2	477.9	480.5	481.5	482.5
125°	502.5	504.3	506.1	507.8	510.1	512.6	515.2	517.8	520.5	521.4	522.4
127.5°	540.8	542.8	544.7	546.6	548.6	550.6	552.5	554.5	556.4	557.8	559.2
130°	565.2	567.3	569.5	571.7	573.5	575.1	576.5	578.1	579.5	581.1	582.6
132.5°	589.4	591.3	593.1	595.0	596.7	598.2	599.7	601.2	602.7	604.0	605.3
135°	621.8	624.0	626.2	628.4	630.1	631.3	632.5	633.8	635.0	636.4	637.7
137.5°	653.5	655.0	656.6	658.1	659.6	661.0	662.4	663.7	665.2	666.5	667.9
140°	674.2	675.4	676.5	677.5	678.9	680.4	681.9	683.4	684.9	686.1	687.3
142.5°	691.9	692.9	693.9	694.8	696.2	697.9	699.6	701.4	703.1	704.2	705.3
145°	718.6	718.5	718.3	718.2	719.3	721.6	723.9	726.3	728.6	729.6	730.6
147.5°	742.5	742.0	741.5	741.0	741.8	744.2	746.4	748.7	751.1	751.7	752.4
150°	757.9	756.9	756.0	754.9	755.6	757.8	759.9	762.2	764.3	765.2	765.9
152.5°	771.0	770.0	768.9	767.8	768.4	770.4	772.5	774.6	776.6	777.5	778.3
155°	790.2	788.9	787.7	786.5	786.7	788.3	790.0	791.6	793.2	794.1	795.0
157.5°	805.6	804.5	803.5	802.5	802.5	803.7	804.8	805.9	807.1	808.0	808.9
160°	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	816.3	817.1
162.5°	822.5	821.7	820.9	820.0	820.0	820.7	821.4	822.2	822.9	823.8	824.7
165°	833.1	832.3	831.5	830.6	830.4	830.9	831.3	831.6	832.1	833.0	834.0
167.5°	841.0	840.2	839.4	838.5	838.3	838.7	839.0	839.5	839.8	840.8	841.8
170°	845.4	844.6	843.8	843.0	842.7	843.0	843.3	843.5	843.8	844.7	845.7
172.5°	848.3	847.6	846.7	845.9	845.7	845.9	846.2	846.4	846.7	847.7	848.7
175°	852.0	851.1	850.2	849.2	848.9	849.1	849.4	849.6	850.0	850.9	851.9
177.5°	852.9	852.1	851.4	850.6	850.2	850.3	850.5	850.6	850.7	851.4	852.2
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	17.1	17.3	16.8	16.9	17.5	17.0	17.0
90°	14.4	15.1	15.5	15.8	16.1	16.4	16.6
92.5°	15.3	15.7	16.0	16.1	16.3	16.4	16.6
95°	26.1	26.8	27.0	26.9	26.8	26.6	26.5
97.5°	33.8	34.4	34.7	34.9	35.0	35.2	35.4
100°	38.4	39.5	40.2	40.5	40.7	41.0	41.2
102.5°	40.4	41.8	42.7	43.0	43.5	43.8	44.3
105°	42.1	43.6	44.6	45.2	45.7	46.2	46.8
107.5°	48.0	46.5	46.0	46.5	47.1	47.6	48.1
110°	66.7	53.0	46.5	47.0	47.5	48.1	48.6



TEST NUMBER: P331438-935

CATALOG NUMBER: SA2XXDIP-C1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	122.1	72.2	47.4	47.9	48.3	48.7	49.2
115°	189.9	126.6	89.9	80.1	70.2	60.4	50.5
117.5°	374.9	359.6	335.7	303.3	271.0	238.6	206.2
120°	456.4	458.1	449.6	431.1	412.7	394.2	375.7
122.5°	483.5	484.5	483.2	479.6	476.0	472.4	468.8
125°	523.3	524.3	525.0	525.4	525.8	526.2	526.6
127.5°	560.6	562.0	562.7	562.8	562.9	563.0	563.1
130°	584.1	585.6	586.3	586.2	586.0	585.8	585.7
132.5°	606.6	607.9	608.5	608.3	608.2	608.0	607.9
135°	639.1	640.5	641.0	640.8	640.5	640.2	639.9
137.5°	669.2	670.5	671.0	670.5	670.0	669.6	669.1
140°	688.5	689.8	690.1	689.4	688.7	688.0	687.3
142.5°	706.5	707.6	707.8	707.1	706.5	705.8	705.1
145°	731.5	732.5	732.5	731.9	731.2	730.6	729.9
147.5°	753.2	753.9	754.0	753.4	752.8	752.3	751.7
150°	766.8	767.6	767.7	767.0	766.3	765.6	764.9
152.5°	779.1	780.0	779.9	779.0	778.1	777.2	776.3
155°	795.7	796.6	796.4	795.3	794.3	793.2	792.0
157.5°	809.9	810.8	810.7	809.7	808.6	807.5	806.5
160°	817.9	818.7	818.6	817.7	816.7	815.8	814.9
162.5°	825.6	826.6	826.5	825.3	824.1	822.9	821.7
165°	835.0	835.9	835.9	835.0	834.0	833.0	832.1
167.5°	842.7	843.7	843.5	842.3	841.1	839.8	838.6
170°	846.6	847.7	847.5	846.3	845.0	843.8	842.6
172.5°	849.6	850.6	850.4	849.2	848.0	846.7	845.5
175°	852.8	853.8	853.6	852.2	850.8	849.5	848.1
177.5°	853.0	853.8	853.7	852.6	851.7	850.7	849.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2

(END OF REPORT)