

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331753-830

Luminaire Tested: **SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331753-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7081.7 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331753-830
CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	85	82	75	72	70	63	61	60	51	50	49	44
2	91	84	78	73	84	78	73	68	66	63	60	56	53	51	46	45	43	38
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	77	66	59	53	71	62	55	50	53	48	44	45	42	39	38	35	33	30
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	35	32	30	26
6	65	54	46	41	60	50	44	39	44	38	34	38	34	30	32	29	27	24
7	61	49	41	36	56	46	39	34	40	35	31	35	30	27	29	26	24	21
8	57	45	37	32	52	42	35	31	37	32	28	32	28	25	27	24	22	20
9	53	41	34	29	49	39	32	28	34	29	25	30	25	23	25	22	20	18
10	50	38	31	26	46	36	29	25	31	26	23	27	23	21	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	2.8
10°-20°	549.1	7.8
20°-30°	707.5	10.0
30°-40°	672.4	9.5
40°-50°	576.0	8.1
50°-60°	438.6	6.2
60°-70°	277.3	3.9
70°-80°	138.5	2.0
80°-90°	39.0	0.6
90°-100°	39.7	0.6
100°-110°	145.5	2.1
110°-120°	389.0	5.5
120°-130°	642.1	9.1
130°-140°	682.9	9.6
140°-150°	634.7	9.0
150°-160°	510.3	7.2
160°-170°	328.8	4.6
170°-180°	113.2	1.6
0°-30°	1453.7	20.5
0°-40°	2126.0	30.0
0°-60°	3140.7	44.3
0°-90°	3595.4	50.8
90°-120°	574.2	8.1
90°-150°	2533.9	35.8
90°-180°	3486.0	49.2
0°-180°	7081.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	28
90°	23	1	23	1	23	11
95°	37	56	37	56	37	35
105°	65	262	65	262	65	68
115°	71	495	71	495	71	177
125°	736	700	736	700	736	637
135°	894	866	894	866	894	689
145°	1020	1005	1020	1005	1020	638
155°	1107	1106	1107	1106	1107	511
165°	1163	1166	1163	1166	1163	328
175°	1185	1192	1185	1192	1185	113
180°	1190	1190	1190	1190	1190	



TEST NUMBER: P331753-830
 CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	13.9	14.4	14.3	14.2	14.1	14.0	13.9	14.2	13.5	13.9	13.0
90°	23.3	22.9	22.4	22.1	21.7	21.0	20.1	19.1	18.2	17.2	15.6
92.5°	23.3	23.0	22.8	22.5	22.3	22.0	21.5	20.9	20.5	20.0	19.2
95°	37.0	37.2	37.4	37.6	37.8	37.4	36.5	35.4	34.5	33.6	32.2
97.5°	49.4	49.2	48.9	48.7	48.4	48.0	47.2	46.5	45.7	45.0	41.8
100°	57.7	57.3	56.9	56.6	56.2	55.2	53.6	52.1	50.6	49.1	45.8
102.5°	61.8	61.3	60.7	60.2	59.7	58.4	56.5	54.4	52.4	50.4	77.7
105°	65.4	64.7	63.9	63.2	62.4	60.9	58.8	56.7	54.6	52.5	104.7
107.5°	67.3	66.5	65.8	65.0	64.3	64.9	67.1	69.2	71.4	73.5	136.1
110°	68.1	67.2	66.4	65.7	64.9	74.1	93.2	112.4	131.5	150.6	205.9



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.7	68.1	67.5	66.8	66.3	100.9	170.6	240.4	310.2	379.9	393.6
115°	70.6	84.4	98.1	111.9	125.6	176.8	265.4	354.0	442.5	531.1	526.3
117.5°	288.2	333.5	378.7	424.0	469.2	502.6	524.1	545.4	566.8	588.2	585.0
120°	525.1	550.9	576.7	602.6	628.4	640.2	637.9	635.6	633.3	630.9	627.5
122.5°	655.3	660.3	665.2	670.3	675.3	677.1	675.7	674.4	673.0	671.7	667.9
125°	736.0	735.5	734.8	734.2	733.7	732.7	731.4	730.1	728.8	727.4	723.8
127.5°	786.9	786.8	786.7	786.6	786.5	785.5	783.5	781.6	779.6	777.7	775.0
130°	818.6	818.8	819.0	819.3	819.4	818.4	816.3	814.3	812.1	810.0	807.9
132.5°	849.6	849.8	850.0	850.2	850.4	849.6	847.8	846.0	844.2	842.4	840.3
135°	894.4	894.8	895.1	895.5	895.9	895.1	893.2	891.4	889.4	887.5	885.8
137.5°	935.2	935.9	936.5	937.2	937.8	937.2	935.3	933.4	931.5	929.7	927.7
140°	960.6	961.7	962.6	963.6	964.5	964.1	962.4	960.6	958.9	957.2	955.2
142.5°	985.4	986.5	987.4	988.4	989.3	989.0	987.4	985.8	984.3	982.7	980.3
145°	1020.1	1021.1	1022.0	1022.9	1023.9	1023.7	1022.4	1021.1	1019.6	1018.3	1015.1
147.5°	1050.6	1051.3	1052.2	1052.9	1053.8	1053.7	1052.6	1051.7	1050.7	1049.7	1046.5
150°	1069.1	1070.1	1071.0	1072.0	1073.0	1072.9	1071.8	1070.5	1069.4	1068.3	1065.3
152.5°	1085.0	1086.3	1087.5	1088.7	1090.1	1090.1	1088.9	1087.8	1086.7	1085.5	1082.6
155°	1107.0	1108.5	1110.0	1111.6	1113.1	1113.3	1112.2	1111.1	1109.8	1108.7	1106.5
157.5°	1127.2	1128.6	1130.1	1131.6	1133.1	1133.2	1131.9	1130.6	1129.4	1128.0	1126.4
160°	1138.9	1140.2	1141.5	1142.8	1144.2	1144.3	1143.2	1142.0	1140.9	1139.7	1138.6
162.5°	1148.5	1150.2	1151.8	1153.5	1155.1	1155.3	1154.0	1152.6	1151.3	1150.1	1149.1
165°	1163.0	1164.3	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0	1162.4
167.5°	1172.1	1173.8	1175.5	1177.2	1178.9	1179.2	1177.8	1176.5	1175.2	1173.8	1173.3
170°	1177.6	1179.3	1181.0	1182.8	1184.5	1184.7	1183.4	1182.0	1180.6	1179.3	1178.9
172.5°	1181.8	1183.5	1185.2	1186.8	1188.6	1188.8	1187.5	1186.1	1184.8	1183.5	1183.1
175°	1185.3	1187.2	1189.2	1191.1	1193.0	1193.3	1191.9	1190.6	1189.3	1187.9	1187.5
177.5°	1187.6	1188.9	1190.3	1191.8	1193.1	1193.3	1192.2	1191.1	1190.1	1188.9	1188.8
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	12.6	12.9	12.6	11.7	11.9	12.0	14.4	17.0	15.1	13.8	13.0
90°	14.1	12.6	11.1	9.2	7.2	5.1	2.9	0.8	2.9	5.1	7.2
92.5°	18.5	17.7	16.9	16.6	16.8	17.0	17.2	17.3	17.2	17.0	16.8
95°	30.9	29.6	28.2	30.7	37.0	43.4	49.7	56.0	49.7	43.4	37.0
97.5°	38.7	35.6	32.5	39.9	57.7	75.5	93.2	111.0	93.2	75.5	57.7
100°	42.6	39.3	36.1	47.5	73.7	99.9	126.1	152.4	126.1	99.9	73.7
102.5°	104.8	132.1	159.3	175.6	181.2	186.7	192.3	197.8	192.3	186.7	181.2
105°	156.9	209.2	261.4	284.6	278.9	273.1	267.4	261.6	267.4	273.1	278.9
107.5°	198.8	261.4	324.0	353.1	348.4	343.7	339.1	334.5	339.1	343.7	348.4
110°	261.2	316.5	371.7	397.4	393.4	389.4	385.4	381.4	385.4	389.4	393.4



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	407.3	420.9	434.6	439.6	436.1	432.5	429.0	425.4	429.0	432.5	436.1
115°	521.6	516.8	512.0	507.9	504.7	501.4	498.2	494.9	498.2	501.4	504.7
117.5°	581.7	578.4	575.1	571.7	568.1	564.4	560.7	557.1	560.7	564.4	568.1
120°	624.1	620.7	617.2	614.1	611.1	608.3	605.4	602.6	605.4	608.3	611.1
122.5°	664.1	660.3	656.6	653.2	650.2	647.1	644.1	641.1	644.1	647.1	650.2
125°	720.1	716.5	712.8	709.8	707.3	704.8	702.3	699.8	702.3	704.8	707.3
127.5°	772.2	769.5	766.8	764.0	761.3	758.6	755.8	753.0	755.8	758.6	761.3
130°	805.8	803.7	801.6	799.0	796.0	792.9	789.9	786.8	789.9	792.9	796.0
132.5°	838.2	836.1	834.0	831.6	829.1	826.4	823.8	821.2	823.8	826.4	829.1
135°	884.1	882.3	880.6	878.3	875.2	872.1	869.0	866.0	869.0	872.1	875.2
137.5°	925.8	923.8	921.9	919.8	917.7	915.6	913.4	911.3	913.4	915.6	917.7
140°	953.0	950.9	948.9	947.0	945.5	944.0	942.4	940.8	942.4	944.0	945.5
142.5°	977.9	975.4	973.1	971.2	969.8	968.5	967.0	965.6	967.0	968.5	969.8
145°	1011.8	1008.6	1005.3	1003.8	1004.0	1004.2	1004.4	1004.6	1004.4	1004.2	1004.0
147.5°	1043.3	1040.0	1036.8	1035.6	1036.3	1037.1	1037.7	1038.5	1037.7	1037.1	1036.3
150°	1062.2	1059.1	1056.0	1055.2	1056.5	1057.8	1059.2	1060.5	1059.2	1057.8	1056.5
152.5°	1079.7	1076.8	1073.8	1073.2	1074.7	1076.1	1077.6	1079.1	1077.6	1076.1	1074.7
155°	1104.2	1101.8	1099.6	1099.3	1101.0	1102.7	1104.5	1106.2	1104.5	1102.7	1101.0
157.5°	1124.8	1123.2	1121.6	1121.5	1122.9	1124.5	1125.9	1127.3	1125.9	1124.5	1122.9
160°	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1138.6	1137.5	1136.2
162.5°	1148.0	1147.1	1146.0	1146.1	1147.3	1148.5	1149.6	1150.8	1149.6	1148.5	1147.3
165°	1161.8	1161.2	1160.6	1160.9	1162.1	1163.3	1164.4	1165.5	1164.4	1163.3	1162.1
167.5°	1172.7	1172.2	1171.7	1172.0	1173.1	1174.3	1175.4	1176.6	1175.4	1174.3	1173.1
170°	1178.6	1178.2	1177.8	1178.2	1179.3	1180.4	1181.6	1182.8	1181.6	1180.4	1179.3
172.5°	1182.7	1182.3	1181.9	1182.3	1183.5	1184.6	1185.7	1186.8	1185.7	1184.6	1183.5
175°	1187.1	1186.8	1186.4	1186.8	1188.2	1189.6	1190.9	1192.2	1190.9	1189.6	1188.2
177.5°	1188.6	1188.5	1188.4	1188.8	1189.9	1191.0	1192.0	1193.1	1192.0	1191.0	1189.9
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	12.8	12.6	11.8	12.1	12.3	12.1	12.3	11.9	12.1	12.3	11.9
90°	9.2	11.1	12.6	14.1	15.6	17.2	18.2	19.1	20.1	21.0	21.7
92.5°	16.6	16.9	17.7	18.5	19.2	20.0	20.5	20.9	21.5	22.0	22.3
95°	30.7	28.2	29.6	30.9	32.2	33.6	34.5	35.4	36.5	37.4	37.8
97.5°	39.9	32.5	35.6	38.7	41.8	45.0	45.7	46.5	47.2	48.0	48.4
100°	47.5	36.1	39.3	42.6	45.8	49.1	50.6	52.1	53.6	55.2	56.2
102.5°	175.6	159.3	132.1	104.8	77.7	50.4	52.4	54.4	56.5	58.4	59.7
105°	284.6	261.4	209.2	156.9	104.7	52.5	54.6	56.7	58.8	60.9	62.4
107.5°	353.1	324.0	261.4	198.8	136.1	73.5	71.4	69.2	67.1	64.9	64.3
110°	397.4	371.7	316.5	261.2	205.9	150.6	131.5	112.4	93.2	74.1	64.9



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	439.6	434.6	420.9	407.3	393.6	379.9	310.2	240.4	170.6	100.9	66.3
115°	507.9	512.0	516.8	521.6	526.3	531.1	442.5	354.0	265.4	176.8	125.6
117.5°	571.7	575.1	578.4	581.7	585.0	588.2	566.8	545.4	524.1	502.6	469.2
120°	614.1	617.2	620.7	624.1	627.5	630.9	633.3	635.6	637.9	640.2	628.4
122.5°	653.2	656.6	660.3	664.1	667.9	671.7	673.0	674.4	675.7	677.1	675.3
125°	709.8	712.8	716.5	720.1	723.8	727.4	728.8	730.1	731.4	732.7	733.7
127.5°	764.0	766.8	769.5	772.2	775.0	777.7	779.6	781.6	783.5	785.5	786.5
130°	799.0	801.6	803.7	805.8	807.9	810.0	812.1	814.3	816.3	818.4	819.4
132.5°	831.6	834.0	836.1	838.2	840.3	842.4	844.2	846.0	847.8	849.6	850.4
135°	878.3	880.6	882.3	884.1	885.8	887.5	889.4	891.4	893.2	895.1	895.9
137.5°	919.8	921.9	923.8	925.8	927.7	929.7	931.5	933.4	935.3	937.2	937.8
140°	947.0	948.9	950.9	953.0	955.2	957.2	958.9	960.6	962.4	964.1	964.5
142.5°	971.2	973.1	975.4	977.9	980.3	982.7	984.3	985.8	987.4	989.0	989.3
145°	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1019.6	1021.1	1022.4	1023.7	1023.9
147.5°	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.7	1051.7	1052.6	1053.7	1053.8
150°	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4	1070.5	1071.8	1072.9	1073.0
152.5°	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7	1087.8	1088.9	1090.1	1090.1
155°	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8	1111.1	1112.2	1113.3	1113.1
157.5°	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4	1130.6	1131.9	1133.2	1133.1
160°	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9	1142.0	1143.2	1144.3	1144.2
162.5°	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3	1152.6	1154.0	1155.3	1155.1
165°	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3	1165.6	1167.0	1168.3	1168.3
167.5°	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2	1176.5	1177.8	1179.2	1178.9
170°	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6	1182.0	1183.4	1184.7	1184.5
172.5°	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8	1186.1	1187.5	1188.8	1188.6
175°	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3	1190.6	1191.9	1193.3	1193.0
177.5°	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1	1191.1	1192.2	1193.3	1193.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	12.0	11.4	12.1	11.6	12.1	11.4	12.0	11.9	12.3	12.1	11.9
90°	22.1	22.4	22.9	23.3	22.9	22.4	22.1	21.7	21.0	20.1	19.1
92.5°	22.5	22.8	23.0	23.3	23.0	22.8	22.5	22.3	22.0	21.5	20.9
95°	37.6	37.4	37.2	37.0	37.2	37.4	37.6	37.8	37.4	36.5	35.4
97.5°	48.7	48.9	49.2	49.4	49.2	48.9	48.7	48.4	48.0	47.2	46.5
100°	56.6	56.9	57.3	57.7	57.3	56.9	56.6	56.2	55.2	53.6	52.1
102.5°	60.2	60.7	61.3	61.8	61.3	60.7	60.2	59.7	58.4	56.5	54.4
105°	63.2	63.9	64.7	65.4	64.7	63.9	63.2	62.4	60.9	58.8	56.7
107.5°	65.0	65.8	66.5	67.3	66.5	65.8	65.0	64.3	64.9	67.1	69.2
110°	65.7	66.4	67.2	68.1	67.2	66.4	65.7	64.9	74.1	93.2	112.4



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	66.8	67.5	68.1	68.7	68.1	67.5	66.8	66.3	100.9	170.6	240.4
115°	111.9	98.1	84.4	70.6	84.4	98.1	111.9	125.6	176.8	265.4	354.0
117.5°	424.0	378.7	333.5	288.2	333.5	378.7	424.0	469.2	502.6	524.1	545.4
120°	602.6	576.7	550.9	525.1	550.9	576.7	602.6	628.4	640.2	637.9	635.6
122.5°	670.3	665.2	660.3	655.3	660.3	665.2	670.3	675.3	677.1	675.7	674.4
125°	734.2	734.8	735.5	736.0	735.5	734.8	734.2	733.7	732.7	731.4	730.1
127.5°	786.6	786.7	786.8	786.9	786.8	786.7	786.6	786.5	785.5	783.5	781.6
130°	819.3	819.0	818.8	818.6	818.8	819.0	819.3	819.4	818.4	816.3	814.3
132.5°	850.2	850.0	849.8	849.6	849.8	850.0	850.2	850.4	849.6	847.8	846.0
135°	895.5	895.1	894.8	894.4	894.8	895.1	895.5	895.9	895.1	893.2	891.4
137.5°	937.2	936.5	935.9	935.2	935.9	936.5	937.2	937.8	937.2	935.3	933.4
140°	963.6	962.6	961.7	960.6	961.7	962.6	963.6	964.5	964.1	962.4	960.6
142.5°	988.4	987.4	986.5	985.4	986.5	987.4	988.4	989.3	989.0	987.4	985.8
145°	1022.9	1022.0	1021.1	1020.1	1021.1	1022.0	1022.9	1023.9	1023.7	1022.4	1021.1
147.5°	1052.9	1052.2	1051.3	1050.6	1051.3	1052.2	1052.9	1053.8	1053.7	1052.6	1051.7
150°	1072.0	1071.0	1070.1	1069.1	1070.1	1071.0	1072.0	1073.0	1072.9	1071.8	1070.5
152.5°	1088.7	1087.5	1086.3	1085.0	1086.3	1087.5	1088.7	1090.1	1090.1	1088.9	1087.8
155°	1111.6	1110.0	1108.5	1107.0	1108.5	1110.0	1111.6	1113.1	1113.3	1112.2	1111.1
157.5°	1131.6	1130.1	1128.6	1127.2	1128.6	1130.1	1131.6	1133.1	1133.2	1131.9	1130.6
160°	1142.8	1141.5	1140.2	1138.9	1140.2	1141.5	1142.8	1144.2	1144.3	1143.2	1142.0
162.5°	1153.5	1151.8	1150.2	1148.5	1150.2	1151.8	1153.5	1155.1	1155.3	1154.0	1152.6
165°	1167.0	1165.6	1164.3	1163.0	1164.3	1165.6	1167.0	1168.3	1168.3	1167.0	1165.6
167.5°	1177.2	1175.5	1173.8	1172.1	1173.8	1175.5	1177.2	1178.9	1179.2	1177.8	1176.5
170°	1182.8	1181.0	1179.3	1177.6	1179.3	1181.0	1182.8	1184.5	1184.7	1183.4	1182.0
172.5°	1186.8	1185.2	1183.5	1181.8	1183.5	1185.2	1186.8	1188.6	1188.8	1187.5	1186.1
175°	1191.1	1189.2	1187.2	1185.3	1187.2	1189.2	1191.1	1193.0	1193.3	1191.9	1190.6
177.5°	1191.8	1190.3	1188.9	1187.6	1188.9	1190.3	1191.8	1193.1	1193.3	1192.2	1191.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	12.3	12.1	12.3	12.1	11.8	12.6	12.8	13.0	13.8	15.1	17.0
90°	18.2	17.2	15.6	14.1	12.6	11.1	9.2	7.2	5.1	2.9	0.8
92.5°	20.5	20.0	19.2	18.5	17.7	16.9	16.6	16.8	17.0	17.2	17.3
95°	34.5	33.6	32.2	30.9	29.6	28.2	30.7	37.0	43.4	49.7	56.0
97.5°	45.7	45.0	41.8	38.7	35.6	32.5	39.9	57.7	75.5	93.2	111.0
100°	50.6	49.1	45.8	42.6	39.3	36.1	47.5	73.7	99.9	126.1	152.4
102.5°	52.4	50.4	77.7	104.8	132.1	159.3	175.6	181.2	186.7	192.3	197.8
105°	54.6	52.5	104.7	156.9	209.2	261.4	284.6	278.9	273.1	267.4	261.6
107.5°	71.4	73.5	136.1	198.8	261.4	324.0	353.1	348.4	343.7	339.1	334.5
110°	131.5	150.6	205.9	261.2	316.5	371.7	397.4	393.4	389.4	385.4	381.4



TEST NUMBER: P331753-830
 CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	310.2	379.9	393.6	407.3	420.9	434.6	439.6	436.1	432.5	429.0	425.4
115°	442.5	531.1	526.3	521.6	516.8	512.0	507.9	504.7	501.4	498.2	494.9
117.5°	566.8	588.2	585.0	581.7	578.4	575.1	571.7	568.1	564.4	560.7	557.1
120°	633.3	630.9	627.5	624.1	620.7	617.2	614.1	611.1	608.3	605.4	602.6
122.5°	673.0	671.7	667.9	664.1	660.3	656.6	653.2	650.2	647.1	644.1	641.1
125°	728.8	727.4	723.8	720.1	716.5	712.8	709.8	707.3	704.8	702.3	699.8
127.5°	779.6	777.7	775.0	772.2	769.5	766.8	764.0	761.3	758.6	755.8	753.0
130°	812.1	810.0	807.9	805.8	803.7	801.6	799.0	796.0	792.9	789.9	786.8
132.5°	844.2	842.4	840.3	838.2	836.1	834.0	831.6	829.1	826.4	823.8	821.2
135°	889.4	887.5	885.8	884.1	882.3	880.6	878.3	875.2	872.1	869.0	866.0
137.5°	931.5	929.7	927.7	925.8	923.8	921.9	919.8	917.7	915.6	913.4	911.3
140°	958.9	957.2	955.2	953.0	950.9	948.9	947.0	945.5	944.0	942.4	940.8
142.5°	984.3	982.7	980.3	977.9	975.4	973.1	971.2	969.8	968.5	967.0	965.6
145°	1019.6	1018.3	1015.1	1011.8	1008.6	1005.3	1003.8	1004.0	1004.2	1004.4	1004.6
147.5°	1050.7	1049.7	1046.5	1043.3	1040.0	1036.8	1035.6	1036.3	1037.1	1037.7	1038.5
150°	1069.4	1068.3	1065.3	1062.2	1059.1	1056.0	1055.2	1056.5	1057.8	1059.2	1060.5
152.5°	1086.7	1085.5	1082.6	1079.7	1076.8	1073.8	1073.2	1074.7	1076.1	1077.6	1079.1
155°	1109.8	1108.7	1106.5	1104.2	1101.8	1099.6	1099.3	1101.0	1102.7	1104.5	1106.2
157.5°	1129.4	1128.0	1126.4	1124.8	1123.2	1121.6	1121.5	1122.9	1124.5	1125.9	1127.3
160°	1140.9	1139.7	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7
162.5°	1151.3	1150.1	1149.1	1148.0	1147.1	1146.0	1146.1	1147.3	1148.5	1149.6	1150.8
165°	1164.3	1163.0	1162.4	1161.8	1161.2	1160.6	1160.9	1162.1	1163.3	1164.4	1165.5
167.5°	1175.2	1173.8	1173.3	1172.7	1172.2	1171.7	1172.0	1173.1	1174.3	1175.4	1176.6
170°	1180.6	1179.3	1178.9	1178.6	1178.2	1177.8	1178.2	1179.3	1180.4	1181.6	1182.8
172.5°	1184.8	1183.5	1183.1	1182.7	1182.3	1181.9	1182.3	1183.5	1184.6	1185.7	1186.8
175°	1189.3	1187.9	1187.5	1187.1	1186.8	1186.4	1186.8	1188.2	1189.6	1190.9	1192.2
177.5°	1190.1	1188.9	1188.8	1188.6	1188.5	1188.4	1188.8	1189.9	1191.0	1192.0	1193.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.4	12.0	11.9	11.7	12.6	12.9	12.6	13.0	13.9	13.5	14.2
90°	2.9	5.1	7.2	9.2	11.1	12.6	14.1	15.6	17.2	18.2	19.1
92.5°	17.2	17.0	16.8	16.6	16.9	17.7	18.5	19.2	20.0	20.5	20.9
95°	49.7	43.4	37.0	30.7	28.2	29.6	30.9	32.2	33.6	34.5	35.4
97.5°	93.2	75.5	57.7	39.9	32.5	35.6	38.7	41.8	45.0	45.7	46.5
100°	126.1	99.9	73.7	47.5	36.1	39.3	42.6	45.8	49.1	50.6	52.1
102.5°	192.3	186.7	181.2	175.6	159.3	132.1	104.8	77.7	50.4	52.4	54.4
105°	267.4	273.1	278.9	284.6	261.4	209.2	156.9	104.7	52.5	54.6	56.7
107.5°	339.1	343.7	348.4	353.1	324.0	261.4	198.8	136.1	73.5	71.4	69.2
110°	385.4	389.4	393.4	397.4	371.7	316.5	261.2	205.9	150.6	131.5	112.4



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	429.0	432.5	436.1	439.6	434.6	420.9	407.3	393.6	379.9	310.2	240.4
115°	498.2	501.4	504.7	507.9	512.0	516.8	521.6	526.3	531.1	442.5	354.0
117.5°	560.7	564.4	568.1	571.7	575.1	578.4	581.7	585.0	588.2	566.8	545.4
120°	605.4	608.3	611.1	614.1	617.2	620.7	624.1	627.5	630.9	633.3	635.6
122.5°	644.1	647.1	650.2	653.2	656.6	660.3	664.1	667.9	671.7	673.0	674.4
125°	702.3	704.8	707.3	709.8	712.8	716.5	720.1	723.8	727.4	728.8	730.1
127.5°	755.8	758.6	761.3	764.0	766.8	769.5	772.2	775.0	777.7	779.6	781.6
130°	789.9	792.9	796.0	799.0	801.6	803.7	805.8	807.9	810.0	812.1	814.3
132.5°	823.8	826.4	829.1	831.6	834.0	836.1	838.2	840.3	842.4	844.2	846.0
135°	869.0	872.1	875.2	878.3	880.6	882.3	884.1	885.8	887.5	889.4	891.4
137.5°	913.4	915.6	917.7	919.8	921.9	923.8	925.8	927.7	929.7	931.5	933.4
140°	942.4	944.0	945.5	947.0	948.9	950.9	953.0	955.2	957.2	958.9	960.6
142.5°	967.0	968.5	969.8	971.2	973.1	975.4	977.9	980.3	982.7	984.3	985.8
145°	1004.4	1004.2	1004.0	1003.8	1005.3	1008.6	1011.8	1015.1	1018.3	1019.6	1021.1
147.5°	1037.7	1037.1	1036.3	1035.6	1036.8	1040.0	1043.3	1046.5	1049.7	1050.7	1051.7
150°	1059.2	1057.8	1056.5	1055.2	1056.0	1059.1	1062.2	1065.3	1068.3	1069.4	1070.5
152.5°	1077.6	1076.1	1074.7	1073.2	1073.8	1076.8	1079.7	1082.6	1085.5	1086.7	1087.8
155°	1104.5	1102.7	1101.0	1099.3	1099.6	1101.8	1104.2	1106.5	1108.7	1109.8	1111.1
157.5°	1125.9	1124.5	1122.9	1121.5	1121.6	1123.2	1124.8	1126.4	1128.0	1129.4	1130.6
160°	1138.6	1137.5	1136.2	1135.1	1135.1	1136.2	1137.5	1138.6	1139.7	1140.9	1142.0
162.5°	1149.6	1148.5	1147.3	1146.1	1146.0	1147.1	1148.0	1149.1	1150.1	1151.3	1152.6
165°	1164.4	1163.3	1162.1	1160.9	1160.6	1161.2	1161.8	1162.4	1163.0	1164.3	1165.6
167.5°	1175.4	1174.3	1173.1	1172.0	1171.7	1172.2	1172.7	1173.3	1173.8	1175.2	1176.5
170°	1181.6	1180.4	1179.3	1178.2	1177.8	1178.2	1178.6	1178.9	1179.3	1180.6	1182.0
172.5°	1185.7	1184.6	1183.5	1182.3	1181.9	1182.3	1182.7	1183.1	1183.5	1184.8	1186.1
175°	1190.9	1189.6	1188.2	1186.8	1186.4	1186.8	1187.1	1187.5	1187.9	1189.3	1190.6
177.5°	1192.0	1191.0	1189.9	1188.8	1188.4	1188.5	1188.6	1188.8	1188.9	1190.1	1191.1
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7



TEST NUMBER: P331753-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	13.9	14.0	14.1	14.2	14.3	14.4	13.9
90°	20.1	21.0	21.7	22.1	22.4	22.9	23.3
92.5°	21.5	22.0	22.3	22.5	22.8	23.0	23.3
95°	36.5	37.4	37.8	37.6	37.4	37.2	37.0
97.5°	47.2	48.0	48.4	48.7	48.9	49.2	49.4
100°	53.6	55.2	56.2	56.6	56.9	57.3	57.7
102.5°	56.5	58.4	59.7	60.2	60.7	61.3	61.8
105°	58.8	60.9	62.4	63.2	63.9	64.7	65.4
107.5°	67.1	64.9	64.3	65.0	65.8	66.5	67.3
110°	93.2	74.1	64.9	65.7	66.4	67.2	68.1



TEST NUMBER: P331753-830
CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.6	100.9	66.3	66.8	67.5	68.1	68.7
115°	265.4	176.8	125.6	111.9	98.1	84.4	70.6
117.5°	524.1	502.6	469.2	424.0	378.7	333.5	288.2
120°	637.9	640.2	628.4	602.6	576.7	550.9	525.1
122.5°	675.7	677.1	675.3	670.3	665.2	660.3	655.3
125°	731.4	732.7	733.7	734.2	734.8	735.5	736.0
127.5°	783.5	785.5	786.5	786.6	786.7	786.8	786.9
130°	816.3	818.4	819.4	819.3	819.0	818.8	818.6
132.5°	847.8	849.6	850.4	850.2	850.0	849.8	849.6
135°	893.2	895.1	895.9	895.5	895.1	894.8	894.4
137.5°	935.3	937.2	937.8	937.2	936.5	935.9	935.2
140°	962.4	964.1	964.5	963.6	962.6	961.7	960.6
142.5°	987.4	989.0	989.3	988.4	987.4	986.5	985.4
145°	1022.4	1023.7	1023.9	1022.9	1022.0	1021.1	1020.1
147.5°	1052.6	1053.7	1053.8	1052.9	1052.2	1051.3	1050.6
150°	1071.8	1072.9	1073.0	1072.0	1071.0	1070.1	1069.1
152.5°	1088.9	1090.1	1090.1	1088.7	1087.5	1086.3	1085.0
155°	1112.2	1113.3	1113.1	1111.6	1110.0	1108.5	1107.0
157.5°	1131.9	1133.2	1133.1	1131.6	1130.1	1128.6	1127.2
160°	1143.2	1144.3	1144.2	1142.8	1141.5	1140.2	1138.9
162.5°	1154.0	1155.3	1155.1	1153.5	1151.8	1150.2	1148.5
165°	1167.0	1168.3	1168.3	1167.0	1165.6	1164.3	1163.0
167.5°	1177.8	1179.2	1178.9	1177.2	1175.5	1173.8	1172.1
170°	1183.4	1184.7	1184.5	1182.8	1181.0	1179.3	1177.6
172.5°	1187.5	1188.8	1188.6	1186.8	1185.2	1183.5	1181.8
175°	1191.9	1193.3	1193.0	1191.1	1189.2	1187.2	1185.3
177.5°	1192.2	1193.3	1193.1	1191.8	1190.3	1188.9	1187.6
180°	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7	1189.7

(END OF REPORT)