

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331755-830

Luminaire Tested: **SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331755-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7000.7 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	99	95	91	88	91	88	85	82	75	73	71	63	61	60	52	51	50				45	
2	91	84	78	73	84	78	73	69	67	63	60	56	54	51	47	45	43				39	
3	83	74	68	62	77	69	63	58	60	55	51	51	47	45	42	40	38				34	
4	77	67	59	53	71	62	55	50	54	49	45	46	42	39	38	36	34				30	
5	71	60	52	46	65	56	49	44	48	43	39	41	38	34	35	32	30				27	
6	66	54	46	41	61	51	44	39	44	39	35	38	34	31	32	29	27				24	
7	61	49	42	36	56	46	39	34	40	35	31	35	31	28	30	27	24				22	
8	57	45	37	32	53	42	36	31	37	32	28	32	28	25	28	24	22				20	
9	53	41	34	29	49	39	32	28	34	29	25	30	26	23	26	22	20				18	
10	50	38	31	26	46	36	30	25	32	27	23	28	24	21	24	21	19				17	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33562	33562	33562	33562
5°	37483	33773	29945	33773
10°	41589	33536	25956	33536
15°	43632	33045	20451	33045
20°	37826	32316	17698	32316
25°	24807	31319	15800	31319
30°	16697	30109	14300	30109
35°	13525	28586	12899	28586
40°	12026	26930	11936	26930
45°	10885	24987	10654	24987
50°	9907	23059	9869	23059
55°	9312	20921	9191	20921
60°	7789	18962	7698	18962
65°	6567	17219	7450	17219
70°	6071	15375	7024	15375
75°	5677	13381	6488	13381
80°	5244	11018	5774	11018
85°	4817	8688	5076	8688



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.1	2.8
10°-20°	549.1	7.8
20°-30°	707.5	10.1
30°-40°	672.4	9.6
40°-50°	576.0	8.2
50°-60°	438.6	6.3
60°-70°	277.3	4.0
70°-80°	138.5	2.0
80°-90°	40.4	0.6
90°-100°	195.6	2.8
100°-110°	663.7	9.5
110°-120°	705.1	10.1
120°-130°	580.4	8.3
130°-140°	466.1	6.7
140°-150°	352.2	5.0
150°-160°	247.5	3.5
160°-170°	145.7	2.1
170°-180°	47.4	0.7
0°-30°	1453.7	20.8
0°-40°	2126.0	30.4
0°-60°	3140.7	44.9
0°-90°	3596.9	51.4
90°-120°	1564.4	22.3
90°-150°	2963.2	42.3
90°-180°	3404.0	48.6
0°-180°	7000.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2079	2079	2079	2079	2079	
5°	2313	2084	1848	2084	2313	228
15°	2610	1977	1224	1977	2610	704
25°	1392	1758	887	1758	1392	661
35°	686	1450	654	1450	686	439
45°	477	1094	467	1094	477	369
55°	331	743	326	743	331	290
65°	172	451	195	451	172	175
75°	91	214	104	214	91	97
85°	26	47	27	47	26	29
90°	31	1	31	1	31	18
95°	107	33	107	33	107	139
105°	1060	115	1060	115	1060	1026
115°	1395	202	1395	202	1395	1366
125°	1132	282	1132	282	1132	1023
135°	938	331	938	331	938	729
145°	749	378	749	378	749	476
155°	629	430	629	430	629	294
165°	552	468	552	468	552	158
175°	498	488	498	488	498	48
180°	489	489	489	489	489	



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2163.0	2164.8	2166.5	2162.5	2162.5	2159.0	2151.5	2145.7	2129.6	2127.2	2127.2
5°	2312.7	2311.3	2314.1	2304.8	2291.8	2288.9	2275.2	2257.1	2238.4	2217.4	2213.1
7.5°	2461.5	2459.4	2453.5	2452.0	2442.0	2420.2	2398.1	2374.5	2343.3	2312.9	2297.5
10°	2536.7	2560.5	2546.0	2520.7	2525.8	2491.9	2473.8	2442.8	2416.8	2371.2	2361.2
12.5°	2610.6	2620.0	2615.4	2601.0	2594.5	2571.0	2546.6	2519.6	2471.6	2430.7	2395.2
15°	2610.3	2624.0	2627.6	2623.3	2627.0	2625.5	2612.4	2590.1	2548.2	2503.4	2464.4
17.5°	2417.6	2427.1	2450.8	2466.8	2487.1	2529.9	2550.9	2559.2	2553.0	2527.4	2499.9
20°	2201.5	2185.6	2252.0	2286.0	2314.9	2387.1	2449.2	2473.0	2511.3	2510.7	2503.4
22.5°	1895.3	1899.0	1962.0	2002.3	2086.7	2158.9	2229.7	2319.4	2393.5	2442.4	2471.1
25°	1392.5	1420.0	1482.8	1537.8	1631.6	1765.9	1888.0	2029.6	2163.2	2268.7	2369.1
27.5°	1045.8	1047.9	1097.7	1148.4	1204.2	1314.3	1467.9	1637.0	1827.5	1984.7	2165.5
30°	895.6	891.3	912.2	943.3	991.0	1076.2	1191.8	1357.9	1547.8	1784.7	1995.6
32.5°	789.3	789.6	805.3	828.3	867.9	925.4	1004.6	1139.4	1319.0	1551.9	1799.2
35°	686.2	685.4	697.0	713.6	730.2	767.0	821.2	892.0	1015.5	1232.9	1485.7
37.5°	612.2	615.4	621.0	631.4	649.8	670.2	702.8	750.3	838.3	966.9	1179.3
40°	570.6	572.0	579.9	588.6	599.5	615.4	642.1	680.4	744.7	847.3	1002.5
42.5°	532.4	534.0	539.5	547.6	556.2	572.0	594.2	627.3	679.4	759.4	887.5
45°	476.7	476.7	481.7	485.4	494.7	509.2	527.3	554.7	590.8	650.1	735.3
47.5°	424.4	424.5	427.9	434.1	440.0	451.3	469.0	491.4	517.7	563.5	636.3
50°	394.4	395.1	397.3	402.3	406.0	416.0	429.8	449.2	476.7	512.1	572.8
52.5°	370.1	369.7	372.4	374.6	377.0	384.3	394.5	411.7	436.2	467.0	517.3
55°	330.8	327.9	332.2	335.8	338.0	340.9	346.7	357.5	378.4	404.4	442.1
57.5°	281.7	280.5	283.6	286.9	293.7	301.5	306.4	313.3	324.1	342.8	380.0
60°	241.2	241.2	247.7	249.9	257.9	268.0	278.1	283.9	294.7	307.0	334.4
62.5°	205.4	206.0	209.1	211.2	215.7	228.1	242.2	255.0	265.2	276.9	295.1
65°	171.9	173.3	173.3	174.7	177.7	180.6	186.3	196.4	214.5	231.1	244.9
67.5°	145.9	146.4	146.8	148.2	148.9	152.1	154.4	158.9	163.1	178.8	195.9
70°	128.6	130.7	130.0	131.5	132.1	133.7	136.5	138.6	145.2	148.8	158.9
72.5°	112.4	114.0	113.9	114.7	116.6	116.9	119.1	121.3	125.5	128.6	134.0
75°	91.0	90.3	91.0	92.5	93.2	93.9	93.9	96.8	99.0	101.8	105.5
77.5°	70.2	71.0	70.8	71.0	71.1	72.4	72.2	73.5	75.7	77.1	78.9
80°	56.4	57.0	56.4	57.0	57.8	58.5	57.8	58.5	60.7	62.1	62.1
82.5°	43.6	43.7	44.2	44.4	44.5	44.7	45.6	45.8	47.4	47.1	47.7
85°	26.0	25.3	25.3	25.3	26.0	26.8	26.0	26.0	26.8	26.8	26.8
87.5°	15.5	16.0	16.0	16.0	16.0	15.8	15.5	16.4	16.0	16.8	16.0
90°	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1	31.0	32.0	31.0
92.5°	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0	103.3	122.2	120.6
95°	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5	322.6	368.7	326.4
97.5°	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1	660.3	629.5	474.1
100°	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8	878.6	743.1	511.7
102.5°	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7	959.9	746.9	497.5
105°	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9	947.3	697.0	469.4
107.5°	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2	864.7	643.7	455.4
110°	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3	812.8	618.0	452.5



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5	776.7	601.4	453.2
115°	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0	731.9	583.2	457.1
117.5°	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5	703.6	574.4	463.9
120°	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9	688.6	569.1	468.4
122.5°	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6	675.8	566.1	473.7
125°	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1	657.5	560.6	481.6
127.5°	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9	640.6	557.4	489.7
130°	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1	629.3	555.9	495.8
132.5°	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0	620.3	555.2	501.7
135°	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8	607.7	554.0	508.9
137.5°	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7	598.8	553.8	515.3
140°	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9	593.6	553.1	518.3
142.5°	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4	588.3	553.1	520.6
145°	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5	581.4	551.2	523.0
147.5°	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0	574.2	547.9	523.8
150°	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8	568.2	545.6	523.0
152.5°	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5	562.9	541.9	521.5
155°	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0	553.1	535.3	519.2
157.5°	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6	543.9	528.5	514.9
160°	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3	537.2	524.0	512.6
162.5°	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1	531.1	520.2	510.4
165°	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7	521.1	512.6	506.1
167.5°	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8	511.3	506.1	501.7
170°	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8	506.1	502.3	499.5
172.5°	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0	500.9	497.9	496.5
175°	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7	493.9	492.9	492.0
177.5°	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2128.4	2123.7	2119.8	2109.3	2104.1	2092.5	2090.8	2090.3	2075.3	2060.8	2056.7
5°	2201.5	2189.9	2172.7	2152.4	2131.5	2109.8	2095.4	2083.8	2054.8	2027.4	2011.6
7.5°	2275.2	2250.3	2220.4	2182.2	2150.2	2114.4	2087.8	2064.0	2023.0	1983.7	1957.2
10°	2330.1	2289.6	2249.8	2197.2	2156.0	2115.5	2078.0	2045.5	1999.2	1947.3	1910.4
12.5°	2364.2	2319.7	2264.9	2213.4	2160.0	2108.7	2058.3	2016.6	1962.3	1908.6	1864.8
15°	2410.3	2362.6	2296.1	2222.4	2153.8	2086.7	2028.9	1976.9	1906.1	1841.8	1788.4
17.5°	2448.0	2382.4	2311.0	2225.8	2146.4	2061.0	1986.6	1920.1	1841.4	1763.8	1700.8
20°	2460.0	2395.1	2312.7	2227.5	2133.6	2033.3	1953.0	1880.8	1796.3	1711.8	1639.6
22.5°	2452.6	2402.0	2310.5	2208.5	2112.2	2007.2	1916.7	1832.9	1739.1	1652.8	1569.1
25°	2401.6	2384.3	2297.5	2186.3	2076.5	1954.5	1849.7	1758.0	1651.1	1558.7	1467.6
27.5°	2282.6	2320.1	2266.3	2147.9	2025.8	1895.0	1777.3	1672.8	1561.9	1457.8	1367.2
30°	2168.3	2254.2	2231.1	2121.3	1984.8	1856.2	1724.1	1615.0	1496.6	1389.7	1300.1
32.5°	2011.7	2153.7	2176.2	2084.3	1943.2	1802.0	1663.4	1554.9	1431.3	1318.6	1231.3
35°	1762.4	1974.7	2072.2	2013.7	1872.2	1719.8	1576.7	1450.3	1326.1	1214.8	1128.2
37.5°	1464.9	1754.2	1916.7	1920.8	1790.8	1632.4	1476.6	1351.1	1224.0	1114.7	1021.1
40°	1272.0	1585.4	1797.1	1844.0	1734.2	1563.0	1405.5	1277.7	1153.5	1046.6	939.0
42.5°	1098.6	1410.9	1671.0	1752.7	1665.5	1495.4	1337.4	1203.7	1083.0	981.8	871.9
45°	888.4	1161.4	1448.1	1594.0	1545.7	1388.2	1221.3	1094.3	980.8	893.4	788.0
47.5°	749.4	941.9	1219.4	1416.6	1415.8	1272.1	1108.0	986.2	881.0	799.1	713.8
50°	670.2	837.8	1072.6	1296.5	1315.2	1194.7	1038.6	918.0	819.8	733.9	665.2
52.5°	599.2	737.3	948.4	1163.0	1216.4	1112.0	960.6	849.2	753.9	674.9	616.1
55°	506.3	613.2	773.5	974.3	1055.3	981.6	847.3	743.2	665.9	599.5	548.9
57.5°	428.3	508.5	637.2	798.8	893.1	846.7	735.8	651.4	585.2	525.1	485.2
60°	379.2	444.9	554.0	689.1	793.1	760.5	665.9	587.2	530.8	478.9	441.3
62.5°	333.0	389.5	483.0	592.6	687.9	674.5	597.2	531.1	481.7	434.4	402.6
65°	268.0	309.2	382.1	468.1	544.6	551.1	495.5	450.7	406.6	369.1	340.9
67.5°	213.4	240.3	291.6	364.0	421.4	441.9	407.9	373.7	338.7	309.7	285.3
70°	179.8	201.5	239.0	297.6	350.3	371.9	352.5	325.7	295.4	271.5	250.6
72.5°	145.7	166.8	194.5	237.5	282.7	306.1	299.4	280.1	255.5	235.7	215.9
75°	109.8	116.3	135.1	164.0	199.3	219.6	224.6	214.5	195.0	179.8	168.2
77.5°	81.2	85.1	94.1	109.2	132.3	150.3	157.8	156.6	143.2	134.3	123.5
80°	65.0	67.2	71.5	78.0	95.4	113.4	118.5	118.5	109.1	105.5	94.6
82.5°	49.4	51.0	53.6	57.2	65.3	81.1	86.7	87.8	81.9	77.1	68.6
85°	28.2	27.4	28.9	31.1	32.5	36.9	45.5	46.9	45.5	39.7	37.5
87.5°	14.9	14.1	13.2	12.1	12.3	12.4	14.6	17.0	15.2	14.2	13.5
90°	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9	3.8	7.5	9.4
92.5°	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5	16.6	23.4	27.4
95°	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9	36.7	46.1	54.6
97.5°	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6	58.7	68.7	81.4
100°	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4	75.2	83.7	98.8
102.5°	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7	91.8	100.3	115.4
105°	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8	118.6	125.1	139.2
107.5°	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9	144.9	151.3	164.3
110°	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9	163.7	169.3	181.5



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4	180.2	186.6	198.1
115°	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3	207.0	212.6	223.9
117.5°	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9	232.7	238.4	248.4
120°	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5	249.3	255.0	263.3
122.5°	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4	264.3	269.9	279.2
125°	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2	285.0	290.7	302.0
127.5°	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8	302.6	310.4	322.8
130°	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6	312.3	321.7	334.9
132.5°	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5	322.1	332.2	346.2
135°	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1	334.9	346.2	360.2
137.5°	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9	348.5	359.7	374.8
140°	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7	357.5	368.7	383.8
142.5°	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4	366.5	377.0	392.1
145°	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1	381.9	391.3	405.5
147.5°	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0	396.8	405.8	418.8
150°	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5	407.3	414.8	427.1
152.5°	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0	416.3	423.9	434.6
155°	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9	430.8	436.5	446.9
157.5°	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3	443.3	447.8	456.8
160°	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6	451.6	455.2	462.8
162.5°	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8	458.3	462.0	468.1
165°	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4	467.5	469.4	475.0
167.5°	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4	475.2	476.9	480.5
170°	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6	479.8	480.7	483.5
172.5°	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7	483.5	483.0	485.8
175°	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2	487.3	486.4	488.2
177.5°	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9	488.4	487.7	489.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2049.3	2045.2	2037.7	2026.1	2019.2	2007.1	1998.9	2003.6	2004.8	2003.6	2002.4
5°	1994.2	1979.1	1958.1	1937.9	1919.1	1898.8	1887.3	1882.3	1872.2	1866.3	1863.5
7.5°	1927.6	1901.5	1871.9	1836.6	1806.7	1775.4	1759.3	1751.3	1730.7	1719.5	1709.6
10°	1877.9	1836.7	1807.1	1761.0	1732.8	1691.6	1663.4	1664.2	1636.0	1620.0	1608.5
12.5°	1823.1	1777.8	1728.5	1687.0	1647.8	1614.8	1580.7	1567.1	1537.2	1521.8	1490.6
15°	1732.0	1679.3	1627.3	1570.9	1531.3	1480.0	1430.9	1370.9	1322.5	1280.6	1269.0
17.5°	1632.7	1567.4	1515.2	1449.1	1381.0	1294.8	1237.8	1203.1	1173.8	1151.8	1135.3
20°	1564.4	1498.0	1442.4	1342.7	1250.9	1192.5	1150.6	1123.9	1093.5	1069.7	1056.7
22.5°	1492.8	1423.4	1347.6	1236.4	1164.9	1117.9	1080.6	1049.9	1029.4	1010.8	998.9
25°	1391.1	1315.2	1190.3	1113.7	1055.9	1006.8	980.8	962.1	940.4	915.1	903.6
27.5°	1283.6	1163.0	1073.3	1016.3	961.2	929.3	905.9	877.9	858.5	847.1	835.1
30°	1203.3	1082.7	1012.7	950.6	911.5	876.1	848.7	832.8	814.0	794.5	786.6
32.5°	1113.7	1017.4	950.3	898.5	858.9	828.8	807.1	781.4	767.8	755.8	739.1
35°	1002.5	929.5	868.2	826.3	788.7	764.2	738.9	723.7	699.2	689.1	682.6
37.5°	908.3	845.1	799.3	755.1	725.3	698.1	682.7	658.6	647.9	633.9	620.2
40°	855.2	793.1	749.0	712.8	679.7	659.4	639.9	620.5	604.5	598.0	581.5
42.5°	800.9	750.3	706.2	666.7	644.4	623.0	598.3	584.0	567.6	557.0	546.8
45°	725.9	681.1	643.6	611.1	586.4	564.1	548.2	524.3	515.0	494.1	485.4
47.5°	660.1	618.4	582.6	551.7	527.7	513.1	489.8	471.2	456.2	443.4	432.3
50°	613.2	578.5	543.8	516.4	494.7	473.8	450.0	440.5	417.5	410.9	404.4
52.5°	570.4	537.5	505.8	478.9	457.2	436.9	415.8	403.6	388.0	381.5	376.7
55°	510.7	478.9	448.6	424.7	403.0	382.1	369.1	353.9	346.7	341.7	335.8
57.5°	450.5	422.0	398.7	374.6	352.8	336.1	321.1	312.0	304.5	297.8	291.0
60°	412.5	384.9	364.0	341.7	319.2	305.5	294.0	283.1	274.5	264.4	261.5
62.5°	371.9	348.0	328.8	307.0	287.5	274.9	263.9	253.6	243.3	228.6	224.5
65°	316.3	297.6	277.4	259.3	242.0	229.7	213.8	202.3	197.9	196.4	195.8
67.5°	266.1	248.4	231.0	212.4	196.7	185.3	177.3	175.5	172.5	171.6	169.6
70°	232.6	215.9	198.6	181.3	166.2	164.0	161.1	158.2	154.6	153.2	151.7
72.5°	202.6	185.3	168.0	154.1	147.6	144.9	142.0	139.1	136.7	135.3	134.3
75°	155.3	139.4	127.8	122.8	119.1	117.0	112.6	110.5	109.1	106.9	106.1
77.5°	111.8	102.8	97.6	94.3	90.6	88.2	85.8	83.6	82.1	81.6	80.5
80°	85.2	80.9	77.3	73.0	71.5	68.6	67.9	65.7	66.4	64.3	64.3
82.5°	66.2	60.7	57.7	55.6	54.2	51.8	51.2	50.1	50.2	48.6	48.6
85°	33.9	32.5	31.1	29.6	29.6	27.4	28.2	27.4	27.4	26.0	25.3
87.5°	13.2	13.2	13.0	14.3	15.5	15.1	14.9	14.1	13.8	14.1	13.8
90°	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1	28.2	30.1	31.0
92.5°	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0	70.4	62.5	56.6
95°	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5	189.1	149.6	128.8
97.5°	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1	470.5	368.7	300.9
100°	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8	742.2	613.3	499.5
102.5°	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7	1018.4	924.2	803.5
105°	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9	1249.2	1261.5	1230.4
107.5°	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2	1232.3	1330.1	1375.6
110°	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3	1179.6	1300.0	1377.1



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5	1117.2	1245.9	1334.3
115°	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0	1031.9	1155.2	1252.1
117.5°	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5	962.7	1074.4	1165.4
120°	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9	926.6	1026.2	1111.9
122.5°	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6	896.5	990.9	1068.3
125°	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1	857.0	939.7	1010.3
127.5°	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9	818.6	896.6	961.8
130°	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1	793.0	867.3	929.4
132.5°	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0	768.9	837.2	895.5
135°	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8	730.9	793.0	845.6
137.5°	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7	700.6	749.9	795.8
140°	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9	681.1	724.3	765.7
142.5°	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4	663.7	701.0	735.7
145°	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5	641.6	670.7	698.0
147.5°	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0	623.5	646.2	666.2
150°	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8	611.4	631.2	648.1
152.5°	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5	601.6	618.4	633.1
155°	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0	586.1	600.1	610.5
157.5°	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6	570.2	582.1	590.2
160°	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3	559.7	570.0	576.6
162.5°	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1	549.9	558.7	563.8
165°	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7	535.3	541.9	545.6
167.5°	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8	521.9	526.4	529.8
170°	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8	513.6	517.4	519.2
172.5°	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0	506.1	509.1	510.2
175°	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7	497.7	498.6	499.5
177.5°	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4	491.4	492.2	492.2
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1996.1	1997.2	1995.6	1996.7	1995.6	1997.2	1996.1	2002.4	2003.6	2004.8	2003.6
5°	1859.8	1851.2	1849.7	1847.6	1849.7	1851.2	1859.8	1863.5	1866.3	1872.2	1882.3
7.5°	1697.2	1695.9	1692.3	1687.2	1692.3	1695.9	1697.2	1709.6	1719.5	1730.7	1751.3
10°	1592.6	1589.0	1588.3	1583.2	1588.3	1589.0	1592.6	1608.5	1620.0	1636.0	1664.2
12.5°	1470.1	1446.9	1444.4	1431.8	1444.4	1446.9	1470.1	1490.6	1521.8	1537.2	1567.1
15°	1251.7	1247.4	1232.9	1223.5	1232.9	1247.4	1251.7	1269.0	1280.6	1322.5	1370.9
17.5°	1126.9	1112.8	1108.2	1106.3	1108.2	1112.8	1126.9	1135.3	1151.8	1173.8	1203.1
20°	1046.6	1033.6	1031.4	1030.0	1031.4	1033.6	1046.6	1056.7	1069.7	1093.5	1123.9
22.5°	991.1	977.5	971.9	967.5	971.9	977.5	991.1	998.9	1010.8	1029.4	1049.9
25°	896.4	891.3	888.4	886.9	888.4	891.3	896.4	903.6	915.1	940.4	962.1
27.5°	822.3	811.2	809.0	805.2	809.0	811.2	822.3	835.1	847.1	858.5	877.9
30°	780.0	776.5	771.4	767.0	771.4	776.5	780.0	786.6	794.5	814.0	832.8
32.5°	730.4	727.4	722.8	720.9	722.8	727.4	730.4	739.1	755.8	767.8	781.4
35°	675.3	665.2	660.9	654.4	660.9	665.2	675.3	682.6	689.1	699.2	723.7
37.5°	617.1	611.8	605.7	607.8	605.7	611.8	617.1	620.2	633.9	647.9	658.6
40°	572.0	568.4	567.0	566.3	567.0	568.4	572.0	581.5	598.0	604.5	620.5
42.5°	536.2	526.2	522.5	522.4	522.5	526.2	536.2	546.8	557.0	567.6	584.0
45°	481.7	472.4	465.9	466.6	465.9	472.4	481.7	485.4	494.1	515.0	524.3
47.5°	426.0	425.7	421.7	422.9	421.7	425.7	426.0	432.3	443.4	456.2	471.2
50°	399.4	395.1	392.2	392.9	392.2	395.1	399.4	404.4	410.9	417.5	440.5
52.5°	374.0	370.2	368.0	371.0	368.0	370.2	374.0	376.7	381.5	388.0	403.6
55°	332.2	327.9	327.2	326.5	327.2	327.9	332.2	335.8	341.7	346.7	353.9
57.5°	285.6	282.7	278.3	276.4	278.3	282.7	285.6	291.0	297.8	304.5	312.0
60°	252.0	246.3	239.0	238.4	239.0	246.3	252.0	261.5	264.4	274.5	283.1
62.5°	221.4	220.3	218.9	218.7	218.9	220.3	221.4	224.5	228.6	243.3	253.6
65°	194.3	193.6	194.3	195.0	194.3	193.6	194.3	195.8	196.4	197.9	202.3
67.5°	169.3	168.0	166.7	167.3	166.7	168.0	169.3	169.6	171.6	172.5	175.5
70°	150.2	149.5	148.8	148.8	148.8	149.5	150.2	151.7	153.2	154.6	158.2
72.5°	131.8	131.6	130.9	130.3	130.9	131.6	131.8	134.3	135.3	136.7	139.1
75°	105.5	104.0	104.0	104.0	104.0	104.0	105.5	106.1	106.9	109.1	110.5
77.5°	80.3	79.6	78.9	78.3	78.9	79.6	80.3	80.5	81.6	82.1	83.6
80°	63.5	62.9	62.1	62.1	62.1	62.9	63.5	64.3	64.3	66.4	65.7
82.5°	48.5	47.8	47.7	47.1	47.7	47.8	48.5	48.6	48.6	50.2	50.1
85°	26.0	26.8	26.0	27.4	26.0	26.8	26.0	25.3	26.0	27.4	27.4
87.5°	13.8	13.1	13.8	13.1	13.8	13.1	13.8	13.8	14.1	13.8	14.1
90°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.1	28.2	30.1
92.5°	55.9	52.9	53.6	52.1	53.6	52.9	55.9	56.6	62.5	70.4	82.0
95°	116.7	109.1	106.3	107.3	106.3	109.1	116.7	128.8	149.6	189.1	246.5
97.5°	255.9	232.7	219.0	211.1	219.0	232.7	255.9	300.9	368.7	470.5	575.1
100°	421.4	381.0	353.7	336.8	353.7	381.0	421.4	499.5	613.3	742.2	858.8
102.5°	718.7	649.6	615.6	592.7	615.6	649.6	718.7	803.5	924.2	1018.4	1044.7
105°	1172.1	1113.8	1073.3	1060.2	1073.3	1113.8	1172.1	1230.4	1261.5	1249.2	1142.9
107.5°	1383.0	1379.8	1371.7	1354.2	1371.7	1379.8	1383.0	1375.6	1330.1	1232.3	1072.2
110°	1417.6	1435.5	1444.0	1443.0	1444.0	1435.5	1417.6	1377.1	1300.0	1179.6	1011.3



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1390.5	1420.4	1436.4	1441.5	1436.4	1420.4	1390.5	1334.3	1245.9	1117.2	955.5
115°	1318.8	1362.1	1386.6	1395.1	1386.6	1362.1	1318.8	1252.1	1155.2	1031.9	887.0
117.5°	1233.4	1279.1	1305.0	1312.0	1305.0	1279.1	1233.4	1165.4	1074.4	962.7	835.5
120°	1177.7	1221.9	1249.2	1258.7	1249.2	1221.9	1177.7	1111.9	1026.2	926.6	809.9
122.5°	1127.3	1170.7	1195.0	1203.0	1195.0	1170.7	1127.3	1068.3	990.9	896.5	789.6
125°	1064.9	1100.6	1124.1	1131.6	1124.1	1100.6	1064.9	1010.3	939.7	857.0	760.1
127.5°	1009.4	1042.8	1063.2	1069.2	1063.2	1042.8	1009.4	961.8	896.6	818.6	730.9
130°	975.5	1007.5	1026.2	1033.8	1026.2	1007.5	975.5	929.4	867.3	793.0	712.1
132.5°	940.8	972.9	990.1	996.9	990.1	972.9	940.8	895.5	837.2	768.9	694.0
135°	886.1	917.2	934.1	937.8	934.1	917.2	886.1	845.6	793.0	730.9	668.8
137.5°	832.7	859.4	874.3	880.0	874.3	859.4	832.7	795.8	749.9	700.6	648.7
140°	795.8	820.3	834.4	840.0	834.4	820.3	795.8	765.7	724.3	681.1	635.9
142.5°	764.2	786.5	799.0	800.1	799.0	786.5	764.2	735.7	701.0	663.7	625.4
145°	720.6	736.6	745.9	748.8	745.9	736.6	720.6	698.0	670.7	641.6	610.5
147.5°	684.9	697.6	704.0	705.7	704.0	697.6	684.9	666.2	646.2	623.5	599.0
150°	662.2	673.5	679.2	680.1	679.2	673.5	662.2	648.1	631.2	611.4	590.8
152.5°	644.1	653.9	658.1	658.3	658.1	653.9	644.1	633.1	618.4	601.6	582.5
155°	620.9	627.5	631.2	629.3	631.2	627.5	620.9	610.5	600.1	586.1	571.0
157.5°	597.5	602.9	604.6	604.6	604.6	602.9	597.5	590.2	582.1	570.2	557.6
160°	583.2	588.0	588.9	588.9	588.9	588.0	583.2	576.6	570.0	559.7	549.3
162.5°	570.4	573.6	574.6	573.8	574.6	573.6	570.4	563.8	558.7	549.9	541.1
165°	549.3	553.1	553.1	552.1	553.1	553.1	549.3	545.6	541.9	535.3	528.7
167.5°	531.5	533.6	533.4	532.3	533.4	533.6	531.5	529.8	526.4	521.9	516.8
170°	520.2	523.0	522.1	520.2	522.1	523.0	520.2	519.2	517.4	513.6	510.8
172.5°	511.1	512.5	511.5	510.4	511.5	512.5	511.1	510.2	509.1	506.1	504.0
175°	499.5	500.5	499.5	497.7	499.5	500.5	499.5	499.5	498.6	497.7	496.7
177.5°	492.2	492.2	491.4	489.9	491.4	492.2	492.2	492.2	492.2	491.4	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	1998.9	2007.1	2019.2	2026.1	2037.7	2045.2	2049.3	2056.7	2060.8	2075.3	2090.3
5°	1887.3	1898.8	1919.1	1937.9	1958.1	1979.1	1994.2	2011.6	2027.4	2054.8	2083.8
7.5°	1759.3	1775.4	1806.7	1836.6	1871.9	1901.5	1927.6	1957.2	1983.7	2023.0	2064.0
10°	1663.4	1691.6	1732.8	1761.0	1807.1	1836.7	1877.9	1910.4	1947.3	1999.2	2045.5
12.5°	1580.7	1614.8	1647.8	1687.0	1728.5	1777.8	1823.1	1864.8	1908.6	1962.3	2016.6
15°	1430.9	1480.0	1531.3	1570.9	1627.3	1679.3	1732.0	1788.4	1841.8	1906.1	1976.9
17.5°	1237.8	1294.8	1381.0	1449.1	1515.2	1567.4	1632.7	1700.8	1763.8	1841.4	1920.1
20°	1150.6	1192.5	1250.9	1342.7	1442.4	1498.0	1564.4	1639.6	1711.8	1796.3	1880.8
22.5°	1080.6	1117.9	1164.9	1236.4	1347.6	1423.4	1492.8	1569.1	1652.8	1739.1	1832.9
25°	980.8	1006.8	1055.9	1113.7	1190.3	1315.2	1391.1	1467.6	1558.7	1651.1	1758.0
27.5°	905.9	929.3	961.2	1016.3	1073.3	1163.0	1283.6	1367.2	1457.8	1561.9	1672.8
30°	848.7	876.1	911.5	950.6	1012.7	1082.7	1203.3	1300.1	1389.7	1496.6	1615.0
32.5°	807.1	828.8	858.9	898.5	950.3	1017.4	1113.7	1231.3	1318.6	1431.3	1554.9
35°	738.9	764.2	788.7	826.3	868.2	929.5	1002.5	1128.2	1214.8	1326.1	1450.3
37.5°	682.7	698.1	725.3	755.1	799.3	845.1	908.3	1021.1	1114.7	1224.0	1351.1
40°	639.9	659.4	679.7	712.8	749.0	793.1	855.2	939.0	1046.6	1153.5	1277.7
42.5°	598.3	623.0	644.4	666.7	706.2	750.3	800.9	871.9	981.8	1083.0	1203.7
45°	548.2	564.1	586.4	611.1	643.6	681.1	725.9	788.0	893.4	980.8	1094.3
47.5°	489.8	513.1	527.7	551.7	582.6	618.4	660.1	713.8	799.1	881.0	986.2
50°	450.0	473.8	494.7	516.4	543.8	578.5	613.2	665.2	733.9	819.8	918.0
52.5°	415.8	436.9	457.2	478.9	505.8	537.5	570.4	616.1	674.9	753.9	849.2
55°	369.1	382.1	403.0	424.7	448.6	478.9	510.7	548.9	599.5	665.9	743.2
57.5°	321.1	336.1	352.8	374.6	398.7	422.0	450.5	485.2	525.1	585.2	651.4
60°	294.0	305.5	319.2	341.7	364.0	384.9	412.5	441.3	478.9	530.8	587.2
62.5°	263.9	274.9	287.5	307.0	328.8	348.0	371.9	402.6	434.4	481.7	531.1
65°	213.8	229.7	242.0	259.3	277.4	297.6	316.3	340.9	369.1	406.6	450.7
67.5°	177.3	185.3	196.7	212.4	231.0	248.4	266.1	285.3	309.7	338.7	373.7
70°	161.1	164.0	166.2	181.3	198.6	215.9	232.6	250.6	271.5	295.4	325.7
72.5°	142.0	144.9	147.6	154.1	168.0	185.3	202.6	215.9	235.7	255.5	280.1
75°	112.6	117.0	119.1	122.8	127.8	139.4	155.3	168.2	179.8	195.0	214.5
77.5°	85.8	88.2	90.6	94.3	97.6	102.8	111.8	123.5	134.3	143.2	156.6
80°	67.9	68.6	71.5	73.0	77.3	80.9	85.2	94.6	105.5	109.1	118.5
82.5°	51.2	51.8	54.2	55.6	57.7	60.7	66.2	68.6	77.1	81.9	87.8
85°	28.2	27.4	29.6	29.6	31.1	32.5	33.9	37.5	39.7	45.5	46.9
87.5°	14.9	15.1	15.5	14.3	13.0	13.2	13.2	13.5	14.2	15.2	17.0
90°	31.0	32.0	31.0	25.4	18.9	14.1	11.3	9.4	7.5	3.8	0.9
92.5°	103.3	122.2	120.6	93.9	64.0	42.7	33.8	27.4	23.4	16.6	11.5
95°	322.6	368.7	326.4	217.3	135.4	92.2	69.7	54.6	46.1	36.7	32.9
97.5°	660.3	629.5	474.1	292.8	178.7	124.3	98.8	81.4	68.7	58.7	53.6
100°	878.6	743.1	511.7	308.6	193.8	143.9	117.6	98.8	83.7	75.2	72.4
102.5°	959.9	746.9	497.5	309.3	207.4	161.3	134.9	115.4	100.3	91.8	89.7
105°	947.3	697.0	469.4	314.1	230.5	186.2	159.9	139.2	125.1	118.6	114.8
107.5°	864.7	643.7	455.4	327.2	254.2	211.3	184.7	164.3	151.3	144.9	141.9
110°	812.8	618.0	452.5	337.7	269.9	228.6	201.3	181.5	169.3	163.7	159.9



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	776.7	601.4	453.2	349.0	285.0	245.2	217.1	198.1	186.6	180.2	176.4
115°	731.9	583.2	457.1	365.9	308.6	268.1	242.7	223.9	212.6	207.0	202.3
117.5°	703.6	574.4	463.9	384.0	330.2	292.8	266.4	248.4	238.4	232.7	228.9
120°	688.6	569.1	468.4	396.1	345.3	308.6	282.2	263.3	255.0	249.3	245.5
122.5°	675.8	566.1	473.7	406.5	359.5	325.1	298.0	279.2	269.9	264.3	261.4
125°	657.5	560.6	481.6	423.3	381.0	347.1	320.7	302.0	290.7	285.0	282.2
127.5°	640.6	557.4	489.7	438.9	401.0	368.0	340.9	322.8	310.4	302.6	298.8
130°	629.3	555.9	495.8	448.7	412.9	380.0	353.7	334.9	321.7	312.3	308.6
132.5°	620.3	555.2	501.7	458.5	423.5	392.1	365.7	346.2	332.2	322.1	317.5
135°	607.7	554.0	508.9	471.3	438.4	408.2	381.9	360.2	346.2	334.9	331.1
137.5°	598.8	553.8	515.3	481.1	450.4	420.7	396.2	374.8	359.7	348.5	343.9
140°	593.6	553.1	518.3	486.4	457.1	429.0	404.5	383.8	368.7	357.5	353.7
142.5°	588.3	553.1	520.6	490.9	462.4	435.0	412.0	392.1	377.0	366.5	363.4
145°	581.4	551.2	523.0	496.7	470.3	445.0	424.2	405.5	391.3	381.9	378.1
147.5°	574.2	547.9	523.8	499.9	476.7	452.9	434.4	418.8	405.8	396.8	394.0
150°	568.2	545.6	523.0	501.3	479.8	458.1	441.2	427.1	414.8	407.3	404.5
152.5°	562.9	541.9	521.5	502.1	482.8	463.4	448.0	434.6	423.9	416.3	415.0
155°	553.1	535.3	519.2	503.2	487.3	471.3	457.1	446.9	436.5	430.8	429.9
157.5°	543.9	528.5	514.9	503.2	490.5	476.9	465.1	456.8	447.8	443.3	442.3
160°	537.2	524.0	512.6	503.2	492.0	480.7	470.3	462.8	455.2	451.6	450.6
162.5°	531.1	520.2	510.4	502.5	492.8	483.0	474.9	468.1	462.0	458.3	458.8
165°	521.1	512.6	506.1	500.5	493.9	485.4	479.8	475.0	469.4	467.5	468.4
167.5°	511.3	506.1	501.7	499.2	493.7	487.5	483.9	480.5	476.9	475.2	476.4
170°	506.1	502.3	499.5	497.7	492.9	488.2	485.4	483.5	480.7	479.8	481.6
172.5°	500.9	497.9	496.5	495.4	492.2	489.0	486.9	485.8	483.0	483.5	484.7
175°	493.9	492.9	492.0	492.9	491.1	489.2	488.2	488.2	486.4	487.3	488.2
177.5°	489.9	489.2	489.9	491.4	489.9	489.2	489.2	489.2	487.7	488.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2090.8	2092.5	2104.1	2109.3	2119.8	2123.7	2128.4	2127.2	2127.2	2129.6	2145.7
5°	2095.4	2109.8	2131.5	2152.4	2172.7	2189.9	2201.5	2213.1	2217.4	2238.4	2257.1
7.5°	2087.8	2114.4	2150.2	2182.2	2220.4	2250.3	2275.2	2297.5	2312.9	2343.3	2374.5
10°	2078.0	2115.5	2156.0	2197.2	2249.8	2289.6	2330.1	2361.2	2371.2	2416.8	2442.8
12.5°	2058.3	2108.7	2160.0	2213.4	2264.9	2319.7	2364.2	2395.2	2430.7	2471.6	2519.6
15°	2028.9	2086.7	2153.8	2222.4	2296.1	2362.6	2410.3	2464.4	2503.4	2548.2	2590.1
17.5°	1986.6	2061.0	2146.4	2225.8	2311.0	2382.4	2448.0	2499.9	2527.4	2553.0	2559.2
20°	1953.0	2033.3	2133.6	2227.5	2312.7	2395.1	2460.0	2503.4	2510.7	2511.3	2473.0
22.5°	1916.7	2007.2	2112.2	2208.5	2310.5	2402.0	2452.6	2471.1	2442.4	2393.5	2319.4
25°	1849.7	1954.5	2076.5	2186.3	2297.5	2384.3	2401.6	2369.1	2268.7	2163.2	2029.6
27.5°	1777.3	1895.0	2025.8	2147.9	2266.3	2320.1	2282.6	2165.5	1984.7	1827.5	1637.0
30°	1724.1	1856.2	1984.8	2121.3	2231.1	2254.2	2168.3	1995.6	1784.7	1547.8	1357.9
32.5°	1663.4	1802.0	1943.2	2084.3	2176.2	2153.7	2011.7	1799.2	1551.9	1319.0	1139.4
35°	1576.7	1719.8	1872.2	2013.7	2072.2	1974.7	1762.4	1485.7	1232.9	1015.5	892.0
37.5°	1476.6	1632.4	1790.8	1920.8	1916.7	1754.2	1464.9	1179.3	966.9	838.3	750.3
40°	1405.5	1563.0	1734.2	1844.0	1797.1	1585.4	1272.0	1002.5	847.3	744.7	680.4
42.5°	1337.4	1495.4	1665.5	1752.7	1671.0	1410.9	1098.6	887.5	759.4	679.4	627.3
45°	1221.3	1388.2	1545.7	1594.0	1448.1	1161.4	888.4	735.3	650.1	590.8	554.7
47.5°	1108.0	1272.1	1415.8	1416.6	1219.4	941.9	749.4	636.3	563.5	517.7	491.4
50°	1038.6	1194.7	1315.2	1296.5	1072.6	837.8	670.2	572.8	512.1	476.7	449.2
52.5°	960.6	1112.0	1216.4	1163.0	948.4	737.3	599.2	517.3	467.0	436.2	411.7
55°	847.3	981.6	1055.3	974.3	773.5	613.2	506.3	442.1	404.4	378.4	357.5
57.5°	735.8	846.7	893.1	798.8	637.2	508.5	428.3	380.0	342.8	324.1	313.3
60°	665.9	760.5	793.1	689.1	554.0	444.9	379.2	334.4	307.0	294.7	283.9
62.5°	597.2	674.5	687.9	592.6	483.0	389.5	333.0	295.1	276.9	265.2	255.0
65°	495.5	551.1	544.6	468.1	382.1	309.2	268.0	244.9	231.1	214.5	196.4
67.5°	407.9	441.9	421.4	364.0	291.6	240.3	213.4	195.9	178.8	163.1	158.9
70°	352.5	371.9	350.3	297.6	239.0	201.5	179.8	158.9	148.8	145.2	138.6
72.5°	299.4	306.1	282.7	237.5	194.5	166.8	145.7	134.0	128.6	125.5	121.3
75°	224.6	219.6	199.3	164.0	135.1	116.3	109.8	105.5	101.8	99.0	96.8
77.5°	157.8	150.3	132.3	109.2	94.1	85.1	81.2	78.9	77.1	75.7	73.5
80°	118.5	113.4	95.4	78.0	71.5	67.2	65.0	62.1	62.1	60.7	58.5
82.5°	86.7	81.1	65.3	57.2	53.6	51.0	49.4	47.7	47.1	47.4	45.8
85°	45.5	36.9	32.5	31.1	28.9	27.4	28.2	26.8	26.8	26.8	26.0
87.5°	14.6	12.4	12.3	12.1	13.2	14.1	14.9	16.0	16.8	16.0	16.4
90°	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0	30.1
92.5°	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3	82.0
95°	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6	246.5
97.5°	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3	575.1
100°	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6	858.8
102.5°	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9	1044.7
105°	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3	1142.9
107.5°	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7	1072.2
110°	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8	1011.3



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7	955.5
115°	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9	887.0
117.5°	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6	835.5
120°	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6	809.9
122.5°	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8	789.6
125°	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5	760.1
127.5°	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6	730.9
130°	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3	712.1
132.5°	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3	694.0
135°	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7	668.8
137.5°	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8	648.7
140°	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6	635.9
142.5°	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3	625.4
145°	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4	610.5
147.5°	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2	599.0
150°	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2	590.8
152.5°	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9	582.5
155°	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1	571.0
157.5°	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9	557.6
160°	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2	549.3
162.5°	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1	541.1
165°	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1	528.7
167.5°	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3	516.8
170°	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1	510.8
172.5°	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9	504.0
175°	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9	496.7
177.5°	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9	491.4
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7	2078.7
2.5°	2151.5	2159.0	2162.5	2162.5	2166.5	2164.8	2163.0
5°	2275.2	2288.9	2291.8	2304.8	2314.1	2311.3	2312.7
7.5°	2398.1	2420.2	2442.0	2452.0	2453.5	2459.4	2461.5
10°	2473.8	2491.9	2525.8	2520.7	2546.0	2560.5	2536.7
12.5°	2546.6	2571.0	2594.5	2601.0	2615.4	2620.0	2610.6
15°	2612.4	2625.5	2627.0	2623.3	2627.6	2624.0	2610.3
17.5°	2550.9	2529.9	2487.1	2466.8	2450.8	2427.1	2417.6
20°	2449.2	2387.1	2314.9	2286.0	2252.0	2185.6	2201.5
22.5°	2229.7	2158.9	2086.7	2002.3	1962.0	1899.0	1895.3
25°	1888.0	1765.9	1631.6	1537.8	1482.8	1420.0	1392.5
27.5°	1467.9	1314.3	1204.2	1148.4	1097.7	1047.9	1045.8
30°	1191.8	1076.2	991.0	943.3	912.2	891.3	895.6
32.5°	1004.6	925.4	867.9	828.3	805.3	789.6	789.3
35°	821.2	767.0	730.2	713.6	697.0	685.4	686.2
37.5°	702.8	670.2	649.8	631.4	621.0	615.4	612.2
40°	642.1	615.4	599.5	588.6	579.9	572.0	570.6
42.5°	594.2	572.0	556.2	547.6	539.5	534.0	532.4
45°	527.3	509.2	494.7	485.4	481.7	476.7	476.7
47.5°	469.0	451.3	440.0	434.1	427.9	424.5	424.4
50°	429.8	416.0	406.0	402.3	397.3	395.1	394.4
52.5°	394.5	384.3	377.0	374.6	372.4	369.7	370.1
55°	346.7	340.9	338.0	335.8	332.2	327.9	330.8
57.5°	306.4	301.5	293.7	286.9	283.6	280.5	281.7
60°	278.1	268.0	257.9	249.9	247.7	241.2	241.2
62.5°	242.2	228.1	215.7	211.2	209.1	206.0	205.4
65°	186.3	180.6	177.7	174.7	173.3	173.3	171.9
67.5°	154.4	152.1	148.9	148.2	146.8	146.4	145.9
70°	136.5	133.7	132.1	131.5	130.0	130.7	128.6
72.5°	119.1	116.9	116.6	114.7	113.9	114.0	112.4
75°	93.9	93.9	93.2	92.5	91.0	90.3	91.0
77.5°	72.2	72.4	71.1	71.0	70.8	71.0	70.2
80°	57.8	58.5	57.8	57.0	56.4	57.0	56.4
82.5°	45.6	44.7	44.5	44.4	44.2	43.7	43.6
85°	26.0	26.8	26.0	25.3	25.3	25.3	26.0
87.5°	15.5	15.8	16.0	16.0	16.0	16.0	15.5
90°	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0



TEST NUMBER: P331755-830

CATALOG NUMBER: SA2XXRDIP-C1005D925U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)