

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331448-935

Luminaire Tested: **SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331448-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6638.9 lumens  
Efficiency: N/A  
Efficacy: 99.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331448-935  
CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	41	37	35	32
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	34	31	28
6	65	54	46	40	61	50	43	38	44	39	35	39	34	31	34	30	27	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	22	28	24	20	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	2.5
10°-20°	475.3	7.2
20°-30°	689.9	10.4
30°-40°	728.0	11.0
40°-50°	644.6	9.7
50°-60°	514.4	7.7
60°-70°	349.6	5.3
70°-80°	179.3	2.7
80°-90°	47.3	0.7
90°-100°	64.5	1.0
100°-110°	200.4	3.0
110°-120°	342.5	5.2
120°-130°	450.4	6.8
130°-140°	505.6	7.6
140°-150°	495.7	7.5
150°-160°	415.8	6.3
160°-170°	275.8	4.2
170°-180°	96.4	1.5
0°-30°	1328.7	20.0
0°-40°	2056.7	31.0
0°-60°	3215.7	48.4
0°-90°	3791.8	57.1
90°-120°	607.4	9.1
90°-150°	2059.1	31.0
90°-180°	2847.0	42.9
0°-180°	6638.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	40
90°	29	1	29	1	29	14
95°	53	45	53	45	53	59
105°	191	185	191	185	191	201
115°	344	344	344	344	344	339
125°	502	500	502	500	502	447
135°	655	647	655	647	655	504
145°	794	785	794	785	794	496
155°	905	898	905	898	905	416
165°	978	977	978	977	978	276
175°	1013	1016	1013	1016	1013	96
180°	1018	1018	1018	1018	1018	



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	19.5	19.5	20.1	19.5	19.4	20.0	20.1	19.5	20.2	20.8	20.5
90°	29.2	29.0	28.8	28.7	28.4	28.6	28.9	29.3	29.7	30.0	25.8
92.5°	27.8	27.8	27.7	27.7	27.7	27.6	27.6	27.5	27.4	27.3	26.3
95°	53.3	53.6	54.1	54.4	54.8	55.0	55.0	55.0	55.0	55.0	54.6
97.5°	92.3	92.3	92.4	92.4	92.5	92.5	92.5	92.5	92.5	92.5	91.7
100°	117.7	117.9	118.1	118.3	118.5	118.6	118.6	118.6	118.6	118.6	118.0
102.5°	146.6	146.8	147.0	147.1	147.3	147.4	147.2	147.1	146.9	146.8	146.0
105°	190.7	190.7	190.7	190.7	190.7	190.5	190.2	189.8	189.4	189.0	188.6
107.5°	232.3	233.2	234.1	235.0	235.8	236.2	236.1	235.9	235.7	235.6	235.6
110°	264.7	265.2	265.8	266.4	266.9	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.6	296.0	296.4	296.9	297.2	297.7	298.2	298.6	299.1	299.5	299.7
115°	343.7	344.2	344.8	345.4	345.9	346.4	346.6	346.7	347.0	347.2	347.5
117.5°	389.6	390.1	390.7	391.3	391.8	392.4	392.9	393.3	393.7	394.3	395.3
120°	421.9	422.5	423.0	423.6	424.2	424.5	424.5	424.5	424.5	424.5	426.0
122.5°	453.5	453.9	454.3	454.8	455.2	455.6	456.1	456.5	457.0	457.4	458.6
125°	501.8	502.0	502.1	502.4	502.6	502.9	503.5	504.1	504.6	505.2	505.8
127.5°	545.8	546.4	547.0	547.6	548.2	548.9	549.6	550.3	551.0	551.6	552.3
130°	577.4	578.2	578.9	579.7	580.5	581.0	581.4	581.8	582.2	582.6	583.0
132.5°	607.7	608.3	608.9	609.5	610.1	610.8	611.7	612.5	613.4	614.2	614.1
135°	654.7	655.3	655.9	656.4	657.0	657.4	657.6	657.8	658.0	658.1	657.8
137.5°	697.3	698.1	698.9	699.6	700.4	700.9	701.0	701.2	701.4	701.5	701.0
140°	726.9	727.7	728.4	729.2	730.0	730.4	730.4	730.4	730.4	730.4	729.4
142.5°	753.7	754.5	755.3	756.0	756.8	757.1	756.9	756.8	756.6	756.5	755.8
145°	793.9	794.7	795.5	796.3	797.0	797.3	797.1	796.9	796.7	796.5	795.4
147.5°	829.8	830.6	831.3	832.1	832.8	832.9	832.5	832.1	831.6	831.2	830.4
150°	853.3	853.8	854.4	855.0	855.5	855.5	855.0	854.4	853.8	853.3	852.5
152.5°	875.2	876.0	876.7	877.4	878.1	878.1	877.4	876.7	876.0	875.2	874.3
155°	904.7	905.3	905.9	906.5	907.1	906.9	905.9	905.0	904.0	903.0	902.5
157.5°	930.2	931.1	932.0	933.0	933.8	933.7	932.4	931.1	929.8	928.5	928.2
160°	946.0	946.8	947.5	948.3	949.1	948.9	947.7	946.6	945.5	944.3	944.1
162.5°	959.8	960.7	961.6	962.5	963.5	963.2	961.9	960.6	959.3	958.0	957.9
165°	977.8	978.8	979.7	980.7	981.6	981.5	980.1	978.8	977.4	976.1	976.1
167.5°	992.6	993.6	994.5	995.6	996.5	996.3	995.1	993.7	992.4	991.0	991.1
170°	1000.1	1001.3	1002.5	1003.6	1004.7	1004.6	1003.3	1001.9	1000.7	999.3	999.4
172.5°	1006.3	1007.5	1008.7	1009.8	1010.9	1010.8	1009.5	1008.1	1006.9	1005.5	1005.6
175°	1013.1	1014.2	1015.3	1016.5	1017.6	1017.5	1016.2	1014.9	1013.5	1012.2	1012.5
177.5°	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2	1016.4
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	20.1	19.4	18.5	18.9	16.9	16.4	13.9	11.8	11.7	11.6	11.0
90°	21.7	17.5	13.3	10.0	7.7	5.4	3.2	0.9	3.2	5.4	7.7
92.5°	25.3	24.4	23.3	22.0	20.3	18.7	17.0	15.3	17.0	18.7	20.3
95°	54.2	53.8	53.5	52.3	50.4	48.5	46.6	44.7	46.6	48.5	50.4
97.5°	91.0	90.3	89.5	88.3	86.7	85.0	83.3	81.6	83.3	85.0	86.7
100°	117.4	116.8	116.3	115.2	113.7	112.2	110.6	109.1	110.6	112.2	113.7
102.5°	145.3	144.6	143.9	142.8	141.6	140.4	139.2	138.0	139.2	140.4	141.6
105°	188.3	187.9	187.5	187.0	186.5	185.9	185.3	184.8	185.3	185.9	186.5
107.5°	235.6	235.6	235.6	235.2	234.4	233.5	232.6	231.8	232.6	233.5	234.4
110°	267.3	267.3	267.3	266.7	265.5	264.3	263.2	262.1	263.2	264.3	265.5





TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	299.8	300.0	300.1	299.6	298.5	297.4	296.2	295.1	296.2	297.4	298.5
115°	347.9	348.3	348.6	348.3	347.2	345.9	344.8	343.7	344.8	345.9	347.2
117.5°	396.3	397.4	398.5	398.3	396.7	395.2	393.6	392.2	393.6	395.2	396.7
120°	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	426.0	427.5	429.0
122.5°	459.6	460.6	461.8	461.3	459.5	457.7	455.8	454.0	455.8	457.7	459.5
125°	506.4	507.0	507.6	507.0	505.2	503.5	501.8	500.1	501.8	503.5	505.2
127.5°	553.0	553.7	554.4	553.6	551.5	549.3	547.1	544.9	547.1	549.3	551.5
130°	583.3	583.7	584.1	583.1	580.6	578.1	575.6	573.1	575.6	578.1	580.6
132.5°	614.1	614.0	613.9	612.9	610.8	608.8	606.7	604.8	606.7	608.8	610.8
135°	657.4	657.0	656.7	655.4	653.3	651.2	649.1	647.0	649.1	651.2	653.3
137.5°	700.5	700.0	699.5	698.4	696.6	694.9	693.2	691.6	693.2	694.9	696.6
140°	728.4	727.5	726.5	725.2	723.5	721.8	720.1	718.3	720.1	721.8	723.5
142.5°	755.2	754.5	753.9	752.7	751.0	749.2	747.5	745.8	747.5	749.2	751.0
145°	794.2	793.1	791.9	790.7	789.4	788.0	786.7	785.3	786.7	788.0	789.4
147.5°	829.7	829.0	828.2	827.0	825.4	823.8	822.2	820.5	822.2	823.8	825.4
150°	851.7	850.9	850.2	849.2	848.1	846.9	845.8	844.6	845.8	846.9	848.1
152.5°	873.4	872.5	871.6	870.6	869.4	868.2	867.1	865.9	867.1	868.2	869.4
155°	901.9	901.4	900.8	900.2	899.7	899.1	898.5	897.9	898.5	899.1	899.7
157.5°	927.8	927.5	927.1	926.8	926.3	926.0	925.6	925.2	925.6	926.0	926.3
160°	943.9	943.7	943.6	943.2	942.9	942.5	942.1	941.8	942.1	942.5	942.9
162.5°	957.7	957.5	957.3	957.2	957.1	957.0	956.9	956.8	956.9	957.0	957.1
165°	976.1	976.1	976.1	976.2	976.4	976.5	976.8	977.0	976.8	976.5	976.4
167.5°	991.1	991.2	991.2	991.5	992.0	992.6	993.2	993.8	993.2	992.6	992.0
170°	999.7	999.9	1000.1	1000.4	1001.0	1001.6	1002.1	1002.7	1002.1	1001.6	1001.0
172.5°	1005.8	1006.1	1006.3	1006.6	1007.2	1007.8	1008.3	1008.9	1008.3	1007.8	1007.2
175°	1013.0	1013.3	1013.7	1014.2	1014.8	1015.3	1015.9	1016.5	1015.9	1015.3	1014.8
177.5°	1016.8	1017.0	1017.4	1017.7	1018.2	1018.6	1019.1	1019.6	1019.1	1018.6	1018.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	11.0	11.1	11.5	12.2	12.6	12.9	12.3	12.2	12.1	11.0	10.9
90°	10.0	13.3	17.5	21.7	25.8	30.0	29.7	29.3	28.9	28.6	28.4
92.5°	22.0	23.3	24.4	25.3	26.3	27.3	27.4	27.5	27.6	27.6	27.7
95°	52.3	53.5	53.8	54.2	54.6	55.0	55.0	55.0	55.0	55.0	54.8
97.5°	88.3	89.5	90.3	91.0	91.7	92.5	92.5	92.5	92.5	92.5	92.5
100°	115.2	116.3	116.8	117.4	118.0	118.6	118.6	118.6	118.6	118.6	118.5
102.5°	142.8	143.9	144.6	145.3	146.0	146.8	146.9	147.1	147.2	147.4	147.3
105°	187.0	187.5	187.9	188.3	188.6	189.0	189.4	189.8	190.2	190.5	190.7
107.5°	235.2	235.6	235.6	235.6	235.6	235.6	235.7	235.9	236.1	236.2	235.8
110°	266.7	267.3	267.3	267.3	267.3	267.3	267.3	267.3	267.3	267.3	266.9



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	299.6	300.1	300.0	299.8	299.7	299.5	299.1	298.6	298.2	297.7	297.2
115°	348.3	348.6	348.3	347.9	347.5	347.2	347.0	346.7	346.6	346.4	345.9
117.5°	398.3	398.5	397.4	396.3	395.3	394.3	393.7	393.3	392.9	392.4	391.8
120°	430.6	430.6	429.0	427.5	426.0	424.5	424.5	424.5	424.5	424.5	424.2
122.5°	461.3	461.8	460.6	459.6	458.6	457.4	457.0	456.5	456.1	455.6	455.2
125°	507.0	507.6	507.0	506.4	505.8	505.2	504.6	504.1	503.5	502.9	502.6
127.5°	553.6	554.4	553.7	553.0	552.3	551.6	551.0	550.3	549.6	548.9	548.2
130°	583.1	584.1	583.7	583.3	583.0	582.6	582.2	581.8	581.4	581.0	580.5
132.5°	612.9	613.9	614.0	614.1	614.1	614.2	613.4	612.5	611.7	610.8	610.1
135°	655.4	656.7	657.0	657.4	657.8	658.1	658.0	657.8	657.6	657.4	657.0
137.5°	698.4	699.5	700.0	700.5	701.0	701.5	701.4	701.2	701.0	700.9	700.4
140°	725.2	726.5	727.5	728.4	729.4	730.4	730.4	730.4	730.4	730.4	730.0
142.5°	752.7	753.9	754.5	755.2	755.8	756.5	756.6	756.8	756.9	757.1	756.8
145°	790.7	791.9	793.1	794.2	795.4	796.5	796.7	796.9	797.1	797.3	797.0
147.5°	827.0	828.2	829.0	829.7	830.4	831.2	831.6	832.1	832.5	832.9	832.8
150°	849.2	850.2	850.9	851.7	852.5	853.3	853.8	854.4	855.0	855.5	855.5
152.5°	870.6	871.6	872.5	873.4	874.3	875.2	876.0	876.7	877.4	878.1	878.1
155°	900.2	900.8	901.4	901.9	902.5	903.0	904.0	905.0	905.9	906.9	907.1
157.5°	926.8	927.1	927.5	927.8	928.2	928.5	929.8	931.1	932.4	933.7	933.8
160°	943.2	943.6	943.7	943.9	944.1	944.3	945.5	946.6	947.7	948.9	949.1
162.5°	957.2	957.3	957.5	957.7	957.9	958.0	959.3	960.6	961.9	963.2	963.5
165°	976.2	976.1	976.1	976.1	976.1	976.1	977.4	978.8	980.1	981.5	981.6
167.5°	991.5	991.2	991.2	991.1	991.1	991.0	992.4	993.7	995.1	996.3	996.5
170°	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7	1001.9	1003.3	1004.6	1004.7
172.5°	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9	1008.1	1009.5	1010.8	1010.9
175°	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5	1014.9	1016.2	1017.5	1017.6
177.5°	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	11.0	10.5	10.6	10.1	10.6	10.5	11.0	10.9	11.0	12.1	12.2
90°	28.7	28.8	29.0	29.2	29.0	28.8	28.7	28.4	28.6	28.9	29.3
92.5°	27.7	27.7	27.8	27.8	27.8	27.7	27.7	27.7	27.6	27.6	27.5
95°	54.4	54.1	53.6	53.3	53.6	54.1	54.4	54.8	55.0	55.0	55.0
97.5°	92.4	92.4	92.3	92.3	92.3	92.4	92.4	92.5	92.5	92.5	92.5
100°	118.3	118.1	117.9	117.7	117.9	118.1	118.3	118.5	118.6	118.6	118.6
102.5°	147.1	147.0	146.8	146.6	146.8	147.0	147.1	147.3	147.4	147.2	147.1
105°	190.7	190.7	190.7	190.7	190.7	190.7	190.7	190.7	190.5	190.2	189.8
107.5°	235.0	234.1	233.2	232.3	233.2	234.1	235.0	235.8	236.2	236.1	235.9
110°	266.4	265.8	265.2	264.7	265.2	265.8	266.4	266.9	267.3	267.3	267.3



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	296.9	296.4	296.0	295.6	296.0	296.4	296.9	297.2	297.7	298.2	298.6
115°	345.4	344.8	344.2	343.7	344.2	344.8	345.4	345.9	346.4	346.6	346.7
117.5°	391.3	390.7	390.1	389.6	390.1	390.7	391.3	391.8	392.4	392.9	393.3
120°	423.6	423.0	422.5	421.9	422.5	423.0	423.6	424.2	424.5	424.5	424.5
122.5°	454.8	454.3	453.9	453.5	453.9	454.3	454.8	455.2	455.6	456.1	456.5
125°	502.4	502.1	502.0	501.8	502.0	502.1	502.4	502.6	502.9	503.5	504.1
127.5°	547.6	547.0	546.4	545.8	546.4	547.0	547.6	548.2	548.9	549.6	550.3
130°	579.7	578.9	578.2	577.4	578.2	578.9	579.7	580.5	581.0	581.4	581.8
132.5°	609.5	608.9	608.3	607.7	608.3	608.9	609.5	610.1	610.8	611.7	612.5
135°	656.4	655.9	655.3	654.7	655.3	655.9	656.4	657.0	657.4	657.6	657.8
137.5°	699.6	698.9	698.1	697.3	698.1	698.9	699.6	700.4	700.9	701.0	701.2
140°	729.2	728.4	727.7	726.9	727.7	728.4	729.2	730.0	730.4	730.4	730.4
142.5°	756.0	755.3	754.5	753.7	754.5	755.3	756.0	756.8	757.1	756.9	756.8
145°	796.3	795.5	794.7	793.9	794.7	795.5	796.3	797.0	797.3	797.1	796.9
147.5°	832.1	831.3	830.6	829.8	830.6	831.3	832.1	832.8	832.9	832.5	832.1
150°	855.0	854.4	853.8	853.3	853.8	854.4	855.0	855.5	855.5	855.0	854.4
152.5°	877.4	876.7	876.0	875.2	876.0	876.7	877.4	878.1	878.1	877.4	876.7
155°	906.5	905.9	905.3	904.7	905.3	905.9	906.5	907.1	906.9	905.9	905.0
157.5°	933.0	932.0	931.1	930.2	931.1	932.0	933.0	933.8	933.7	932.4	931.1
160°	948.3	947.5	946.8	946.0	946.8	947.5	948.3	949.1	948.9	947.7	946.6
162.5°	962.5	961.6	960.7	959.8	960.7	961.6	962.5	963.5	963.2	961.9	960.6
165°	980.7	979.7	978.8	977.8	978.8	979.7	980.7	981.6	981.5	980.1	978.8
167.5°	995.6	994.5	993.6	992.6	993.6	994.5	995.6	996.5	996.3	995.1	993.7
170°	1003.6	1002.5	1001.3	1000.1	1001.3	1002.5	1003.6	1004.7	1004.6	1003.3	1001.9
172.5°	1009.8	1008.7	1007.5	1006.3	1007.5	1008.7	1009.8	1010.9	1010.8	1009.5	1008.1
175°	1016.5	1015.3	1014.2	1013.1	1014.2	1015.3	1016.5	1017.6	1017.5	1016.2	1014.9
177.5°	1018.9	1018.0	1017.0	1016.2	1017.0	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	12.3	12.9	12.6	12.2	11.5	11.1	11.0	11.0	11.6	11.7	11.8
90°	29.7	30.0	25.8	21.7	17.5	13.3	10.0	7.7	5.4	3.2	0.9
92.5°	27.4	27.3	26.3	25.3	24.4	23.3	22.0	20.3	18.7	17.0	15.3
95°	55.0	55.0	54.6	54.2	53.8	53.5	52.3	50.4	48.5	46.6	44.7
97.5°	92.5	92.5	91.7	91.0	90.3	89.5	88.3	86.7	85.0	83.3	81.6
100°	118.6	118.6	118.0	117.4	116.8	116.3	115.2	113.7	112.2	110.6	109.1
102.5°	146.9	146.8	146.0	145.3	144.6	143.9	142.8	141.6	140.4	139.2	138.0
105°	189.4	189.0	188.6	188.3	187.9	187.5	187.0	186.5	185.9	185.3	184.8
107.5°	235.7	235.6	235.6	235.6	235.6	235.6	235.2	234.4	233.5	232.6	231.8
110°	267.3	267.3	267.3	267.3	267.3	267.3	266.7	265.5	264.3	263.2	262.1



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	299.1	299.5	299.7	299.8	300.0	300.1	299.6	298.5	297.4	296.2	295.1
115°	347.0	347.2	347.5	347.9	348.3	348.6	348.3	347.2	345.9	344.8	343.7
117.5°	393.7	394.3	395.3	396.3	397.4	398.5	398.3	396.7	395.2	393.6	392.2
120°	424.5	424.5	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5
122.5°	457.0	457.4	458.6	459.6	460.6	461.8	461.3	459.5	457.7	455.8	454.0
125°	504.6	505.2	505.8	506.4	507.0	507.6	507.0	505.2	503.5	501.8	500.1
127.5°	551.0	551.6	552.3	553.0	553.7	554.4	553.6	551.5	549.3	547.1	544.9
130°	582.2	582.6	583.0	583.3	583.7	584.1	583.1	580.6	578.1	575.6	573.1
132.5°	613.4	614.2	614.1	614.1	614.0	613.9	612.9	610.8	608.8	606.7	604.8
135°	658.0	658.1	657.8	657.4	657.0	656.7	655.4	653.3	651.2	649.1	647.0
137.5°	701.4	701.5	701.0	700.5	700.0	699.5	698.4	696.6	694.9	693.2	691.6
140°	730.4	730.4	729.4	728.4	727.5	726.5	725.2	723.5	721.8	720.1	718.3
142.5°	756.6	756.5	755.8	755.2	754.5	753.9	752.7	751.0	749.2	747.5	745.8
145°	796.7	796.5	795.4	794.2	793.1	791.9	790.7	789.4	788.0	786.7	785.3
147.5°	831.6	831.2	830.4	829.7	829.0	828.2	827.0	825.4	823.8	822.2	820.5
150°	853.8	853.3	852.5	851.7	850.9	850.2	849.2	848.1	846.9	845.8	844.6
152.5°	876.0	875.2	874.3	873.4	872.5	871.6	870.6	869.4	868.2	867.1	865.9
155°	904.0	903.0	902.5	901.9	901.4	900.8	900.2	899.7	899.1	898.5	897.9
157.5°	929.8	928.5	928.2	927.8	927.5	927.1	926.8	926.3	926.0	925.6	925.2
160°	945.5	944.3	944.1	943.9	943.7	943.6	943.2	942.9	942.5	942.1	941.8
162.5°	959.3	958.0	957.9	957.7	957.5	957.3	957.2	957.1	957.0	956.9	956.8
165°	977.4	976.1	976.1	976.1	976.1	976.1	976.2	976.4	976.5	976.8	977.0
167.5°	992.4	991.0	991.1	991.1	991.2	991.2	991.5	992.0	992.6	993.2	993.8
170°	1000.7	999.3	999.4	999.7	999.9	1000.1	1000.4	1001.0	1001.6	1002.1	1002.7
172.5°	1006.9	1005.5	1005.6	1005.8	1006.1	1006.3	1006.6	1007.2	1007.8	1008.3	1008.9
175°	1013.5	1012.2	1012.5	1013.0	1013.3	1013.7	1014.2	1014.8	1015.3	1015.9	1016.5
177.5°	1017.0	1016.2	1016.4	1016.8	1017.0	1017.4	1017.7	1018.2	1018.6	1019.1	1019.6
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.9	16.4	16.9	18.9	18.5	19.4	20.1	20.5	20.8	20.2	19.5
90°	3.2	5.4	7.7	10.0	13.3	17.5	21.7	25.8	30.0	29.7	29.3
92.5°	17.0	18.7	20.3	22.0	23.3	24.4	25.3	26.3	27.3	27.4	27.5
95°	46.6	48.5	50.4	52.3	53.5	53.8	54.2	54.6	55.0	55.0	55.0
97.5°	83.3	85.0	86.7	88.3	89.5	90.3	91.0	91.7	92.5	92.5	92.5
100°	110.6	112.2	113.7	115.2	116.3	116.8	117.4	118.0	118.6	118.6	118.6
102.5°	139.2	140.4	141.6	142.8	143.9	144.6	145.3	146.0	146.8	146.9	147.1
105°	185.3	185.9	186.5	187.0	187.5	187.9	188.3	188.6	189.0	189.4	189.8
107.5°	232.6	233.5	234.4	235.2	235.6	235.6	235.6	235.6	235.6	235.7	235.9
110°	263.2	264.3	265.5	266.7	267.3	267.3	267.3	267.3	267.3	267.3	267.3





TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	296.2	297.4	298.5	299.6	300.1	300.0	299.8	299.7	299.5	299.1	298.6
115°	344.8	345.9	347.2	348.3	348.6	348.3	347.9	347.5	347.2	347.0	346.7
117.5°	393.6	395.2	396.7	398.3	398.5	397.4	396.3	395.3	394.3	393.7	393.3
120°	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	424.5	424.5
122.5°	455.8	457.7	459.5	461.3	461.8	460.6	459.6	458.6	457.4	457.0	456.5
125°	501.8	503.5	505.2	507.0	507.6	507.0	506.4	505.8	505.2	504.6	504.1
127.5°	547.1	549.3	551.5	553.6	554.4	553.7	553.0	552.3	551.6	551.0	550.3
130°	575.6	578.1	580.6	583.1	584.1	583.7	583.3	583.0	582.6	582.2	581.8
132.5°	606.7	608.8	610.8	612.9	613.9	614.0	614.1	614.1	614.2	613.4	612.5
135°	649.1	651.2	653.3	655.4	656.7	657.0	657.4	657.8	658.1	658.0	657.8
137.5°	693.2	694.9	696.6	698.4	699.5	700.0	700.5	701.0	701.5	701.4	701.2
140°	720.1	721.8	723.5	725.2	726.5	727.5	728.4	729.4	730.4	730.4	730.4
142.5°	747.5	749.2	751.0	752.7	753.9	754.5	755.2	755.8	756.5	756.6	756.8
145°	786.7	788.0	789.4	790.7	791.9	793.1	794.2	795.4	796.5	796.7	796.9
147.5°	822.2	823.8	825.4	827.0	828.2	829.0	829.7	830.4	831.2	831.6	832.1
150°	845.8	846.9	848.1	849.2	850.2	850.9	851.7	852.5	853.3	853.8	854.4
152.5°	867.1	868.2	869.4	870.6	871.6	872.5	873.4	874.3	875.2	876.0	876.7
155°	898.5	899.1	899.7	900.2	900.8	901.4	901.9	902.5	903.0	904.0	905.0
157.5°	925.6	926.0	926.3	926.8	927.1	927.5	927.8	928.2	928.5	929.8	931.1
160°	942.1	942.5	942.9	943.2	943.6	943.7	943.9	944.1	944.3	945.5	946.6
162.5°	956.9	957.0	957.1	957.2	957.3	957.5	957.7	957.9	958.0	959.3	960.6
165°	976.8	976.5	976.4	976.2	976.1	976.1	976.1	976.1	976.1	977.4	978.8
167.5°	993.2	992.6	992.0	991.5	991.2	991.2	991.1	991.1	991.0	992.4	993.7
170°	1002.1	1001.6	1001.0	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7	1001.9
172.5°	1008.3	1007.8	1007.2	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9	1008.1
175°	1015.9	1015.3	1014.8	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5	1014.9
177.5°	1019.1	1018.6	1018.2	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0	1018.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	20.1	20.0	19.4	19.5	20.1	19.5	19.5
90°	28.9	28.6	28.4	28.7	28.8	29.0	29.2
92.5°	27.6	27.6	27.7	27.7	27.7	27.8	27.8
95°	55.0	55.0	54.8	54.4	54.1	53.6	53.3
97.5°	92.5	92.5	92.5	92.4	92.4	92.3	92.3
100°	118.6	118.6	118.5	118.3	118.1	117.9	117.7
102.5°	147.2	147.4	147.3	147.1	147.0	146.8	146.6
105°	190.2	190.5	190.7	190.7	190.7	190.7	190.7
107.5°	236.1	236.2	235.8	235.0	234.1	233.2	232.3
110°	267.3	267.3	266.9	266.4	265.8	265.2	264.7



TEST NUMBER: P331448-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	298.2	297.7	297.2	296.9	296.4	296.0	295.6
115°	346.6	346.4	345.9	345.4	344.8	344.2	343.7
117.5°	392.9	392.4	391.8	391.3	390.7	390.1	389.6
120°	424.5	424.5	424.2	423.6	423.0	422.5	421.9
122.5°	456.1	455.6	455.2	454.8	454.3	453.9	453.5
125°	503.5	502.9	502.6	502.4	502.1	502.0	501.8
127.5°	549.6	548.9	548.2	547.6	547.0	546.4	545.8
130°	581.4	581.0	580.5	579.7	578.9	578.2	577.4
132.5°	611.7	610.8	610.1	609.5	608.9	608.3	607.7
135°	657.6	657.4	657.0	656.4	655.9	655.3	654.7
137.5°	701.0	700.9	700.4	699.6	698.9	698.1	697.3
140°	730.4	730.4	730.0	729.2	728.4	727.7	726.9
142.5°	756.9	757.1	756.8	756.0	755.3	754.5	753.7
145°	797.1	797.3	797.0	796.3	795.5	794.7	793.9
147.5°	832.5	832.9	832.8	832.1	831.3	830.6	829.8
150°	855.0	855.5	855.5	855.0	854.4	853.8	853.3
152.5°	877.4	878.1	878.1	877.4	876.7	876.0	875.2
155°	905.9	906.9	907.1	906.5	905.9	905.3	904.7
157.5°	932.4	933.7	933.8	933.0	932.0	931.1	930.2
160°	947.7	948.9	949.1	948.3	947.5	946.8	946.0
162.5°	961.9	963.2	963.5	962.5	961.6	960.7	959.8
165°	980.1	981.5	981.6	980.7	979.7	978.8	977.8
167.5°	995.1	996.3	996.5	995.6	994.5	993.6	992.6
170°	1003.3	1004.6	1004.7	1003.6	1002.5	1001.3	1000.1
172.5°	1009.5	1010.8	1010.9	1009.8	1008.7	1007.5	1006.3
175°	1016.2	1017.5	1017.6	1016.5	1015.3	1014.2	1013.1
177.5°	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2

(END OF REPORT)