

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331449-935

Luminaire Tested: **SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331449-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6901.2 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331449-935
CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	69	67	64	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	39	42	37	34	36	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	37	31	27	32	27	24	28	24	22	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20	17
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.5	2.4
10°-20°	475.3	6.9
20°-30°	689.9	10.0
30°-40°	728.0	10.5
40°-50°	644.6	9.3
50°-60°	514.4	7.5
60°-70°	349.6	5.1
70°-80°	179.3	2.6
80°-90°	47.2	0.7
90°-100°	178.7	2.6
100°-110°	606.3	8.8
110°-120°	644.1	9.3
120°-130°	530.2	7.7
130°-140°	425.8	6.2
140°-150°	321.8	4.7
150°-160°	226.1	3.3
160°-170°	133.1	1.9
170°-180°	43.3	0.6
0°-30°	1328.7	19.3
0°-40°	2056.7	29.8
0°-60°	3215.7	46.6
0°-90°	3791.8	54.9
90°-120°	1429.1	20.7
90°-150°	2706.8	39.2
90°-180°	3109.0	45.1
0°-180°	6901.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	40
90°	28	1	28	1	28	17
95°	98	30	98	30	98	127
105°	968	105	968	105	968	937
115°	1274	185	1274	185	1274	1248
125°	1034	258	1034	258	1034	934
135°	857	302	857	302	857	666
145°	684	345	684	345	684	434
155°	575	393	575	393	575	268
165°	504	428	504	428	504	144
175°	455	446	455	446	455	44
180°	447	447	447	447	447	



TEST NUMBER: P331449-935
 CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	19.4	19.4	19.9	19.4	19.4	19.7	19.4	19.2	19.9	20.7	21.0
90°	28.3	28.3	28.3	28.3	28.3	27.5	25.7	27.5	28.3	29.2	28.3
92.5°	47.6	49.0	48.3	51.1	51.7	57.1	64.3	74.9	94.4	111.7	110.1
95°	98.0	97.1	99.7	106.6	117.7	136.6	172.7	225.2	294.7	336.8	298.2
97.5°	192.9	200.0	212.6	233.8	274.8	336.8	429.8	525.4	603.2	575.1	433.1
100°	307.6	323.1	348.0	385.0	456.3	560.3	678.0	784.5	802.6	678.8	467.4
102.5°	541.4	562.3	593.4	656.5	734.0	844.2	930.3	954.3	876.8	682.3	454.4
105°	968.5	980.4	1017.4	1070.7	1123.9	1152.4	1141.2	1044.0	865.3	636.7	428.8
107.5°	1237.1	1253.0	1260.4	1263.3	1256.6	1215.0	1125.7	979.5	789.9	588.0	416.0
110°	1318.2	1319.1	1311.3	1294.9	1258.0	1187.6	1077.5	923.8	742.4	564.6	413.4



TEST NUMBER: P331449-935
 CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1316.8	1312.2	1297.5	1270.2	1218.8	1138.1	1020.5	872.9	709.5	549.4	414.0
115°	1274.4	1266.6	1244.2	1204.7	1143.8	1055.2	942.6	810.3	668.6	532.8	417.6
117.5°	1198.5	1192.1	1168.5	1126.7	1064.5	981.5	879.4	763.2	642.7	524.7	423.8
120°	1149.8	1141.2	1116.2	1075.8	1015.7	937.5	846.4	739.9	629.0	519.9	427.9
122.5°	1098.9	1091.7	1069.4	1029.8	975.9	905.2	818.9	721.3	617.3	517.1	432.7
125°	1033.7	1026.8	1005.4	972.8	922.9	858.4	782.8	694.3	600.6	512.1	440.0
127.5°	976.7	971.2	952.6	922.0	878.6	819.1	747.8	667.7	585.2	509.2	447.4
130°	944.3	937.5	920.3	891.1	849.0	792.3	724.4	650.5	574.9	507.8	452.9
132.5°	910.7	904.5	888.7	859.5	818.0	764.7	702.4	634.0	566.6	507.1	458.3
135°	856.7	853.3	837.8	809.4	772.5	724.4	667.7	611.0	555.1	506.1	464.9
137.5°	803.8	798.7	785.1	760.7	726.9	685.0	640.0	592.5	547.0	505.9	470.7
140°	767.3	762.2	749.3	726.9	699.5	661.7	622.2	580.9	542.3	505.2	473.5
142.5°	730.9	729.9	718.4	698.1	672.0	640.3	606.3	571.3	537.4	505.2	475.5
145°	684.0	681.4	672.9	658.2	637.6	612.7	586.1	557.7	531.1	503.5	477.8
147.5°	644.6	643.1	637.2	625.6	608.6	590.3	569.6	547.2	524.5	500.5	478.5
150°	621.3	620.4	615.3	604.9	592.0	576.6	558.5	539.7	519.0	498.4	477.8
152.5°	601.3	601.2	597.4	588.4	578.3	564.9	549.6	532.1	514.2	495.0	476.4
155°	574.9	576.6	573.2	567.1	557.7	548.2	535.4	521.6	505.2	489.0	474.3
157.5°	552.3	552.3	550.8	545.8	539.2	531.8	520.9	509.4	496.9	482.8	470.4
160°	538.0	538.0	537.1	532.8	526.8	520.7	511.3	501.8	490.7	478.6	468.3
162.5°	524.2	524.9	524.0	521.1	515.1	510.4	502.3	494.3	485.2	475.2	466.2
165°	504.4	505.2	505.2	501.8	498.4	495.0	489.0	482.9	476.0	468.3	462.3
167.5°	486.2	487.2	487.4	485.5	484.0	480.9	476.7	472.1	467.1	462.3	458.3
170°	475.2	476.9	477.8	475.2	474.3	472.6	469.2	466.6	462.3	458.8	456.3
172.5°	466.2	467.3	468.1	466.9	466.1	465.0	462.3	460.4	457.5	454.8	453.6
175°	454.6	456.3	457.2	456.3	456.3	455.5	454.6	453.7	451.2	450.3	449.4
177.5°	447.5	448.9	449.6	449.6	449.6	449.6	448.9	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	20.5	19.3	18.4	18.9	17.0	16.7	13.9	11.8	11.8	12.0	11.2
90°	23.2	17.2	12.9	10.3	8.6	6.9	3.4	0.9	3.4	6.9	8.6
92.5°	85.8	58.5	39.0	30.9	25.1	21.4	15.2	10.5	15.2	21.4	25.1
95°	198.5	123.7	84.2	63.6	49.9	42.1	33.5	30.0	33.5	42.1	49.9
97.5°	267.4	163.2	113.6	90.2	74.4	62.8	53.6	49.0	53.6	62.8	74.4
100°	281.9	177.0	131.5	107.5	90.2	76.5	68.7	66.1	68.7	76.5	90.2
102.5°	282.6	189.4	147.3	123.2	105.4	91.6	83.9	82.0	83.9	91.6	105.4
105°	287.0	210.5	170.1	146.1	127.2	114.3	108.3	104.9	108.3	114.3	127.2
107.5°	298.9	232.2	193.0	168.8	150.1	138.2	132.3	129.6	132.3	138.2	150.1
110°	308.5	246.6	208.8	183.9	165.8	154.6	149.6	146.1	149.6	154.6	165.8



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	318.8	260.4	223.9	198.3	181.0	170.5	164.6	161.2	164.6	170.5	181.0
115°	334.2	281.9	244.9	221.7	204.5	194.2	189.1	184.8	189.1	194.2	204.5
117.5°	350.8	301.6	267.4	243.3	226.9	217.7	212.6	209.1	212.6	217.7	226.9
120°	361.8	315.4	281.9	257.8	240.6	232.9	227.7	224.3	227.7	232.9	240.6
122.5°	371.3	328.4	297.0	272.2	255.0	246.6	241.4	238.8	241.4	246.6	255.0
125°	386.7	348.0	317.1	293.0	275.9	265.5	260.4	257.8	260.4	265.5	275.9
127.5°	401.0	366.3	336.1	311.4	294.9	283.5	276.4	272.9	276.4	283.5	294.9
130°	409.9	377.2	347.2	323.1	305.9	293.9	285.2	281.9	285.2	293.9	305.9
132.5°	418.8	386.8	358.2	334.1	316.2	303.5	294.2	290.1	294.2	303.5	316.2
135°	430.5	400.5	372.9	348.9	329.1	316.2	305.9	302.5	305.9	316.2	329.1
137.5°	439.5	411.5	384.3	362.0	342.3	328.6	318.3	314.2	318.3	328.6	342.3
140°	444.3	417.6	391.8	369.5	350.6	336.8	326.6	323.1	326.6	336.8	350.6
142.5°	448.4	422.4	397.4	376.3	358.2	344.4	334.8	332.0	334.8	344.4	358.2
145°	453.7	429.6	406.5	387.5	370.4	357.5	348.9	345.4	348.9	357.5	370.4
147.5°	456.7	435.5	413.7	396.8	382.5	370.7	362.5	359.9	362.5	370.7	382.5
150°	458.0	438.2	418.4	403.0	390.1	378.9	372.0	369.5	372.0	378.9	390.1
152.5°	458.7	441.0	423.3	409.2	397.0	387.2	380.3	379.1	380.3	387.2	397.0
155°	459.7	445.1	430.5	417.6	408.2	398.7	393.6	392.7	393.6	398.7	408.2
157.5°	459.7	448.1	435.7	424.8	417.2	409.1	404.9	404.1	404.9	409.1	417.2
160°	459.7	449.4	439.1	429.6	422.8	415.9	412.5	411.6	412.5	415.9	422.8
162.5°	459.0	450.1	441.2	433.8	427.6	422.1	418.6	419.1	418.6	422.1	427.6
165°	457.2	451.2	443.4	438.2	433.9	428.8	427.1	427.9	427.1	428.8	433.9
167.5°	456.0	451.0	445.3	442.0	438.9	435.7	434.1	435.1	434.1	435.7	438.9
170°	454.6	450.3	446.0	443.4	441.7	439.1	438.2	440.0	438.2	439.1	441.7
172.5°	452.5	449.6	446.7	444.8	443.8	441.2	441.7	442.7	441.7	441.2	443.8
175°	450.3	448.6	446.9	446.0	446.0	444.3	445.1	446.0	445.1	444.3	446.0
177.5°	448.9	447.5	446.9	446.9	446.9	445.5	446.2	447.5	446.2	445.5	446.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	11.0	11.0	11.4	12.6	13.1	12.7	12.0	11.8	11.5	10.8	10.9
90°	10.3	12.9	17.2	23.2	28.3	29.2	28.3	27.5	25.7	27.5	28.3
92.5°	30.9	39.0	58.5	85.8	110.1	111.7	94.4	74.9	64.3	57.1	51.7
95°	63.6	84.2	123.7	198.5	298.2	336.8	294.7	225.2	172.7	136.6	117.7
97.5°	90.2	113.6	163.2	267.4	433.1	575.1	603.2	525.4	429.8	336.8	274.8
100°	107.5	131.5	177.0	281.9	467.4	678.8	802.6	784.5	678.0	560.3	456.3
102.5°	123.2	147.3	189.4	282.6	454.4	682.3	876.8	954.3	930.3	844.2	734.0
105°	146.1	170.1	210.5	287.0	428.8	636.7	865.3	1044.0	1141.2	1152.4	1123.9
107.5°	168.8	193.0	232.2	298.9	416.0	588.0	789.9	979.5	1125.7	1215.0	1256.6
110°	183.9	208.8	246.6	308.5	413.4	564.6	742.4	923.8	1077.5	1187.6	1258.0



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.3	223.9	260.4	318.8	414.0	549.4	709.5	872.9	1020.5	1138.1	1218.8
115°	221.7	244.9	281.9	334.2	417.6	532.8	668.6	810.3	942.6	1055.2	1143.8
117.5°	243.3	267.4	301.6	350.8	423.8	524.7	642.7	763.2	879.4	981.5	1064.5
120°	257.8	281.9	315.4	361.8	427.9	519.9	629.0	739.9	846.4	937.5	1015.7
122.5°	272.2	297.0	328.4	371.3	432.7	517.1	617.3	721.3	818.9	905.2	975.9
125°	293.0	317.1	348.0	386.7	440.0	512.1	600.6	694.3	782.8	858.4	922.9
127.5°	311.4	336.1	366.3	401.0	447.4	509.2	585.2	667.7	747.8	819.1	878.6
130°	323.1	347.2	377.2	409.9	452.9	507.8	574.9	650.5	724.4	792.3	849.0
132.5°	334.1	358.2	386.8	418.8	458.3	507.1	566.6	634.0	702.4	764.7	818.0
135°	348.9	372.9	400.5	430.5	464.9	506.1	555.1	611.0	667.7	724.4	772.5
137.5°	362.0	384.3	411.5	439.5	470.7	505.9	547.0	592.5	640.0	685.0	726.9
140°	369.5	391.8	417.6	444.3	473.5	505.2	542.3	580.9	622.2	661.7	699.5
142.5°	376.3	397.4	422.4	448.4	475.5	505.2	537.4	571.3	606.3	640.3	672.0
145°	387.5	406.5	429.6	453.7	477.8	503.5	531.1	557.7	586.1	612.7	637.6
147.5°	396.8	413.7	435.5	456.7	478.5	500.5	524.5	547.2	569.6	590.3	608.6
150°	403.0	418.4	438.2	458.0	477.8	498.4	519.0	539.7	558.5	576.6	592.0
152.5°	409.2	423.3	441.0	458.7	476.4	495.0	514.2	532.1	549.6	564.9	578.3
155°	417.6	430.5	445.1	459.7	474.3	489.0	505.2	521.6	535.4	548.2	557.7
157.5°	424.8	435.7	448.1	459.7	470.4	482.8	496.9	509.4	520.9	531.8	539.2
160°	429.6	439.1	449.4	459.7	468.3	478.6	490.7	501.8	511.3	520.7	526.8
162.5°	433.8	441.2	450.1	459.0	466.2	475.2	485.2	494.3	502.3	510.4	515.1
165°	438.2	443.4	451.2	457.2	462.3	468.3	476.0	482.9	489.0	495.0	498.4
167.5°	442.0	445.3	451.0	456.0	458.3	462.3	467.1	472.1	476.7	480.9	484.0
170°	443.4	446.0	450.3	454.6	456.3	458.8	462.3	466.6	469.2	472.6	474.3
172.5°	444.8	446.7	449.6	452.5	453.6	454.8	457.5	460.4	462.3	465.0	466.1
175°	446.0	446.9	448.6	450.3	449.4	450.3	451.2	453.7	454.6	455.5	456.3
177.5°	446.9	446.9	447.5	448.9	447.5	446.9	447.5	448.9	448.9	449.6	449.6
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331449-935
 CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	10.9	10.4	10.4	9.9	10.4	10.4	10.9	10.9	10.8	11.5	11.8
90°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	27.5	25.7	27.5
92.5°	51.1	48.3	49.0	47.6	49.0	48.3	51.1	51.7	57.1	64.3	74.9
95°	106.6	99.7	97.1	98.0	97.1	99.7	106.6	117.7	136.6	172.7	225.2
97.5°	233.8	212.6	200.0	192.9	200.0	212.6	233.8	274.8	336.8	429.8	525.4
100°	385.0	348.0	323.1	307.6	323.1	348.0	385.0	456.3	560.3	678.0	784.5
102.5°	656.5	593.4	562.3	541.4	562.3	593.4	656.5	734.0	844.2	930.3	954.3
105°	1070.7	1017.4	980.4	968.5	980.4	1017.4	1070.7	1123.9	1152.4	1141.2	1044.0
107.5°	1263.3	1260.4	1253.0	1237.1	1253.0	1260.4	1263.3	1256.6	1215.0	1125.7	979.5
110°	1294.9	1311.3	1319.1	1318.2	1319.1	1311.3	1294.9	1258.0	1187.6	1077.5	923.8



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1270.2	1297.5	1312.2	1316.8	1312.2	1297.5	1270.2	1218.8	1138.1	1020.5	872.9
115°	1204.7	1244.2	1266.6	1274.4	1266.6	1244.2	1204.7	1143.8	1055.2	942.6	810.3
117.5°	1126.7	1168.5	1192.1	1198.5	1192.1	1168.5	1126.7	1064.5	981.5	879.4	763.2
120°	1075.8	1116.2	1141.2	1149.8	1141.2	1116.2	1075.8	1015.7	937.5	846.4	739.9
122.5°	1029.8	1069.4	1091.7	1098.9	1091.7	1069.4	1029.8	975.9	905.2	818.9	721.3
125°	972.8	1005.4	1026.8	1033.7	1026.8	1005.4	972.8	922.9	858.4	782.8	694.3
127.5°	922.0	952.6	971.2	976.7	971.2	952.6	922.0	878.6	819.1	747.8	667.7
130°	891.1	920.3	937.5	944.3	937.5	920.3	891.1	849.0	792.3	724.4	650.5
132.5°	859.5	888.7	904.5	910.7	904.5	888.7	859.5	818.0	764.7	702.4	634.0
135°	809.4	837.8	853.3	856.7	853.3	837.8	809.4	772.5	724.4	667.7	611.0
137.5°	760.7	785.1	798.7	803.8	798.7	785.1	760.7	726.9	685.0	640.0	592.5
140°	726.9	749.3	762.2	767.3	762.2	749.3	726.9	699.5	661.7	622.2	580.9
142.5°	698.1	718.4	729.9	730.9	729.9	718.4	698.1	672.0	640.3	606.3	571.3
145°	658.2	672.9	681.4	684.0	681.4	672.9	658.2	637.6	612.7	586.1	557.7
147.5°	625.6	637.2	643.1	644.6	643.1	637.2	625.6	608.6	590.3	569.6	547.2
150°	604.9	615.3	620.4	621.3	620.4	615.3	604.9	592.0	576.6	558.5	539.7
152.5°	588.4	597.4	601.2	601.3	601.2	597.4	588.4	578.3	564.9	549.6	532.1
155°	567.1	573.2	576.6	574.9	576.6	573.2	567.1	557.7	548.2	535.4	521.6
157.5°	545.8	550.8	552.3	552.3	552.3	550.8	545.8	539.2	531.8	520.9	509.4
160°	532.8	537.1	538.0	538.0	538.0	537.1	532.8	526.8	520.7	511.3	501.8
162.5°	521.1	524.0	524.9	524.2	524.9	524.0	521.1	515.1	510.4	502.3	494.3
165°	501.8	505.2	505.2	504.4	505.2	505.2	501.8	498.4	495.0	489.0	482.9
167.5°	485.5	487.4	487.2	486.2	487.2	487.4	485.5	484.0	480.9	476.7	472.1
170°	475.2	477.8	476.9	475.2	476.9	477.8	475.2	474.3	472.6	469.2	466.6
172.5°	466.9	468.1	467.3	466.2	467.3	468.1	466.9	466.1	465.0	462.3	460.4
175°	456.3	457.2	456.3	454.6	456.3	457.2	456.3	456.3	455.5	454.6	453.7
177.5°	449.6	449.6	448.9	447.5	448.9	449.6	449.6	449.6	449.6	448.9	448.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	12.0	12.7	13.1	12.6	11.4	11.0	11.0	11.2	12.0	11.8	11.8
90°	28.3	29.2	28.3	23.2	17.2	12.9	10.3	8.6	6.9	3.4	0.9
92.5°	94.4	111.7	110.1	85.8	58.5	39.0	30.9	25.1	21.4	15.2	10.5
95°	294.7	336.8	298.2	198.5	123.7	84.2	63.6	49.9	42.1	33.5	30.0
97.5°	603.2	575.1	433.1	267.4	163.2	113.6	90.2	74.4	62.8	53.6	49.0
100°	802.6	678.8	467.4	281.9	177.0	131.5	107.5	90.2	76.5	68.7	66.1
102.5°	876.8	682.3	454.4	282.6	189.4	147.3	123.2	105.4	91.6	83.9	82.0
105°	865.3	636.7	428.8	287.0	210.5	170.1	146.1	127.2	114.3	108.3	104.9
107.5°	789.9	588.0	416.0	298.9	232.2	193.0	168.8	150.1	138.2	132.3	129.6
110°	742.4	564.6	413.4	308.5	246.6	208.8	183.9	165.8	154.6	149.6	146.1



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	709.5	549.4	414.0	318.8	260.4	223.9	198.3	181.0	170.5	164.6	161.2
115°	668.6	532.8	417.6	334.2	281.9	244.9	221.7	204.5	194.2	189.1	184.8
117.5°	642.7	524.7	423.8	350.8	301.6	267.4	243.3	226.9	217.7	212.6	209.1
120°	629.0	519.9	427.9	361.8	315.4	281.9	257.8	240.6	232.9	227.7	224.3
122.5°	617.3	517.1	432.7	371.3	328.4	297.0	272.2	255.0	246.6	241.4	238.8
125°	600.6	512.1	440.0	386.7	348.0	317.1	293.0	275.9	265.5	260.4	257.8
127.5°	585.2	509.2	447.4	401.0	366.3	336.1	311.4	294.9	283.5	276.4	272.9
130°	574.9	507.8	452.9	409.9	377.2	347.2	323.1	305.9	293.9	285.2	281.9
132.5°	566.6	507.1	458.3	418.8	386.8	358.2	334.1	316.2	303.5	294.2	290.1
135°	555.1	506.1	464.9	430.5	400.5	372.9	348.9	329.1	316.2	305.9	302.5
137.5°	547.0	505.9	470.7	439.5	411.5	384.3	362.0	342.3	328.6	318.3	314.2
140°	542.3	505.2	473.5	444.3	417.6	391.8	369.5	350.6	336.8	326.6	323.1
142.5°	537.4	505.2	475.5	448.4	422.4	397.4	376.3	358.2	344.4	334.8	332.0
145°	531.1	503.5	477.8	453.7	429.6	406.5	387.5	370.4	357.5	348.9	345.4
147.5°	524.5	500.5	478.5	456.7	435.5	413.7	396.8	382.5	370.7	362.5	359.9
150°	519.0	498.4	477.8	458.0	438.2	418.4	403.0	390.1	378.9	372.0	369.5
152.5°	514.2	495.0	476.4	458.7	441.0	423.3	409.2	397.0	387.2	380.3	379.1
155°	505.2	489.0	474.3	459.7	445.1	430.5	417.6	408.2	398.7	393.6	392.7
157.5°	496.9	482.8	470.4	459.7	448.1	435.7	424.8	417.2	409.1	404.9	404.1
160°	490.7	478.6	468.3	459.7	449.4	439.1	429.6	422.8	415.9	412.5	411.6
162.5°	485.2	475.2	466.2	459.0	450.1	441.2	433.8	427.6	422.1	418.6	419.1
165°	476.0	468.3	462.3	457.2	451.2	443.4	438.2	433.9	428.8	427.1	427.9
167.5°	467.1	462.3	458.3	456.0	451.0	445.3	442.0	438.9	435.7	434.1	435.1
170°	462.3	458.8	456.3	454.6	450.3	446.0	443.4	441.7	439.1	438.2	440.0
172.5°	457.5	454.8	453.6	452.5	449.6	446.7	444.8	443.8	441.2	441.7	442.7
175°	451.2	450.3	449.4	450.3	448.6	446.9	446.0	446.0	444.3	445.1	446.0
177.5°	447.5	446.9	447.5	448.9	447.5	446.9	446.9	446.9	445.5	446.2	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.9	16.7	17.0	18.9	18.4	19.3	20.5	21.0	20.7	19.9	19.2
90°	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3	27.5
92.5°	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4	74.9
95°	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7	225.2
97.5°	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2	525.4
100°	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6	784.5
102.5°	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8	954.3
105°	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3	1044.0
107.5°	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9	979.5
110°	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4	923.8



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5	872.9
115°	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6	810.3
117.5°	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7	763.2
120°	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0	739.9
122.5°	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3	721.3
125°	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6	694.3
127.5°	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2	667.7
130°	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9	650.5
132.5°	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6	634.0
135°	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1	611.0
137.5°	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0	592.5
140°	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3	580.9
142.5°	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4	571.3
145°	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1	557.7
147.5°	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5	547.2
150°	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0	539.7
152.5°	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2	532.1
155°	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2	521.6
157.5°	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9	509.4
160°	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7	501.8
162.5°	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2	494.3
165°	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0	482.9
167.5°	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1	472.1
170°	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3	466.6
172.5°	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5	460.4
175°	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2	453.7
177.5°	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5	448.9
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	19.4	19.7	19.4	19.4	19.9	19.4	19.4
90°	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2



TEST NUMBER: P331449-935

CATALOG NUMBER: SA2XXDIP-C1005D925U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)