

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331282-935

Luminaire Tested: **SA2XXDIP-C290D1080U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331282-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4744.9 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	91	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	25	18
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	54	67	59	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	47	38	31	26	29	24	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	8	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	0.8
10°-20°	107.6	2.3
20°-30°	158.2	3.3
30°-40°	183.8	3.9
40°-50°	183.6	3.9
50°-60°	160.1	3.4
60°-70°	118.4	2.5
70°-80°	67.0	1.4
80°-90°	21.1	0.4
90°-100°	42.2	0.9
100°-110°	154.7	3.3
110°-120°	413.6	8.7
120°-130°	682.8	14.4
130°-140°	726.1	15.3
140°-150°	674.9	14.2
150°-160°	542.6	11.4
160°-170°	349.7	7.4
170°-180°	120.4	2.5
0°-30°	304.1	6.4
0°-40°	487.8	10.3
0°-60°	831.5	17.5
0°-90°	1038.0	21.9
90°-120°	610.5	12.9
90°-150°	2694.3	56.8
90°-180°	3707.0	78.1
0°-180°	4744.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	11	18	23	25	4
95°	60	31	36	40	39	73
105°	278	290	56	66	70	297
115°	526	542	565	161	75	518
125°	744	756	773	780	783	663
135°	921	935	944	952	951	711
145°	1068	1068	1083	1089	1085	668
155°	1176	1169	1179	1184	1177	542
165°	1239	1234	1237	1242	1237	350
175°	1268	1262	1263	1269	1260	121
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.9	6.1	6.5	6.7	7.1	7.3	7.5	7.7	7.8	8.0	8.0
90°	0.9	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3
92.5°	18.5	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8
95°	59.5	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7
97.5°	118.0	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6
100°	162.0	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8
102.5°	210.3	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8
105°	278.3	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0
107.5°	355.7	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9
110°	405.4	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8



TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	452.4	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8
115°	526.3	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5
117.5°	592.4	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7
120°	640.7	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3
122.5°	681.7	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6
125°	744.2	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8
127.5°	800.7	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0
130°	836.5	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5
132.5°	873.1	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6
135°	920.8	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7
137.5°	968.9	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5
140°	1000.4	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6
142.5°	1026.7	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5
145°	1068.2	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2
147.5°	1104.2	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1
150°	1127.7	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1
152.5°	1147.4	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4
155°	1176.1	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1
157.5°	1198.7	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8
160°	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1
162.5°	1223.6	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2
165°	1239.3	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9
167.5°	1251.0	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5
170°	1257.6	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3
172.5°	1262.0	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7
175°	1267.7	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6
177.5°	1268.6	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.1	8.1
90°	20.3	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.3	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	37.7	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	49.4	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	55.4	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	57.9	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	60.3	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	73.6	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	119.5	99.2	78.8	69.1	69.8	70.7	71.5	72.3



TEST NUMBER: P331282-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.6	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	376.3	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	580.0	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	675.8	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	717.0	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	776.3	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	831.0	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	865.7	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	899.5	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	947.7	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	992.5	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1021.5	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1048.2	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1085.6	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1118.2	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1138.3	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1156.6	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1181.3	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1202.1	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1214.3	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1225.5	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1250.9	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1256.8	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1261.2	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1265.9	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1266.4	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)