

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331283-935

Luminaire Tested: **SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331283-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4353.5 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331283-935
CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331283-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	21	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	18	16	14	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	18	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331283-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	0.9
10°-20°	107.6	2.5
20°-30°	158.2	3.6
30°-40°	183.8	4.2
40°-50°	183.6	4.2
50°-60°	160.1	3.7
60°-70°	118.4	2.7
70°-80°	67.0	1.5
80°-90°	22.7	0.5
90°-100°	75.1	1.7
100°-110°	233.2	5.4
110°-120°	398.7	9.2
120°-130°	524.3	12.0
130°-140°	588.5	13.5
140°-150°	577.0	13.3
150°-160°	484.0	11.1
160°-170°	321.0	7.4
170°-180°	112.2	2.6
0°-30°	304.1	7.0
0°-40°	487.8	11.2
0°-60°	831.5	19.1
0°-90°	1039.6	23.9
90°-120°	707.0	16.2
90°-150°	2396.8	55.1
90°-180°	3314.0	76.1
0°-180°	4353.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	14	35	33	34	4
95°	52	62	64	64	62	60
105°	215	218	220	222	222	227
115°	400	406	404	403	400	396
125°	582	590	588	585	584	520
135°	753	764	766	765	762	582
145°	914	921	927	928	924	571
155°	1045	1048	1051	1056	1053	481
165°	1137	1136	1136	1142	1138	321
175°	1183	1180	1178	1184	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331283-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.9	6.2	6.6	7.0	7.4	8.0	8.9	9.7	10.5	11.4	11.1
90°	1.0	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5
92.5°	17.8	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9
95°	52.0	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0
97.5°	95.1	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6
100°	127.0	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0
102.5°	160.7	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0
105°	215.0	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5
107.5°	269.8	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4
110°	305.1	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331283-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.5	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1
115°	400.0	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8
117.5°	456.4	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3
120°	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0
122.5°	528.5	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9
125°	582.0	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4
127.5°	634.3	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3
130°	667.1	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6
132.5°	703.9	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9
135°	753.1	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9
137.5°	804.9	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3
140°	836.1	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1
142.5°	868.1	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7
145°	914.1	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3
147.5°	955.1	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0
150°	983.1	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8
152.5°	1007.9	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6
155°	1045.2	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2
157.5°	1076.9	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3
160°	1096.1	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4
162.5°	1113.7	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6
165°	1137.1	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7
167.5°	1156.8	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1
170°	1167.2	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7
172.5°	1174.3	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9
175°	1183.2	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7
177.5°	1186.7	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331283-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	10.8	10.5	10.2	10.0	10.0	10.0	10.0	9.9
90°	34.1	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	31.9	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.2	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	220.9	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.6	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331283-935

CATALOG NUMBER: SA2XXDIP-C290D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	347.6	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.6	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.8	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	531.4	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.8	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	640.5	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	677.2	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.9	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.7	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.1	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	880.9	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.6	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	968.5	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1053.3	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1083.7	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1101.8	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1118.2	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1139.3	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1156.7	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1166.2	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1173.5	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1181.3	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)