

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331650-830

Luminaire Tested: **SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331650-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2806.4 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331650-830
CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331650-830

CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57				
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49				
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46	42				
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36				
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	32				
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31	28				
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25				
7	61	49	41	35	57	46	39	34	40	35	31	35	31	28	31	27	25	22				
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20				
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20	18				
10	49	37	30	26	46	35	29	24	32	26	22	28	24	20	25	21	18	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12558	12558	12558
5°	12606	12402	12470
10°	12511	12198	12095
15°	12366	11836	11497
20°	12167	11320	10753
25°	11965	10735	10033
30°	11680	10133	9107
35°	11404	9477	8296
40°	11126	8800	7358
45°	10803	8035	6510
50°	10467	7267	5674
55°	10125	6441	4873
60°	9726	5570	4046
65°	9280	4676	3683
70°	8738	3852	3389
75°	8079	3512	3163
80°	7132	3133	2882
85°	5613	2482	2482



TEST NUMBER: P331650-830

CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	2.6
10°-20°	199.9	7.1
20°-30°	280.7	10.0
30°-40°	306.1	10.9
40°-50°	281.5	10.0
50°-60°	221.1	7.9
60°-70°	144.1	5.1
70°-80°	74.3	2.6
80°-90°	20.8	0.7
90°-100°	69.2	2.5
100°-110°	235.0	8.4
110°-120°	249.6	8.9
120°-130°	205.5	7.3
130°-140°	165.0	5.9
140°-150°	124.7	4.4
150°-160°	87.6	3.1
160°-170°	51.6	1.8
170°-180°	16.8	0.6
0°-30°	553.4	19.7
0°-40°	859.6	30.6
0°-60°	1362.1	48.5
0°-90°	1601.4	57.1
90°-120°	553.8	19.7
90°-150°	1049.0	37.4
90°-180°	1205.0	42.9
0°-180°	2806.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	774	765	771	769	74
15°	740	731	708	695	688	208
25°	672	648	603	575	563	309
35°	579	541	481	438	421	362
45°	473	424	352	304	285	365
55°	360	304	229	188	173	321
65°	243	186	122	100	96	241
75°	130	82	56	52	51	137
85°	30	16	13	13	13	36
90°	0	4	11	11	11	2
95°	12	29	130	49	38	12
105°	41	61	247	441	375	43
115°	72	90	206	426	494	71
125°	100	118	198	345	401	89
135°	117	140	196	290	332	91
145°	134	154	195	242	265	84
155°	152	164	190	214	223	70
165°	166	171	182	192	196	47
175°	173	173	174	177	176	16
180°	173	173	173	173	173	



TEST NUMBER: P331650-830

CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	780.6	780.0	779.4	778.7	778.2	777.1	775.8	774.4	773.0	771.7	772.9
5°	777.8	777.0	776.3	775.5	774.7	773.3	771.3	769.2	767.2	765.2	766.6
7.5°	769.8	768.8	767.9	766.9	765.9	764.2	761.9	759.5	757.1	754.8	755.2
10°	763.1	762.0	760.8	759.8	758.7	756.6	753.5	750.3	747.2	744.0	743.6
12.5°	754.6	753.3	751.9	750.5	749.2	746.6	742.5	738.6	734.5	730.6	729.7
15°	739.8	738.1	736.4	734.6	732.9	729.4	724.1	718.8	713.5	708.1	705.2
17.5°	721.7	719.1	716.4	713.8	711.1	706.4	699.6	692.8	686.0	679.1	675.6
20°	708.1	705.0	701.9	698.8	695.6	690.1	682.3	674.5	666.7	658.8	655.0
22.5°	693.5	690.0	686.5	683.0	679.5	673.4	664.5	655.6	646.9	638.0	633.0
25°	671.6	666.6	661.6	656.5	651.5	643.9	633.5	623.2	612.8	602.6	596.2
27.5°	645.1	639.6	634.1	628.8	623.3	614.7	603.1	591.4	579.9	568.2	560.7
30°	626.5	620.6	614.6	608.7	602.8	593.5	581.0	568.4	555.9	543.5	535.5
32.5°	608.5	601.5	594.6	587.7	580.7	570.8	558.1	545.3	532.5	519.8	510.7
35°	578.6	570.6	562.7	554.7	546.7	535.8	522.1	508.3	494.6	480.8	470.9
37.5°	548.7	540.0	531.2	522.5	513.8	502.0	487.4	472.7	458.0	443.4	432.4
40°	527.9	518.6	509.2	499.8	490.4	478.2	463.0	447.8	432.6	417.5	406.3
42.5°	506.5	496.6	486.7	476.9	467.0	454.2	438.6	422.8	407.2	391.5	380.0
45°	473.1	462.6	452.0	441.6	431.1	417.6	401.2	384.8	368.3	351.9	340.8
47.5°	440.4	429.2	418.2	407.1	396.0	381.9	365.0	348.0	331.0	314.1	303.0
50°	416.7	405.6	394.5	383.4	372.3	358.2	340.9	323.8	306.5	289.3	278.5
52.5°	393.6	382.0	370.4	358.8	347.2	333.0	316.1	299.4	282.5	265.7	255.2
55°	359.7	347.5	335.3	323.1	310.9	296.3	279.5	262.6	245.6	228.8	219.4
57.5°	324.9	312.5	299.9	287.4	274.8	260.5	244.3	228.0	211.8	195.6	186.9
60°	301.2	288.8	276.3	263.7	251.2	237.0	220.8	204.7	188.6	172.5	164.5
62.5°	278.1	265.7	253.2	240.6	228.1	214.2	198.9	183.5	168.1	152.8	145.2
65°	242.9	230.2	217.5	204.8	192.2	178.8	164.8	150.6	136.6	122.4	117.2
67.5°	208.8	196.2	183.6	171.1	158.4	145.8	133.2	120.6	107.8	95.2	92.7
70°	185.1	173.0	160.7	148.5	136.3	124.8	114.0	103.2	92.5	81.6	80.1
72.5°	162.6	150.9	139.2	127.5	115.8	105.7	97.0	88.3	79.6	71.0	69.7
75°	129.5	118.6	107.6	96.7	85.7	77.6	72.3	66.9	61.6	56.3	55.2
77.5°	97.0	87.4	77.8	68.1	58.6	52.5	50.0	47.4	44.8	42.2	41.6
80°	76.7	68.7	60.8	52.8	44.8	40.1	38.5	36.9	35.3	33.7	33.2
82.5°	58.2	51.9	45.7	39.5	33.3	29.6	28.6	27.4	26.4	25.4	25.0
85°	30.3	27.0	23.7	20.5	17.2	15.3	14.8	14.3	13.9	13.4	13.4
87.5°	9.0	8.3	7.5	6.7	5.8	5.5	5.8	6.3	6.7	6.8	6.6
90°	0.4	1.3	2.6	3.3	4.0	5.0	6.7	9.0	11.0	11.3	11.0
92.5°	4.1	5.8	8.3	9.7	12.0	15.1	22.6	33.3	42.7	43.3	36.6
95°	11.7	13.0	16.3	19.3	24.6	32.6	48.0	76.9	115.6	130.5	114.2
97.5°	18.9	20.7	24.3	28.8	35.0	44.0	63.2	103.7	167.9	222.8	233.8
100°	25.6	26.7	29.6	35.0	41.7	51.0	68.6	109.2	181.2	263.1	311.0
102.5°	31.8	32.5	35.5	40.8	47.8	57.1	73.4	109.5	176.1	264.4	339.8
105°	40.6	41.9	44.3	49.3	56.6	66.0	81.6	111.2	166.2	246.8	335.4
107.5°	50.2	51.3	53.5	58.2	65.4	74.8	90.0	115.8	161.3	227.8	306.1
110°	56.6	58.0	59.9	64.3	71.3	81.0	95.6	119.5	160.2	218.8	287.8



TEST NUMBER: P331650-830

CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.5	63.8	66.1	70.1	76.8	86.8	100.9	123.6	160.4	212.9	274.9
115°	71.6	73.2	75.3	79.3	86.0	94.9	109.2	129.5	161.8	206.5	259.1
117.5°	81.1	82.4	84.4	87.9	94.3	103.7	116.9	135.9	164.3	203.3	249.1
120°	86.9	88.2	90.3	93.2	99.9	109.2	122.2	140.3	165.9	201.5	243.7
122.5°	92.6	93.6	95.6	98.9	105.5	115.1	127.2	143.9	167.7	200.4	239.2
125°	99.9	100.9	102.9	106.9	113.6	122.9	134.9	149.9	170.5	198.5	232.8
127.5°	105.8	107.1	109.9	114.3	120.6	130.3	141.9	155.4	173.3	197.4	226.8
130°	109.2	110.6	113.9	118.6	125.3	134.5	146.2	158.8	175.5	196.8	222.8
132.5°	112.4	114.0	117.6	122.5	129.5	138.8	150.0	162.3	177.7	196.5	219.6
135°	117.3	118.6	122.5	127.5	135.3	144.5	155.2	166.8	180.2	196.1	215.1
137.5°	121.8	123.4	127.3	132.7	140.3	148.9	159.5	170.3	182.5	196.0	212.0
140°	125.3	126.6	130.5	135.9	143.2	151.8	161.8	172.2	183.5	195.9	210.1
142.5°	128.7	129.8	133.5	138.8	145.9	154.0	163.7	173.8	184.3	195.9	208.3
145°	133.8	135.3	138.6	143.5	150.2	157.5	166.5	175.9	185.1	195.1	205.9
147.5°	139.5	140.4	143.6	148.3	153.8	160.3	168.8	177.0	185.4	194.0	203.3
150°	143.2	144.2	146.8	151.2	156.2	162.2	169.8	177.5	185.1	193.1	201.1
152.5°	146.9	147.4	150.1	153.8	158.6	164.0	170.9	177.8	184.6	191.8	199.3
155°	152.2	152.5	154.5	158.2	161.8	166.8	172.5	178.1	183.8	189.5	195.9
157.5°	156.6	156.9	158.5	161.7	164.7	168.8	173.6	178.1	182.3	187.1	192.6
160°	159.5	159.9	161.2	163.8	166.5	170.2	174.2	178.1	181.5	185.5	190.1
162.5°	162.5	162.2	163.6	165.7	168.1	171.0	174.5	177.9	180.7	184.2	188.0
165°	165.9	165.5	166.2	168.1	169.8	171.8	174.8	177.2	179.2	181.5	184.5
167.5°	168.6	168.2	168.8	170.1	171.4	172.6	174.7	176.7	177.7	179.2	181.1
170°	170.5	169.8	170.2	171.2	171.8	172.9	174.5	176.2	176.8	177.9	179.2
172.5°	171.5	171.2	171.0	172.0	172.4	173.1	174.3	175.4	175.8	176.3	177.3
175°	172.9	172.5	172.2	172.9	172.9	173.1	173.8	174.5	174.2	174.5	174.8
177.5°	173.4	172.9	172.7	173.1	173.1	173.1	173.4	174.0	173.4	173.1	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1



TEST NUMBER: P331650-830

CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	777.8	777.8	777.8	777.8	777.8	777.8	777.8	777.8
2.5°	774.1	775.4	776.7	777.1	776.9	776.7	776.4	776.2
5°	768.0	769.4	770.8	771.3	770.8	770.3	769.9	769.4
7.5°	755.5	755.9	756.4	756.2	755.4	754.5	753.8	752.9
10°	743.1	742.6	742.2	741.5	740.6	739.6	738.7	737.7
12.5°	728.9	728.0	727.2	725.9	724.3	722.8	721.2	719.7
15°	702.2	699.3	696.3	694.0	692.4	690.9	689.3	687.8
17.5°	672.0	668.5	665.0	661.9	659.2	656.5	653.8	651.1
20°	651.0	647.1	643.2	639.5	636.1	632.6	629.2	625.8
22.5°	627.9	622.9	617.9	614.1	611.5	609.0	606.4	603.8
25°	589.7	583.3	576.9	572.5	570.1	567.8	565.5	563.2
27.5°	553.3	545.7	538.3	532.7	529.0	525.3	521.5	517.8
30°	527.4	519.5	511.5	505.4	501.1	497.0	492.8	488.5
32.5°	501.5	492.5	483.3	476.8	472.9	468.9	464.9	460.9
35°	461.1	451.2	441.4	434.7	431.3	427.8	424.4	420.9
37.5°	421.6	410.8	399.9	392.5	388.6	384.7	380.7	376.7
40°	395.2	384.1	373.0	365.4	361.4	357.3	353.2	349.1
42.5°	368.5	357.0	345.6	337.9	333.9	330.0	326.0	322.1
45°	329.7	318.7	307.6	300.1	296.3	292.6	288.8	285.1
47.5°	292.0	281.0	269.9	262.7	259.3	255.9	252.4	249.0
50°	267.7	256.9	246.1	239.1	235.8	232.5	229.2	225.9
52.5°	244.8	234.4	223.9	217.3	214.2	211.2	208.1	205.1
55°	210.0	200.6	191.2	185.0	182.1	179.1	176.2	173.1
57.5°	178.3	169.8	161.2	155.6	153.1	150.6	148.1	145.5
60°	156.5	148.5	140.5	135.3	132.8	130.3	127.8	125.3
62.5°	137.5	130.0	122.3	117.8	116.3	114.8	113.3	111.8
65°	111.9	106.5	101.2	98.3	97.8	97.4	96.9	96.4
67.5°	90.3	87.8	85.4	84.0	83.4	82.9	82.5	81.9
70°	78.5	77.0	75.4	74.3	73.7	73.0	72.4	71.8
72.5°	68.3	67.0	65.7	64.8	64.5	64.1	63.7	63.3
75°	54.1	53.1	51.9	51.3	51.2	51.0	50.8	50.7
77.5°	41.0	40.3	39.8	39.3	39.0	38.8	38.5	38.3
80°	32.5	32.0	31.3	31.0	31.0	31.0	31.0	31.0
82.5°	24.6	24.2	23.8	23.7	23.7	23.7	23.7	23.7
85°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4
87.5°	6.4	6.1	6.1	6.1	6.1	6.1	6.1	6.1
90°	10.7	10.0	10.7	11.0	11.0	11.0	11.0	11.0
92.5°	29.0	24.9	22.1	20.1	19.8	18.8	18.9	18.5
95°	87.3	66.9	53.0	45.6	41.3	38.6	37.6	38.0
97.5°	203.6	166.5	130.5	106.5	90.6	82.4	77.6	74.7
100°	304.1	262.8	217.2	176.8	149.2	134.9	125.3	119.2
102.5°	369.9	360.5	327.2	284.5	254.4	230.0	217.9	209.8
105°	404.6	442.2	446.6	435.6	414.9	394.3	379.9	375.3
107.5°	379.6	436.3	470.9	487.0	489.7	488.5	485.6	479.5
110°	358.0	417.6	460.2	487.6	501.9	508.2	511.2	510.9



TEST NUMBER: P331650-830

CATALOG NUMBER: SA2XXRDIP-C485D330U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	338.3	395.5	441.0	472.4	492.3	502.8	508.5	510.3
115°	314.1	365.3	409.0	443.3	466.9	482.2	490.9	493.9
117.5°	295.8	340.8	380.4	412.6	436.7	452.9	461.9	464.5
120°	286.7	328.0	363.4	393.6	417.0	432.6	442.2	445.6
122.5°	279.6	317.4	350.8	378.1	399.1	414.5	423.1	425.8
125°	269.1	303.4	332.7	357.7	377.0	389.6	397.9	400.7
127.5°	258.7	289.8	317.4	340.4	357.3	369.2	376.4	378.5
130°	252.1	280.8	307.1	329.0	345.3	356.7	363.4	366.0
132.5°	245.7	272.2	296.4	317.1	333.1	344.4	350.5	353.0
135°	236.8	258.7	280.8	299.4	313.7	324.7	330.7	332.1
137.5°	229.7	248.1	265.5	281.7	294.8	304.3	309.5	311.5
140°	225.1	241.1	256.5	271.1	281.7	290.4	295.4	297.4
142.5°	221.4	235.0	248.2	260.4	270.5	278.4	282.9	283.2
145°	216.1	227.2	237.4	247.1	255.1	260.8	264.1	265.0
147.5°	212.1	220.7	228.8	235.8	242.4	246.9	249.2	249.9
150°	209.2	216.5	223.5	229.4	234.4	238.5	240.4	240.8
152.5°	206.2	213.0	219.0	224.1	228.1	231.5	233.0	233.1
155°	202.2	207.5	212.4	216.1	219.8	222.2	223.5	222.8
157.5°	197.5	201.9	206.0	209.0	211.5	213.5	214.1	214.1
160°	194.4	198.1	201.8	204.2	206.5	208.1	208.5	208.5
162.5°	191.5	194.7	197.8	199.6	202.0	203.1	203.4	203.1
165°	187.2	189.5	191.8	193.1	194.4	195.9	195.9	195.5
167.5°	182.9	184.7	186.3	187.6	188.1	188.9	188.8	188.4
170°	180.9	181.8	183.1	183.8	184.2	185.1	184.8	184.2
172.5°	178.4	179.2	180.2	180.6	181.0	181.4	181.1	180.7
175°	175.9	176.2	176.5	176.8	176.8	177.2	176.8	176.2
177.5°	174.0	174.0	174.3	174.3	174.3	174.3	174.0	173.4
180°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	173.1

(END OF REPORT)