

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331256-935

Luminaire Tested: **SA2XXDIP-C290D530U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331256-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2664.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331256-935
CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331256-935

CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39	33				
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27				
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23				
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20				
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14				
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12				
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331256-935

CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.4
10°-20°	107.6	4.0
20°-30°	158.2	5.9
30°-40°	183.8	6.9
40°-50°	183.6	6.9
50°-60°	160.1	6.0
60°-70°	118.4	4.4
70°-80°	67.0	2.5
80°-90°	20.3	0.8
90°-100°	36.9	1.4
100°-110°	114.5	4.3
110°-120°	195.7	7.3
120°-130°	257.4	9.7
130°-140°	288.9	10.8
140°-150°	283.3	10.6
150°-160°	237.6	8.9
160°-170°	157.6	5.9
170°-180°	55.1	2.1
0°-30°	304.1	11.4
0°-40°	487.8	18.3
0°-60°	831.5	31.2
0°-90°	1037.2	38.9
90°-120°	347.1	13.0
90°-150°	1176.6	44.2
90°-180°	1627.0	61.1
0°-180°	2664.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	0	7	17	16	17	2
95°	26	30	31	31	30	29
105°	106	107	108	109	109	112
115°	196	199	198	198	196	194
125°	286	290	289	287	287	255
135°	370	375	376	376	374	285
145°	449	452	455	456	454	280
155°	513	515	516	518	517	236
165°	558	558	558	561	559	157
175°	581	579	578	581	579	55
180°	582	582	582	582	582	



TEST NUMBER: P331256-935
 CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.8	5.9	5.9	6.1	6.2	6.5	6.8	7.1	7.5	7.8	7.6
90°	0.5	1.8	3.1	4.4	5.8	7.6	10.0	12.4	14.8	17.2	17.0
92.5°	8.8	9.7	10.7	11.6	12.6	13.3	13.9	14.5	15.1	15.6	15.7
95°	25.6	26.6	27.7	28.8	29.9	30.6	30.7	31.0	31.2	31.4	31.4
97.5°	46.7	47.6	48.6	49.5	50.5	51.1	51.6	52.0	52.4	52.9	52.9
100°	62.3	63.2	64.1	65.0	65.9	66.5	66.8	67.1	67.4	67.8	67.8
102.5°	78.9	79.6	80.2	80.9	81.6	82.2	82.7	83.0	83.4	83.9	83.9
105°	105.6	105.9	106.2	106.5	106.9	107.1	107.4	107.5	107.8	108.1	108.2
107.5°	132.5	132.9	133.5	133.9	134.4	134.7	134.7	134.7	134.7	134.7	134.7
110°	149.7	150.4	151.0	151.7	152.4	152.7	152.7	152.7	152.7	152.7	152.7



TEST NUMBER: P331256-935

CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.6	169.3	169.9	170.6	171.3	171.5	171.4	171.3	171.3	171.2	170.9
115°	196.4	197.1	197.7	198.4	199.0	199.2	199.0	198.8	198.5	198.4	198.3
117.5°	224.1	225.0	225.8	226.7	227.6	227.7	227.1	226.4	225.8	225.2	225.0
120°	242.5	243.4	244.3	245.1	246.1	246.1	245.1	244.3	243.4	242.5	242.5
122.5°	259.4	260.5	261.6	262.6	263.6	263.8	263.2	262.6	262.0	261.4	261.1
125°	285.8	286.7	287.7	288.7	289.6	290.0	289.6	289.4	289.0	288.7	288.3
127.5°	311.3	312.6	313.8	315.1	316.3	316.8	316.4	316.0	315.6	315.2	314.8
130°	327.5	328.9	330.3	331.7	333.1	333.7	333.6	333.3	333.1	332.9	332.7
132.5°	345.5	346.7	347.8	349.0	350.2	350.8	350.9	350.9	350.9	350.9	350.5
135°	369.7	370.9	372.1	373.3	374.5	375.2	375.4	375.7	375.9	376.1	376.0
137.5°	395.1	396.1	397.1	398.1	399.1	399.7	400.0	400.3	400.5	400.8	400.7
140°	410.4	411.5	412.4	413.4	414.4	415.2	415.7	416.2	416.8	417.3	417.3
142.5°	426.2	427.1	428.2	429.1	430.1	430.8	431.2	431.5	431.9	432.2	432.3
145°	448.8	449.5	450.3	451.1	451.9	452.5	453.1	453.8	454.5	455.1	455.2
147.5°	468.9	469.8	470.7	471.7	472.5	473.2	473.6	474.1	474.5	475.0	475.2
150°	482.7	483.3	484.0	484.6	485.3	485.8	486.2	486.6	487.1	487.6	487.8
152.5°	494.8	495.5	496.1	496.8	497.4	498.0	498.5	499.0	499.6	500.2	500.5
155°	513.1	513.4	513.8	514.0	514.4	514.7	515.1	515.4	515.7	516.0	516.6
157.5°	528.7	528.9	529.1	529.3	529.6	529.8	529.9	530.2	530.4	530.5	531.3
160°	538.1	538.3	538.6	538.7	539.0	539.2	539.2	539.3	539.5	539.6	540.3
162.5°	546.7	546.8	546.8	546.9	546.9	547.0	547.1	547.3	547.3	547.4	548.2
165°	558.3	558.1	558.0	557.9	557.8	557.8	557.8	557.8	557.8	557.8	558.5
167.5°	567.8	567.6	567.2	566.9	566.5	566.4	566.4	566.4	566.3	566.3	567.1
170°	573.0	572.7	572.3	572.0	571.7	571.4	571.4	571.2	571.1	571.0	571.8
172.5°	576.5	576.2	575.8	575.5	575.2	575.0	574.9	574.8	574.6	574.5	575.3
175°	580.8	580.5	580.1	579.9	579.5	579.3	579.0	578.9	578.6	578.3	579.1
177.5°	582.6	582.3	582.0	581.8	581.5	581.3	581.2	581.0	580.8	580.7	581.2
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331256-935

CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	7.3	7.1	6.8	6.6	6.6	6.5	6.5	6.5
90°	16.8	16.5	16.3	16.3	16.4	16.4	16.6	16.7
92.5°	15.7	15.8	15.8	15.8	15.8	15.8	15.9	15.9
95°	31.4	31.4	31.4	31.3	31.1	30.9	30.7	30.5
97.5°	52.9	52.9	52.9	52.8	52.8	52.8	52.8	52.7
100°	67.8	67.8	67.8	67.7	67.6	67.5	67.4	67.2
102.5°	84.0	84.1	84.2	84.2	84.1	83.9	83.9	83.8
105°	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0
107.5°	134.8	134.9	135.0	134.7	134.2	133.8	133.3	132.8
110°	152.7	152.7	152.7	152.6	152.2	151.9	151.5	151.2



TEST NUMBER: P331256-935

CATALOG NUMBER: SA2XXDIP-C290D530U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.4	170.1	169.9	169.6	169.4	169.1	168.9
115°	198.1	198.0	197.9	197.7	197.3	197.1	196.7	196.4
117.5°	224.7	224.5	224.2	223.9	223.6	223.3	222.9	222.6
120°	242.5	242.5	242.5	242.4	242.0	241.8	241.4	241.1
122.5°	260.9	260.6	260.4	260.1	259.8	259.6	259.4	259.2
125°	288.0	287.7	287.4	287.1	287.1	287.0	286.8	286.7
127.5°	314.4	314.0	313.7	313.2	312.9	312.5	312.2	311.9
130°	332.4	332.3	332.0	331.7	331.2	330.8	330.4	329.9
132.5°	350.0	349.5	349.0	348.6	348.3	347.9	347.6	347.2
135°	375.9	375.7	375.7	375.4	375.1	374.8	374.4	374.1
137.5°	400.6	400.5	400.5	400.2	399.8	399.3	398.9	398.5
140°	417.3	417.3	417.3	417.2	416.6	416.2	415.8	415.3
142.5°	432.4	432.5	432.6	432.4	432.0	431.5	431.1	430.7
145°	455.4	455.5	455.6	455.4	455.0	454.5	454.1	453.7
147.5°	475.4	475.7	476.0	475.9	475.4	475.0	474.6	474.2
150°	488.2	488.5	488.9	488.9	488.5	488.2	487.8	487.6
152.5°	500.9	501.4	501.8	501.8	501.4	500.9	500.5	500.2
155°	517.1	517.6	518.2	518.3	518.0	517.6	517.3	517.0
157.5°	532.0	532.8	533.6	533.6	533.1	532.6	532.1	531.5
160°	540.9	541.6	542.2	542.3	541.9	541.5	541.0	540.5
162.5°	548.9	549.7	550.4	550.5	550.0	549.5	549.0	548.5
165°	559.3	560.1	560.8	560.9	560.3	559.8	559.3	558.7
167.5°	567.8	568.6	569.4	569.5	568.9	568.3	567.7	567.1
170°	572.6	573.3	574.0	574.1	573.4	572.8	572.1	571.5
172.5°	576.1	576.9	577.6	577.6	577.0	576.4	575.7	575.1
175°	579.9	580.7	581.4	581.5	580.8	580.1	579.5	578.9
177.5°	581.7	582.2	582.7	582.7	582.2	581.7	581.2	580.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8

(END OF REPORT)