

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331259-935

Luminaire Tested: **SA2XXDIP-C290D725U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331259-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3355.9 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25				
3	79	70	63	57	71	63	57	53	51	47	43	40	37	35	29	27	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	19	18	15				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.4
10°-20°	140.9	4.2
20°-30°	204.5	6.1
30°-40°	215.8	6.4
40°-50°	191.1	5.7
50°-60°	152.5	4.5
60°-70°	103.6	3.1
70°-80°	53.1	1.6
80°-90°	16.0	0.5
90°-100°	50.5	1.5
100°-110°	157.0	4.7
110°-120°	268.3	8.0
120°-130°	352.8	10.5
130°-140°	396.0	11.8
140°-150°	388.3	11.6
150°-160°	325.7	9.7
160°-170°	216.0	6.4
170°-180°	75.5	2.2
0°-30°	393.9	11.7
0°-40°	609.7	18.2
0°-60°	953.2	28.4
0°-90°	1126.0	33.6
90°-120°	475.8	14.2
90°-150°	1612.8	48.1
90°-180°	2230.0	66.4
0°-180°	3355.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	23	1	23	1	23	10
95°	42	35	42	35	42	47
105°	149	145	149	145	149	157
115°	269	269	269	269	269	266
125°	393	392	393	392	393	350
135°	513	507	513	507	513	395
145°	622	615	622	615	622	388
155°	709	703	709	703	709	326
165°	766	765	766	765	766	216
175°	794	796	794	796	794	75
180°	798	798	798	798	798	



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	8.6	8.6	8.8	8.5	8.5	8.7	8.8	8.7	8.9	9.1	8.6
90°	22.9	22.7	22.6	22.5	22.3	22.4	22.6	23.0	23.2	23.6	20.2
92.5°	21.8	21.8	21.8	21.7	21.7	21.6	21.6	21.5	21.4	21.4	20.7
95°	41.8	42.0	42.4	42.6	43.0	43.0	43.0	43.0	43.0	43.0	42.8
97.5°	72.2	72.3	72.3	72.4	72.4	72.4	72.4	72.4	72.4	72.4	71.8
100°	92.2	92.4	92.5	92.6	92.8	92.9	92.9	92.9	92.9	92.9	92.4
102.5°	114.8	114.9	115.1	115.3	115.4	115.5	115.3	115.2	115.0	114.9	114.3
105°	149.4	149.4	149.4	149.4	149.4	149.3	149.0	148.7	148.4	148.1	147.7
107.5°	182.0	182.7	183.4	184.1	184.8	185.0	184.9	184.8	184.7	184.5	184.5
110°	207.2	207.8	208.2	208.6	209.1	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.5	231.9	232.1	232.5	232.8	233.2	233.5	233.8	234.3	234.6	234.7
115°	269.2	269.7	270.1	270.5	271.0	271.3	271.5	271.6	271.7	271.9	272.2
117.5°	305.1	305.6	306.0	306.5	306.9	307.3	307.7	308.1	308.4	308.8	309.6
120°	330.5	330.9	331.3	331.7	332.3	332.4	332.4	332.4	332.4	332.4	333.6
122.5°	355.2	355.5	355.9	356.2	356.5	356.9	357.2	357.6	357.9	358.3	359.1
125°	393.0	393.2	393.3	393.5	393.6	393.9	394.3	394.9	395.3	395.7	396.1
127.5°	427.5	428.0	428.4	429.0	429.4	429.9	430.4	431.0	431.5	432.0	432.6
130°	452.3	452.9	453.5	454.0	454.6	455.1	455.4	455.7	456.0	456.3	456.6
132.5°	476.0	476.4	476.9	477.3	477.9	478.5	479.1	479.7	480.4	481.0	481.0
135°	512.8	513.2	513.8	514.2	514.6	514.9	515.1	515.2	515.4	515.5	515.2
137.5°	546.2	546.8	547.4	548.0	548.6	549.0	549.1	549.2	549.3	549.4	549.1
140°	569.4	570.0	570.6	571.2	571.7	572.0	572.0	572.0	572.0	572.0	571.3
142.5°	590.4	591.0	591.5	592.1	592.7	593.0	592.9	592.7	592.6	592.5	592.0
145°	621.8	622.4	623.0	623.6	624.2	624.5	624.3	624.1	624.1	623.9	622.9
147.5°	650.0	650.6	651.1	651.7	652.3	652.4	652.0	651.7	651.3	651.1	650.5
150°	668.3	668.7	669.2	669.6	670.1	670.1	669.6	669.2	668.7	668.3	667.7
152.5°	685.5	686.0	686.6	687.3	687.8	687.8	687.3	686.6	686.0	685.5	684.8
155°	708.7	709.1	709.6	710.0	710.5	710.3	709.6	708.8	708.1	707.3	706.9
157.5°	728.6	729.3	730.0	730.7	731.4	731.3	730.3	729.3	728.2	727.2	726.9
160°	741.0	741.6	742.2	742.8	743.4	743.2	742.4	741.4	740.5	739.6	739.5
162.5°	751.7	752.4	753.2	753.9	754.6	754.5	753.5	752.4	751.4	750.4	750.3
165°	765.9	766.6	767.3	768.1	768.9	768.7	767.7	766.6	765.6	764.5	764.5
167.5°	777.5	778.3	779.0	779.8	780.6	780.4	779.4	778.3	777.3	776.2	776.3
170°	783.3	784.3	785.1	786.1	787.0	786.9	785.8	784.8	783.8	782.6	782.8
172.5°	788.2	789.1	790.0	790.9	791.8	791.7	790.7	789.6	788.6	787.6	787.7
175°	793.5	794.4	795.2	796.2	797.0	796.9	795.9	794.9	793.8	792.8	793.1
177.5°	795.9	796.6	797.3	798.1	798.7	798.7	798.1	797.3	796.6	795.9	796.1
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	8.1	7.4	6.8	6.5	5.8	5.4	4.4	3.6	3.8	4.0	4.0
90°	17.0	13.7	10.4	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	19.8	19.0	18.3	17.2	15.9	14.6	13.3	12.0	13.3	14.6	15.9
95°	42.4	42.2	41.8	41.0	39.5	38.0	36.5	35.0	36.5	38.0	39.5
97.5°	71.3	70.7	70.2	69.2	67.8	66.6	65.3	64.0	65.3	66.6	67.8
100°	92.0	91.5	91.1	90.2	89.0	87.8	86.7	85.5	86.7	87.8	89.0
102.5°	113.8	113.2	112.7	111.9	111.0	110.0	109.0	108.1	109.0	110.0	111.0
105°	147.5	147.1	146.9	146.5	146.0	145.6	145.2	144.7	145.2	145.6	146.0
107.5°	184.5	184.5	184.5	184.2	183.6	182.9	182.3	181.6	182.3	182.9	183.6
110°	209.3	209.3	209.3	208.9	207.9	207.1	206.1	205.3	206.1	207.1	207.9



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	234.9	235.0	235.1	234.7	233.8	232.9	232.0	231.1	232.0	232.9	233.8
115°	272.5	272.8	273.1	272.8	271.9	271.0	270.1	269.2	270.1	271.0	271.9
117.5°	310.5	311.3	312.1	311.9	310.7	309.5	308.3	307.1	308.3	309.5	310.7
120°	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	333.6	334.8	336.0
122.5°	360.0	360.8	361.6	361.4	359.9	358.5	357.1	355.6	357.1	358.5	359.9
125°	396.6	397.1	397.5	397.1	395.7	394.3	393.0	391.7	393.0	394.3	395.7
127.5°	433.2	433.7	434.2	433.6	432.0	430.2	428.5	426.8	428.5	430.2	432.0
130°	456.8	457.2	457.4	456.7	454.7	452.8	450.8	448.9	450.8	452.8	454.7
132.5°	481.0	480.9	480.8	480.0	478.4	476.8	475.3	473.6	475.3	476.8	478.4
135°	514.9	514.6	514.3	513.3	511.7	510.1	508.4	506.8	508.4	510.1	511.7
137.5°	548.6	548.3	547.9	547.0	545.7	544.3	542.9	541.7	542.9	544.3	545.7
140°	570.6	569.8	569.0	568.0	566.6	565.3	564.0	562.7	564.0	565.3	566.6
142.5°	591.5	591.0	590.5	589.5	588.2	586.9	585.5	584.2	585.5	586.9	588.2
145°	622.1	621.2	620.3	619.3	618.3	617.3	616.1	615.1	616.1	617.3	618.3
147.5°	649.9	649.3	648.7	647.7	646.4	645.2	643.9	642.7	643.9	645.2	646.4
150°	667.1	666.5	665.9	665.1	664.3	663.3	662.5	661.6	662.5	663.3	664.3
152.5°	684.1	683.4	682.6	681.8	681.0	680.0	679.2	678.2	679.2	680.0	681.0
155°	706.5	705.9	705.5	705.1	704.6	704.2	703.7	703.3	703.7	704.2	704.6
157.5°	726.7	726.4	726.2	725.9	725.6	725.3	725.0	724.7	725.0	725.3	725.6
160°	739.3	739.2	739.0	738.8	738.5	738.2	737.9	737.6	737.9	738.2	738.5
162.5°	750.1	749.9	749.8	749.7	749.6	749.6	749.5	749.4	749.5	749.6	749.6
165°	764.5	764.5	764.5	764.6	764.7	764.9	765.1	765.2	765.1	764.9	764.7
167.5°	776.3	776.4	776.4	776.6	777.1	777.5	777.9	778.3	777.9	777.5	777.1
170°	783.0	783.2	783.3	783.6	784.0	784.5	785.0	785.4	785.0	784.5	784.0
172.5°	787.8	788.0	788.2	788.4	788.8	789.4	789.8	790.2	789.8	789.4	788.8
175°	793.4	793.7	794.0	794.4	794.8	795.2	795.7	796.2	795.7	795.2	794.8
177.5°	796.3	796.6	796.9	797.1	797.5	797.9	798.2	798.6	798.2	797.9	797.5
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	4.2	4.6	5.1	5.8	6.3	6.7	6.5	6.5	6.4	6.0	6.0
90°	7.8	10.4	13.7	17.0	20.2	23.6	23.2	23.0	22.6	22.4	22.3
92.5°	17.2	18.3	19.0	19.8	20.7	21.4	21.4	21.5	21.6	21.6	21.7
95°	41.0	41.8	42.2	42.4	42.8	43.0	43.0	43.0	43.0	43.0	43.0
97.5°	69.2	70.2	70.7	71.3	71.8	72.4	72.4	72.4	72.4	72.4	72.4
100°	90.2	91.1	91.5	92.0	92.4	92.9	92.9	92.9	92.9	92.9	92.8
102.5°	111.9	112.7	113.2	113.8	114.3	114.9	115.0	115.2	115.3	115.5	115.4
105°	146.5	146.9	147.1	147.5	147.7	148.1	148.4	148.7	149.0	149.3	149.4
107.5°	184.2	184.5	184.5	184.5	184.5	184.5	184.7	184.8	184.9	185.0	184.8
110°	208.9	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.1



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	234.7	235.1	235.0	234.9	234.7	234.6	234.3	233.8	233.5	233.2	232.8
115°	272.8	273.1	272.8	272.5	272.2	271.9	271.7	271.6	271.5	271.3	271.0
117.5°	311.9	312.1	311.3	310.5	309.6	308.8	308.4	308.1	307.7	307.3	306.9
120°	337.3	337.3	336.0	334.8	333.6	332.4	332.4	332.4	332.4	332.4	332.3
122.5°	361.4	361.6	360.8	360.0	359.1	358.3	357.9	357.6	357.2	356.9	356.5
125°	397.1	397.5	397.1	396.6	396.1	395.7	395.3	394.9	394.3	393.9	393.6
127.5°	433.6	434.2	433.7	433.2	432.6	432.0	431.5	431.0	430.4	429.9	429.4
130°	456.7	457.4	457.2	456.8	456.6	456.3	456.0	455.7	455.4	455.1	454.6
132.5°	480.0	480.8	480.9	481.0	481.0	481.0	480.4	479.7	479.1	478.5	477.9
135°	513.3	514.3	514.6	514.9	515.2	515.5	515.4	515.2	515.1	514.9	514.6
137.5°	547.0	547.9	548.3	548.6	549.1	549.4	549.3	549.2	549.1	549.0	548.6
140°	568.0	569.0	569.8	570.6	571.3	572.0	572.0	572.0	572.0	572.0	571.7
142.5°	589.5	590.5	591.0	591.5	592.0	592.5	592.6	592.7	592.9	593.0	592.7
145°	619.3	620.3	621.2	622.1	622.9	623.9	624.1	624.1	624.3	624.5	624.2
147.5°	647.7	648.7	649.3	649.9	650.5	651.1	651.3	651.7	652.0	652.4	652.3
150°	665.1	665.9	666.5	667.1	667.7	668.3	668.7	669.2	669.6	670.1	670.1
152.5°	681.8	682.6	683.4	684.1	684.8	685.5	686.0	686.6	687.3	687.8	687.8
155°	705.1	705.5	705.9	706.5	706.9	707.3	708.1	708.8	709.6	710.3	710.5
157.5°	725.9	726.2	726.4	726.7	726.9	727.2	728.2	729.3	730.3	731.3	731.4
160°	738.8	739.0	739.2	739.3	739.5	739.6	740.5	741.4	742.4	743.2	743.4
162.5°	749.7	749.8	749.9	750.1	750.3	750.4	751.4	752.4	753.5	754.5	754.6
165°	764.6	764.5	764.5	764.5	764.5	764.5	765.6	766.6	767.7	768.7	768.9
167.5°	776.6	776.4	776.4	776.3	776.3	776.2	777.3	778.3	779.4	780.4	780.6
170°	783.6	783.3	783.2	783.0	782.8	782.6	783.8	784.8	785.8	786.9	787.0
172.5°	788.4	788.2	788.0	787.8	787.7	787.6	788.6	789.6	790.7	791.7	791.8
175°	794.4	794.0	793.7	793.4	793.1	792.8	793.8	794.9	795.9	796.9	797.0
177.5°	797.1	796.9	796.6	796.3	796.1	795.9	796.6	797.3	798.1	798.7	798.7
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	6.0	5.9	5.9	5.9	5.9	5.9	6.0	6.0	6.0	6.4	6.5
90°	22.5	22.6	22.7	22.9	22.7	22.6	22.5	22.3	22.4	22.6	23.0
92.5°	21.7	21.8	21.8	21.8	21.8	21.8	21.7	21.7	21.6	21.6	21.5
95°	42.6	42.4	42.0	41.8	42.0	42.4	42.6	43.0	43.0	43.0	43.0
97.5°	72.4	72.3	72.3	72.2	72.3	72.3	72.4	72.4	72.4	72.4	72.4
100°	92.6	92.5	92.4	92.2	92.4	92.5	92.6	92.8	92.9	92.9	92.9
102.5°	115.3	115.1	114.9	114.8	114.9	115.1	115.3	115.4	115.5	115.3	115.2
105°	149.4	149.4	149.4	149.4	149.4	149.4	149.4	149.4	149.3	149.0	148.7
107.5°	184.1	183.4	182.7	182.0	182.7	183.4	184.1	184.8	185.0	184.9	184.8
110°	208.6	208.2	207.8	207.2	207.8	208.2	208.6	209.1	209.3	209.3	209.3



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	232.5	232.1	231.9	231.5	231.9	232.1	232.5	232.8	233.2	233.5	233.8
115°	270.5	270.1	269.7	269.2	269.7	270.1	270.5	271.0	271.3	271.5	271.6
117.5°	306.5	306.0	305.6	305.1	305.6	306.0	306.5	306.9	307.3	307.7	308.1
120°	331.7	331.3	330.9	330.5	330.9	331.3	331.7	332.3	332.4	332.4	332.4
122.5°	356.2	355.9	355.5	355.2	355.5	355.9	356.2	356.5	356.9	357.2	357.6
125°	393.5	393.3	393.2	393.0	393.2	393.3	393.5	393.6	393.9	394.3	394.9
127.5°	429.0	428.4	428.0	427.5	428.0	428.4	429.0	429.4	429.9	430.4	431.0
130°	454.0	453.5	452.9	452.3	452.9	453.5	454.0	454.6	455.1	455.4	455.7
132.5°	477.3	476.9	476.4	476.0	476.4	476.9	477.3	477.9	478.5	479.1	479.7
135°	514.2	513.8	513.2	512.8	513.2	513.8	514.2	514.6	514.9	515.1	515.2
137.5°	548.0	547.4	546.8	546.2	546.8	547.4	548.0	548.6	549.0	549.1	549.2
140°	571.2	570.6	570.0	569.4	570.0	570.6	571.2	571.7	572.0	572.0	572.0
142.5°	592.1	591.5	591.0	590.4	591.0	591.5	592.1	592.7	593.0	592.9	592.7
145°	623.6	623.0	622.4	621.8	622.4	623.0	623.6	624.2	624.5	624.3	624.1
147.5°	651.7	651.1	650.6	650.0	650.6	651.1	651.7	652.3	652.4	652.0	651.7
150°	669.6	669.2	668.7	668.3	668.7	669.2	669.6	670.1	670.1	669.6	669.2
152.5°	687.3	686.6	686.0	685.5	686.0	686.6	687.3	687.8	687.8	687.3	686.6
155°	710.0	709.6	709.1	708.7	709.1	709.6	710.0	710.5	710.3	709.6	708.8
157.5°	730.7	730.0	729.3	728.6	729.3	730.0	730.7	731.4	731.3	730.3	729.3
160°	742.8	742.2	741.6	741.0	741.6	742.2	742.8	743.4	743.2	742.4	741.4
162.5°	753.9	753.2	752.4	751.7	752.4	753.2	753.9	754.6	754.5	753.5	752.4
165°	768.1	767.3	766.6	765.9	766.6	767.3	768.1	768.9	768.7	767.7	766.6
167.5°	779.8	779.0	778.3	777.5	778.3	779.0	779.8	780.6	780.4	779.4	778.3
170°	786.1	785.1	784.3	783.3	784.3	785.1	786.1	787.0	786.9	785.8	784.8
172.5°	790.9	790.0	789.1	788.2	789.1	790.0	790.9	791.8	791.7	790.7	789.6
175°	796.2	795.2	794.4	793.5	794.4	795.2	796.2	797.0	796.9	795.9	794.9
177.5°	798.1	797.3	796.6	795.9	796.6	797.3	798.1	798.7	798.7	798.1	797.3
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	6.5	6.7	6.3	5.8	5.1	4.6	4.2	4.0	4.0	3.8	3.6
90°	23.2	23.6	20.2	17.0	13.7	10.4	7.8	6.0	4.3	2.5	0.7
92.5°	21.4	21.4	20.7	19.8	19.0	18.3	17.2	15.9	14.6	13.3	12.0
95°	43.0	43.0	42.8	42.4	42.2	41.8	41.0	39.5	38.0	36.5	35.0
97.5°	72.4	72.4	71.8	71.3	70.7	70.2	69.2	67.8	66.6	65.3	64.0
100°	92.9	92.9	92.4	92.0	91.5	91.1	90.2	89.0	87.8	86.7	85.5
102.5°	115.0	114.9	114.3	113.8	113.2	112.7	111.9	111.0	110.0	109.0	108.1
105°	148.4	148.1	147.7	147.5	147.1	146.9	146.5	146.0	145.6	145.2	144.7
107.5°	184.7	184.5	184.5	184.5	184.5	184.5	184.2	183.6	182.9	182.3	181.6
110°	209.3	209.3	209.3	209.3	209.3	209.3	208.9	207.9	207.1	206.1	205.3



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	234.3	234.6	234.7	234.9	235.0	235.1	234.7	233.8	232.9	232.0	231.1
115°	271.7	271.9	272.2	272.5	272.8	273.1	272.8	271.9	271.0	270.1	269.2
117.5°	308.4	308.8	309.6	310.5	311.3	312.1	311.9	310.7	309.5	308.3	307.1
120°	332.4	332.4	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4
122.5°	357.9	358.3	359.1	360.0	360.8	361.6	361.4	359.9	358.5	357.1	355.6
125°	395.3	395.7	396.1	396.6	397.1	397.5	397.1	395.7	394.3	393.0	391.7
127.5°	431.5	432.0	432.6	433.2	433.7	434.2	433.6	432.0	430.2	428.5	426.8
130°	456.0	456.3	456.6	456.8	457.2	457.4	456.7	454.7	452.8	450.8	448.9
132.5°	480.4	481.0	481.0	481.0	480.9	480.8	480.0	478.4	476.8	475.3	473.6
135°	515.4	515.5	515.2	514.9	514.6	514.3	513.3	511.7	510.1	508.4	506.8
137.5°	549.3	549.4	549.1	548.6	548.3	547.9	547.0	545.7	544.3	542.9	541.7
140°	572.0	572.0	571.3	570.6	569.8	569.0	568.0	566.6	565.3	564.0	562.7
142.5°	592.6	592.5	592.0	591.5	591.0	590.5	589.5	588.2	586.9	585.5	584.2
145°	624.1	623.9	622.9	622.1	621.2	620.3	619.3	618.3	617.3	616.1	615.1
147.5°	651.3	651.1	650.5	649.9	649.3	648.7	647.7	646.4	645.2	643.9	642.7
150°	668.7	668.3	667.7	667.1	666.5	665.9	665.1	664.3	663.3	662.5	661.6
152.5°	686.0	685.5	684.8	684.1	683.4	682.6	681.8	681.0	680.0	679.2	678.2
155°	708.1	707.3	706.9	706.5	705.9	705.5	705.1	704.6	704.2	703.7	703.3
157.5°	728.2	727.2	726.9	726.7	726.4	726.2	725.9	725.6	725.3	725.0	724.7
160°	740.5	739.6	739.5	739.3	739.2	739.0	738.8	738.5	738.2	737.9	737.6
162.5°	751.4	750.4	750.3	750.1	749.9	749.8	749.7	749.6	749.6	749.5	749.4
165°	765.6	764.5	764.5	764.5	764.5	764.5	764.6	764.7	764.9	765.1	765.2
167.5°	777.3	776.2	776.3	776.3	776.4	776.4	776.6	777.1	777.5	777.9	778.3
170°	783.8	782.6	782.8	783.0	783.2	783.3	783.6	784.0	784.5	785.0	785.4
172.5°	788.6	787.6	787.7	787.8	788.0	788.2	788.4	788.8	789.4	789.8	790.2
175°	793.8	792.8	793.1	793.4	793.7	794.0	794.4	794.8	795.2	795.7	796.2
177.5°	796.6	795.9	796.1	796.3	796.6	796.9	797.1	797.5	797.9	798.2	798.6
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.4	5.4	5.8	6.5	6.8	7.4	8.1	8.6	9.1	8.9	8.7
90°	2.5	4.3	6.0	7.8	10.4	13.7	17.0	20.2	23.6	23.2	23.0
92.5°	13.3	14.6	15.9	17.2	18.3	19.0	19.8	20.7	21.4	21.4	21.5
95°	36.5	38.0	39.5	41.0	41.8	42.2	42.4	42.8	43.0	43.0	43.0
97.5°	65.3	66.6	67.8	69.2	70.2	70.7	71.3	71.8	72.4	72.4	72.4
100°	86.7	87.8	89.0	90.2	91.1	91.5	92.0	92.4	92.9	92.9	92.9
102.5°	109.0	110.0	111.0	111.9	112.7	113.2	113.8	114.3	114.9	115.0	115.2
105°	145.2	145.6	146.0	146.5	146.9	147.1	147.5	147.7	148.1	148.4	148.7
107.5°	182.3	182.9	183.6	184.2	184.5	184.5	184.5	184.5	184.5	184.7	184.8
110°	206.1	207.1	207.9	208.9	209.3	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	232.0	232.9	233.8	234.7	235.1	235.0	234.9	234.7	234.6	234.3	233.8
115°	270.1	271.0	271.9	272.8	273.1	272.8	272.5	272.2	271.9	271.7	271.6
117.5°	308.3	309.5	310.7	311.9	312.1	311.3	310.5	309.6	308.8	308.4	308.1
120°	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	332.4	332.4
122.5°	357.1	358.5	359.9	361.4	361.6	360.8	360.0	359.1	358.3	357.9	357.6
125°	393.0	394.3	395.7	397.1	397.5	397.1	396.6	396.1	395.7	395.3	394.9
127.5°	428.5	430.2	432.0	433.6	434.2	433.7	433.2	432.6	432.0	431.5	431.0
130°	450.8	452.8	454.7	456.7	457.4	457.2	456.8	456.6	456.3	456.0	455.7
132.5°	475.3	476.8	478.4	480.0	480.8	480.9	481.0	481.0	481.0	480.4	479.7
135°	508.4	510.1	511.7	513.3	514.3	514.6	514.9	515.2	515.5	515.4	515.2
137.5°	542.9	544.3	545.7	547.0	547.9	548.3	548.6	549.1	549.4	549.3	549.2
140°	564.0	565.3	566.6	568.0	569.0	569.8	570.6	571.3	572.0	572.0	572.0
142.5°	585.5	586.9	588.2	589.5	590.5	591.0	591.5	592.0	592.5	592.6	592.7
145°	616.1	617.3	618.3	619.3	620.3	621.2	622.1	622.9	623.9	624.1	624.1
147.5°	643.9	645.2	646.4	647.7	648.7	649.3	649.9	650.5	651.1	651.3	651.7
150°	662.5	663.3	664.3	665.1	665.9	666.5	667.1	667.7	668.3	668.7	669.2
152.5°	679.2	680.0	681.0	681.8	682.6	683.4	684.1	684.8	685.5	686.0	686.6
155°	703.7	704.2	704.6	705.1	705.5	705.9	706.5	706.9	707.3	708.1	708.8
157.5°	725.0	725.3	725.6	725.9	726.2	726.4	726.7	726.9	727.2	728.2	729.3
160°	737.9	738.2	738.5	738.8	739.0	739.2	739.3	739.5	739.6	740.5	741.4
162.5°	749.5	749.6	749.6	749.7	749.8	749.9	750.1	750.3	750.4	751.4	752.4
165°	765.1	764.9	764.7	764.6	764.5	764.5	764.5	764.5	764.5	765.6	766.6
167.5°	777.9	777.5	777.1	776.6	776.4	776.4	776.3	776.3	776.2	777.3	778.3
170°	785.0	784.5	784.0	783.6	783.3	783.2	783.0	782.8	782.6	783.8	784.8
172.5°	789.8	789.4	788.8	788.4	788.2	788.0	787.8	787.7	787.6	788.6	789.6
175°	795.7	795.2	794.8	794.4	794.0	793.7	793.4	793.1	792.8	793.8	794.9
177.5°	798.2	797.9	797.5	797.1	796.9	796.6	796.3	796.1	795.9	796.6	797.3
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	8.8	8.7	8.5	8.5	8.8	8.6	8.6
90°	22.6	22.4	22.3	22.5	22.6	22.7	22.9
92.5°	21.6	21.6	21.7	21.7	21.8	21.8	21.8
95°	43.0	43.0	43.0	42.6	42.4	42.0	41.8
97.5°	72.4	72.4	72.4	72.4	72.3	72.3	72.2
100°	92.9	92.9	92.8	92.6	92.5	92.4	92.2
102.5°	115.3	115.5	115.4	115.3	115.1	114.9	114.8
105°	149.0	149.3	149.4	149.4	149.4	149.4	149.4
107.5°	184.9	185.0	184.8	184.1	183.4	182.7	182.0
110°	209.3	209.3	209.1	208.6	208.2	207.8	207.2



TEST NUMBER: P331259-935

CATALOG NUMBER: SA2XXDIP-C290D725U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.2	232.8	232.5	232.1	231.9	231.5
115°	271.5	271.3	271.0	270.5	270.1	269.7	269.2
117.5°	307.7	307.3	306.9	306.5	306.0	305.6	305.1
120°	332.4	332.4	332.3	331.7	331.3	330.9	330.5
122.5°	357.2	356.9	356.5	356.2	355.9	355.5	355.2
125°	394.3	393.9	393.6	393.5	393.3	393.2	393.0
127.5°	430.4	429.9	429.4	429.0	428.4	428.0	427.5
130°	455.4	455.1	454.6	454.0	453.5	452.9	452.3
132.5°	479.1	478.5	477.9	477.3	476.9	476.4	476.0
135°	515.1	514.9	514.6	514.2	513.8	513.2	512.8
137.5°	549.1	549.0	548.6	548.0	547.4	546.8	546.2
140°	572.0	572.0	571.7	571.2	570.6	570.0	569.4
142.5°	592.9	593.0	592.7	592.1	591.5	591.0	590.4
145°	624.3	624.5	624.2	623.6	623.0	622.4	621.8
147.5°	652.0	652.4	652.3	651.7	651.1	650.6	650.0
150°	669.6	670.1	670.1	669.6	669.2	668.7	668.3
152.5°	687.3	687.8	687.8	687.3	686.6	686.0	685.5
155°	709.6	710.3	710.5	710.0	709.6	709.1	708.7
157.5°	730.3	731.3	731.4	730.7	730.0	729.3	728.6
160°	742.4	743.2	743.4	742.8	742.2	741.6	741.0
162.5°	753.5	754.5	754.6	753.9	753.2	752.4	751.7
165°	767.7	768.7	768.9	768.1	767.3	766.6	765.9
167.5°	779.4	780.4	780.6	779.8	779.0	778.3	777.5
170°	785.8	786.9	787.0	786.1	785.1	784.3	783.3
172.5°	790.7	791.7	791.8	790.9	790.0	789.1	788.2
175°	795.9	796.9	797.0	796.2	795.2	794.4	793.5
177.5°	798.1	798.7	798.7	798.1	797.3	796.6	795.9
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5

(END OF REPORT)