

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331657-830

Luminaire Tested: **SA2XXRDIP-C485D725U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331657-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4483.6 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	81	78	69	66	65	55	53	52	42	41	40	34
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	37	36	35	30
3	81	72	65	59	73	66	60	55	54	50	47	44	41	38	34	32	30	26
4	74	64	57	51	67	59	52	47	49	44	40	39	36	33	31	28	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	29	28	26	24	20
6	63	52	44	38	57	47	41	36	40	35	31	32	29	26	26	23	21	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	23	24	21	19	17
8	54	43	35	30	49	39	33	28	33	28	25	27	24	21	22	19	17	15
9	51	39	32	27	46	36	30	25	31	26	22	25	22	19	20	18	16	14
10	47	36	29	24	43	33	27	23	28	23	20	23	20	17	19	16	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16356	16356	16356	16356
5°	18266	16459	14593	16459
10°	20266	16342	12650	16342
15°	21264	16104	9967	16104
20°	18433	15747	8624	15747
25°	12089	15262	7701	15262
30°	8138	14673	6969	14673
35°	6591	13931	6286	13931
40°	5861	13122	5817	13122
45°	5304	12177	5190	12177
50°	4828	11235	4808	11235
55°	4538	10196	4479	10196
60°	3794	9242	3749	9242
65°	3202	8390	3629	8390
70°	2960	7492	3423	7492
75°	2770	6519	3163	6519
80°	2548	5365	2817	5365
85°	2334	4242	2482	4242



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	2.1
10°-20°	267.6	6.0
20°-30°	344.8	7.7
30°-40°	327.7	7.3
40°-50°	280.7	6.3
50°-60°	213.8	4.8
60°-70°	135.1	3.0
70°-80°	67.5	1.5
80°-90°	19.9	0.4
90°-100°	31.1	0.7
100°-110°	114.0	2.5
110°-120°	304.7	6.8
120°-130°	502.9	11.2
130°-140°	534.9	11.9
140°-150°	497.1	11.1
150°-160°	399.7	8.9
160°-170°	257.6	5.7
170°-180°	88.7	2.0
0°-30°	708.4	15.8
0°-40°	1036.1	23.1
0°-60°	1530.5	34.1
0°-90°	1753.0	39.1
90°-120°	449.7	10.0
90°-150°	1984.7	44.3
90°-180°	2731.0	60.9
0°-180°	4483.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1013	1013	1013	1013	1013	
5°	1127	1016	900	1016	1127	111
15°	1272	963	596	963	1272	343
25°	679	857	432	857	679	322
35°	334	707	319	707	334	214
45°	232	533	227	533	232	180
55°	161	362	159	362	161	141
65°	84	220	95	220	84	85
75°	44	104	51	104	44	47
85°	13	23	13	23	13	14
90°	18	1	18	1	18	9
95°	29	44	29	44	29	27
105°	51	205	51	205	51	53
115°	55	388	55	388	55	138
125°	576	548	576	548	576	499
135°	700	678	700	678	700	540
145°	799	787	799	787	799	500
155°	867	866	867	866	867	400
165°	911	913	911	913	911	257
175°	928	934	928	934	928	88
180°	932	932	932	932	932	



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1054.1	1055.0	1055.8	1053.9	1053.9	1052.2	1048.5	1045.7	1037.7	1036.6	1036.6
5°	1127.0	1126.3	1127.8	1123.1	1116.8	1115.4	1108.7	1099.9	1090.8	1080.5	1078.5
7.5°	1199.6	1198.5	1195.7	1194.9	1190.1	1179.4	1168.7	1157.2	1142.0	1127.1	1119.6
10°	1236.1	1247.7	1240.8	1228.4	1230.9	1214.4	1205.5	1190.4	1177.7	1155.6	1150.7
12.5°	1272.1	1276.8	1274.5	1267.5	1264.4	1252.9	1241.0	1227.9	1204.5	1184.6	1167.2
15°	1272.1	1278.7	1280.5	1278.4	1280.2	1279.4	1273.1	1262.2	1241.8	1219.9	1201.0
17.5°	1178.2	1182.8	1194.3	1202.1	1212.0	1232.8	1243.1	1247.2	1244.1	1231.6	1218.2
20°	1072.8	1065.1	1097.5	1114.0	1128.1	1163.3	1193.5	1205.1	1223.8	1223.5	1219.9
22.5°	923.6	925.4	956.1	975.7	1016.9	1052.1	1086.6	1130.3	1166.4	1190.2	1204.2
25°	678.6	692.0	722.6	749.3	795.1	860.6	920.1	989.1	1054.1	1105.6	1154.5
27.5°	509.6	510.7	534.9	559.7	586.8	640.5	715.4	797.8	890.6	967.1	1055.3
30°	436.5	434.3	444.6	459.7	483.0	524.4	580.8	661.8	754.3	869.8	972.5
32.5°	384.7	384.7	392.5	403.7	422.9	450.9	489.6	555.3	642.8	756.3	876.8
35°	334.4	334.0	339.7	347.8	355.8	373.8	400.2	434.7	494.9	600.9	724.1
37.5°	298.3	299.9	302.7	307.7	316.6	326.6	342.5	365.6	408.5	471.2	574.7
40°	278.1	278.8	282.7	286.9	292.2	299.9	312.9	331.6	362.9	412.8	488.5
42.5°	259.5	260.1	263.0	266.8	271.0	278.8	289.5	305.7	331.1	370.0	432.5
45°	232.3	232.3	234.8	236.5	241.1	248.2	256.9	270.3	287.9	316.8	358.4
47.5°	206.8	206.9	208.5	211.5	214.4	219.9	228.6	239.5	252.3	274.7	310.1
50°	192.2	192.6	193.6	196.0	197.8	202.7	209.4	219.0	232.3	249.6	279.1
52.5°	180.3	180.1	181.4	182.6	183.7	187.3	192.3	200.7	212.6	227.6	252.1
55°	161.2	159.8	161.9	163.6	164.8	166.2	168.9	174.3	184.5	197.1	215.4
57.5°	137.2	136.7	138.2	139.8	143.1	146.9	149.3	152.7	158.0	167.0	185.2
60°	117.5	117.5	120.7	121.8	125.6	130.5	135.5	138.4	143.6	149.6	163.0
62.5°	100.1	100.4	101.9	102.9	105.1	111.1	118.1	124.2	129.2	135.0	143.8
65°	83.8	84.5	84.5	85.2	86.6	88.0	90.8	95.8	104.5	112.6	119.3
67.5°	71.1	71.4	71.5	72.2	72.6	74.1	75.2	77.5	79.5	87.2	95.5
70°	62.7	63.7	63.3	64.1	64.4	65.1	66.5	67.6	70.8	72.5	77.5
72.5°	54.8	55.5	55.5	55.9	56.8	56.9	58.1	59.1	61.2	62.7	65.3
75°	44.4	44.0	44.4	45.1	45.4	45.7	45.7	47.1	48.3	49.7	51.4
77.5°	34.2	34.6	34.5	34.6	34.6	35.3	35.2	35.8	36.9	37.6	38.5
80°	27.4	27.8	27.4	27.8	28.2	28.5	28.2	28.5	29.6	30.3	30.3
82.5°	21.3	21.3	21.6	21.6	21.7	21.8	22.2	22.3	23.1	22.9	23.2
85°	12.6	12.3	12.3	12.3	12.6	13.0	12.6	12.6	13.0	13.0	13.0
87.5°	8.1	8.4	8.3	8.3	8.2	8.1	7.9	8.1	7.6	7.7	7.3
90°	18.2	17.9	17.6	17.3	17.0	16.5	15.7	15.0	14.2	13.5	12.3
92.5°	18.2	18.0	17.8	17.6	17.5	17.2	16.8	16.4	16.0	15.6	15.1
95°	29.0	29.1	29.3	29.4	29.6	29.3	28.6	27.8	27.1	26.3	25.3
97.5°	38.7	38.5	38.4	38.2	38.0	37.6	36.9	36.4	35.8	35.2	32.8
100°	45.1	44.9	44.6	44.3	44.0	43.3	42.0	40.8	39.6	38.5	35.9
102.5°	48.4	48.0	47.6	47.1	46.8	45.7	44.2	42.6	41.1	39.5	60.8
105°	51.3	50.6	50.0	49.5	48.8	47.7	46.1	44.4	42.8	41.1	82.0
107.5°	52.7	52.1	51.6	50.9	50.3	50.9	52.5	54.2	55.9	57.6	106.6
110°	53.3	52.7	52.0	51.5	50.9	58.1	73.0	88.0	103.0	118.0	161.3



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	53.8	53.3	52.9	52.4	51.8	79.0	133.7	188.3	243.0	297.6	308.3
115°	55.3	66.1	76.8	87.7	98.4	138.6	207.9	277.3	346.7	416.0	412.3
117.5°	225.7	261.2	296.6	332.1	367.5	393.6	410.4	427.3	444.0	460.8	458.2
120°	411.3	431.5	451.8	471.9	492.2	501.4	499.6	497.9	496.0	494.2	491.5
122.5°	513.2	517.2	521.0	525.0	529.0	530.4	529.2	528.2	527.1	526.0	523.1
125°	576.5	576.0	575.6	575.1	574.7	573.9	572.9	571.8	570.8	569.8	566.8
127.5°	616.4	616.3	616.2	616.1	616.0	615.2	613.7	612.2	610.7	609.1	607.0
130°	641.2	641.3	641.5	641.7	641.8	641.0	639.4	637.7	636.1	634.4	632.8
132.5°	665.4	665.6	665.8	665.9	666.1	665.4	664.0	662.6	661.2	659.8	658.2
135°	700.5	700.8	701.2	701.4	701.7	701.2	699.6	698.1	696.6	695.1	693.8
137.5°	732.4	733.0	733.5	734.1	734.5	734.1	732.5	731.1	729.6	728.2	726.6
140°	752.4	753.2	753.9	754.7	755.4	755.2	753.8	752.4	751.1	749.8	748.1
142.5°	771.8	772.6	773.4	774.1	774.9	774.6	773.4	772.1	770.9	769.7	767.8
145°	799.0	799.7	800.5	801.3	801.9	801.8	800.8	799.7	798.7	797.6	795.0
147.5°	822.8	823.5	824.1	824.7	825.4	825.3	824.5	823.7	822.9	822.2	819.6
150°	837.4	838.1	838.9	839.6	840.4	840.3	839.4	838.5	837.6	836.7	834.3
152.5°	849.8	850.8	851.8	852.8	853.8	853.8	852.9	852.0	851.1	850.2	847.9
155°	867.0	868.3	869.5	870.6	871.9	872.0	871.1	870.2	869.3	868.4	866.6
157.5°	882.9	884.0	885.1	886.4	887.5	887.6	886.6	885.5	884.6	883.5	882.2
160°	892.0	893.1	894.1	895.1	896.2	896.3	895.4	894.5	893.6	892.7	891.7
162.5°	899.6	900.9	902.1	903.4	904.7	904.8	903.8	902.8	901.8	900.8	900.0
165°	910.9	911.9	912.9	914.1	915.1	915.1	914.1	912.9	911.9	910.9	910.4
167.5°	918.0	919.4	920.8	922.1	923.4	923.6	922.6	921.5	920.4	919.4	919.0
170°	922.4	923.7	925.0	926.4	927.7	927.9	926.8	925.8	924.7	923.7	923.4
172.5°	925.6	926.9	928.3	929.6	930.9	931.1	930.1	929.1	928.0	926.9	926.6
175°	928.4	929.9	931.4	932.9	934.4	934.6	933.6	932.6	931.5	930.5	930.1
177.5°	930.2	931.2	932.4	933.4	934.5	934.6	933.8	932.9	932.1	931.2	931.1
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1037.2	1035.0	1033.0	1027.9	1025.4	1019.7	1018.9	1018.6	1011.3	1004.3	1002.3
5°	1072.8	1067.2	1058.8	1048.9	1038.7	1028.1	1021.1	1015.5	1001.4	988.0	980.2
7.5°	1108.7	1096.6	1082.0	1063.4	1047.8	1030.4	1017.5	1005.8	985.8	966.7	953.8
10°	1135.5	1115.8	1096.5	1070.7	1050.7	1031.0	1012.7	996.8	974.3	949.0	930.9
12.5°	1152.1	1130.4	1103.7	1078.6	1052.6	1027.6	1003.1	982.7	956.3	930.1	908.7
15°	1174.6	1151.3	1119.0	1083.1	1049.6	1016.9	988.7	963.4	928.9	897.6	871.5
17.5°	1193.0	1160.9	1126.1	1084.7	1045.9	1004.4	968.1	935.7	897.3	859.5	828.9
20°	1198.8	1167.2	1127.0	1085.5	1039.7	990.8	951.8	916.5	875.3	834.2	799.0
22.5°	1195.1	1170.5	1125.9	1076.2	1029.4	978.2	934.1	893.2	847.5	805.5	764.7
25°	1170.4	1161.9	1119.6	1065.5	1011.9	952.4	901.4	856.7	804.6	759.6	715.2
27.5°	1112.4	1130.7	1104.5	1046.7	987.2	923.4	866.1	815.2	761.1	710.4	666.2
30°	1056.7	1098.5	1087.2	1033.8	967.2	904.6	840.2	787.0	729.3	677.2	633.6
32.5°	980.3	1049.5	1060.5	1015.8	947.0	878.1	810.6	757.7	697.5	642.5	600.0
35°	858.8	962.3	1009.8	981.3	912.3	838.1	768.4	706.8	646.2	592.0	549.8
37.5°	713.9	854.8	934.1	936.0	872.7	795.5	719.6	658.5	596.4	543.3	497.6
40°	619.8	772.6	875.7	898.6	845.1	761.7	684.9	622.6	562.1	510.0	457.6
42.5°	535.4	687.6	814.4	854.1	811.6	728.8	651.8	586.6	527.7	478.4	424.9
45°	432.9	566.0	705.7	776.8	753.3	676.5	595.2	533.3	478.0	435.4	384.0
47.5°	365.2	459.0	594.2	690.4	689.9	619.9	540.0	480.6	429.3	389.5	347.8
50°	326.6	408.3	522.7	631.8	640.9	582.2	506.1	447.3	399.5	357.6	324.1
52.5°	292.0	359.3	462.1	566.8	592.8	541.9	468.2	413.9	367.4	328.9	300.2
55°	246.8	298.8	377.0	474.9	514.3	478.3	412.8	362.2	324.5	292.2	267.5
57.5°	208.7	247.8	310.5	389.3	435.2	412.6	358.6	317.4	285.2	255.9	236.5
60°	184.8	216.8	269.9	335.8	386.4	370.6	324.5	286.2	258.7	233.4	215.1
62.5°	162.3	189.8	235.4	288.8	335.3	328.7	291.1	258.8	234.8	211.7	196.2
65°	130.5	150.6	186.2	228.1	265.4	268.5	241.5	219.6	198.1	179.8	166.2
67.5°	104.0	117.1	142.1	177.4	205.4	215.4	198.8	182.1	165.0	150.9	139.0
70°	87.7	98.2	116.5	145.1	170.7	181.3	171.7	158.7	143.9	132.3	122.2
72.5°	71.1	81.3	94.8	115.7	137.8	149.2	145.9	136.5	124.5	114.9	105.3
75°	53.5	56.6	65.8	79.9	97.2	107.0	109.4	104.5	95.0	87.7	82.0
77.5°	39.6	41.5	45.8	53.3	64.5	73.2	76.9	76.3	69.7	65.5	60.2
80°	31.7	32.7	34.9	38.0	46.5	55.2	57.7	57.7	53.2	51.4	46.1
82.5°	24.0	24.9	26.1	27.9	31.9	39.5	42.2	42.8	39.9	37.6	33.5
85°	13.8	13.4	14.0	15.2	15.8	17.9	22.1	22.9	22.1	19.3	18.3
87.5°	7.0	7.1	6.8	6.2	6.2	6.1	7.3	8.3	7.5	7.0	6.8
90°	11.1	9.9	8.7	7.3	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	14.4	13.9	13.3	13.0	13.2	13.3	13.5	13.6	13.5	13.3	13.2
95°	24.2	23.2	22.1	24.0	29.0	33.9	38.9	43.8	38.9	33.9	29.0
97.5°	30.3	27.9	25.4	31.2	45.1	59.1	73.0	87.0	73.0	59.1	45.1
100°	33.4	30.8	28.3	37.2	57.8	78.3	98.8	119.3	98.8	78.3	57.8
102.5°	82.1	103.4	124.7	137.5	141.9	146.3	150.6	155.0	150.6	146.3	141.9
105°	122.9	163.8	204.7	222.9	218.5	214.0	209.4	205.0	209.4	214.0	218.5
107.5°	155.7	204.7	253.8	276.5	272.9	269.3	265.6	262.0	265.6	269.3	272.9
110°	204.6	247.9	291.2	311.2	308.1	305.0	301.8	298.7	301.8	305.0	308.1



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	319.0	329.7	340.4	344.3	341.6	338.7	336.0	333.2	336.0	338.7	341.6
115°	408.5	404.7	401.1	397.8	395.3	392.8	390.2	387.7	390.2	392.8	395.3
117.5°	455.6	453.1	450.4	447.7	444.9	442.1	439.2	436.4	439.2	442.1	444.9
120°	488.8	486.2	483.4	481.0	478.7	476.5	474.2	471.9	474.2	476.5	478.7
122.5°	520.2	517.3	514.3	511.6	509.3	506.9	504.5	502.2	504.5	506.9	509.3
125°	564.0	561.2	558.4	555.9	554.0	552.0	550.1	548.2	550.1	552.0	554.0
127.5°	604.8	602.8	600.6	598.4	596.3	594.2	592.0	589.8	592.0	594.2	596.3
130°	631.1	629.5	627.8	625.8	623.4	621.0	618.7	616.2	618.7	621.0	623.4
132.5°	656.5	654.9	653.2	651.4	649.3	647.3	645.3	643.2	645.3	647.3	649.3
135°	692.4	691.1	689.8	687.9	685.5	683.1	680.7	678.3	680.7	683.1	685.5
137.5°	725.1	723.6	722.1	720.5	718.8	717.1	715.4	713.8	715.4	717.1	718.8
140°	746.5	744.8	743.2	741.7	740.6	739.3	738.1	737.0	738.1	739.3	740.6
142.5°	765.9	764.0	762.1	760.6	759.6	758.6	757.4	756.4	757.4	758.6	759.6
145°	792.5	789.9	787.4	786.3	786.4	786.6	786.6	786.8	786.6	786.6	786.4
147.5°	817.1	814.6	812.1	811.2	811.7	812.3	812.8	813.4	812.8	812.3	811.7
150°	831.9	829.5	827.2	826.4	827.6	828.6	829.6	830.7	829.6	828.6	827.6
152.5°	845.6	843.4	841.1	840.6	841.7	842.9	844.0	845.2	844.0	842.9	841.7
155°	864.8	863.0	861.2	861.0	862.3	863.7	865.1	866.4	865.1	863.7	862.3
157.5°	881.0	879.8	878.4	878.4	879.6	880.7	881.8	883.0	881.8	880.7	879.6
160°	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	891.7	890.9	889.9
162.5°	899.2	898.4	897.7	897.7	898.6	899.6	900.4	901.4	900.4	899.6	898.6
165°	910.0	909.6	909.1	909.3	910.2	911.2	912.0	912.9	912.0	911.2	910.2
167.5°	918.5	918.1	917.7	917.9	918.9	919.7	920.7	921.5	920.7	919.7	918.9
170°	923.1	922.8	922.5	922.8	923.7	924.6	925.5	926.4	925.5	924.6	923.7
172.5°	926.3	926.0	925.8	926.0	926.9	927.8	928.7	929.6	928.7	927.8	926.9
175°	929.8	929.5	929.3	929.6	930.7	931.7	932.7	933.8	932.7	931.7	930.7
177.5°	931.0	930.9	930.8	931.1	932.0	932.8	933.7	934.5	933.7	932.8	932.0
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	998.6	996.6	993.0	987.4	984.0	978.1	974.1	976.4	976.9	976.4	975.8
5°	971.9	964.4	954.2	944.3	935.2	925.4	919.7	917.3	912.3	909.6	908.1
7.5°	939.3	926.6	912.2	895.0	880.4	865.2	857.3	853.5	843.4	837.9	833.1
10°	915.1	895.0	880.6	858.1	844.4	824.3	810.6	811.0	797.2	789.5	783.8
12.5°	888.4	866.4	842.4	822.1	803.0	786.9	770.3	763.6	749.0	741.6	726.4
15°	844.0	818.3	793.1	765.5	746.2	721.2	697.3	668.1	644.5	624.1	618.4
17.5°	795.6	763.8	738.4	706.2	673.0	630.9	603.2	586.3	572.0	561.3	553.3
20°	762.4	730.0	702.9	654.3	609.6	581.1	560.7	547.7	532.9	521.3	514.9
22.5°	727.5	693.7	656.8	602.5	567.7	544.8	526.6	511.6	501.6	492.6	486.8
25°	677.9	640.9	580.0	542.7	514.6	490.7	478.0	468.8	458.3	445.9	440.4
27.5°	625.6	566.8	523.0	495.3	468.4	452.9	441.5	427.8	418.4	412.8	407.0
30°	586.4	527.6	493.5	463.2	444.2	427.0	413.6	405.9	396.7	387.2	383.3
32.5°	542.7	495.8	463.1	437.9	418.6	403.9	393.3	380.8	374.2	368.3	360.2
35°	488.5	453.0	423.1	402.7	384.4	372.4	360.1	352.7	340.7	335.8	332.6
37.5°	442.6	411.8	389.5	368.0	353.5	340.3	332.7	320.9	315.8	308.9	302.2
40°	416.7	386.4	365.0	347.4	331.2	321.3	311.9	302.4	294.6	291.4	283.3
42.5°	390.3	365.6	344.1	324.9	314.1	303.6	291.6	284.6	276.5	271.5	266.5
45°	353.7	332.0	313.6	297.7	285.8	274.9	267.1	255.5	251.0	240.7	236.5
47.5°	321.6	301.3	283.9	268.8	257.1	250.1	238.7	229.6	222.3	216.0	210.7
50°	298.8	281.9	265.0	251.7	241.1	230.9	219.3	214.7	203.4	200.3	197.1
52.5°	278.0	261.9	246.5	233.4	222.8	212.9	202.6	196.7	189.1	185.9	183.6
55°	248.8	233.4	218.6	207.0	196.4	186.2	179.8	172.5	168.9	166.5	163.6
57.5°	219.5	205.7	194.3	182.6	171.9	163.8	156.5	152.0	148.4	145.2	141.8
60°	201.0	187.6	177.4	166.5	155.6	148.9	143.3	138.0	133.7	128.8	127.4
62.5°	181.3	169.6	160.2	149.6	140.1	133.9	128.7	123.7	118.6	111.4	109.4
65°	154.2	145.1	135.2	126.4	117.9	112.0	104.2	98.6	96.4	95.8	95.4
67.5°	129.7	121.0	112.5	103.6	95.9	90.3	86.3	85.5	84.1	83.6	82.7
70°	113.3	105.3	96.8	88.3	81.0	79.9	78.5	77.1	75.3	74.6	73.9
72.5°	98.7	90.3	81.9	75.1	71.9	70.6	69.2	67.8	66.6	65.9	65.5
75°	75.7	68.0	62.3	59.9	58.1	57.0	55.0	53.8	53.2	52.1	51.7
77.5°	54.5	50.1	47.5	46.0	44.1	43.0	41.8	40.7	40.0	39.8	39.2
80°	41.6	39.4	37.7	35.5	34.9	33.5	33.1	32.0	32.4	31.3	31.3
82.5°	32.2	29.6	28.1	27.1	26.4	25.3	24.9	24.4	24.5	23.8	23.8
85°	16.6	15.8	15.2	14.4	14.4	13.4	13.8	13.4	13.4	12.6	12.3
87.5°	6.8	6.8	6.5	6.7	7.0	6.9	7.1	7.0	7.1	7.3	7.1
90°	7.3	8.7	9.9	11.1	12.3	13.5	14.2	15.0	15.7	16.5	17.0
92.5°	13.0	13.3	13.9	14.4	15.1	15.6	16.0	16.4	16.8	17.2	17.5
95°	24.0	22.1	23.2	24.2	25.3	26.3	27.1	27.8	28.6	29.3	29.6
97.5°	31.2	25.4	27.9	30.3	32.8	35.2	35.8	36.4	36.9	37.6	38.0
100°	37.2	28.3	30.8	33.4	35.9	38.5	39.6	40.8	42.0	43.3	44.0
102.5°	137.5	124.7	103.4	82.1	60.8	39.5	41.1	42.6	44.2	45.7	46.8
105°	222.9	204.7	163.8	122.9	82.0	41.1	42.8	44.4	46.1	47.7	48.8
107.5°	276.5	253.8	204.7	155.7	106.6	57.6	55.9	54.2	52.5	50.9	50.3
110°	311.2	291.2	247.9	204.6	161.3	118.0	103.0	88.0	73.0	58.1	50.9



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	344.3	340.4	329.7	319.0	308.3	297.6	243.0	188.3	133.7	79.0	51.8
115°	397.8	401.1	404.7	408.5	412.3	416.0	346.7	277.3	207.9	138.6	98.4
117.5°	447.7	450.4	453.1	455.6	458.2	460.8	444.0	427.3	410.4	393.6	367.5
120°	481.0	483.4	486.2	488.8	491.5	494.2	496.0	497.9	499.6	501.4	492.2
122.5°	511.6	514.3	517.3	520.2	523.1	526.0	527.1	528.2	529.2	530.4	529.0
125°	555.9	558.4	561.2	564.0	566.8	569.8	570.8	571.8	572.9	573.9	574.7
127.5°	598.4	600.6	602.8	604.8	607.0	609.1	610.7	612.2	613.7	615.2	616.0
130°	625.8	627.8	629.5	631.1	632.8	634.4	636.1	637.7	639.4	641.0	641.8
132.5°	651.4	653.2	654.9	656.5	658.2	659.8	661.2	662.6	664.0	665.4	666.1
135°	687.9	689.8	691.1	692.4	693.8	695.1	696.6	698.1	699.6	701.2	701.7
137.5°	720.5	722.1	723.6	725.1	726.6	728.2	729.6	731.1	732.5	734.1	734.5
140°	741.7	743.2	744.8	746.5	748.1	749.8	751.1	752.4	753.8	755.2	755.4
142.5°	760.6	762.1	764.0	765.9	767.8	769.7	770.9	772.1	773.4	774.6	774.9
145°	786.3	787.4	789.9	792.5	795.0	797.6	798.7	799.7	800.8	801.8	801.9
147.5°	811.2	812.1	814.6	817.1	819.6	822.2	822.9	823.7	824.5	825.3	825.4
150°	826.4	827.2	829.5	831.9	834.3	836.7	837.6	838.5	839.4	840.3	840.4
152.5°	840.6	841.1	843.4	845.6	847.9	850.2	851.1	852.0	852.9	853.8	853.8
155°	861.0	861.2	863.0	864.8	866.6	868.4	869.3	870.2	871.1	872.0	871.9
157.5°	878.4	878.4	879.8	881.0	882.2	883.5	884.6	885.5	886.6	887.6	887.5
160°	889.1	889.1	889.9	890.9	891.7	892.7	893.6	894.5	895.4	896.3	896.2
162.5°	897.7	897.7	898.4	899.2	900.0	900.8	901.8	902.8	903.8	904.8	904.7
165°	909.3	909.1	909.6	910.0	910.4	910.9	911.9	912.9	914.1	915.1	915.1
167.5°	917.9	917.7	918.1	918.5	919.0	919.4	920.4	921.5	922.6	923.6	923.4
170°	922.8	922.5	922.8	923.1	923.4	923.7	924.7	925.8	926.8	927.9	927.7
172.5°	926.0	925.8	926.0	926.3	926.6	926.9	928.0	929.1	930.1	931.1	930.9
175°	929.6	929.3	929.5	929.8	930.1	930.5	931.5	932.6	933.6	934.6	934.4
177.5°	931.1	930.8	930.9	931.0	931.1	931.2	932.1	932.9	933.8	934.6	934.5
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	972.7	973.3	972.4	973.0	972.4	973.3	972.7	975.8	976.4	976.9	976.4
5°	906.3	902.1	901.4	900.4	901.4	902.1	906.3	908.1	909.6	912.3	917.3
7.5°	827.1	826.4	824.7	822.2	824.7	826.4	827.1	833.1	837.9	843.4	853.5
10°	776.1	774.4	774.0	771.6	774.0	774.4	776.1	783.8	789.5	797.2	811.0
12.5°	716.4	705.1	703.9	697.8	703.9	705.1	716.4	726.4	741.6	749.0	763.6
15°	610.0	607.8	600.9	596.3	600.9	607.8	610.0	618.4	624.1	644.5	668.1
17.5°	549.1	542.2	540.1	539.1	540.1	542.2	549.1	553.3	561.3	572.0	586.3
20°	510.0	503.7	502.7	501.9	502.7	503.7	510.0	514.9	521.3	532.9	547.7
22.5°	483.0	476.4	473.6	471.6	473.6	476.4	483.0	486.8	492.6	501.6	511.6
25°	436.8	434.3	432.9	432.3	432.9	434.3	436.8	440.4	445.9	458.3	468.8
27.5°	400.7	395.3	394.2	392.4	394.2	395.3	400.7	407.0	412.8	418.4	427.8
30°	380.1	378.3	375.9	373.8	375.9	378.3	380.1	383.3	387.2	396.7	405.9
32.5°	355.9	354.5	352.2	351.3	352.2	354.5	355.9	360.2	368.3	374.2	380.8
35°	329.1	324.1	322.1	318.9	322.1	324.1	329.1	332.6	335.8	340.7	352.7
37.5°	300.8	298.1	295.2	296.2	295.2	298.1	300.8	302.2	308.9	315.8	320.9
40°	278.8	277.0	276.3	276.0	276.3	277.0	278.8	283.3	291.4	294.6	302.4
42.5°	261.3	256.5	254.6	254.6	254.6	256.5	261.3	266.5	271.5	276.5	284.6
45°	234.8	230.2	227.1	227.3	227.1	230.2	234.8	236.5	240.7	251.0	255.5
47.5°	207.6	207.5	205.5	206.1	205.5	207.5	207.6	210.7	216.0	222.3	229.6
50°	194.6	192.6	191.1	191.4	191.1	192.6	194.6	197.1	200.3	203.4	214.7
52.5°	182.3	180.4	179.3	180.8	179.3	180.4	182.3	183.6	185.9	189.1	196.7
55°	161.9	159.8	159.5	159.1	159.5	159.8	161.9	163.6	166.5	168.9	172.5
57.5°	139.2	137.8	135.6	134.8	135.6	137.8	139.2	141.8	145.2	148.4	152.0
60°	122.8	120.0	116.5	116.1	116.5	120.0	122.8	127.4	128.8	133.7	138.0
62.5°	107.9	107.4	106.7	106.6	106.7	107.4	107.9	109.4	111.4	118.6	123.7
65°	94.7	94.3	94.7	95.0	94.7	94.3	94.7	95.4	95.8	96.4	98.6
67.5°	82.5	81.9	81.2	81.5	81.2	81.9	82.5	82.7	83.6	84.1	85.5
70°	73.2	72.9	72.5	72.5	72.5	72.9	73.2	73.9	74.6	75.3	77.1
72.5°	64.2	64.1	63.8	63.5	63.8	64.1	64.2	65.5	65.9	66.6	67.8
75°	51.4	50.7	50.7	50.7	50.7	50.7	51.4	51.7	52.1	53.2	53.8
77.5°	39.1	38.8	38.5	38.2	38.5	38.8	39.1	39.2	39.8	40.0	40.7
80°	31.0	30.6	30.3	30.3	30.3	30.6	31.0	31.3	31.3	32.4	32.0
82.5°	23.7	23.3	23.2	22.9	23.2	23.3	23.7	23.8	23.8	24.5	24.4
85°	12.6	13.0	12.6	13.4	12.6	13.0	12.6	12.3	12.6	13.4	13.4
87.5°	7.2	6.9	7.3	7.0	7.3	6.9	7.2	7.1	7.3	7.1	7.0
90°	17.3	17.6	17.9	18.2	17.9	17.6	17.3	17.0	16.5	15.7	15.0
92.5°	17.6	17.8	18.0	18.2	18.0	17.8	17.6	17.5	17.2	16.8	16.4
95°	29.4	29.3	29.1	29.0	29.1	29.3	29.4	29.6	29.3	28.6	27.8
97.5°	38.2	38.4	38.5	38.7	38.5	38.4	38.2	38.0	37.6	36.9	36.4
100°	44.3	44.6	44.9	45.1	44.9	44.6	44.3	44.0	43.3	42.0	40.8
102.5°	47.1	47.6	48.0	48.4	48.0	47.6	47.1	46.8	45.7	44.2	42.6
105°	49.5	50.0	50.6	51.3	50.6	50.0	49.5	48.8	47.7	46.1	44.4
107.5°	50.9	51.6	52.1	52.7	52.1	51.6	50.9	50.3	50.9	52.5	54.2
110°	51.5	52.0	52.7	53.3	52.7	52.0	51.5	50.9	58.1	73.0	88.0



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	52.4	52.9	53.3	53.8	53.3	52.9	52.4	51.8	79.0	133.7	188.3
115°	87.7	76.8	66.1	55.3	66.1	76.8	87.7	98.4	138.6	207.9	277.3
117.5°	332.1	296.6	261.2	225.7	261.2	296.6	332.1	367.5	393.6	410.4	427.3
120°	471.9	451.8	431.5	411.3	431.5	451.8	471.9	492.2	501.4	499.6	497.9
122.5°	525.0	521.0	517.2	513.2	517.2	521.0	525.0	529.0	530.4	529.2	528.2
125°	575.1	575.6	576.0	576.5	576.0	575.6	575.1	574.7	573.9	572.9	571.8
127.5°	616.1	616.2	616.3	616.4	616.3	616.2	616.1	616.0	615.2	613.7	612.2
130°	641.7	641.5	641.3	641.2	641.3	641.5	641.7	641.8	641.0	639.4	637.7
132.5°	665.9	665.8	665.6	665.4	665.6	665.8	665.9	666.1	665.4	664.0	662.6
135°	701.4	701.2	700.8	700.5	700.8	701.2	701.4	701.7	701.2	699.6	698.1
137.5°	734.1	733.5	733.0	732.4	733.0	733.5	734.1	734.5	734.1	732.5	731.1
140°	754.7	753.9	753.2	752.4	753.2	753.9	754.7	755.4	755.2	753.8	752.4
142.5°	774.1	773.4	772.6	771.8	772.6	773.4	774.1	774.9	774.6	773.4	772.1
145°	801.3	800.5	799.7	799.0	799.7	800.5	801.3	801.9	801.8	800.8	799.7
147.5°	824.7	824.1	823.5	822.8	823.5	824.1	824.7	825.4	825.3	824.5	823.7
150°	839.6	838.9	838.1	837.4	838.1	838.9	839.6	840.4	840.3	839.4	838.5
152.5°	852.8	851.8	850.8	849.8	850.8	851.8	852.8	853.8	853.8	852.9	852.0
155°	870.6	869.5	868.3	867.0	868.3	869.5	870.6	871.9	872.0	871.1	870.2
157.5°	886.4	885.1	884.0	882.9	884.0	885.1	886.4	887.5	887.6	886.6	885.5
160°	895.1	894.1	893.1	892.0	893.1	894.1	895.1	896.2	896.3	895.4	894.5
162.5°	903.4	902.1	900.9	899.6	900.9	902.1	903.4	904.7	904.8	903.8	902.8
165°	914.1	912.9	911.9	910.9	911.9	912.9	914.1	915.1	915.1	914.1	912.9
167.5°	922.1	920.8	919.4	918.0	919.4	920.8	922.1	923.4	923.6	922.6	921.5
170°	926.4	925.0	923.7	922.4	923.7	925.0	926.4	927.7	927.9	926.8	925.8
172.5°	929.6	928.3	926.9	925.6	926.9	928.3	929.6	930.9	931.1	930.1	929.1
175°	932.9	931.4	929.9	928.4	929.9	931.4	932.9	934.4	934.6	933.6	932.6
177.5°	933.4	932.4	931.2	930.2	931.2	932.4	933.4	934.5	934.6	933.8	932.9
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	974.1	978.1	984.0	987.4	993.0	996.6	998.6	1002.3	1004.3	1011.3	1018.6
5°	919.7	925.4	935.2	944.3	954.2	964.4	971.9	980.2	988.0	1001.4	1015.5
7.5°	857.3	865.2	880.4	895.0	912.2	926.6	939.3	953.8	966.7	985.8	1005.8
10°	810.6	824.3	844.4	858.1	880.6	895.0	915.1	930.9	949.0	974.3	996.8
12.5°	770.3	786.9	803.0	822.1	842.4	866.4	888.4	908.7	930.1	956.3	982.7
15°	697.3	721.2	746.2	765.5	793.1	818.3	844.0	871.5	897.6	928.9	963.4
17.5°	603.2	630.9	673.0	706.2	738.4	763.8	795.6	828.9	859.5	897.3	935.7
20°	560.7	581.1	609.6	654.3	702.9	730.0	762.4	799.0	834.2	875.3	916.5
22.5°	526.6	544.8	567.7	602.5	656.8	693.7	727.5	764.7	805.5	847.5	893.2
25°	478.0	490.7	514.6	542.7	580.0	640.9	677.9	715.2	759.6	804.6	856.7
27.5°	441.5	452.9	468.4	495.3	523.0	566.8	625.6	666.2	710.4	761.1	815.2
30°	413.6	427.0	444.2	463.2	493.5	527.6	586.4	633.6	677.2	729.3	787.0
32.5°	393.3	403.9	418.6	437.9	463.1	495.8	542.7	600.0	642.5	697.5	757.7
35°	360.1	372.4	384.4	402.7	423.1	453.0	488.5	549.8	592.0	646.2	706.8
37.5°	332.7	340.3	353.5	368.0	389.5	411.8	442.6	497.6	543.3	596.4	658.5
40°	311.9	321.3	331.2	347.4	365.0	386.4	416.7	457.6	510.0	562.1	622.6
42.5°	291.6	303.6	314.1	324.9	344.1	365.6	390.3	424.9	478.4	527.7	586.6
45°	267.1	274.9	285.8	297.7	313.6	332.0	353.7	384.0	435.4	478.0	533.3
47.5°	238.7	250.1	257.1	268.8	283.9	301.3	321.6	347.8	389.5	429.3	480.6
50°	219.3	230.9	241.1	251.7	265.0	281.9	298.8	324.1	357.6	399.5	447.3
52.5°	202.6	212.9	222.8	233.4	246.5	261.9	278.0	300.2	328.9	367.4	413.9
55°	179.8	186.2	196.4	207.0	218.6	233.4	248.8	267.5	292.2	324.5	362.2
57.5°	156.5	163.8	171.9	182.6	194.3	205.7	219.5	236.5	255.9	285.2	317.4
60°	143.3	148.9	155.6	166.5	177.4	187.6	201.0	215.1	233.4	258.7	286.2
62.5°	128.7	133.9	140.1	149.6	160.2	169.6	181.3	196.2	211.7	234.8	258.8
65°	104.2	112.0	117.9	126.4	135.2	145.1	154.2	166.2	179.8	198.1	219.6
67.5°	86.3	90.3	95.9	103.6	112.5	121.0	129.7	139.0	150.9	165.0	182.1
70°	78.5	79.9	81.0	88.3	96.8	105.3	113.3	122.2	132.3	143.9	158.7
72.5°	69.2	70.6	71.9	75.1	81.9	90.3	98.7	105.3	114.9	124.5	136.5
75°	55.0	57.0	58.1	59.9	62.3	68.0	75.7	82.0	87.7	95.0	104.5
77.5°	41.8	43.0	44.1	46.0	47.5	50.1	54.5	60.2	65.5	69.7	76.3
80°	33.1	33.5	34.9	35.5	37.7	39.4	41.6	46.1	51.4	53.2	57.7
82.5°	24.9	25.3	26.4	27.1	28.1	29.6	32.2	33.5	37.6	39.9	42.8
85°	13.8	13.4	14.4	14.4	15.2	15.8	16.6	18.3	19.3	22.1	22.9
87.5°	7.1	6.9	7.0	6.7	6.5	6.8	6.8	6.8	7.0	7.5	8.3
90°	14.2	13.5	12.3	11.1	9.9	8.7	7.3	5.7	4.0	2.4	0.7
92.5°	16.0	15.6	15.1	14.4	13.9	13.3	13.0	13.2	13.3	13.5	13.6
95°	27.1	26.3	25.3	24.2	23.2	22.1	24.0	29.0	33.9	38.9	43.8
97.5°	35.8	35.2	32.8	30.3	27.9	25.4	31.2	45.1	59.1	73.0	87.0
100°	39.6	38.5	35.9	33.4	30.8	28.3	37.2	57.8	78.3	98.8	119.3
102.5°	41.1	39.5	60.8	82.1	103.4	124.7	137.5	141.9	146.3	150.6	155.0
105°	42.8	41.1	82.0	122.9	163.8	204.7	222.9	218.5	214.0	209.4	205.0
107.5°	55.9	57.6	106.6	155.7	204.7	253.8	276.5	272.9	269.3	265.6	262.0
110°	103.0	118.0	161.3	204.6	247.9	291.2	311.2	308.1	305.0	301.8	298.7



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	243.0	297.6	308.3	319.0	329.7	340.4	344.3	341.6	338.7	336.0	333.2
115°	346.7	416.0	412.3	408.5	404.7	401.1	397.8	395.3	392.8	390.2	387.7
117.5°	444.0	460.8	458.2	455.6	453.1	450.4	447.7	444.9	442.1	439.2	436.4
120°	496.0	494.2	491.5	488.8	486.2	483.4	481.0	478.7	476.5	474.2	471.9
122.5°	527.1	526.0	523.1	520.2	517.3	514.3	511.6	509.3	506.9	504.5	502.2
125°	570.8	569.8	566.8	564.0	561.2	558.4	555.9	554.0	552.0	550.1	548.2
127.5°	610.7	609.1	607.0	604.8	602.8	600.6	598.4	596.3	594.2	592.0	589.8
130°	636.1	634.4	632.8	631.1	629.5	627.8	625.8	623.4	621.0	618.7	616.2
132.5°	661.2	659.8	658.2	656.5	654.9	653.2	651.4	649.3	647.3	645.3	643.2
135°	696.6	695.1	693.8	692.4	691.1	689.8	687.9	685.5	683.1	680.7	678.3
137.5°	729.6	728.2	726.6	725.1	723.6	722.1	720.5	718.8	717.1	715.4	713.8
140°	751.1	749.8	748.1	746.5	744.8	743.2	741.7	740.6	739.3	738.1	737.0
142.5°	770.9	769.7	767.8	765.9	764.0	762.1	760.6	759.6	758.6	757.4	756.4
145°	798.7	797.6	795.0	792.5	789.9	787.4	786.3	786.4	786.6	786.6	786.8
147.5°	822.9	822.2	819.6	817.1	814.6	812.1	811.2	811.7	812.3	812.8	813.4
150°	837.6	836.7	834.3	831.9	829.5	827.2	826.4	827.6	828.6	829.6	830.7
152.5°	851.1	850.2	847.9	845.6	843.4	841.1	840.6	841.7	842.9	844.0	845.2
155°	869.3	868.4	866.6	864.8	863.0	861.2	861.0	862.3	863.7	865.1	866.4
157.5°	884.6	883.5	882.2	881.0	879.8	878.4	878.4	879.6	880.7	881.8	883.0
160°	893.6	892.7	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7
162.5°	901.8	900.8	900.0	899.2	898.4	897.7	897.7	898.6	899.6	900.4	901.4
165°	911.9	910.9	910.4	910.0	909.6	909.1	909.3	910.2	911.2	912.0	912.9
167.5°	920.4	919.4	919.0	918.5	918.1	917.7	917.9	918.9	919.7	920.7	921.5
170°	924.7	923.7	923.4	923.1	922.8	922.5	922.8	923.7	924.6	925.5	926.4
172.5°	928.0	926.9	926.6	926.3	926.0	925.8	926.0	926.9	927.8	928.7	929.6
175°	931.5	930.5	930.1	929.8	929.5	929.3	929.6	930.7	931.7	932.7	933.8
177.5°	932.1	931.2	931.1	931.0	930.9	930.8	931.1	932.0	932.8	933.7	934.5
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1018.9	1019.7	1025.4	1027.9	1033.0	1035.0	1037.2	1036.6	1036.6	1037.7	1045.7
5°	1021.1	1028.1	1038.7	1048.9	1058.8	1067.2	1072.8	1078.5	1080.5	1090.8	1099.9
7.5°	1017.5	1030.4	1047.8	1063.4	1082.0	1096.6	1108.7	1119.6	1127.1	1142.0	1157.2
10°	1012.7	1031.0	1050.7	1070.7	1096.5	1115.8	1135.5	1150.7	1155.6	1177.7	1190.4
12.5°	1003.1	1027.6	1052.6	1078.6	1103.7	1130.4	1152.1	1167.2	1184.6	1204.5	1227.9
15°	988.7	1016.9	1049.6	1083.1	1119.0	1151.3	1174.6	1201.0	1219.9	1241.8	1262.2
17.5°	968.1	1004.4	1045.9	1084.7	1126.1	1160.9	1193.0	1218.2	1231.6	1244.1	1247.2
20°	951.8	990.8	1039.7	1085.5	1127.0	1167.2	1198.8	1219.9	1223.5	1223.8	1205.1
22.5°	934.1	978.2	1029.4	1076.2	1125.9	1170.5	1195.1	1204.2	1190.2	1166.4	1130.3
25°	901.4	952.4	1011.9	1065.5	1119.6	1161.9	1170.4	1154.5	1105.6	1054.1	989.1
27.5°	866.1	923.4	987.2	1046.7	1104.5	1130.7	1112.4	1055.3	967.1	890.6	797.8
30°	840.2	904.6	967.2	1033.8	1087.2	1098.5	1056.7	972.5	869.8	754.3	661.8
32.5°	810.6	878.1	947.0	1015.8	1060.5	1049.5	980.3	876.8	756.3	642.8	555.3
35°	768.4	838.1	912.3	981.3	1009.8	962.3	858.8	724.1	600.9	494.9	434.7
37.5°	719.6	795.5	872.7	936.0	934.1	854.8	713.9	574.7	471.2	408.5	365.6
40°	684.9	761.7	845.1	898.6	875.7	772.6	619.8	488.5	412.8	362.9	331.6
42.5°	651.8	728.8	811.6	854.1	814.4	687.6	535.4	432.5	370.0	331.1	305.7
45°	595.2	676.5	753.3	776.8	705.7	566.0	432.9	358.4	316.8	287.9	270.3
47.5°	540.0	619.9	689.9	690.4	594.2	459.0	365.2	310.1	274.7	252.3	239.5
50°	506.1	582.2	640.9	631.8	522.7	408.3	326.6	279.1	249.6	232.3	219.0
52.5°	468.2	541.9	592.8	566.8	462.1	359.3	292.0	252.1	227.6	212.6	200.7
55°	412.8	478.3	514.3	474.9	377.0	298.8	246.8	215.4	197.1	184.5	174.3
57.5°	358.6	412.6	435.2	389.3	310.5	247.8	208.7	185.2	167.0	158.0	152.7
60°	324.5	370.6	386.4	335.8	269.9	216.8	184.8	163.0	149.6	143.6	138.4
62.5°	291.1	328.7	335.3	288.8	235.4	189.8	162.3	143.8	135.0	129.2	124.2
65°	241.5	268.5	265.4	228.1	186.2	150.6	130.5	119.3	112.6	104.5	95.8
67.5°	198.8	215.4	205.4	177.4	142.1	117.1	104.0	95.5	87.2	79.5	77.5
70°	171.7	181.3	170.7	145.1	116.5	98.2	87.7	77.5	72.5	70.8	67.6
72.5°	145.9	149.2	137.8	115.7	94.8	81.3	71.1	65.3	62.7	61.2	59.1
75°	109.4	107.0	97.2	79.9	65.8	56.6	53.5	51.4	49.7	48.3	47.1
77.5°	76.9	73.2	64.5	53.3	45.8	41.5	39.6	38.5	37.6	36.9	35.8
80°	57.7	55.2	46.5	38.0	34.9	32.7	31.7	30.3	30.3	29.6	28.5
82.5°	42.2	39.5	31.9	27.9	26.1	24.9	24.0	23.2	22.9	23.1	22.3
85°	22.1	17.9	15.8	15.2	14.0	13.4	13.8	13.0	13.0	13.0	12.6
87.5°	7.3	6.1	6.2	6.2	6.8	7.1	7.0	7.3	7.7	7.6	8.1
90°	2.4	4.0	5.7	7.3	8.7	9.9	11.1	12.3	13.5	14.2	15.0
92.5°	13.5	13.3	13.2	13.0	13.3	13.9	14.4	15.1	15.6	16.0	16.4
95°	38.9	33.9	29.0	24.0	22.1	23.2	24.2	25.3	26.3	27.1	27.8
97.5°	73.0	59.1	45.1	31.2	25.4	27.9	30.3	32.8	35.2	35.8	36.4
100°	98.8	78.3	57.8	37.2	28.3	30.8	33.4	35.9	38.5	39.6	40.8
102.5°	150.6	146.3	141.9	137.5	124.7	103.4	82.1	60.8	39.5	41.1	42.6
105°	209.4	214.0	218.5	222.9	204.7	163.8	122.9	82.0	41.1	42.8	44.4
107.5°	265.6	269.3	272.9	276.5	253.8	204.7	155.7	106.6	57.6	55.9	54.2
110°	301.8	305.0	308.1	311.2	291.2	247.9	204.6	161.3	118.0	103.0	88.0



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.0	338.7	341.6	344.3	340.4	329.7	319.0	308.3	297.6	243.0	188.3
115°	390.2	392.8	395.3	397.8	401.1	404.7	408.5	412.3	416.0	346.7	277.3
117.5°	439.2	442.1	444.9	447.7	450.4	453.1	455.6	458.2	460.8	444.0	427.3
120°	474.2	476.5	478.7	481.0	483.4	486.2	488.8	491.5	494.2	496.0	497.9
122.5°	504.5	506.9	509.3	511.6	514.3	517.3	520.2	523.1	526.0	527.1	528.2
125°	550.1	552.0	554.0	555.9	558.4	561.2	564.0	566.8	569.8	570.8	571.8
127.5°	592.0	594.2	596.3	598.4	600.6	602.8	604.8	607.0	609.1	610.7	612.2
130°	618.7	621.0	623.4	625.8	627.8	629.5	631.1	632.8	634.4	636.1	637.7
132.5°	645.3	647.3	649.3	651.4	653.2	654.9	656.5	658.2	659.8	661.2	662.6
135°	680.7	683.1	685.5	687.9	689.8	691.1	692.4	693.8	695.1	696.6	698.1
137.5°	715.4	717.1	718.8	720.5	722.1	723.6	725.1	726.6	728.2	729.6	731.1
140°	738.1	739.3	740.6	741.7	743.2	744.8	746.5	748.1	749.8	751.1	752.4
142.5°	757.4	758.6	759.6	760.6	762.1	764.0	765.9	767.8	769.7	770.9	772.1
145°	786.6	786.6	786.4	786.3	787.4	789.9	792.5	795.0	797.6	798.7	799.7
147.5°	812.8	812.3	811.7	811.2	812.1	814.6	817.1	819.6	822.2	822.9	823.7
150°	829.6	828.6	827.6	826.4	827.2	829.5	831.9	834.3	836.7	837.6	838.5
152.5°	844.0	842.9	841.7	840.6	841.1	843.4	845.6	847.9	850.2	851.1	852.0
155°	865.1	863.7	862.3	861.0	861.2	863.0	864.8	866.6	868.4	869.3	870.2
157.5°	881.8	880.7	879.6	878.4	878.4	879.8	881.0	882.2	883.5	884.6	885.5
160°	891.7	890.9	889.9	889.1	889.1	889.9	890.9	891.7	892.7	893.6	894.5
162.5°	900.4	899.6	898.6	897.7	897.7	898.4	899.2	900.0	900.8	901.8	902.8
165°	912.0	911.2	910.2	909.3	909.1	909.6	910.0	910.4	910.9	911.9	912.9
167.5°	920.7	919.7	918.9	917.9	917.7	918.1	918.5	919.0	919.4	920.4	921.5
170°	925.5	924.6	923.7	922.8	922.5	922.8	923.1	923.4	923.7	924.7	925.8
172.5°	928.7	927.8	926.9	926.0	925.8	926.0	926.3	926.6	926.9	928.0	929.1
175°	932.7	931.7	930.7	929.6	929.3	929.5	929.8	930.1	930.5	931.5	932.6
177.5°	933.7	932.8	932.0	931.1	930.8	930.9	931.0	931.1	931.2	932.1	932.9
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8	931.8



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0	1013.0
2.5°	1048.5	1052.2	1053.9	1053.9	1055.8	1055.0	1054.1
5°	1108.7	1115.4	1116.8	1123.1	1127.8	1126.3	1127.0
7.5°	1168.7	1179.4	1190.1	1194.9	1195.7	1198.5	1199.6
10°	1205.5	1214.4	1230.9	1228.4	1240.8	1247.7	1236.1
12.5°	1241.0	1252.9	1264.4	1267.5	1274.5	1276.8	1272.1
15°	1273.1	1279.4	1280.2	1278.4	1280.5	1278.7	1272.1
17.5°	1243.1	1232.8	1212.0	1202.1	1194.3	1182.8	1178.2
20°	1193.5	1163.3	1128.1	1114.0	1097.5	1065.1	1072.8
22.5°	1086.6	1052.1	1016.9	975.7	956.1	925.4	923.6
25°	920.1	860.6	795.1	749.3	722.6	692.0	678.6
27.5°	715.4	640.5	586.8	559.7	534.9	510.7	509.6
30°	580.8	524.4	483.0	459.7	444.6	434.3	436.5
32.5°	489.6	450.9	422.9	403.7	392.5	384.7	384.7
35°	400.2	373.8	355.8	347.8	339.7	334.0	334.4
37.5°	342.5	326.6	316.6	307.7	302.7	299.9	298.3
40°	312.9	299.9	292.2	286.9	282.7	278.8	278.1
42.5°	289.5	278.8	271.0	266.8	263.0	260.1	259.5
45°	256.9	248.2	241.1	236.5	234.8	232.3	232.3
47.5°	228.6	219.9	214.4	211.5	208.5	206.9	206.8
50°	209.4	202.7	197.8	196.0	193.6	192.6	192.2
52.5°	192.3	187.3	183.7	182.6	181.4	180.1	180.3
55°	168.9	166.2	164.8	163.6	161.9	159.8	161.2
57.5°	149.3	146.9	143.1	139.8	138.2	136.7	137.2
60°	135.5	130.5	125.6	121.8	120.7	117.5	117.5
62.5°	118.1	111.1	105.1	102.9	101.9	100.4	100.1
65°	90.8	88.0	86.6	85.2	84.5	84.5	83.8
67.5°	75.2	74.1	72.6	72.2	71.5	71.4	71.1
70°	66.5	65.1	64.4	64.1	63.3	63.7	62.7
72.5°	58.1	56.9	56.8	55.9	55.5	55.5	54.8
75°	45.7	45.7	45.4	45.1	44.4	44.0	44.4
77.5°	35.2	35.3	34.6	34.6	34.5	34.6	34.2
80°	28.2	28.5	28.2	27.8	27.4	27.8	27.4
82.5°	22.2	21.8	21.7	21.6	21.6	21.3	21.3
85°	12.6	13.0	12.6	12.3	12.3	12.3	12.6
87.5°	7.9	8.1	8.2	8.3	8.3	8.4	8.1
90°	15.7	16.5	17.0	17.3	17.6	17.9	18.2
92.5°	16.8	17.2	17.5	17.6	17.8	18.0	18.2
95°	28.6	29.3	29.6	29.4	29.3	29.1	29.0
97.5°	36.9	37.6	38.0	38.2	38.4	38.5	38.7
100°	42.0	43.3	44.0	44.3	44.6	44.9	45.1
102.5°	44.2	45.7	46.8	47.1	47.6	48.0	48.4
105°	46.1	47.7	48.8	49.5	50.0	50.6	51.3
107.5°	52.5	50.9	50.3	50.9	51.6	52.1	52.7
110°	73.0	58.1	50.9	51.5	52.0	52.7	53.3



TEST NUMBER: P331657-830

CATALOG NUMBER: SA2XXRDIP-C485D725U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	133.7	79.0	51.8	52.4	52.9	53.3	53.8
115°	207.9	138.6	98.4	87.7	76.8	66.1	55.3
117.5°	410.4	393.6	367.5	332.1	296.6	261.2	225.7
120°	499.6	501.4	492.2	471.9	451.8	431.5	411.3
122.5°	529.2	530.4	529.0	525.0	521.0	517.2	513.2
125°	572.9	573.9	574.7	575.1	575.6	576.0	576.5
127.5°	613.7	615.2	616.0	616.1	616.2	616.3	616.4
130°	639.4	641.0	641.8	641.7	641.5	641.3	641.2
132.5°	664.0	665.4	666.1	665.9	665.8	665.6	665.4
135°	699.6	701.2	701.7	701.4	701.2	700.8	700.5
137.5°	732.5	734.1	734.5	734.1	733.5	733.0	732.4
140°	753.8	755.2	755.4	754.7	753.9	753.2	752.4
142.5°	773.4	774.6	774.9	774.1	773.4	772.6	771.8
145°	800.8	801.8	801.9	801.3	800.5	799.7	799.0
147.5°	824.5	825.3	825.4	824.7	824.1	823.5	822.8
150°	839.4	840.3	840.4	839.6	838.9	838.1	837.4
152.5°	852.9	853.8	853.8	852.8	851.8	850.8	849.8
155°	871.1	872.0	871.9	870.6	869.5	868.3	867.0
157.5°	886.6	887.6	887.5	886.4	885.1	884.0	882.9
160°	895.4	896.3	896.2	895.1	894.1	893.1	892.0
162.5°	903.8	904.8	904.7	903.4	902.1	900.9	899.6
165°	914.1	915.1	915.1	914.1	912.9	911.9	910.9
167.5°	922.6	923.6	923.4	922.1	920.8	919.4	918.0
170°	926.8	927.9	927.7	926.4	925.0	923.7	922.4
172.5°	930.1	931.1	930.9	929.6	928.3	926.9	925.6
175°	933.6	934.6	934.4	932.9	931.4	929.9	928.4
177.5°	933.8	934.6	934.5	933.4	932.4	931.2	930.2
180°	931.8	931.8	931.8	931.8	931.8	931.8	931.8

(END OF REPORT)