

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331323-935

Luminaire Tested: **SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331323-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5469.8 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331323-935
CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	35	29				
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	1.5
10°-20°	231.6	4.2
20°-30°	336.2	6.1
30°-40°	354.8	6.5
40°-50°	314.1	5.7
50°-60°	250.7	4.6
60°-70°	170.4	3.1
70°-80°	87.4	1.6
80°-90°	25.7	0.5
90°-100°	208.0	3.8
100°-110°	705.7	12.9
110°-120°	749.7	13.7
120°-130°	617.2	11.3
130°-140°	495.6	9.1
140°-150°	374.5	6.8
150°-160°	263.2	4.8
160°-170°	154.9	2.8
170°-180°	50.4	0.9
0°-30°	647.5	11.8
0°-40°	1002.3	18.3
0°-60°	1567.1	28.6
0°-90°	1850.5	33.8
90°-120°	1663.4	30.4
90°-150°	3150.7	57.6
90°-180°	3619.0	66.2
0°-180°	5469.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	33	1	33	1	33	18
95°	114	35	114	35	114	148
105°	1127	122	1127	122	1127	1091
115°	1483	215	1483	215	1483	1453
125°	1203	300	1203	300	1203	1087
135°	997	352	997	352	997	775
145°	796	402	796	402	796	506
155°	669	457	669	457	669	312
165°	587	498	587	498	587	168
175°	529	519	529	519	529	51
180°	520	520	520	520	520	



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	13.3	13.3	13.5	13.3	13.3	13.3	12.9	13.1	13.5	14.0	14.0
90°	33.0	33.0	33.0	33.0	33.0	32.0	30.0	32.0	33.0	34.0	33.0
92.5°	55.4	57.0	56.2	59.4	60.2	66.4	74.8	87.2	109.9	130.0	128.2
95°	114.0	113.0	116.1	124.0	137.0	159.0	201.0	262.1	343.1	392.1	347.1
97.5°	224.5	232.8	247.5	272.1	319.9	392.1	500.3	611.5	702.1	669.3	504.1
100°	358.1	376.1	405.1	448.1	531.1	652.1	789.2	913.2	934.2	790.1	544.1
102.5°	630.2	654.5	690.8	764.1	854.4	982.6	1082.8	1110.9	1020.6	794.2	528.9
105°	1127.2	1141.3	1184.2	1246.2	1308.3	1341.3	1328.3	1215.2	1007.2	741.1	499.1
107.5°	1439.9	1458.4	1467.1	1470.5	1462.7	1414.3	1310.3	1140.1	919.4	684.3	484.3
110°	1534.3	1535.3	1526.3	1507.3	1464.3	1382.2	1254.2	1075.2	864.2	657.1	481.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1532.7	1527.3	1510.3	1478.5	1418.7	1324.6	1187.8	1016.0	825.8	639.6	481.9
115°	1483.3	1474.3	1448.3	1402.3	1331.3	1228.2	1097.3	943.2	778.2	620.1	486.1
117.5°	1395.1	1387.5	1360.0	1311.5	1239.1	1142.5	1023.6	888.4	748.1	610.7	493.3
120°	1338.3	1328.3	1299.2	1252.2	1182.2	1091.2	985.2	861.2	732.1	605.1	498.1
122.5°	1279.0	1270.7	1244.8	1198.6	1135.8	1053.6	953.2	839.6	718.5	601.9	503.7
125°	1203.2	1195.2	1170.3	1132.2	1074.2	999.2	911.2	808.1	699.1	596.2	512.1
127.5°	1136.9	1130.4	1108.8	1073.2	1022.6	953.4	870.4	777.1	681.1	592.7	520.7
130°	1099.2	1091.2	1071.3	1037.2	988.2	922.2	843.2	757.2	669.2	591.1	527.1
132.5°	1060.0	1052.8	1034.4	1000.4	952.2	890.2	817.6	738.0	659.5	590.3	533.5
135°	997.2	993.2	975.2	942.2	899.1	843.2	777.1	711.1	646.1	589.1	541.1
137.5°	935.6	929.6	913.8	885.4	846.2	797.4	744.9	689.7	636.7	588.9	547.9
140°	893.2	887.2	872.2	846.2	814.2	770.2	724.2	676.1	631.1	588.1	551.1
142.5°	850.8	849.5	836.2	812.5	782.1	745.4	705.8	665.0	625.5	588.1	553.5
145°	796.2	793.2	783.2	766.1	742.2	713.2	682.2	649.1	618.1	586.1	556.1
147.5°	750.4	748.6	741.8	728.1	708.3	687.2	663.0	637.0	610.5	582.6	556.9
150°	723.2	722.1	716.2	704.1	689.1	671.1	650.1	628.1	604.1	580.1	556.1
152.5°	699.9	699.7	695.3	684.9	673.1	657.5	639.7	619.3	598.5	576.1	554.5
155°	669.2	671.1	667.1	660.1	649.1	638.1	623.1	607.1	588.1	569.1	552.1
157.5°	642.9	642.9	641.1	635.3	627.5	618.9	606.3	592.9	578.3	561.9	547.5
160°	626.1	626.1	625.1	620.1	613.1	606.1	595.1	584.1	571.1	557.2	545.1
162.5°	610.1	610.9	609.9	606.5	599.5	594.1	584.7	575.3	564.7	553.1	542.7
165°	587.1	588.1	588.1	584.1	580.1	576.1	569.1	562.1	554.1	545.1	538.1
167.5°	565.9	567.1	567.3	565.1	563.4	559.7	554.9	549.5	543.7	538.1	533.5
170°	553.1	555.1	556.1	553.1	552.1	550.1	546.1	543.1	538.1	534.1	531.1
172.5°	542.7	543.9	544.9	543.5	542.5	541.3	538.1	535.9	532.5	529.3	527.9
175°	529.1	531.1	532.1	531.1	531.1	530.1	529.1	528.1	525.1	524.1	523.1
177.5°	520.9	522.5	523.3	523.3	523.3	523.3	522.5	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	13.1	11.7	10.7	10.6	9.5	9.0	7.2	5.9	6.2	6.7	6.6
90°	27.0	20.0	15.0	12.0	10.0	8.0	4.0	1.0	4.0	8.0	10.0
92.5°	99.8	68.0	45.4	36.0	29.2	24.8	17.6	12.2	17.6	24.8	29.2
95°	231.0	144.0	98.0	74.0	58.0	49.0	39.0	35.0	39.0	49.0	58.0
97.5°	311.3	190.0	132.2	105.0	86.6	73.0	62.4	57.0	62.4	73.0	86.6
100°	328.0	206.0	153.0	125.0	105.0	89.0	80.0	77.0	80.0	89.0	105.0
102.5°	328.9	220.4	171.4	143.4	122.6	106.6	97.6	95.4	97.6	106.6	122.6
105°	334.1	245.0	198.0	170.0	148.0	133.0	126.1	122.0	126.1	133.0	148.0
107.5°	347.8	270.3	224.6	196.5	174.6	160.8	154.0	150.8	154.0	160.8	174.6
110°	359.0	287.1	243.1	214.0	193.0	180.0	174.0	170.0	174.0	180.0	193.0



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	371.1	303.1	260.6	230.8	210.6	198.5	191.7	187.6	191.7	198.5	210.6
115°	389.1	328.0	285.1	258.0	238.1	226.0	220.1	215.1	220.1	226.0	238.1
117.5°	408.3	351.0	311.3	283.3	264.1	253.5	247.5	243.5	247.5	253.5	264.1
120°	421.1	367.0	328.0	300.1	280.1	271.0	265.0	261.1	265.0	271.0	280.1
122.5°	432.3	382.3	345.7	316.8	296.9	287.1	281.0	277.8	281.0	287.1	296.9
125°	450.1	405.1	369.1	341.0	321.1	309.1	303.1	300.1	303.1	309.1	321.1
127.5°	466.7	426.3	391.2	362.5	343.3	330.1	321.7	317.6	321.7	330.1	343.3
130°	477.1	439.1	404.1	376.1	356.1	342.1	332.1	328.0	332.1	342.1	356.1
132.5°	487.5	450.3	416.9	388.9	368.1	353.3	342.5	337.7	342.5	353.3	368.1
135°	501.1	466.1	434.1	406.0	383.1	368.1	356.1	352.1	356.1	368.1	383.1
137.5°	511.5	478.9	447.3	421.3	398.5	382.5	370.5	365.7	370.5	382.5	398.5
140°	517.1	486.1	456.1	430.1	408.1	392.1	380.0	376.1	380.0	392.1	408.1
142.5°	521.9	491.7	462.5	438.1	416.9	400.9	389.7	386.5	389.7	400.9	416.9
145°	528.1	500.1	473.1	451.1	431.1	416.1	406.0	402.1	406.0	416.1	431.1
147.5°	531.5	506.9	481.5	461.9	445.3	431.4	421.9	418.9	421.9	431.4	445.3
150°	533.1	510.1	487.1	469.1	454.1	441.1	433.1	430.1	433.1	441.1	454.1
152.5°	533.9	513.3	492.7	476.3	462.1	450.6	442.7	441.3	442.7	450.6	462.1
155°	535.1	518.1	501.1	486.1	475.1	464.1	458.1	457.1	458.1	464.1	475.1
157.5°	535.1	521.5	507.1	494.5	485.7	476.1	471.3	470.3	471.3	476.1	485.7
160°	535.1	523.1	511.1	500.1	492.1	484.1	480.1	479.1	480.1	484.1	492.1
162.5°	534.3	523.9	513.5	504.9	497.7	491.3	487.3	487.9	487.3	491.3	497.7
165°	532.1	525.1	516.1	510.1	505.1	499.1	497.1	498.1	497.1	499.1	505.1
167.5°	530.7	524.9	518.3	514.5	510.9	507.1	505.3	506.5	505.3	507.1	510.9
170°	529.1	524.1	519.1	516.1	514.1	511.1	510.1	512.1	510.1	511.1	514.1
172.5°	526.7	523.3	519.9	517.7	516.5	513.5	514.1	515.3	514.1	513.5	516.5
175°	524.1	522.1	520.1	519.1	519.1	517.1	518.1	519.1	518.1	517.1	519.1
177.5°	522.5	520.9	520.1	520.1	520.1	518.5	519.3	520.9	519.3	518.5	520.1
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	6.8	7.1	7.8	9.3	10.2	10.2	9.7	9.5	9.1	9.0	9.2
90°	12.0	15.0	20.0	27.0	33.0	34.0	33.0	32.0	30.0	32.0	33.0
92.5°	36.0	45.4	68.0	99.8	128.2	130.0	109.9	87.2	74.8	66.4	60.2
95°	74.0	98.0	144.0	231.0	347.1	392.1	343.1	262.1	201.0	159.0	137.0
97.5°	105.0	132.2	190.0	311.3	504.1	669.3	702.1	611.5	500.3	392.1	319.9
100°	125.0	153.0	206.0	328.0	544.1	790.1	934.2	913.2	789.2	652.1	531.1
102.5°	143.4	171.4	220.4	328.9	528.9	794.2	1020.6	1110.9	1082.8	982.6	854.4
105°	170.0	198.0	245.0	334.1	499.1	741.1	1007.2	1215.2	1328.3	1341.3	1308.3
107.5°	196.5	224.6	270.3	347.8	484.3	684.3	919.4	1140.1	1310.3	1414.3	1462.7
110°	214.0	243.1	287.1	359.0	481.1	657.1	864.2	1075.2	1254.2	1382.2	1464.3



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.8	260.6	303.1	371.1	481.9	639.6	825.8	1016.0	1187.8	1324.6	1418.7
115°	258.0	285.1	328.0	389.1	486.1	620.1	778.2	943.2	1097.3	1228.2	1331.3
117.5°	283.3	311.3	351.0	408.3	493.3	610.7	748.1	888.4	1023.6	1142.5	1239.1
120°	300.1	328.0	367.0	421.1	498.1	605.1	732.1	861.2	985.2	1091.2	1182.2
122.5°	316.8	345.7	382.3	432.3	503.7	601.9	718.5	839.6	953.2	1053.6	1135.8
125°	341.0	369.1	405.1	450.1	512.1	596.2	699.1	808.1	911.2	999.2	1074.2
127.5°	362.5	391.2	426.3	466.7	520.7	592.7	681.1	777.1	870.4	953.4	1022.6
130°	376.1	404.1	439.1	477.1	527.1	591.1	669.2	757.2	843.2	922.2	988.2
132.5°	388.9	416.9	450.3	487.5	533.5	590.3	659.5	738.0	817.6	890.2	952.2
135°	406.0	434.1	466.1	501.1	541.1	589.1	646.1	711.1	777.1	843.2	899.1
137.5°	421.3	447.3	478.9	511.5	547.9	588.9	636.7	689.7	744.9	797.4	846.2
140°	430.1	456.1	486.1	517.1	551.1	588.1	631.1	676.1	724.2	770.2	814.2
142.5°	438.1	462.5	491.7	521.9	553.5	588.1	625.5	665.0	705.8	745.4	782.1
145°	451.1	473.1	500.1	528.1	556.1	586.1	618.1	649.1	682.2	713.2	742.2
147.5°	461.9	481.5	506.9	531.5	556.9	582.6	610.5	637.0	663.0	687.2	708.3
150°	469.1	487.1	510.1	533.1	556.1	580.1	604.1	628.1	650.1	671.1	689.1
152.5°	476.3	492.7	513.3	533.9	554.5	576.1	598.5	619.3	639.7	657.5	673.1
155°	486.1	501.1	518.1	535.1	552.1	569.1	588.1	607.1	623.1	638.1	649.1
157.5°	494.5	507.1	521.5	535.1	547.5	561.9	578.3	592.9	606.3	618.9	627.5
160°	500.1	511.1	523.1	535.1	545.1	557.2	571.1	584.1	595.1	606.1	613.1
162.5°	504.9	513.5	523.9	534.3	542.7	553.1	564.7	575.3	584.7	594.1	599.5
165°	510.1	516.1	525.1	532.1	538.1	545.1	554.1	562.1	569.1	576.1	580.1
167.5°	514.5	518.3	524.9	530.7	533.5	538.1	543.7	549.5	554.9	559.7	563.4
170°	516.1	519.1	524.1	529.1	531.1	534.1	538.1	543.1	546.1	550.1	552.1
172.5°	517.7	519.9	523.3	526.7	527.9	529.3	532.5	535.9	538.1	541.3	542.5
175°	519.1	520.1	522.1	524.1	523.1	524.1	525.1	528.1	529.1	530.1	531.1
177.5°	520.1	520.1	520.9	522.5	520.9	520.1	520.9	522.5	522.5	523.3	523.3
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	9.2	9.0	9.0	8.7	9.0	9.0	9.2	9.2	9.0	9.1	9.5
90°	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	32.0	30.0	32.0
92.5°	59.4	56.2	57.0	55.4	57.0	56.2	59.4	60.2	66.4	74.8	87.2
95°	124.0	116.1	113.0	114.0	113.0	116.1	124.0	137.0	159.0	201.0	262.1
97.5°	272.1	247.5	232.8	224.5	232.8	247.5	272.1	319.9	392.1	500.3	611.5
100°	448.1	405.1	376.1	358.1	376.1	405.1	448.1	531.1	652.1	789.2	913.2
102.5°	764.1	690.8	654.5	630.2	654.5	690.8	764.1	854.4	982.6	1082.8	1110.9
105°	1246.2	1184.2	1141.3	1127.2	1141.3	1184.2	1246.2	1308.3	1341.3	1328.3	1215.2
107.5°	1470.5	1467.1	1458.4	1439.9	1458.4	1467.1	1470.5	1462.7	1414.3	1310.3	1140.1
110°	1507.3	1526.3	1535.3	1534.3	1535.3	1526.3	1507.3	1464.3	1382.2	1254.2	1075.2



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1478.5	1510.3	1527.3	1532.7	1527.3	1510.3	1478.5	1418.7	1324.6	1187.8	1016.0
115°	1402.3	1448.3	1474.3	1483.3	1474.3	1448.3	1402.3	1331.3	1228.2	1097.3	943.2
117.5°	1311.5	1360.0	1387.5	1395.1	1387.5	1360.0	1311.5	1239.1	1142.5	1023.6	888.4
120°	1252.2	1299.2	1328.3	1338.3	1328.3	1299.2	1252.2	1182.2	1091.2	985.2	861.2
122.5°	1198.6	1244.8	1270.7	1279.0	1270.7	1244.8	1198.6	1135.8	1053.6	953.2	839.6
125°	1132.2	1170.3	1195.2	1203.2	1195.2	1170.3	1132.2	1074.2	999.2	911.2	808.1
127.5°	1073.2	1108.8	1130.4	1136.9	1130.4	1108.8	1073.2	1022.6	953.4	870.4	777.1
130°	1037.2	1071.3	1091.2	1099.2	1091.2	1071.3	1037.2	988.2	922.2	843.2	757.2
132.5°	1000.4	1034.4	1052.8	1060.0	1052.8	1034.4	1000.4	952.2	890.2	817.6	738.0
135°	942.2	975.2	993.2	997.2	993.2	975.2	942.2	899.1	843.2	777.1	711.1
137.5°	885.4	913.8	929.6	935.6	929.6	913.8	885.4	846.2	797.4	744.9	689.7
140°	846.2	872.2	887.2	893.2	887.2	872.2	846.2	814.2	770.2	724.2	676.1
142.5°	812.5	836.2	849.5	850.8	849.5	836.2	812.5	782.1	745.4	705.8	665.0
145°	766.1	783.2	793.2	796.2	793.2	783.2	766.1	742.2	713.2	682.2	649.1
147.5°	728.1	741.8	748.6	750.4	748.6	741.8	728.1	708.3	687.2	663.0	637.0
150°	704.1	716.2	722.1	723.2	722.1	716.2	704.1	689.1	671.1	650.1	628.1
152.5°	684.9	695.3	699.7	699.9	699.7	695.3	684.9	673.1	657.5	639.7	619.3
155°	660.1	667.1	671.1	669.2	671.1	667.1	660.1	649.1	638.1	623.1	607.1
157.5°	635.3	641.1	642.9	642.9	642.9	641.1	635.3	627.5	618.9	606.3	592.9
160°	620.1	625.1	626.1	626.1	626.1	625.1	620.1	613.1	606.1	595.1	584.1
162.5°	606.5	609.9	610.9	610.1	610.9	609.9	606.5	599.5	594.1	584.7	575.3
165°	584.1	588.1	588.1	587.1	588.1	588.1	584.1	580.1	576.1	569.1	562.1
167.5°	565.1	567.3	567.1	565.9	567.1	567.3	565.1	563.4	559.7	554.9	549.5
170°	553.1	556.1	555.1	553.1	555.1	556.1	553.1	552.1	550.1	546.1	543.1
172.5°	543.5	544.9	543.9	542.7	543.9	544.9	543.5	542.5	541.3	538.1	535.9
175°	531.1	532.1	531.1	529.1	531.1	532.1	531.1	531.1	530.1	529.1	528.1
177.5°	523.3	523.3	522.5	520.9	522.5	523.3	523.3	523.3	523.3	522.5	522.5
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	9.7	10.2	10.2	9.3	7.8	7.1	6.8	6.6	6.7	6.2	5.9
90°	33.0	34.0	33.0	27.0	20.0	15.0	12.0	10.0	8.0	4.0	1.0
92.5°	109.9	130.0	128.2	99.8	68.0	45.4	36.0	29.2	24.8	17.6	12.2
95°	343.1	392.1	347.1	231.0	144.0	98.0	74.0	58.0	49.0	39.0	35.0
97.5°	702.1	669.3	504.1	311.3	190.0	132.2	105.0	86.6	73.0	62.4	57.0
100°	934.2	790.1	544.1	328.0	206.0	153.0	125.0	105.0	89.0	80.0	77.0
102.5°	1020.6	794.2	528.9	328.9	220.4	171.4	143.4	122.6	106.6	97.6	95.4
105°	1007.2	741.1	499.1	334.1	245.0	198.0	170.0	148.0	133.0	126.1	122.0
107.5°	919.4	684.3	484.3	347.8	270.3	224.6	196.5	174.6	160.8	154.0	150.8
110°	864.2	657.1	481.1	359.0	287.1	243.1	214.0	193.0	180.0	174.0	170.0



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	825.8	639.6	481.9	371.1	303.1	260.6	230.8	210.6	198.5	191.7	187.6
115°	778.2	620.1	486.1	389.1	328.0	285.1	258.0	238.1	226.0	220.1	215.1
117.5°	748.1	610.7	493.3	408.3	351.0	311.3	283.3	264.1	253.5	247.5	243.5
120°	732.1	605.1	498.1	421.1	367.0	328.0	300.1	280.1	271.0	265.0	261.1
122.5°	718.5	601.9	503.7	432.3	382.3	345.7	316.8	296.9	287.1	281.0	277.8
125°	699.1	596.2	512.1	450.1	405.1	369.1	341.0	321.1	309.1	303.1	300.1
127.5°	681.1	592.7	520.7	466.7	426.3	391.2	362.5	343.3	330.1	321.7	317.6
130°	669.2	591.1	527.1	477.1	439.1	404.1	376.1	356.1	342.1	332.1	328.0
132.5°	659.5	590.3	533.5	487.5	450.3	416.9	388.9	368.1	353.3	342.5	337.7
135°	646.1	589.1	541.1	501.1	466.1	434.1	406.0	383.1	368.1	356.1	352.1
137.5°	636.7	588.9	547.9	511.5	478.9	447.3	421.3	398.5	382.5	370.5	365.7
140°	631.1	588.1	551.1	517.1	486.1	456.1	430.1	408.1	392.1	380.0	376.1
142.5°	625.5	588.1	553.5	521.9	491.7	462.5	438.1	416.9	400.9	389.7	386.5
145°	618.1	586.1	556.1	528.1	500.1	473.1	451.1	431.1	416.1	406.0	402.1
147.5°	610.5	582.6	556.9	531.5	506.9	481.5	461.9	445.3	431.4	421.9	418.9
150°	604.1	580.1	556.1	533.1	510.1	487.1	469.1	454.1	441.1	433.1	430.1
152.5°	598.5	576.1	554.5	533.9	513.3	492.7	476.3	462.1	450.6	442.7	441.3
155°	588.1	569.1	552.1	535.1	518.1	501.1	486.1	475.1	464.1	458.1	457.1
157.5°	578.3	561.9	547.5	535.1	521.5	507.1	494.5	485.7	476.1	471.3	470.3
160°	571.1	557.2	545.1	535.1	523.1	511.1	500.1	492.1	484.1	480.1	479.1
162.5°	564.7	553.1	542.7	534.3	523.9	513.5	504.9	497.7	491.3	487.3	487.9
165°	554.1	545.1	538.1	532.1	525.1	516.1	510.1	505.1	499.1	497.1	498.1
167.5°	543.7	538.1	533.5	530.7	524.9	518.3	514.5	510.9	507.1	505.3	506.5
170°	538.1	534.1	531.1	529.1	524.1	519.1	516.1	514.1	511.1	510.1	512.1
172.5°	532.5	529.3	527.9	526.7	523.3	519.9	517.7	516.5	513.5	514.1	515.3
175°	525.1	524.1	523.1	524.1	522.1	520.1	519.1	519.1	517.1	518.1	519.1
177.5°	520.9	520.1	520.9	522.5	520.9	520.1	520.1	520.1	518.5	519.3	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	7.2	9.0	9.5	10.6	10.7	11.7	13.1	14.0	14.0	13.5	13.1
90°	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0	32.0
92.5°	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9	87.2
95°	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1	262.1
97.5°	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1	611.5
100°	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2	913.2
102.5°	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6	1110.9
105°	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2	1215.2
107.5°	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4	1140.1
110°	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2	1075.2



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8	1016.0
115°	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2	943.2
117.5°	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1	888.4
120°	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1	861.2
122.5°	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5	839.6
125°	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1	808.1
127.5°	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1	777.1
130°	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2	757.2
132.5°	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5	738.0
135°	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1	711.1
137.5°	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7	689.7
140°	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1	676.1
142.5°	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5	665.0
145°	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1	649.1
147.5°	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5	637.0
150°	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1	628.1
152.5°	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5	619.3
155°	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1	607.1
157.5°	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3	592.9
160°	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1	584.1
162.5°	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7	575.3
165°	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1	562.1
167.5°	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7	549.5
170°	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1	543.1
172.5°	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5	535.9
175°	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1	528.1
177.5°	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9	522.5
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	12.9	13.3	13.3	13.3	13.5	13.3	13.3
90°	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3



TEST NUMBER: P331323-935

CATALOG NUMBER: SA2XXDIP-C485D1080U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)