

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331701-830

Luminaire Tested: **SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331701-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6360.2 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	96	92	88	85	87	83	80	78	68	66	64	54	52	51	40	40	39	33				
2	88	81	75	70	79	73	69	65	60	57	54	48	46	44	36	35	34	29				
3	80	71	65	59	73	65	59	55	54	49	46	43	40	38	33	31	29	25				
4	74	64	56	51	67	58	52	47	48	43	40	39	35	33	30	28	26	22				
5	68	57	49	44	62	52	46	41	43	38	35	35	31	29	27	25	23	20				
6	63	51	44	38	57	47	40	36	39	34	31	32	28	26	25	23	21	18				
7	58	46	39	34	53	43	36	32	36	31	27	29	26	23	23	20	19	16				
8	54	42	35	30	49	39	33	28	33	28	24	27	23	21	21	19	17	14				
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13				
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.1
10°-20°	365.7	5.8
20°-30°	471.3	7.4
30°-40°	447.9	7.0
40°-50°	383.7	6.0
50°-60°	292.2	4.6
60°-70°	184.7	2.9
70°-80°	92.2	1.5
80°-90°	29.1	0.5
90°-100°	227.7	3.6
100°-110°	772.5	12.1
110°-120°	820.7	12.9
120°-130°	675.6	10.6
130°-140°	542.5	8.5
140°-150°	410.0	6.4
150°-160°	288.1	4.5
160°-170°	169.6	2.7
170°-180°	55.2	0.9
0°-30°	968.3	15.2
0°-40°	1416.2	22.3
0°-60°	2092.1	32.9
0°-90°	2398.2	37.7
90°-120°	1820.9	28.6
90°-150°	3449.0	54.2
90°-180°	3962.0	62.3
0°-180°	6360.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	20
90°	36	1	36	1	36	20
95°	125	38	125	38	125	162
105°	1234	134	1234	134	1234	1194
115°	1624	235	1624	235	1624	1590
125°	1317	328	1317	328	1317	1190
135°	1092	385	1092	385	1092	848
145°	872	440	872	440	872	554
155°	732	500	732	500	732	342
165°	643	545	643	545	643	184
175°	579	568	579	568	579	56
180°	569	569	569	569	569	



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	13.4	13.8	13.8	13.8	13.8	13.6	13.1	13.9	13.8	14.3	13.8
90°	36.1	36.1	36.1	36.1	36.1	35.1	32.9	35.1	36.1	37.2	36.1
92.5°	60.7	62.4	61.5	65.0	65.9	72.7	81.9	95.5	120.3	142.3	140.3
95°	124.8	123.8	127.1	135.7	150.0	174.1	220.1	286.9	375.6	429.2	379.9
97.5°	245.7	254.9	270.9	297.8	350.2	429.2	547.7	669.4	768.6	732.7	551.9
100°	392.0	411.7	443.5	490.5	581.4	713.9	863.9	999.7	1022.7	865.0	595.6
102.5°	689.8	716.5	756.2	836.5	935.3	1075.6	1185.3	1216.1	1117.3	869.4	579.0
105°	1234.0	1249.3	1296.4	1364.2	1432.2	1468.3	1454.1	1330.3	1102.6	811.3	546.4
107.5°	1576.2	1596.6	1606.0	1609.8	1601.2	1548.2	1434.4	1248.0	1006.4	749.1	530.2
110°	1679.6	1680.7	1670.8	1650.0	1603.0	1513.2	1373.0	1177.0	946.0	719.3	526.7



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1677.8	1672.0	1653.3	1618.5	1553.0	1450.1	1300.3	1112.2	904.0	700.1	527.5
115°	1623.8	1613.9	1585.5	1535.1	1457.4	1344.5	1201.2	1032.6	851.9	678.8	532.2
117.5°	1527.2	1518.9	1488.8	1435.7	1356.4	1250.7	1120.6	972.5	819.0	668.5	540.0
120°	1465.0	1454.1	1422.3	1370.8	1294.2	1194.6	1078.5	942.7	801.4	662.4	545.3
122.5°	1400.1	1391.0	1362.7	1312.1	1243.4	1153.4	1043.5	919.1	786.6	658.9	551.4
125°	1317.2	1308.4	1281.1	1239.4	1175.9	1093.8	997.5	884.7	765.3	652.6	560.6
127.5°	1244.5	1237.5	1213.8	1174.9	1119.5	1043.7	952.8	850.7	745.6	648.8	570.0
130°	1203.3	1194.6	1172.7	1135.5	1081.8	1009.6	923.0	828.9	732.5	647.1	577.0
132.5°	1160.4	1152.5	1132.4	1095.1	1042.4	974.5	895.0	807.9	722.0	646.2	584.0
135°	1091.7	1087.2	1067.5	1031.4	984.3	923.0	850.7	778.4	707.3	644.9	592.4
137.5°	1024.2	1017.7	1000.3	969.2	926.3	872.9	815.5	755.1	697.0	644.7	599.8
140°	977.8	971.2	954.8	926.3	891.3	843.1	792.8	740.2	690.9	643.9	603.3
142.5°	931.3	930.0	915.4	889.5	856.2	816.0	772.6	727.9	684.8	643.9	606.0
145°	871.6	868.3	857.3	838.7	812.5	780.7	746.8	710.6	676.7	641.6	608.8
147.5°	821.4	819.4	812.0	797.1	775.4	752.2	725.8	697.3	668.4	637.7	609.6
150°	791.6	790.5	784.0	770.8	754.4	734.7	711.7	687.6	661.3	635.1	608.8
152.5°	766.2	766.0	761.2	749.8	736.9	719.8	700.3	678.0	655.2	630.7	607.0
155°	732.5	734.7	730.3	722.6	710.6	698.5	682.1	664.6	643.9	623.0	604.4
157.5°	703.8	703.8	701.8	695.5	686.9	677.5	663.7	649.0	633.1	615.1	599.4
160°	685.4	685.4	684.3	678.8	671.2	663.5	651.5	639.4	625.2	609.9	596.7
162.5°	667.9	668.7	667.7	663.9	656.3	650.4	640.1	629.8	618.2	605.5	594.1
165°	642.7	643.9	643.9	639.4	635.1	630.7	623.0	615.4	606.6	596.7	589.1
167.5°	619.5	620.9	621.0	618.6	616.7	612.7	607.5	601.5	595.2	589.1	584.0
170°	605.5	607.7	608.8	605.5	604.4	602.2	597.9	594.6	589.1	584.7	581.4
172.5°	594.1	595.4	596.5	595.0	593.9	592.6	589.1	586.6	583.0	579.5	577.9
175°	579.2	581.4	582.5	581.4	581.4	580.3	579.2	578.2	574.9	573.7	572.7
177.5°	570.2	572.0	572.9	572.9	572.9	572.9	572.0	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	12.4	11.3	10.2	9.1	9.1	9.0	10.1	11.4	10.5	10.2	9.9
90°	29.6	21.9	16.4	13.1	10.9	8.8	4.3	1.1	4.3	8.8	10.9
92.5°	109.2	74.5	49.7	39.4	32.0	27.1	19.2	13.4	19.2	27.1	32.0
95°	252.9	157.7	107.3	81.1	63.5	53.6	42.7	38.4	42.7	53.6	63.5
97.5°	340.7	208.0	144.8	115.0	94.8	79.9	68.3	62.4	68.3	79.9	94.8
100°	359.1	225.6	167.5	136.9	115.0	97.5	87.6	84.3	87.6	97.5	115.0
102.5°	360.1	241.3	187.7	157.0	134.2	116.7	106.9	104.4	106.9	116.7	134.2
105°	365.7	268.2	216.8	186.2	162.0	145.6	138.0	133.6	138.0	145.6	162.0
107.5°	380.8	295.9	245.9	215.1	191.1	176.1	168.6	165.1	168.6	176.1	191.1
110°	393.0	314.2	266.1	234.3	211.3	197.1	190.5	186.2	190.5	197.1	211.3



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	406.2	331.8	285.3	252.7	230.5	217.3	209.8	205.4	209.8	217.3	230.5
115°	425.9	359.1	312.1	282.5	260.6	247.4	240.9	235.4	240.9	247.4	260.6
117.5°	447.0	384.3	340.7	310.1	289.1	277.5	270.9	266.6	270.9	277.5	289.1
120°	461.0	401.8	359.1	328.5	306.6	296.7	290.1	285.8	290.1	296.7	306.6
122.5°	473.3	418.5	378.4	346.9	325.0	314.2	307.6	304.2	307.6	314.2	325.0
125°	492.8	443.5	404.1	373.3	351.5	338.4	331.8	328.5	331.8	338.4	351.5
127.5°	510.9	466.7	428.3	396.8	375.8	361.4	352.1	347.7	352.1	361.4	375.8
130°	522.3	480.7	442.3	411.7	389.8	374.5	363.5	359.1	363.5	374.5	389.8
132.5°	533.7	492.9	456.4	425.7	402.9	386.7	374.9	369.7	374.9	386.7	402.9
135°	548.6	510.2	475.2	444.5	419.3	402.9	389.8	385.4	389.8	402.9	419.3
137.5°	560.0	524.2	489.7	461.2	436.2	418.7	405.6	400.3	405.6	418.7	436.2
140°	566.1	532.2	499.3	470.8	446.8	429.2	416.0	411.7	416.0	429.2	446.8
142.5°	571.4	538.3	506.3	479.6	456.4	438.8	426.6	423.1	426.6	438.8	456.4
145°	578.2	547.4	517.9	493.8	471.9	455.5	444.5	440.2	444.5	455.5	471.9
147.5°	581.8	554.9	527.1	505.7	487.5	472.3	461.8	458.5	461.8	472.3	487.5
150°	583.6	558.5	533.2	513.5	497.1	482.9	474.1	470.8	474.1	482.9	497.1
152.5°	584.5	561.9	539.3	521.4	505.9	493.3	484.7	483.1	484.7	493.3	505.9
155°	585.8	567.1	548.6	532.2	520.1	508.0	501.4	500.4	501.4	508.0	520.1
157.5°	585.8	570.9	555.2	541.3	531.7	521.2	515.9	514.8	515.9	521.2	531.7
160°	585.8	572.7	559.5	547.4	538.7	529.9	525.6	524.4	525.6	529.9	538.7
162.5°	584.9	573.5	562.1	552.7	544.8	537.8	533.5	534.1	533.5	537.8	544.8
165°	582.5	574.9	565.0	558.5	552.9	546.4	544.2	545.3	544.2	546.4	552.9
167.5°	581.0	574.6	567.4	563.3	559.3	555.2	553.2	554.5	553.2	555.2	559.3
170°	579.2	573.7	568.3	565.0	562.8	559.5	558.5	560.6	558.5	559.5	562.8
172.5°	576.6	572.9	569.1	566.8	565.4	562.1	562.8	564.1	562.8	562.1	565.4
175°	573.7	571.6	569.4	568.3	568.3	566.1	567.1	568.3	567.1	566.1	568.3
177.5°	572.0	570.2	569.4	569.4	569.4	567.6	568.4	570.2	568.4	567.6	569.4
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	9.9	10.2	10.6	12.1	13.4	13.2	13.0	12.4	12.0	12.4	12.3
90°	13.1	16.4	21.9	29.6	36.1	37.2	36.1	35.1	32.9	35.1	36.1
92.5°	39.4	49.7	74.5	109.2	140.3	142.3	120.3	95.5	81.9	72.7	65.9
95°	81.1	107.3	157.7	252.9	379.9	429.2	375.6	286.9	220.1	174.1	150.0
97.5°	115.0	144.8	208.0	340.7	551.9	732.7	768.6	669.4	547.7	429.2	350.2
100°	136.9	167.5	225.6	359.1	595.6	865.0	1022.7	999.7	863.9	713.9	581.4
102.5°	157.0	187.7	241.3	360.1	579.0	869.4	1117.3	1216.1	1185.3	1075.6	935.3
105°	186.2	216.8	268.2	365.7	546.4	811.3	1102.6	1330.3	1454.1	1468.3	1432.2
107.5°	215.1	245.9	295.9	380.8	530.2	749.1	1006.4	1248.0	1434.4	1548.2	1601.2
110°	234.3	266.1	314.2	393.0	526.7	719.3	946.0	1177.0	1373.0	1513.2	1603.0



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	252.7	285.3	331.8	406.2	527.5	700.1	904.0	1112.2	1300.3	1450.1	1553.0
115°	282.5	312.1	359.1	425.9	532.2	678.8	851.9	1032.6	1201.2	1344.5	1457.4
117.5°	310.1	340.7	384.3	447.0	540.0	668.5	819.0	972.5	1120.6	1250.7	1356.4
120°	328.5	359.1	401.8	461.0	545.3	662.4	801.4	942.7	1078.5	1194.6	1294.2
122.5°	346.9	378.4	418.5	473.3	551.4	658.9	786.6	919.1	1043.5	1153.4	1243.4
125°	373.3	404.1	443.5	492.8	560.6	652.6	765.3	884.7	997.5	1093.8	1175.9
127.5°	396.8	428.3	466.7	510.9	570.0	648.8	745.6	850.7	952.8	1043.7	1119.5
130°	411.7	442.3	480.7	522.3	577.0	647.1	732.5	828.9	923.0	1009.6	1081.8
132.5°	425.7	456.4	492.9	533.7	584.0	646.2	722.0	807.9	895.0	974.5	1042.4
135°	444.5	475.2	510.2	548.6	592.4	644.9	707.3	778.4	850.7	923.0	984.3
137.5°	461.2	489.7	524.2	560.0	599.8	644.7	697.0	755.1	815.5	872.9	926.3
140°	470.8	499.3	532.2	566.1	603.3	643.9	690.9	740.2	792.8	843.1	891.3
142.5°	479.6	506.3	538.3	571.4	606.0	643.9	684.8	727.9	772.6	816.0	856.2
145°	493.8	517.9	547.4	578.2	608.8	641.6	676.7	710.6	746.8	780.7	812.5
147.5°	505.7	527.1	554.9	581.8	609.6	637.7	668.4	697.3	725.8	752.2	775.4
150°	513.5	533.2	558.5	583.6	608.8	635.1	661.3	687.6	711.7	734.7	754.4
152.5°	521.4	539.3	561.9	584.5	607.0	630.7	655.2	678.0	700.3	719.8	736.9
155°	532.2	548.6	567.1	585.8	604.4	623.0	643.9	664.6	682.1	698.5	710.6
157.5°	541.3	555.2	570.9	585.8	599.4	615.1	633.1	649.0	663.7	677.5	686.9
160°	547.4	559.5	572.7	585.8	596.7	609.9	625.2	639.4	651.5	663.5	671.2
162.5°	552.7	562.1	573.5	584.9	594.1	605.5	618.2	629.8	640.1	650.4	656.3
165°	558.5	565.0	574.9	582.5	589.1	596.7	606.6	615.4	623.0	630.7	635.1
167.5°	563.3	567.4	574.6	581.0	584.0	589.1	595.2	601.5	607.5	612.7	616.7
170°	565.0	568.3	573.7	579.2	581.4	584.7	589.1	594.6	597.9	602.2	604.4
172.5°	566.8	569.1	572.9	576.6	577.9	579.5	583.0	586.6	589.1	592.6	593.9
175°	568.3	569.4	571.6	573.7	572.7	573.7	574.9	578.2	579.2	580.3	581.4
177.5°	569.4	569.4	570.2	572.0	570.2	569.4	570.2	572.0	572.0	572.9	572.9
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	12.3	11.9	12.3	11.9	12.3	11.9	12.3	12.3	12.4	12.0	12.4
90°	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	35.1	32.9	35.1
92.5°	65.0	61.5	62.4	60.7	62.4	61.5	65.0	65.9	72.7	81.9	95.5
95°	135.7	127.1	123.8	124.8	123.8	127.1	135.7	150.0	174.1	220.1	286.9
97.5°	297.8	270.9	254.9	245.7	254.9	270.9	297.8	350.2	429.2	547.7	669.4
100°	490.5	443.5	411.7	392.0	411.7	443.5	490.5	581.4	713.9	863.9	999.7
102.5°	836.5	756.2	716.5	689.8	716.5	756.2	836.5	935.3	1075.6	1185.3	1216.1
105°	1364.2	1296.4	1249.3	1234.0	1249.3	1296.4	1364.2	1432.2	1468.3	1454.1	1330.3
107.5°	1609.8	1606.0	1596.6	1576.2	1596.6	1606.0	1609.8	1601.2	1548.2	1434.4	1248.0
110°	1650.0	1670.8	1680.7	1679.6	1680.7	1670.8	1650.0	1603.0	1513.2	1373.0	1177.0



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1618.5	1653.3	1672.0	1677.8	1672.0	1653.3	1618.5	1553.0	1450.1	1300.3	1112.2
115°	1535.1	1585.5	1613.9	1623.8	1613.9	1585.5	1535.1	1457.4	1344.5	1201.2	1032.6
117.5°	1435.7	1488.8	1518.9	1527.2	1518.9	1488.8	1435.7	1356.4	1250.7	1120.6	972.5
120°	1370.8	1422.3	1454.1	1465.0	1454.1	1422.3	1370.8	1294.2	1194.6	1078.5	942.7
122.5°	1312.1	1362.7	1391.0	1400.1	1391.0	1362.7	1312.1	1243.4	1153.4	1043.5	919.1
125°	1239.4	1281.1	1308.4	1317.2	1308.4	1281.1	1239.4	1175.9	1093.8	997.5	884.7
127.5°	1174.9	1213.8	1237.5	1244.5	1237.5	1213.8	1174.9	1119.5	1043.7	952.8	850.7
130°	1135.5	1172.7	1194.6	1203.3	1194.6	1172.7	1135.5	1081.8	1009.6	923.0	828.9
132.5°	1095.1	1132.4	1152.5	1160.4	1152.5	1132.4	1095.1	1042.4	974.5	895.0	807.9
135°	1031.4	1067.5	1087.2	1091.7	1087.2	1067.5	1031.4	984.3	923.0	850.7	778.4
137.5°	969.2	1000.3	1017.7	1024.2	1017.7	1000.3	969.2	926.3	872.9	815.5	755.1
140°	926.3	954.8	971.2	977.8	971.2	954.8	926.3	891.3	843.1	792.8	740.2
142.5°	889.5	915.4	930.0	931.3	930.0	915.4	889.5	856.2	816.0	772.6	727.9
145°	838.7	857.3	868.3	871.6	868.3	857.3	838.7	812.5	780.7	746.8	710.6
147.5°	797.1	812.0	819.4	821.4	819.4	812.0	797.1	775.4	752.2	725.8	697.3
150°	770.8	784.0	790.5	791.6	790.5	784.0	770.8	754.4	734.7	711.7	687.6
152.5°	749.8	761.2	766.0	766.2	766.0	761.2	749.8	736.9	719.8	700.3	678.0
155°	722.6	730.3	734.7	732.5	734.7	730.3	722.6	710.6	698.5	682.1	664.6
157.5°	695.5	701.8	703.8	703.8	703.8	701.8	695.5	686.9	677.5	663.7	649.0
160°	678.8	684.3	685.4	685.4	685.4	684.3	678.8	671.2	663.5	651.5	639.4
162.5°	663.9	667.7	668.7	667.9	668.7	667.7	663.9	656.3	650.4	640.1	629.8
165°	639.4	643.9	643.9	642.7	643.9	643.9	639.4	635.1	630.7	623.0	615.4
167.5°	618.6	621.0	620.9	619.5	620.9	621.0	618.6	616.7	612.7	607.5	601.5
170°	605.5	608.8	607.7	605.5	607.7	608.8	605.5	604.4	602.2	597.9	594.6
172.5°	595.0	596.5	595.4	594.1	595.4	596.5	595.0	593.9	592.6	589.1	586.6
175°	581.4	582.5	581.4	579.2	581.4	582.5	581.4	581.4	580.3	579.2	578.2
177.5°	572.9	572.9	572.0	570.2	572.0	572.9	572.9	572.9	572.9	572.0	572.0
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	13.0	13.2	13.4	12.1	10.6	10.2	9.9	9.9	10.2	10.5	11.4
90°	36.1	37.2	36.1	29.6	21.9	16.4	13.1	10.9	8.8	4.3	1.1
92.5°	120.3	142.3	140.3	109.2	74.5	49.7	39.4	32.0	27.1	19.2	13.4
95°	375.6	429.2	379.9	252.9	157.7	107.3	81.1	63.5	53.6	42.7	38.4
97.5°	768.6	732.7	551.9	340.7	208.0	144.8	115.0	94.8	79.9	68.3	62.4
100°	1022.7	865.0	595.6	359.1	225.6	167.5	136.9	115.0	97.5	87.6	84.3
102.5°	1117.3	869.4	579.0	360.1	241.3	187.7	157.0	134.2	116.7	106.9	104.4
105°	1102.6	811.3	546.4	365.7	268.2	216.8	186.2	162.0	145.6	138.0	133.6
107.5°	1006.4	749.1	530.2	380.8	295.9	245.9	215.1	191.1	176.1	168.6	165.1
110°	946.0	719.3	526.7	393.0	314.2	266.1	234.3	211.3	197.1	190.5	186.2



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	904.0	700.1	527.5	406.2	331.8	285.3	252.7	230.5	217.3	209.8	205.4
115°	851.9	678.8	532.2	425.9	359.1	312.1	282.5	260.6	247.4	240.9	235.4
117.5°	819.0	668.5	540.0	447.0	384.3	340.7	310.1	289.1	277.5	270.9	266.6
120°	801.4	662.4	545.3	461.0	401.8	359.1	328.5	306.6	296.7	290.1	285.8
122.5°	786.6	658.9	551.4	473.3	418.5	378.4	346.9	325.0	314.2	307.6	304.2
125°	765.3	652.6	560.6	492.8	443.5	404.1	373.3	351.5	338.4	331.8	328.5
127.5°	745.6	648.8	570.0	510.9	466.7	428.3	396.8	375.8	361.4	352.1	347.7
130°	732.5	647.1	577.0	522.3	480.7	442.3	411.7	389.8	374.5	363.5	359.1
132.5°	722.0	646.2	584.0	533.7	492.9	456.4	425.7	402.9	386.7	374.9	369.7
135°	707.3	644.9	592.4	548.6	510.2	475.2	444.5	419.3	402.9	389.8	385.4
137.5°	697.0	644.7	599.8	560.0	524.2	489.7	461.2	436.2	418.7	405.6	400.3
140°	690.9	643.9	603.3	566.1	532.2	499.3	470.8	446.8	429.2	416.0	411.7
142.5°	684.8	643.9	606.0	571.4	538.3	506.3	479.6	456.4	438.8	426.6	423.1
145°	676.7	641.6	608.8	578.2	547.4	517.9	493.8	471.9	455.5	444.5	440.2
147.5°	668.4	637.7	609.6	581.8	554.9	527.1	505.7	487.5	472.3	461.8	458.5
150°	661.3	635.1	608.8	583.6	558.5	533.2	513.5	497.1	482.9	474.1	470.8
152.5°	655.2	630.7	607.0	584.5	561.9	539.3	521.4	505.9	493.3	484.7	483.1
155°	643.9	623.0	604.4	585.8	567.1	548.6	532.2	520.1	508.0	501.4	500.4
157.5°	633.1	615.1	599.4	585.8	570.9	555.2	541.3	531.7	521.2	515.9	514.8
160°	625.2	609.9	596.7	585.8	572.7	559.5	547.4	538.7	529.9	525.6	524.4
162.5°	618.2	605.5	594.1	584.9	573.5	562.1	552.7	544.8	537.8	533.5	534.1
165°	606.6	596.7	589.1	582.5	574.9	565.0	558.5	552.9	546.4	544.2	545.3
167.5°	595.2	589.1	584.0	581.0	574.6	567.4	563.3	559.3	555.2	553.2	554.5
170°	589.1	584.7	581.4	579.2	573.7	568.3	565.0	562.8	559.5	558.5	560.6
172.5°	583.0	579.5	577.9	576.6	572.9	569.1	566.8	565.4	562.1	562.8	564.1
175°	574.9	573.7	572.7	573.7	571.6	569.4	568.3	568.3	566.1	567.1	568.3
177.5°	570.2	569.4	570.2	572.0	570.2	569.4	569.4	569.4	567.6	568.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	10.1	9.0	9.1	9.1	10.2	11.3	12.4	13.8	14.3	13.8	13.9
90°	4.3	8.8	10.9	13.1	16.4	21.9	29.6	36.1	37.2	36.1	35.1
92.5°	19.2	27.1	32.0	39.4	49.7	74.5	109.2	140.3	142.3	120.3	95.5
95°	42.7	53.6	63.5	81.1	107.3	157.7	252.9	379.9	429.2	375.6	286.9
97.5°	68.3	79.9	94.8	115.0	144.8	208.0	340.7	551.9	732.7	768.6	669.4
100°	87.6	97.5	115.0	136.9	167.5	225.6	359.1	595.6	865.0	1022.7	999.7
102.5°	106.9	116.7	134.2	157.0	187.7	241.3	360.1	579.0	869.4	1117.3	1216.1
105°	138.0	145.6	162.0	186.2	216.8	268.2	365.7	546.4	811.3	1102.6	1330.3
107.5°	168.6	176.1	191.1	215.1	245.9	295.9	380.8	530.2	749.1	1006.4	1248.0
110°	190.5	197.1	211.3	234.3	266.1	314.2	393.0	526.7	719.3	946.0	1177.0



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	209.8	217.3	230.5	252.7	285.3	331.8	406.2	527.5	700.1	904.0	1112.2
115°	240.9	247.4	260.6	282.5	312.1	359.1	425.9	532.2	678.8	851.9	1032.6
117.5°	270.9	277.5	289.1	310.1	340.7	384.3	447.0	540.0	668.5	819.0	972.5
120°	290.1	296.7	306.6	328.5	359.1	401.8	461.0	545.3	662.4	801.4	942.7
122.5°	307.6	314.2	325.0	346.9	378.4	418.5	473.3	551.4	658.9	786.6	919.1
125°	331.8	338.4	351.5	373.3	404.1	443.5	492.8	560.6	652.6	765.3	884.7
127.5°	352.1	361.4	375.8	396.8	428.3	466.7	510.9	570.0	648.8	745.6	850.7
130°	363.5	374.5	389.8	411.7	442.3	480.7	522.3	577.0	647.1	732.5	828.9
132.5°	374.9	386.7	402.9	425.7	456.4	492.9	533.7	584.0	646.2	722.0	807.9
135°	389.8	402.9	419.3	444.5	475.2	510.2	548.6	592.4	644.9	707.3	778.4
137.5°	405.6	418.7	436.2	461.2	489.7	524.2	560.0	599.8	644.7	697.0	755.1
140°	416.0	429.2	446.8	470.8	499.3	532.2	566.1	603.3	643.9	690.9	740.2
142.5°	426.6	438.8	456.4	479.6	506.3	538.3	571.4	606.0	643.9	684.8	727.9
145°	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	676.7	710.6
147.5°	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.4	697.3
150°	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3	687.6
152.5°	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2	678.0
155°	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9	664.6
157.5°	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1	649.0
160°	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2	639.4
162.5°	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2	629.8
165°	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6	615.4
167.5°	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2	601.5
170°	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1	594.6
172.5°	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0	586.6
175°	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9	578.2
177.5°	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2	572.0
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	13.1	13.6	13.8	13.8	13.8	13.8	13.4
90°	32.9	35.1	36.1	36.1	36.1	36.1	36.1
92.5°	81.9	72.7	65.9	65.0	61.5	62.4	60.7
95°	220.1	174.1	150.0	135.7	127.1	123.8	124.8
97.5°	547.7	429.2	350.2	297.8	270.9	254.9	245.7
100°	863.9	713.9	581.4	490.5	443.5	411.7	392.0
102.5°	1185.3	1075.6	935.3	836.5	756.2	716.5	689.8
105°	1454.1	1468.3	1432.2	1364.2	1296.4	1249.3	1234.0
107.5°	1434.4	1548.2	1601.2	1609.8	1606.0	1596.6	1576.2
110°	1373.0	1513.2	1603.0	1650.0	1670.8	1680.7	1679.6



TEST NUMBER: P331701-830

CATALOG NUMBER: SA2XXRDIP-C675D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1300.3	1450.1	1553.0	1618.5	1653.3	1672.0	1677.8
115°	1201.2	1344.5	1457.4	1535.1	1585.5	1613.9	1623.8
117.5°	1120.6	1250.7	1356.4	1435.7	1488.8	1518.9	1527.2
120°	1078.5	1194.6	1294.2	1370.8	1422.3	1454.1	1465.0
122.5°	1043.5	1153.4	1243.4	1312.1	1362.7	1391.0	1400.1
125°	997.5	1093.8	1175.9	1239.4	1281.1	1308.4	1317.2
127.5°	952.8	1043.7	1119.5	1174.9	1213.8	1237.5	1244.5
130°	923.0	1009.6	1081.8	1135.5	1172.7	1194.6	1203.3
132.5°	895.0	974.5	1042.4	1095.1	1132.4	1152.5	1160.4
135°	850.7	923.0	984.3	1031.4	1067.5	1087.2	1091.7
137.5°	815.5	872.9	926.3	969.2	1000.3	1017.7	1024.2
140°	792.8	843.1	891.3	926.3	954.8	971.2	977.8
142.5°	772.6	816.0	856.2	889.5	915.4	930.0	931.3
145°	746.8	780.7	812.5	838.7	857.3	868.3	871.6
147.5°	725.8	752.2	775.4	797.1	812.0	819.4	821.4
150°	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)