

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331679-830

Luminaire Tested: **SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331679-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3291.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331679-830
CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331679-830

CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66				
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	76	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42				
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37				
5	73	61	53	47	68	58	51	45	52	46	42	47	42	39	42	38	35	32				
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29				
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23				
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21				
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331679-830

CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	3.0
10°-20°	273.3	8.3
20°-30°	383.7	11.7
30°-40°	418.4	12.7
40°-50°	384.7	11.7
50°-60°	302.2	9.2
60°-70°	197.0	6.0
70°-80°	101.6	3.1
80°-90°	27.9	0.8
90°-100°	25.0	0.8
100°-110°	77.7	2.4
110°-120°	132.8	4.0
120°-130°	174.6	5.3
130°-140°	195.9	6.0
140°-150°	192.1	5.8
150°-160°	161.1	4.9
160°-170°	106.9	3.2
170°-180°	37.4	1.1
0°-30°	756.5	23.0
0°-40°	1174.9	35.7
0°-60°	1861.8	56.6
0°-90°	2188.4	66.5
90°-120°	235.4	7.2
90°-150°	798.0	24.2
90°-180°	1103.0	33.5
0°-180°	3291.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	0	5	12	11	11	3
95°	17	20	21	21	21	20
105°	72	73	73	74	74	76
115°	133	135	134	134	133	132
125°	194	197	196	195	194	173
135°	251	254	255	255	254	194
145°	304	307	309	309	308	190
155°	348	349	350	352	351	160
165°	379	378	378	380	379	107
175°	394	393	392	394	393	37
180°	395	395	395	395	395	



TEST NUMBER: P331679-830

CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.3	11.2	10.0	8.8	7.6	7.2	7.5	7.8	8.2	8.5	8.3
90°	0.4	1.2	2.1	3.0	3.9	5.2	6.8	8.4	10.0	11.7	11.5
92.5°	5.9	6.6	7.3	7.9	8.6	9.0	9.4	9.8	10.2	10.6	10.7
95°	17.3	18.1	18.8	19.5	20.3	20.7	20.8	21.0	21.2	21.3	21.3
97.5°	31.7	32.3	32.9	33.6	34.2	34.7	35.0	35.3	35.5	35.8	35.8
100°	42.3	42.9	43.5	44.1	44.7	45.1	45.2	45.5	45.7	46.0	46.0
102.5°	53.4	53.9	54.4	54.9	55.3	55.8	56.0	56.3	56.6	56.8	56.9
105°	71.6	71.8	72.0	72.3	72.5	72.7	72.9	73.0	73.1	73.2	73.4
107.5°	89.8	90.2	90.5	90.9	91.1	91.3	91.3	91.3	91.3	91.3	91.3
110°	101.6	102.0	102.5	102.9	103.3	103.6	103.6	103.6	103.6	103.6	103.6



TEST NUMBER: P331679-830

CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.3	114.8	115.3	115.6	116.1	116.3	116.2	116.2	116.1	116.1	115.9
115°	133.2	133.7	134.1	134.5	135.0	135.2	135.0	134.8	134.7	134.5	134.5
117.5°	151.9	152.6	153.2	153.7	154.4	154.5	154.0	153.6	153.2	152.8	152.6
120°	164.5	165.1	165.7	166.3	166.8	166.8	166.3	165.7	165.1	164.5	164.5
122.5°	176.0	176.6	177.4	178.0	178.8	179.0	178.5	178.1	177.7	177.3	177.1
125°	193.8	194.4	195.1	195.8	196.4	196.7	196.4	196.2	196.0	195.8	195.6
127.5°	211.2	212.1	212.9	213.7	214.5	214.8	214.6	214.3	214.1	213.8	213.5
130°	222.2	223.1	224.0	225.0	225.9	226.4	226.2	226.1	225.9	225.7	225.6
132.5°	234.4	235.2	235.9	236.7	237.5	237.9	237.9	238.0	238.0	238.0	237.7
135°	250.7	251.6	252.4	253.2	254.0	254.5	254.7	254.8	255.0	255.1	255.0
137.5°	268.0	268.6	269.3	270.0	270.7	271.1	271.3	271.5	271.6	271.8	271.8
140°	278.4	279.1	279.7	280.4	281.1	281.5	281.9	282.3	282.7	283.0	283.0
142.5°	289.1	289.7	290.4	291.1	291.7	292.2	292.4	292.7	292.9	293.1	293.2
145°	304.3	304.9	305.4	305.9	306.4	306.9	307.4	307.8	308.2	308.7	308.8
147.5°	318.0	318.7	319.2	319.9	320.5	320.9	321.2	321.6	321.9	322.2	322.3
150°	327.3	327.8	328.2	328.7	329.1	329.5	329.8	330.1	330.4	330.6	330.9
152.5°	335.6	336.0	336.5	337.0	337.3	337.8	338.1	338.5	338.8	339.2	339.5
155°	348.0	348.2	348.5	348.6	348.8	349.1	349.3	349.5	349.8	350.0	350.3
157.5°	358.5	358.7	358.8	359.0	359.2	359.3	359.5	359.6	359.7	359.9	360.3
160°	365.0	365.1	365.2	365.4	365.5	365.7	365.7	365.8	365.9	366.0	366.4
162.5°	370.8	370.9	370.9	370.9	371.0	371.0	371.1	371.2	371.3	371.3	371.8
165°	378.6	378.5	378.4	378.4	378.3	378.2	378.2	378.2	378.2	378.2	378.8
167.5°	385.1	384.9	384.7	384.5	384.3	384.2	384.1	384.1	384.1	384.1	384.6
170°	388.6	388.4	388.1	388.0	387.8	387.6	387.5	387.4	387.4	387.3	387.8
172.5°	391.0	390.8	390.6	390.3	390.1	389.9	389.9	389.8	389.7	389.6	390.2
175°	394.0	393.7	393.5	393.2	393.0	392.9	392.8	392.6	392.4	392.3	392.8
177.5°	395.1	394.9	394.7	394.6	394.5	394.3	394.2	394.1	393.9	393.8	394.2
180°	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6



TEST NUMBER: P331679-830

CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	8.1	7.9	7.7	7.6	7.6	7.6	7.6	7.6
90°	11.4	11.2	11.0	11.0	11.1	11.2	11.2	11.3
92.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
95°	21.3	21.3	21.3	21.2	21.1	20.9	20.8	20.6
97.5°	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.7
100°	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.6
102.5°	57.0	57.0	57.1	57.1	57.0	56.9	56.9	56.8
105°	73.5	73.7	73.9	73.9	73.9	73.9	73.9	73.9
107.5°	91.4	91.5	91.5	91.4	91.0	90.8	90.4	90.0
110°	103.6	103.6	103.6	103.5	103.2	103.0	102.8	102.5



TEST NUMBER: P331679-830

CATALOG NUMBER: SA2XXRDIP-C675D330U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.7	115.6	115.4	115.2	115.1	114.9	114.7	114.5
115°	134.4	134.3	134.2	134.1	133.8	133.7	133.5	133.2
117.5°	152.4	152.2	152.0	151.8	151.7	151.5	151.2	151.0
120°	164.5	164.5	164.5	164.4	164.2	163.9	163.7	163.5
122.5°	176.9	176.7	176.5	176.4	176.3	176.1	175.9	175.8
125°	195.4	195.1	194.9	194.7	194.7	194.6	194.5	194.4
127.5°	213.3	213.0	212.7	212.4	212.3	212.0	211.8	211.5
130°	225.5	225.4	225.2	225.0	224.7	224.3	224.0	223.8
132.5°	237.3	237.0	236.8	236.5	236.2	236.0	235.7	235.5
135°	255.0	254.9	254.8	254.7	254.4	254.2	254.0	253.7
137.5°	271.7	271.6	271.6	271.5	271.2	270.9	270.6	270.2
140°	283.0	283.0	283.0	282.9	282.6	282.3	282.0	281.7
142.5°	293.3	293.3	293.4	293.3	293.0	292.7	292.4	292.1
145°	308.9	308.9	309.0	308.9	308.6	308.3	308.0	307.6
147.5°	322.4	322.6	322.8	322.7	322.4	322.2	321.9	321.6
150°	331.1	331.3	331.6	331.6	331.3	331.1	330.9	330.6
152.5°	339.8	340.1	340.4	340.4	340.1	339.8	339.5	339.2
155°	350.7	351.1	351.5	351.6	351.3	351.1	350.9	350.6
157.5°	360.8	361.4	361.8	361.9	361.6	361.2	360.9	360.5
160°	366.8	367.3	367.8	367.8	367.5	367.2	366.9	366.6
162.5°	372.3	372.8	373.3	373.3	373.1	372.7	372.3	371.9
165°	379.3	379.8	380.3	380.4	380.0	379.7	379.3	379.0
167.5°	385.1	385.6	386.2	386.3	385.9	385.4	385.0	384.7
170°	388.3	388.8	389.4	389.4	389.0	388.5	388.0	387.6
172.5°	390.7	391.2	391.7	391.8	391.3	390.9	390.5	390.0
175°	393.3	393.8	394.4	394.4	394.0	393.5	393.0	392.6
177.5°	394.5	394.8	395.2	395.2	394.8	394.5	394.2	393.8
180°	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6

(END OF REPORT)