

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331291-935

Luminaire Tested: **SA2XXDIP-C485D330U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331291-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D330U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2829.8 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331291-935  
CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331291-935

CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	42
3	83	73	66	60	77	69	62	57	60	55	51	52	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10797	10797	10797
5°	10838	10682	10746
10°	10775	10575	10627
15°	10641	10437	10425
20°	10452	10232	10220
25°	10265	9978	9978
30°	10023	9747	9661
35°	9798	9469	9329
40°	9514	9190	9012
45°	9236	8912	8690
50°	8932	8626	8317
55°	8617	8290	7983
60°	8263	7892	7598
65°	7885	7492	7148
70°	7407	7010	6680
75°	6744	6457	6301
80°	5979	5793	5504
85°	4872	4650	4168



TEST NUMBER: P331291-935

CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.9	2.2
10°-20°	176.9	6.3
20°-30°	260.1	9.2
30°-40°	302.1	10.7
40°-50°	301.8	10.7
50°-60°	263.2	9.3
60°-70°	194.6	6.9
70°-80°	110.2	3.9
80°-90°	30.6	1.1
90°-100°	12.8	0.5
100°-110°	47.1	1.7
110°-120°	125.8	4.4
120°-130°	207.7	7.3
130°-140°	220.8	7.8
140°-150°	205.3	7.3
150°-160°	165.0	5.8
160°-170°	106.3	3.8
170°-180°	36.6	1.3
0°-30°	499.9	17.7
0°-40°	802.0	28.3
0°-60°	1366.9	48.3
0°-90°	1702.3	60.2
90°-120°	185.7	6.6
90°-150°	819.5	29.0
90°-180°	1127.0	39.8
0°-180°	2829.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	669	669	669	669	669	
5°	669	666	659	664	663	63
15°	637	632	624	627	624	179
25°	576	571	560	561	560	265
35°	497	490	480	476	473	310
45°	404	400	390	384	381	312
55°	306	302	294	287	284	274
65°	206	202	196	190	187	204
75°	108	107	104	100	101	115
85°	26	26	25	23	22	30
90°	0	3	6	7	8	2
95°	18	10	11	12	12	22
105°	85	88	17	20	21	90
115°	160	165	172	49	23	158
125°	226	230	235	237	238	202
135°	280	284	287	290	289	216
145°	325	325	329	331	330	203
155°	358	356	358	360	358	165
165°	377	375	376	378	376	106
175°	386	384	384	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P331291-935

CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	671.8	671.2	670.7	670.1	669.5	668.7	667.4	666.2	664.9	663.6	664.8
5°	668.7	668.1	667.6	667.0	666.5	665.4	663.8	662.3	660.6	659.1	660.2
7.5°	662.8	661.9	661.1	660.1	659.3	658.1	656.4	654.9	653.2	651.6	652.8
10°	657.2	656.2	655.1	654.2	653.2	651.8	650.1	648.4	646.7	645.0	646.1
12.5°	649.5	648.6	647.6	646.8	645.9	644.6	642.9	641.2	639.5	637.7	638.5
15°	636.6	635.8	634.9	634.0	633.2	631.8	629.9	628.1	626.2	624.4	624.9
17.5°	620.1	619.3	618.5	617.6	616.7	615.4	613.5	611.6	609.7	607.8	608.5
20°	608.3	607.4	606.6	605.7	604.9	603.5	601.4	599.4	597.4	595.5	595.9
22.5°	596.5	595.3	594.1	592.9	591.7	590.1	588.2	586.3	584.4	582.6	582.6
25°	576.2	575.0	573.9	572.7	571.6	569.8	567.4	564.9	562.5	560.1	560.3
27.5°	553.0	552.0	551.0	549.9	548.9	547.4	545.5	543.5	541.7	539.8	539.3
30°	537.6	536.4	535.3	534.2	533.0	531.3	529.2	527.1	525.0	522.8	522.4
32.5°	521.1	520.2	519.3	518.3	517.5	515.8	513.6	511.3	509.1	506.9	506.1
35°	497.1	495.6	494.2	492.8	491.4	489.5	487.2	484.9	482.6	480.4	479.5
37.5°	469.9	468.6	467.4	466.1	464.9	463.1	460.8	458.6	456.2	454.0	452.9
40°	451.4	450.2	449.1	448.0	446.9	445.1	442.8	440.6	438.2	436.0	434.7
42.5°	433.4	432.2	431.1	430.0	428.9	427.1	424.8	422.6	420.3	417.9	416.6
45°	404.5	403.5	402.4	401.5	400.5	398.9	396.7	394.6	392.4	390.3	388.7
47.5°	375.7	374.7	373.8	372.8	371.9	370.3	368.1	365.8	363.6	361.4	359.7
50°	355.6	354.9	354.1	353.4	352.8	351.4	349.4	347.4	345.3	343.4	341.4
52.5°	336.0	335.1	334.2	333.2	332.3	330.9	329.0	327.1	325.2	323.3	321.7
55°	306.1	305.2	304.4	303.5	302.6	301.4	299.6	297.9	296.2	294.5	292.8
57.5°	276.0	275.3	274.6	274.0	273.3	272.0	270.1	268.2	266.3	264.4	262.7
60°	255.9	255.4	254.8	254.2	253.7	252.4	250.4	248.3	246.3	244.4	242.8
62.5°	236.3	235.5	234.5	233.6	232.7	231.5	230.0	228.4	226.9	225.3	223.9
65°	206.4	205.5	204.7	203.8	203.0	201.8	200.4	199.0	197.5	196.1	194.8
67.5°	175.9	175.2	174.5	173.8	173.1	172.2	170.9	169.6	168.3	167.0	166.1
70°	156.9	156.4	155.8	155.2	154.6	153.7	152.4	151.1	149.8	148.5	147.6
72.5°	137.3	136.8	136.2	135.6	135.1	134.4	133.5	132.7	131.9	131.0	130.0
75°	108.1	107.7	107.5	107.2	106.9	106.4	105.6	105.0	104.3	103.5	102.6
77.5°	81.8	81.3	80.8	80.3	79.8	79.5	79.2	78.9	78.6	78.4	77.9
80°	64.3	64.1	64.1	63.9	63.7	63.5	63.2	62.9	62.7	62.3	61.9
82.5°	47.9	47.8	47.8	47.8	47.7	47.6	47.4	47.3	47.1	46.9	46.4
85°	26.3	26.3	26.1	25.9	25.8	25.7	25.5	25.4	25.2	25.1	24.6
87.5°	9.3	9.2	9.1	9.0	9.0	8.9	8.7	8.6	8.4	8.4	8.0
90°	0.3	0.9	1.6	2.3	3.0	3.6	4.0	4.6	5.1	5.6	5.9
92.5°	5.6	5.6	5.5	5.4	5.3	5.5	5.7	5.9	6.2	6.5	6.6
95°	18.1	16.0	14.0	12.0	9.9	9.1	9.6	10.0	10.4	10.8	11.2
97.5°	35.9	30.1	24.4	18.7	12.9	10.5	11.5	12.5	13.5	14.6	14.8
100°	49.2	40.8	32.3	23.8	15.4	11.6	12.7	13.8	14.8	15.8	16.4
102.5°	64.0	62.2	60.4	58.6	56.8	51.5	42.7	33.9	25.1	16.3	17.0
105°	84.6	86.4	88.3	90.2	92.0	84.6	67.7	50.8	33.8	17.0	17.7
107.5°	108.1	109.7	111.2	112.7	114.2	104.8	84.6	64.3	44.0	23.8	23.1
110°	123.3	124.6	126.0	127.3	128.5	120.2	102.4	84.5	66.6	48.7	42.5



TEST NUMBER: P331291-935

CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	137.6	138.7	139.9	141.0	142.2	140.5	136.1	131.7	127.3	122.9	100.3
115°	160.1	161.1	162.2	163.2	164.3	165.6	167.1	168.7	170.2	171.8	143.1
117.5°	180.2	181.3	182.5	183.7	184.9	186.0	187.1	188.1	189.2	190.3	183.3
120°	194.8	195.8	196.7	197.7	198.5	199.6	200.7	201.8	202.9	204.1	204.8
122.5°	207.3	208.4	209.3	210.3	211.3	212.3	213.5	214.7	216.0	217.2	217.7
125°	226.4	227.1	227.9	228.8	229.5	230.6	231.7	232.9	234.0	235.2	235.7
127.5°	243.5	244.4	245.3	246.2	247.1	248.0	248.8	249.8	250.6	251.5	252.1
130°	254.4	255.5	256.4	257.4	258.4	259.2	259.9	260.6	261.3	262.0	262.6
132.5°	265.6	266.4	267.3	268.1	269.0	269.7	270.4	271.0	271.7	272.4	273.0
135°	280.1	281.0	282.1	283.0	284.0	284.8	285.3	285.9	286.5	287.1	287.7
137.5°	294.7	295.4	296.1	296.8	297.5	298.2	298.8	299.4	300.1	300.7	301.3
140°	304.3	304.8	305.2	305.7	306.3	306.9	307.5	308.2	308.9	309.5	310.1
142.5°	312.3	312.7	313.1	313.7	314.1	314.7	315.5	316.2	317.0	317.8	318.3
145°	324.9	324.9	324.8	324.7	324.6	325.1	326.1	327.3	328.3	329.3	329.8
147.5°	335.9	335.6	335.4	335.1	334.9	335.3	336.3	337.4	338.5	339.5	339.8
150°	342.9	342.5	342.1	341.6	341.2	341.6	342.5	343.5	344.5	345.5	345.9
152.5°	349.0	348.5	348.0	347.5	347.1	347.2	348.2	349.1	350.1	351.0	351.4
155°	357.7	357.1	356.6	356.0	355.5	355.6	356.4	357.1	357.8	358.5	359.0
157.5°	364.5	364.1	363.6	363.2	362.7	362.7	363.3	363.8	364.3	364.8	365.2
160°	368.6	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.9
162.5°	372.1	371.8	371.4	371.0	370.7	370.7	370.9	371.3	371.6	372.0	372.4
165°	376.9	376.6	376.2	375.8	375.5	375.4	375.6	375.7	375.9	376.1	376.5
167.5°	380.5	380.1	379.8	379.4	379.0	378.9	379.1	379.3	379.4	379.6	380.0
170°	382.5	382.1	381.8	381.4	381.0	380.9	381.0	381.2	381.3	381.4	381.9
172.5°	383.8	383.5	383.1	382.7	382.4	382.2	382.4	382.5	382.6	382.7	383.1
175°	385.6	385.1	384.7	384.3	383.8	383.7	383.8	383.9	384.1	384.2	384.6
177.5°	385.8	385.5	385.1	384.8	384.4	384.4	384.4	384.4	384.4	384.5	384.9
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331291-935

CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	665.9	667.0	668.1	668.7	668.4	668.1	668.0	667.7
5°	661.4	662.5	663.7	664.1	663.8	663.5	663.2	663.0
7.5°	653.9	655.0	656.3	656.6	656.3	656.0	655.7	655.4
10°	647.2	648.4	649.5	649.9	649.5	649.0	648.6	648.2
12.5°	639.4	640.2	640.9	641.2	640.8	640.6	640.2	639.9
15°	625.5	626.1	626.6	626.5	625.9	625.2	624.5	623.7
17.5°	609.1	609.8	610.4	610.4	609.7	609.1	608.4	607.7
20°	596.3	596.8	597.2	597.1	596.5	595.9	595.4	594.8
22.5°	582.7	582.8	582.9	582.8	582.5	582.1	581.8	581.4
25°	560.7	560.9	561.2	561.2	560.9	560.7	560.3	560.1
27.5°	538.9	538.5	538.0	537.5	536.8	536.1	535.5	534.8
30°	521.9	521.5	521.1	520.6	520.0	519.4	518.8	518.2
32.5°	505.3	504.5	503.8	503.1	502.5	502.0	501.4	500.8
35°	478.6	477.8	476.9	476.1	475.4	474.7	474.0	473.3
37.5°	451.9	450.8	449.8	448.8	448.2	447.5	446.8	446.2
40°	433.4	432.1	430.8	429.9	429.3	428.8	428.2	427.6
42.5°	415.2	413.8	412.3	411.3	410.4	409.7	408.9	408.0
45°	387.2	385.6	384.0	383.0	382.4	381.9	381.3	380.6
47.5°	358.1	356.4	354.7	353.5	352.7	351.9	351.0	350.2
50°	339.4	337.3	335.4	334.0	333.3	332.6	331.8	331.1
52.5°	320.0	318.3	316.7	315.4	314.4	313.5	312.5	311.6
55°	291.1	289.4	287.7	286.5	285.7	285.0	284.3	283.6
57.5°	261.1	259.3	257.7	256.6	256.0	255.5	254.9	254.3
60°	241.2	239.6	238.1	237.0	236.6	236.2	235.7	235.3
62.5°	222.4	220.9	219.5	218.5	217.9	217.4	216.9	216.3
65°	193.6	192.3	191.0	189.9	189.2	188.6	187.9	187.1
67.5°	165.1	164.0	163.1	162.3	161.7	161.1	160.6	160.0
70°	146.5	145.5	144.6	143.8	143.2	142.6	142.1	141.5
72.5°	129.1	128.0	127.1	126.3	125.9	125.4	124.9	124.5
75°	101.8	101.0	100.1	99.8	100.1	100.4	100.7	101.0
77.5°	77.5	77.1	76.6	76.2	75.8	75.4	75.0	74.6
80°	61.5	61.0	60.7	60.3	60.0	59.8	59.4	59.2
82.5°	45.9	45.3	44.8	44.4	44.4	44.3	44.3	44.3
85°	24.2	23.8	23.3	23.1	22.9	22.8	22.6	22.5
87.5°	7.7	7.5	7.2	7.0	6.9	6.8	6.7	6.6
90°	6.2	6.5	6.8	7.1	7.1	7.2	7.4	7.5
92.5°	6.8	7.0	7.1	7.2	7.3	7.4	7.4	7.5
95°	11.5	11.8	12.1	12.2	12.1	12.1	12.1	12.0
97.5°	15.1	15.2	15.5	15.7	15.8	15.8	15.9	16.0
100°	16.9	17.4	17.8	18.2	18.3	18.4	18.5	18.7
102.5°	17.6	18.3	18.9	19.3	19.5	19.6	19.8	20.0
105°	18.3	19.0	19.7	20.1	20.4	20.7	20.9	21.2
107.5°	22.4	21.7	21.0	20.8	21.0	21.3	21.5	21.8
110°	36.3	30.1	23.9	21.0	21.3	21.5	21.8	22.0





TEST NUMBER: P331291-935

CATALOG NUMBER: SA2XXDIP-C485D330U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	77.7	55.2	32.6	21.4	21.6	21.8	22.0	22.2
115°	114.5	85.8	57.2	40.6	36.2	31.8	27.3	22.8
117.5°	176.4	169.4	162.6	151.8	137.2	122.5	107.9	93.2
120°	205.5	206.3	207.0	203.2	194.8	186.5	178.1	169.8
122.5°	218.1	218.5	219.0	218.3	216.8	215.2	213.5	211.9
125°	236.1	236.5	236.9	237.3	237.5	237.6	237.8	238.0
127.5°	252.8	253.4	254.0	254.3	254.4	254.4	254.4	254.5
130°	263.3	264.0	264.7	265.0	264.9	264.8	264.8	264.8
132.5°	273.6	274.1	274.7	275.0	274.9	274.9	274.8	274.7
135°	288.3	288.9	289.5	289.7	289.6	289.5	289.4	289.2
137.5°	301.9	302.5	303.1	303.2	303.1	302.9	302.6	302.5
140°	310.6	311.3	311.8	311.9	311.6	311.3	311.0	310.6
142.5°	318.8	319.3	319.9	319.9	319.6	319.3	319.0	318.7
145°	330.2	330.6	331.1	331.1	330.8	330.5	330.2	329.8
147.5°	340.1	340.4	340.8	340.8	340.5	340.3	340.0	339.8
150°	346.2	346.6	347.0	347.0	346.7	346.4	346.0	345.8
152.5°	351.8	352.1	352.5	352.5	352.1	351.7	351.3	350.9
155°	359.3	359.6	360.1	360.0	359.5	359.0	358.5	358.0
157.5°	365.7	366.1	366.4	366.4	365.9	365.5	365.0	364.5
160°	369.4	369.7	370.1	370.1	369.6	369.2	368.8	368.3
162.5°	372.7	373.2	373.6	373.6	373.0	372.5	372.0	371.4
165°	376.9	377.4	377.8	377.8	377.4	376.9	376.5	376.1
167.5°	380.5	380.9	381.3	381.3	380.7	380.1	379.6	379.0
170°	382.3	382.7	383.1	383.1	382.5	381.9	381.4	380.8
172.5°	383.6	384.0	384.4	384.4	383.8	383.3	382.7	382.2
175°	385.0	385.5	385.9	385.8	385.2	384.6	383.9	383.3
177.5°	385.2	385.6	385.9	385.8	385.4	385.0	384.5	384.1
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7

(END OF REPORT)