

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331697-830

Luminaire Tested: **SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331697-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5307.9 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331697-830
CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331697-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				36
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30				30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26				26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23				23
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20				20
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18				18
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16				16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14				14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331697-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	1.9
10°-20°	273.3	5.1
20°-30°	383.7	7.2
30°-40°	418.4	7.9
40°-50°	384.7	7.2
50°-60°	302.2	5.7
60°-70°	197.0	3.7
70°-80°	101.6	1.9
80°-90°	30.8	0.6
90°-100°	70.6	1.3
100°-110°	219.4	4.1
110°-120°	375.0	7.1
120°-130°	493.1	9.3
130°-140°	553.4	10.4
140°-150°	542.7	10.2
150°-160°	455.2	8.6
160°-170°	301.9	5.7
170°-180°	105.5	2.0
0°-30°	756.5	14.3
0°-40°	1174.9	22.1
0°-60°	1861.8	35.1
0°-90°	2191.2	41.3
90°-120°	665.0	12.5
90°-150°	2254.1	42.5
90°-180°	3117.0	58.7
0°-180°	5307.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	1	13	33	31	32	4
95°	49	58	60	60	58	56
105°	202	205	207	209	209	214
115°	376	381	380	379	376	372
125°	547	555	553	550	549	489
135°	708	718	720	719	717	547
145°	860	866	872	873	869	537
155°	983	986	988	993	990	452
165°	1070	1069	1069	1074	1070	301
175°	1113	1110	1108	1114	1109	106
180°	1115	1115	1115	1115	1115	



TEST NUMBER: P331697-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.5	11.6	10.7	9.9	9.0	9.0	10.0	10.9	11.8	12.7	12.4
90°	0.9	3.5	5.9	8.5	10.9	14.5	19.1	23.8	28.3	32.9	32.5
92.5°	16.8	18.6	20.5	22.2	24.1	25.5	26.7	27.7	28.8	29.9	30.0
95°	48.9	51.0	53.1	55.1	57.3	58.5	58.9	59.4	59.8	60.2	60.2
97.5°	89.4	91.2	93.0	94.9	96.7	98.0	98.9	99.6	100.4	101.2	101.2
100°	119.4	121.1	122.8	124.5	126.1	127.3	127.9	128.6	129.2	129.8	129.8
102.5°	151.1	152.4	153.7	155.0	156.4	157.5	158.3	159.1	159.9	160.7	160.8
105°	202.3	202.8	203.5	204.2	204.7	205.3	205.7	206.1	206.5	206.9	207.4
107.5°	253.7	254.7	255.6	256.6	257.5	257.9	257.9	257.9	257.9	257.9	258.1
110°	286.9	288.1	289.4	290.7	291.9	292.6	292.6	292.6	292.6	292.6	292.6



TEST NUMBER: P331697-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	323.0	324.2	325.6	326.8	328.0	328.6	328.4	328.2	328.1	327.9	327.4
115°	376.3	377.5	378.7	380.0	381.3	381.6	381.3	380.9	380.4	380.0	379.8
117.5°	429.3	430.9	432.6	434.3	436.0	436.2	435.1	433.9	432.7	431.6	431.0
120°	464.7	466.4	468.0	469.7	471.4	471.4	469.7	468.0	466.4	464.7	464.7
122.5°	497.0	499.0	501.1	503.0	505.0	505.5	504.3	503.1	502.0	500.8	500.3
125°	547.4	549.3	551.2	553.1	555.0	555.6	555.0	554.3	553.7	553.1	552.4
127.5°	596.5	598.9	601.3	603.7	606.1	606.9	606.1	605.4	604.6	603.9	603.1
130°	627.4	630.1	632.8	635.6	638.3	639.4	638.9	638.6	638.2	637.7	637.3
132.5°	662.0	664.2	666.5	668.6	670.9	672.0	672.1	672.2	672.2	672.3	671.5
135°	708.3	710.6	712.8	715.2	717.5	718.9	719.3	719.6	720.1	720.5	720.3
137.5°	757.1	758.8	760.7	762.6	764.5	765.7	766.3	766.9	767.4	767.9	767.8
140°	786.4	788.2	790.1	792.0	793.9	795.3	796.4	797.4	798.5	799.6	799.6
142.5°	816.4	818.3	820.2	822.1	824.0	825.3	826.0	826.7	827.4	828.1	828.3
145°	859.7	861.2	862.6	864.1	865.5	867.0	868.2	869.4	870.7	871.9	872.1
147.5°	898.2	900.0	901.8	903.5	905.3	906.6	907.5	908.2	909.1	909.9	910.4
150°	924.6	925.9	927.1	928.4	929.6	930.7	931.5	932.4	933.2	934.1	934.6
152.5°	947.9	949.2	950.5	951.7	953.0	954.1	955.1	956.1	957.1	958.1	958.9
155°	983.0	983.5	984.2	984.9	985.4	986.1	986.7	987.3	988.0	988.5	989.7
157.5°	1012.9	1013.2	1013.7	1014.1	1014.6	1014.9	1015.3	1015.7	1016.1	1016.4	1017.9
160°	1031.0	1031.3	1031.7	1032.2	1032.6	1032.9	1033.1	1033.3	1033.5	1033.7	1035.0
162.5°	1047.4	1047.5	1047.6	1047.7	1047.8	1047.9	1048.2	1048.4	1048.6	1048.8	1050.2
165°	1069.5	1069.3	1069.0	1068.8	1068.7	1068.6	1068.6	1068.6	1068.6	1068.6	1070.0
167.5°	1087.9	1087.3	1086.7	1086.0	1085.4	1085.1	1085.1	1085.0	1085.0	1084.9	1086.4
170°	1097.7	1097.0	1096.5	1095.8	1095.1	1094.8	1094.6	1094.4	1094.1	1093.9	1095.4
172.5°	1104.5	1103.8	1103.2	1102.6	1101.9	1101.5	1101.4	1101.1	1100.9	1100.7	1102.2
175°	1112.8	1112.1	1111.4	1110.9	1110.2	1109.7	1109.3	1108.9	1108.4	1108.1	1109.5
177.5°	1116.2	1115.6	1115.1	1114.7	1114.1	1113.7	1113.3	1113.0	1112.7	1112.4	1113.3
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7



TEST NUMBER: P331697-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	12.3	12.0	11.7	11.6	11.7	11.7	11.8	11.8
90°	32.0	31.7	31.3	31.1	31.4	31.6	31.8	32.0
92.5°	30.1	30.2	30.3	30.3	30.3	30.3	30.4	30.4
95°	60.2	60.2	60.2	59.9	59.6	59.2	58.7	58.3
97.5°	101.2	101.2	101.2	101.2	101.1	101.1	101.0	101.0
100°	129.8	129.8	129.8	129.7	129.5	129.3	129.0	128.8
102.5°	161.0	161.2	161.4	161.3	161.1	160.9	160.7	160.5
105°	207.7	208.2	208.6	208.8	208.8	208.8	208.8	208.8
107.5°	258.3	258.4	258.5	258.2	257.2	256.3	255.3	254.3
110°	292.6	292.6	292.6	292.2	291.6	291.0	290.3	289.7



TEST NUMBER: P331697-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.9	326.4	325.9	325.4	325.0	324.5	324.0	323.6
115°	379.6	379.4	379.2	378.7	378.1	377.5	376.8	376.3
117.5°	430.6	430.1	429.5	429.0	428.4	427.7	427.1	426.5
120°	464.7	464.7	464.7	464.4	463.7	463.1	462.5	461.8
122.5°	499.7	499.3	498.8	498.3	497.9	497.4	496.9	496.4
125°	551.9	551.2	550.5	550.2	550.0	549.7	549.5	549.3
127.5°	602.4	601.6	600.9	600.1	599.5	598.8	598.1	597.5
130°	636.9	636.5	636.0	635.5	634.6	633.8	632.9	632.1
132.5°	670.5	669.6	668.6	667.9	667.2	666.6	665.9	665.2
135°	720.1	719.9	719.6	719.3	718.6	718.0	717.4	716.7
137.5°	767.6	767.4	767.2	766.8	765.9	765.1	764.2	763.4
140°	799.6	799.6	799.6	799.1	798.2	797.4	796.6	795.8
142.5°	828.5	828.6	828.8	828.5	827.6	826.8	826.0	825.1
145°	872.3	872.6	872.8	872.5	871.7	870.8	870.0	869.1
147.5°	910.9	911.3	911.8	911.6	910.9	910.0	909.3	908.4
150°	935.3	935.9	936.5	936.5	935.9	935.3	934.6	934.1
152.5°	959.7	960.5	961.3	961.3	960.5	959.7	958.9	958.1
155°	990.7	991.7	992.8	993.0	992.3	991.7	991.1	990.4
157.5°	1019.3	1020.7	1022.1	1022.3	1021.3	1020.3	1019.3	1018.3
160°	1036.2	1037.5	1038.8	1039.0	1038.1	1037.3	1036.4	1035.6
162.5°	1051.6	1053.0	1054.4	1054.7	1053.7	1052.6	1051.7	1050.7
165°	1071.5	1072.9	1074.4	1074.6	1073.6	1072.5	1071.5	1070.4
167.5°	1087.8	1089.3	1090.7	1090.9	1089.9	1088.7	1087.7	1086.6
170°	1096.8	1098.3	1099.8	1099.9	1098.6	1097.4	1096.1	1094.9
172.5°	1103.6	1105.1	1106.5	1106.6	1105.4	1104.2	1102.9	1101.6
175°	1111.0	1112.4	1113.9	1114.0	1112.8	1111.4	1110.2	1109.0
177.5°	1114.4	1115.4	1116.3	1116.3	1115.4	1114.4	1113.3	1112.4
180°	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7	1114.7

(END OF REPORT)