

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331310-935

Luminaire Tested: **SA2XXDIP-C485D725U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331310-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3934.5 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10797	10797	10797
5°	10838	10682	10746
10°	10775	10575	10627
15°	10641	10437	10425
20°	10452	10232	10220
25°	10265	9978	9978
30°	10023	9747	9661
35°	9798	9469	9329
40°	9514	9190	9012
45°	9236	8912	8690
50°	8932	8626	8317
55°	8617	8290	7983
60°	8263	7892	7598
65°	7885	7492	7148
70°	7407	7010	6680
75°	6744	6457	6301
80°	5979	5793	5504
85°	4872	4650	4168



TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	1.6
10°-20°	176.9	4.5
20°-30°	260.1	6.6
30°-40°	302.1	7.7
40°-50°	301.8	7.7
50°-60°	263.2	6.7
60°-70°	194.6	4.9
70°-80°	110.2	2.8
80°-90°	32.8	0.8
90°-100°	50.5	1.3
100°-110°	157.0	4.0
110°-120°	268.3	6.8
120°-130°	352.8	9.0
130°-140°	396.0	10.1
140°-150°	388.3	9.9
150°-160°	325.7	8.3
160°-170°	216.0	5.5
170°-180°	75.5	1.9
0°-30°	499.9	12.7
0°-40°	802.0	20.4
0°-60°	1366.9	34.7
0°-90°	1704.6	43.3
90°-120°	475.8	12.1
90°-150°	1612.8	41.0
90°-180°	2230.0	56.7
0°-180°	3934.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	669	669	669	669	669	
5°	669	666	659	664	663	63
15°	637	632	624	627	624	179
25°	576	571	560	561	560	265
35°	497	490	480	476	473	310
45°	404	400	390	384	381	312
55°	306	302	294	287	284	274
65°	206	202	196	190	187	204
75°	108	107	104	100	101	115
85°	26	26	25	23	22	30
90°	1	9	24	22	23	3
95°	35	41	43	43	42	40
105°	145	147	148	149	149	153
115°	269	273	272	271	269	266
125°	392	397	396	394	393	350
135°	507	514	516	515	513	391
145°	615	620	624	624	622	384
155°	703	705	707	710	709	324
165°	765	765	764	769	766	216
175°	796	794	793	797	794	76
180°	798	798	798	798	798	



TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	671.8	671.2	670.7	670.1	669.5	668.7	667.4	666.2	664.9	663.6	664.8
5°	668.7	668.1	667.6	667.0	666.5	665.4	663.8	662.3	660.6	659.1	660.2
7.5°	662.8	661.9	661.1	660.1	659.3	658.1	656.4	654.9	653.2	651.6	652.8
10°	657.2	656.2	655.1	654.2	653.2	651.8	650.1	648.4	646.7	645.0	646.1
12.5°	649.5	648.6	647.6	646.8	645.9	644.6	642.9	641.2	639.5	637.7	638.5
15°	636.6	635.8	634.9	634.0	633.2	631.8	629.9	628.1	626.2	624.4	624.9
17.5°	620.1	619.3	618.5	617.6	616.7	615.4	613.5	611.6	609.7	607.8	608.5
20°	608.3	607.4	606.6	605.7	604.9	603.5	601.4	599.4	597.4	595.5	595.9
22.5°	596.5	595.3	594.1	592.9	591.7	590.1	588.2	586.3	584.4	582.6	582.6
25°	576.2	575.0	573.9	572.7	571.6	569.8	567.4	564.9	562.5	560.1	560.3
27.5°	553.0	552.0	551.0	549.9	548.9	547.4	545.5	543.5	541.7	539.8	539.3
30°	537.6	536.4	535.3	534.2	533.0	531.3	529.2	527.1	525.0	522.8	522.4
32.5°	521.1	520.2	519.3	518.3	517.5	515.8	513.6	511.3	509.1	506.9	506.1
35°	497.1	495.6	494.2	492.8	491.4	489.5	487.2	484.9	482.6	480.4	479.5
37.5°	469.9	468.6	467.4	466.1	464.9	463.1	460.8	458.6	456.2	454.0	452.9
40°	451.4	450.2	449.1	448.0	446.9	445.1	442.8	440.6	438.2	436.0	434.7
42.5°	433.4	432.2	431.1	430.0	428.9	427.1	424.8	422.6	420.3	417.9	416.6
45°	404.5	403.5	402.4	401.5	400.5	398.9	396.7	394.6	392.4	390.3	388.7
47.5°	375.7	374.7	373.8	372.8	371.9	370.3	368.1	365.8	363.6	361.4	359.7
50°	355.6	354.9	354.1	353.4	352.8	351.4	349.4	347.4	345.3	343.4	341.4
52.5°	336.0	335.1	334.2	333.2	332.3	330.9	329.0	327.1	325.2	323.3	321.7
55°	306.1	305.2	304.4	303.5	302.6	301.4	299.6	297.9	296.2	294.5	292.8
57.5°	276.0	275.3	274.6	274.0	273.3	272.0	270.1	268.2	266.3	264.4	262.7
60°	255.9	255.4	254.8	254.2	253.7	252.4	250.4	248.3	246.3	244.4	242.8
62.5°	236.3	235.5	234.5	233.6	232.7	231.5	230.0	228.4	226.9	225.3	223.9
65°	206.4	205.5	204.7	203.8	203.0	201.8	200.4	199.0	197.5	196.1	194.8
67.5°	175.9	175.2	174.5	173.8	173.1	172.2	170.9	169.6	168.3	167.0	166.1
70°	156.9	156.4	155.8	155.2	154.6	153.7	152.4	151.1	149.8	148.5	147.6
72.5°	137.3	136.8	136.2	135.6	135.1	134.4	133.5	132.7	131.9	131.0	130.0
75°	108.1	107.7	107.5	107.2	106.9	106.4	105.6	105.0	104.3	103.5	102.6
77.5°	81.8	81.3	80.8	80.3	79.8	79.5	79.2	78.9	78.6	78.4	77.9
80°	64.3	64.1	64.1	63.9	63.7	63.5	63.2	62.9	62.7	62.3	61.9
82.5°	47.9	47.8	47.8	47.8	47.7	47.6	47.4	47.3	47.1	46.9	46.4
85°	26.3	26.3	26.1	25.9	25.8	25.7	25.5	25.4	25.2	25.1	24.6
87.5°	9.4	9.6	9.6	9.8	9.9	10.2	10.6	11.0	11.5	11.9	11.5
90°	0.7	2.5	4.3	6.0	7.8	10.4	13.7	17.0	20.2	23.6	23.2
92.5°	12.0	13.3	14.6	15.9	17.2	18.3	19.0	19.8	20.7	21.4	21.4
95°	35.0	36.5	38.0	39.5	41.0	41.8	42.2	42.4	42.8	43.0	43.0
97.5°	64.0	65.3	66.6	67.8	69.2	70.2	70.7	71.3	71.8	72.4	72.4
100°	85.5	86.7	87.8	89.0	90.2	91.1	91.5	92.0	92.4	92.9	92.9
102.5°	108.1	109.0	110.0	111.0	111.9	112.7	113.2	113.8	114.3	114.9	115.0
105°	144.7	145.2	145.6	146.0	146.5	146.9	147.1	147.5	147.7	148.1	148.4
107.5°	181.6	182.3	182.9	183.6	184.2	184.5	184.5	184.5	184.5	184.5	184.7
110°	205.3	206.1	207.1	207.9	208.9	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.1	232.0	232.9	233.8	234.7	235.1	235.0	234.9	234.7	234.6	234.3
115°	269.2	270.1	271.0	271.9	272.8	273.1	272.8	272.5	272.2	271.9	271.7
117.5°	307.1	308.3	309.5	310.7	311.9	312.1	311.3	310.5	309.6	308.8	308.4
120°	332.4	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	332.4
122.5°	355.6	357.1	358.5	359.9	361.4	361.6	360.8	360.0	359.1	358.3	357.9
125°	391.7	393.0	394.3	395.7	397.1	397.5	397.1	396.6	396.1	395.7	395.3
127.5°	426.8	428.5	430.2	432.0	433.6	434.2	433.7	433.2	432.6	432.0	431.5
130°	448.9	450.8	452.8	454.7	456.7	457.4	457.2	456.8	456.6	456.3	456.0
132.5°	473.6	475.3	476.8	478.4	480.0	480.8	480.9	481.0	481.0	481.0	480.4
135°	506.8	508.4	510.1	511.7	513.3	514.3	514.6	514.9	515.2	515.5	515.4
137.5°	541.7	542.9	544.3	545.7	547.0	547.9	548.3	548.6	549.1	549.4	549.3
140°	562.7	564.0	565.3	566.6	568.0	569.0	569.8	570.6	571.3	572.0	572.0
142.5°	584.2	585.5	586.9	588.2	589.5	590.5	591.0	591.5	592.0	592.5	592.6
145°	615.1	616.1	617.3	618.3	619.3	620.3	621.2	622.1	622.9	623.9	624.1
147.5°	642.7	643.9	645.2	646.4	647.7	648.7	649.3	649.9	650.5	651.1	651.3
150°	661.6	662.5	663.3	664.3	665.1	665.9	666.5	667.1	667.7	668.3	668.7
152.5°	678.2	679.2	680.0	681.0	681.8	682.6	683.4	684.1	684.8	685.5	686.0
155°	703.3	703.7	704.2	704.6	705.1	705.5	705.9	706.5	706.9	707.3	708.1
157.5°	724.7	725.0	725.3	725.6	725.9	726.2	726.4	726.7	726.9	727.2	728.2
160°	737.6	737.9	738.2	738.5	738.8	739.0	739.2	739.3	739.5	739.6	740.5
162.5°	749.4	749.5	749.6	749.6	749.7	749.8	749.9	750.1	750.3	750.4	751.4
165°	765.2	765.1	764.9	764.7	764.6	764.5	764.5	764.5	764.5	764.5	765.6
167.5°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.3	776.3	776.2	777.3
170°	785.4	785.0	784.5	784.0	783.6	783.3	783.2	783.0	782.8	782.6	783.8
172.5°	790.2	789.8	789.4	788.8	788.4	788.2	788.0	787.8	787.7	787.6	788.6
175°	796.2	795.7	795.2	794.8	794.4	794.0	793.7	793.4	793.1	792.8	793.8
177.5°	798.6	798.2	797.9	797.5	797.1	796.9	796.6	796.3	796.1	795.9	796.6
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	665.9	667.0	668.1	668.7	668.4	668.1	668.0	667.7
5°	661.4	662.5	663.7	664.1	663.8	663.5	663.2	663.0
7.5°	653.9	655.0	656.3	656.6	656.3	656.0	655.7	655.4
10°	647.2	648.4	649.5	649.9	649.5	649.0	648.6	648.2
12.5°	639.4	640.2	640.9	641.2	640.8	640.6	640.2	639.9
15°	625.5	626.1	626.6	626.5	625.9	625.2	624.5	623.7
17.5°	609.1	609.8	610.4	610.4	609.7	609.1	608.4	607.7
20°	596.3	596.8	597.2	597.1	596.5	595.9	595.4	594.8
22.5°	582.7	582.8	582.9	582.8	582.5	582.1	581.8	581.4
25°	560.7	560.9	561.2	561.2	560.9	560.7	560.3	560.1
27.5°	538.9	538.5	538.0	537.5	536.8	536.1	535.5	534.8
30°	521.9	521.5	521.1	520.6	520.0	519.4	518.8	518.2
32.5°	505.3	504.5	503.8	503.1	502.5	502.0	501.4	500.8
35°	478.6	477.8	476.9	476.1	475.4	474.7	474.0	473.3
37.5°	451.9	450.8	449.8	448.8	448.2	447.5	446.8	446.2
40°	433.4	432.1	430.8	429.9	429.3	428.8	428.2	427.6
42.5°	415.2	413.8	412.3	411.3	410.4	409.7	408.9	408.0
45°	387.2	385.6	384.0	383.0	382.4	381.9	381.3	380.6
47.5°	358.1	356.4	354.7	353.5	352.7	351.9	351.0	350.2
50°	339.4	337.3	335.4	334.0	333.3	332.6	331.8	331.1
52.5°	320.0	318.3	316.7	315.4	314.4	313.5	312.5	311.6
55°	291.1	289.4	287.7	286.5	285.7	285.0	284.3	283.6
57.5°	261.1	259.3	257.7	256.6	256.0	255.5	254.9	254.3
60°	241.2	239.6	238.1	237.0	236.6	236.2	235.7	235.3
62.5°	222.4	220.9	219.5	218.5	217.9	217.4	216.9	216.3
65°	193.6	192.3	191.0	189.9	189.2	188.6	187.9	187.1
67.5°	165.1	164.0	163.1	162.3	161.7	161.1	160.6	160.0
70°	146.5	145.5	144.6	143.8	143.2	142.6	142.1	141.5
72.5°	129.1	128.0	127.1	126.3	125.9	125.4	124.9	124.5
75°	101.8	101.0	100.1	99.8	100.1	100.4	100.7	101.0
77.5°	77.5	77.1	76.6	76.2	75.8	75.4	75.0	74.6
80°	61.5	61.0	60.7	60.3	60.0	59.8	59.4	59.2
82.5°	45.9	45.3	44.8	44.4	44.4	44.3	44.3	44.3
85°	24.2	23.8	23.3	23.1	22.9	22.8	22.6	22.5
87.5°	11.1	10.7	10.3	10.1	10.0	9.9	9.8	9.7
90°	23.0	22.6	22.4	22.3	22.5	22.6	22.7	22.9
92.5°	21.5	21.6	21.6	21.7	21.7	21.8	21.8	21.8
95°	43.0	43.0	43.0	43.0	42.6	42.4	42.0	41.8
97.5°	72.4	72.4	72.4	72.4	72.4	72.3	72.3	72.2
100°	92.9	92.9	92.9	92.8	92.6	92.5	92.4	92.2
102.5°	115.2	115.3	115.5	115.4	115.3	115.1	114.9	114.8
105°	148.7	149.0	149.3	149.4	149.4	149.4	149.4	149.4
107.5°	184.8	184.9	185.0	184.8	184.1	183.4	182.7	182.0
110°	209.3	209.3	209.3	209.1	208.6	208.2	207.8	207.2



TEST NUMBER: P331310-935

CATALOG NUMBER: SA2XXDIP-C485D725U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	233.8	233.5	233.2	232.8	232.5	232.1	231.9	231.5
115°	271.6	271.5	271.3	271.0	270.5	270.1	269.7	269.2
117.5°	308.1	307.7	307.3	306.9	306.5	306.0	305.6	305.1
120°	332.4	332.4	332.4	332.3	331.7	331.3	330.9	330.5
122.5°	357.6	357.2	356.9	356.5	356.2	355.9	355.5	355.2
125°	394.9	394.3	393.9	393.6	393.5	393.3	393.2	393.0
127.5°	431.0	430.4	429.9	429.4	429.0	428.4	428.0	427.5
130°	455.7	455.4	455.1	454.6	454.0	453.5	452.9	452.3
132.5°	479.7	479.1	478.5	477.9	477.3	476.9	476.4	476.0
135°	515.2	515.1	514.9	514.6	514.2	513.8	513.2	512.8
137.5°	549.2	549.1	549.0	548.6	548.0	547.4	546.8	546.2
140°	572.0	572.0	572.0	571.7	571.2	570.6	570.0	569.4
142.5°	592.7	592.9	593.0	592.7	592.1	591.5	591.0	590.4
145°	624.1	624.3	624.5	624.2	623.6	623.0	622.4	621.8
147.5°	651.7	652.0	652.4	652.3	651.7	651.1	650.6	650.0
150°	669.2	669.6	670.1	670.1	669.6	669.2	668.7	668.3
152.5°	686.6	687.3	687.8	687.8	687.3	686.6	686.0	685.5
155°	708.8	709.6	710.3	710.5	710.0	709.6	709.1	708.7
157.5°	729.3	730.3	731.3	731.4	730.7	730.0	729.3	728.6
160°	741.4	742.4	743.2	743.4	742.8	742.2	741.6	741.0
162.5°	752.4	753.5	754.5	754.6	753.9	753.2	752.4	751.7
165°	766.6	767.7	768.7	768.9	768.1	767.3	766.6	765.9
167.5°	778.3	779.4	780.4	780.6	779.8	779.0	778.3	777.5
170°	784.8	785.8	786.9	787.0	786.1	785.1	784.3	783.3
172.5°	789.6	790.7	791.7	791.8	790.9	790.0	789.1	788.2
175°	794.9	795.9	796.9	797.0	796.2	795.2	794.4	793.5
177.5°	797.3	798.1	798.7	798.7	798.1	797.3	796.6	795.9
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5

(END OF REPORT)