

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331698-830

Luminaire Tested: **SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331698-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5595.0 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331698-830  
CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331698-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34				
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29				
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22				
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	23	19				
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17				
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15				
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14				
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331698-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.5	1.8
10°-20°	273.3	4.9
20°-30°	383.7	6.9
30°-40°	418.4	7.5
40°-50°	384.7	6.9
50°-60°	302.2	5.4
60°-70°	197.0	3.5
70°-80°	101.6	1.8
80°-90°	30.8	0.5
90°-100°	195.6	3.5
100°-110°	663.7	11.9
110°-120°	705.1	12.6
120°-130°	580.4	10.4
130°-140°	466.1	8.3
140°-150°	352.2	6.3
150°-160°	247.5	4.4
160°-170°	145.7	2.6
170°-180°	47.4	0.8
0°-30°	756.5	13.5
0°-40°	1174.9	21.0
0°-60°	1861.8	33.3
0°-90°	2191.2	39.2
90°-120°	1564.4	28.0
90°-150°	2963.2	53.0
90°-180°	3404.0	60.8
0°-180°	5595.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	1	13	32	31	31	4
95°	33	81	369	139	107	35
105°	115	173	697	1246	1060	122
115°	202	255	583	1204	1395	200
125°	282	334	561	975	1132	251
135°	331	395	554	819	938	256
145°	378	435	551	684	749	237
155°	430	464	535	605	629	198
165°	468	483	513	544	552	132
175°	488	489	493	499	498	46
180°	489	489	489	489	489	



TEST NUMBER: P331698-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.5	11.7	11.1	10.1	9.1	9.0	9.9	11.2	12.3	12.5	12.2
90°	0.9	3.8	7.5	9.4	11.3	14.1	18.9	25.4	31.0	32.0	31.0
92.5°	11.5	16.6	23.4	27.4	33.8	42.7	64.0	93.9	120.6	122.2	103.3
95°	32.9	36.7	46.1	54.6	69.7	92.2	135.4	217.3	326.4	368.7	322.6
97.5°	53.6	58.7	68.7	81.4	98.8	124.3	178.7	292.8	474.1	629.5	660.3
100°	72.4	75.2	83.7	98.8	117.6	143.9	193.8	308.6	511.7	743.1	878.6
102.5°	89.7	91.8	100.3	115.4	134.9	161.3	207.4	309.3	497.5	746.9	959.9
105°	114.8	118.6	125.1	139.2	159.9	186.2	230.5	314.1	469.4	697.0	947.3
107.5°	141.9	144.9	151.3	164.3	184.7	211.3	254.2	327.2	455.4	643.7	864.7
110°	159.9	163.7	169.3	181.5	201.3	228.6	269.9	337.7	452.5	618.0	812.8



TEST NUMBER: P331698-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.4	180.2	186.6	198.1	217.1	245.2	285.0	349.0	453.2	601.4	776.7
115°	202.3	207.0	212.6	223.9	242.7	268.1	308.6	365.9	457.1	583.2	731.9
117.5°	228.9	232.7	238.4	248.4	266.4	292.8	330.2	384.0	463.9	574.4	703.6
120°	245.5	249.3	255.0	263.3	282.2	308.6	345.3	396.1	468.4	569.1	688.6
122.5°	261.4	264.3	269.9	279.2	298.0	325.1	359.5	406.5	473.7	566.1	675.8
125°	282.2	285.0	290.7	302.0	320.7	347.1	381.0	423.3	481.6	560.6	657.5
127.5°	298.8	302.6	310.4	322.8	340.9	368.0	401.0	438.9	489.7	557.4	640.6
130°	308.6	312.3	321.7	334.9	353.7	380.0	412.9	448.7	495.8	555.9	629.3
132.5°	317.5	322.1	332.2	346.2	365.7	392.1	423.5	458.5	501.7	555.2	620.3
135°	331.1	334.9	346.2	360.2	381.9	408.2	438.4	471.3	508.9	554.0	607.7
137.5°	343.9	348.5	359.7	374.8	396.2	420.7	450.4	481.1	515.3	553.8	598.8
140°	353.7	357.5	368.7	383.8	404.5	429.0	457.1	486.4	518.3	553.1	593.6
142.5°	363.4	366.5	377.0	392.1	412.0	435.0	462.4	490.9	520.6	553.1	588.3
145°	378.1	381.9	391.3	405.5	424.2	445.0	470.3	496.7	523.0	551.2	581.4
147.5°	394.0	396.8	405.8	418.8	434.4	452.9	476.7	499.9	523.8	547.9	574.2
150°	404.5	407.3	414.8	427.1	441.2	458.1	479.8	501.3	523.0	545.6	568.2
152.5°	415.0	416.3	423.9	434.6	448.0	463.4	482.8	502.1	521.5	541.9	562.9
155°	429.9	430.8	436.5	446.9	457.1	471.3	487.3	503.2	519.2	535.3	553.1
157.5°	442.3	443.3	447.8	456.8	465.1	476.9	490.5	503.2	514.9	528.5	543.9
160°	450.6	451.6	455.2	462.8	470.3	480.7	492.0	503.2	512.6	524.0	537.2
162.5°	458.8	458.3	462.0	468.1	474.9	483.0	492.8	502.5	510.4	520.2	531.1
165°	468.4	467.5	469.4	475.0	479.8	485.4	493.9	500.5	506.1	512.6	521.1
167.5°	476.4	475.2	476.9	480.5	483.9	487.5	493.7	499.2	501.7	506.1	511.3
170°	481.6	479.8	480.7	483.5	485.4	488.2	492.9	497.7	499.5	502.3	506.1
172.5°	484.7	483.5	483.0	485.8	486.9	489.0	492.2	495.4	496.5	497.9	500.9
175°	488.2	487.3	486.4	488.2	488.2	489.2	491.1	492.9	492.0	492.9	493.9
177.5°	489.9	488.4	487.7	489.2	489.2	489.2	489.9	491.4	489.9	489.2	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2



TEST NUMBER: P331698-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	11.9	11.3	11.5	11.6	11.6	11.6	11.6	11.6
90°	30.1	28.2	30.1	31.0	31.0	31.0	31.0	31.0
92.5°	82.0	70.4	62.5	56.6	55.9	52.9	53.6	52.1
95°	246.5	189.1	149.6	128.8	116.7	109.1	106.3	107.3
97.5°	575.1	470.5	368.7	300.9	255.9	232.7	219.0	211.1
100°	858.8	742.2	613.3	499.5	421.4	381.0	353.7	336.8
102.5°	1044.7	1018.4	924.2	803.5	718.7	649.6	615.6	592.7
105°	1142.9	1249.2	1261.5	1230.4	1172.1	1113.8	1073.3	1060.2
107.5°	1072.2	1232.3	1330.1	1375.6	1383.0	1379.8	1371.7	1354.2
110°	1011.3	1179.6	1300.0	1377.1	1417.6	1435.5	1444.0	1443.0





TEST NUMBER: P331698-830

CATALOG NUMBER: SA2XXRDIP-C675D925U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	955.5	1117.2	1245.9	1334.3	1390.5	1420.4	1436.4	1441.5
115°	887.0	1031.9	1155.2	1252.1	1318.8	1362.1	1386.6	1395.1
117.5°	835.5	962.7	1074.4	1165.4	1233.4	1279.1	1305.0	1312.0
120°	809.9	926.6	1026.2	1111.9	1177.7	1221.9	1249.2	1258.7
122.5°	789.6	896.5	990.9	1068.3	1127.3	1170.7	1195.0	1203.0
125°	760.1	857.0	939.7	1010.3	1064.9	1100.6	1124.1	1131.6
127.5°	730.9	818.6	896.6	961.8	1009.4	1042.8	1063.2	1069.2
130°	712.1	793.0	867.3	929.4	975.5	1007.5	1026.2	1033.8
132.5°	694.0	768.9	837.2	895.5	940.8	972.9	990.1	996.9
135°	668.8	730.9	793.0	845.6	886.1	917.2	934.1	937.8
137.5°	648.7	700.6	749.9	795.8	832.7	859.4	874.3	880.0
140°	635.9	681.1	724.3	765.7	795.8	820.3	834.4	840.0
142.5°	625.4	663.7	701.0	735.7	764.2	786.5	799.0	800.1
145°	610.5	641.6	670.7	698.0	720.6	736.6	745.9	748.8
147.5°	599.0	623.5	646.2	666.2	684.9	697.6	704.0	705.7
150°	590.8	611.4	631.2	648.1	662.2	673.5	679.2	680.1
152.5°	582.5	601.6	618.4	633.1	644.1	653.9	658.1	658.3
155°	571.0	586.1	600.1	610.5	620.9	627.5	631.2	629.3
157.5°	557.6	570.2	582.1	590.2	597.5	602.9	604.6	604.6
160°	549.3	559.7	570.0	576.6	583.2	588.0	588.9	588.9
162.5°	541.1	549.9	558.7	563.8	570.4	573.6	574.6	573.8
165°	528.7	535.3	541.9	545.6	549.3	553.1	553.1	552.1
167.5°	516.8	521.9	526.4	529.8	531.5	533.6	533.4	532.3
170°	510.8	513.6	517.4	519.2	520.2	523.0	522.1	520.2
172.5°	504.0	506.1	509.1	510.2	511.1	512.5	511.5	510.4
175°	496.7	497.7	498.6	499.5	499.5	500.5	499.5	497.7
177.5°	491.4	491.4	492.2	492.2	492.2	492.2	491.4	489.9
180°	489.2	489.2	489.2	489.2	489.2	489.2	489.2	489.2

(END OF REPORT)