

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331373-935

Luminaire Tested: **SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331373-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5644.2 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	42	41	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	39	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	1.5
10°-20°	241.9	4.3
20°-30°	355.5	6.3
30°-40°	412.9	7.3
40°-50°	412.5	7.3
50°-60°	359.7	6.4
60°-70°	266.0	4.7
70°-80°	150.6	2.7
80°-90°	45.2	0.8
90°-100°	75.1	1.3
100°-110°	233.2	4.1
110°-120°	398.7	7.1
120°-130°	524.3	9.3
130°-140°	588.5	10.4
140°-150°	577.0	10.2
150°-160°	484.0	8.6
160°-170°	321.0	5.7
170°-180°	112.2	2.0
0°-30°	683.3	12.1
0°-40°	1096.3	19.4
0°-60°	1868.5	33.1
0°-90°	2330.4	41.3
90°-120°	707.0	12.5
90°-150°	2396.8	42.5
90°-180°	3314.0	58.7
0°-180°	5644.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	1	14	35	33	34	4
95°	52	62	64	64	62	60
105°	215	218	220	222	222	227
115°	400	406	404	403	400	396
125°	582	590	588	585	584	520
135°	753	764	766	765	762	582
145°	914	921	927	928	924	571
155°	1045	1048	1051	1056	1053	481
165°	1137	1136	1136	1142	1138	321
175°	1183	1180	1178	1184	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.8	13.1	13.3	13.5	13.8	14.2	14.8	15.5	16.2	16.9	16.3
90°	1.0	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5
92.5°	17.8	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9
95°	52.0	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0
97.5°	95.1	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6
100°	127.0	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0
102.5°	160.7	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0
105°	215.0	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5
107.5°	269.8	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4
110°	305.1	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.5	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1
115°	400.0	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8
117.5°	456.4	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3
120°	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0
122.5°	528.5	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9
125°	582.0	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4
127.5°	634.3	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3
130°	667.1	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6
132.5°	703.9	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9
135°	753.1	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9
137.5°	804.9	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3
140°	836.1	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1
142.5°	868.1	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7
145°	914.1	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3
147.5°	955.1	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0
150°	983.1	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8
152.5°	1007.9	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6
155°	1045.2	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2
157.5°	1076.9	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3
160°	1096.1	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4
162.5°	1113.7	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6
165°	1137.1	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7
167.5°	1156.8	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1
170°	1167.2	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7
172.5°	1174.3	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9
175°	1183.2	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7
177.5°	1186.7	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	15.8	15.2	14.6	14.3	14.2	14.0	13.9	13.9
90°	34.1	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	31.9	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.2	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	220.9	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.6	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331373-935

CATALOG NUMBER: SA2XXDIP-C675D1080U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	347.6	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.6	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.8	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	531.4	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.8	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	640.5	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	677.2	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.9	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.7	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.1	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	880.9	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.6	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	968.5	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1053.3	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1083.7	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1101.8	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1118.2	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1139.3	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1156.7	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1166.2	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1173.5	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1181.3	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)