

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331708-830

Luminaire Tested: **SA2XXRDIP-C865D330U830-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331708-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4077.8 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331708-830
CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331708-830

CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	60	57	55	51
3	86	77	70	64	82	73	67	62	66	61	57	60	55	52	53	50	48	44
4	79	69	61	55	75	65	58	53	59	54	49	54	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22315	22315	22315
5°	22400	22034	22156
10°	22228	21674	21489
15°	21972	21031	20425
20°	21618	20113	19105
25°	21257	19073	17826
30°	20752	18000	16183
35°	20262	16837	14741
40°	19770	15633	13076
45°	19192	14280	11565
50°	18600	12913	10083
55°	17990	11443	8659
60°	17286	9894	7188
65°	16485	8313	6548
70°	15526	6850	6019
75°	14361	6245	5614
80°	12673	5579	5114
85°	9967	4409	4409



TEST NUMBER: P331708-830

CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.4	3.2
10°-20°	355.2	8.7
20°-30°	498.8	12.2
30°-40°	543.9	13.3
40°-50°	500.1	12.3
50°-60°	392.8	9.6
60°-70°	256.1	6.3
70°-80°	132.0	3.2
80°-90°	35.3	0.9
90°-100°	14.0	0.3
100°-110°	51.5	1.3
110°-120°	137.7	3.4
120°-130°	227.3	5.6
130°-140°	241.8	5.9
140°-150°	224.7	5.5
150°-160°	180.7	4.4
160°-170°	116.4	2.9
170°-180°	40.1	1.0
0°-30°	983.3	24.1
0°-40°	1527.2	37.5
0°-60°	2420.1	59.3
0°-90°	2843.5	69.7
90°-120°	203.3	5.0
90°-150°	897.1	22.0
90°-180°	1234.0	30.3
0°-180°	4077.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1382	1375	1360	1370	1367	131
15°	1314	1299	1258	1235	1222	370
25°	1193	1151	1071	1021	1001	548
35°	1028	962	854	778	748	643
45°	840	754	625	540	506	649
55°	639	539	406	334	308	571
65°	432	330	218	177	171	428
75°	230	145	100	92	90	244
85°	54	29	24	24	24	63
90°	0	4	6	8	8	3
95°	20	10	12	13	13	24
105°	93	97	19	22	23	99
115°	175	181	188	54	25	172
125°	248	252	258	260	260	221
135°	307	311	314	317	317	237
145°	356	356	360	362	361	222
155°	392	389	392	394	392	180
165°	413	411	412	414	412	117
175°	422	420	421	422	420	40
180°	421	421	421	421	421	



TEST NUMBER: P331708-830

CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1387.0	1385.9	1384.8	1383.7	1382.6	1380.8	1378.4	1375.9	1373.5	1371.0	1373.3
5°	1382.1	1380.6	1379.2	1377.8	1376.5	1373.9	1370.4	1366.8	1363.1	1359.5	1362.0
7.5°	1367.7	1366.0	1364.3	1362.6	1360.8	1357.9	1353.7	1349.4	1345.2	1341.0	1341.7
10°	1355.8	1353.8	1351.9	1349.9	1347.9	1344.3	1338.7	1333.1	1327.6	1322.0	1321.2
12.5°	1340.8	1338.3	1336.0	1333.6	1331.2	1326.4	1319.3	1312.2	1305.0	1298.0	1296.5
15°	1314.5	1311.5	1308.3	1305.3	1302.2	1296.0	1286.6	1277.1	1267.6	1258.2	1252.9
17.5°	1282.2	1277.5	1272.9	1268.2	1263.6	1255.2	1243.0	1230.9	1218.8	1206.6	1200.4
20°	1258.2	1252.6	1247.1	1241.5	1236.0	1226.2	1212.3	1198.4	1184.6	1170.6	1163.7
22.5°	1232.2	1226.0	1219.7	1213.5	1207.3	1196.4	1180.6	1165.0	1149.3	1133.6	1124.6
25°	1193.2	1184.3	1175.4	1166.5	1157.6	1144.0	1125.6	1107.3	1088.9	1070.6	1059.2
27.5°	1146.1	1136.4	1126.8	1117.1	1107.5	1092.3	1071.6	1050.9	1030.2	1009.6	996.3
30°	1113.1	1102.6	1092.0	1081.5	1070.9	1054.5	1032.3	1010.0	987.8	965.5	951.4
32.5°	1081.1	1068.7	1056.4	1044.1	1031.7	1014.3	991.6	968.8	946.2	923.5	907.4
35°	1028.0	1013.9	999.8	985.5	971.4	952.1	927.6	903.1	878.7	854.2	836.7
37.5°	975.1	959.5	944.0	928.3	912.8	891.9	865.9	839.8	813.8	787.7	768.4
40°	938.0	921.3	904.7	888.0	871.3	849.5	822.6	795.6	768.6	741.7	721.9
42.5°	900.0	882.4	864.9	847.3	829.7	807.0	779.2	751.3	723.5	695.6	675.2
45°	840.5	821.8	803.2	784.6	766.0	742.1	712.9	683.7	654.5	625.4	605.6
47.5°	782.4	762.7	743.0	723.2	703.5	678.5	648.5	618.3	588.1	558.1	538.5
50°	740.5	720.7	701.0	681.2	661.5	636.3	605.8	575.1	544.6	514.1	494.8
52.5°	699.4	678.7	658.2	637.5	616.9	591.6	561.8	531.8	501.9	472.0	453.5
55°	639.1	617.5	595.8	574.1	552.4	526.5	496.5	466.5	436.5	406.5	389.8
57.5°	577.3	555.1	532.8	510.6	488.4	462.9	433.9	405.1	376.3	347.4	332.2
60°	535.3	513.0	490.9	468.6	446.4	420.9	392.3	363.6	335.1	306.4	292.3
62.5°	494.3	472.0	449.8	427.5	405.3	380.6	353.3	326.0	298.7	271.4	257.9
65°	431.5	409.0	386.4	363.9	341.5	317.6	292.7	267.7	242.6	217.6	208.2
67.5°	371.0	348.6	326.3	303.9	281.5	259.1	236.7	214.1	191.6	169.1	164.8
70°	328.9	307.3	285.6	263.9	242.2	221.8	202.6	183.4	164.3	145.1	142.3
72.5°	288.9	268.2	247.3	226.6	205.8	187.7	172.3	156.8	141.5	126.1	123.8
75°	230.2	210.7	191.2	171.7	152.3	137.9	128.4	118.9	109.5	100.1	98.1
77.5°	172.4	155.2	138.2	121.1	104.1	93.3	88.7	84.2	79.6	75.0	73.9
80°	136.3	122.2	108.0	93.8	79.6	71.2	68.3	65.6	62.8	60.0	58.9
82.5°	103.3	92.3	81.2	70.1	59.1	52.6	50.7	48.8	46.9	45.1	44.4
85°	53.8	48.0	42.1	36.3	30.4	27.1	26.3	25.4	24.6	23.8	23.8
87.5°	16.0	14.4	12.8	11.2	9.5	8.8	8.9	9.0	9.1	9.2	9.0
90°	0.3	1.0	1.8	2.5	3.3	4.0	4.4	5.0	5.6	6.1	6.4
92.5°	6.1	6.1	6.0	5.9	5.8	6.0	6.2	6.5	6.8	7.1	7.3
95°	19.8	17.5	15.4	13.1	10.8	10.0	10.5	10.9	11.4	11.9	12.3
97.5°	39.3	33.0	26.7	20.5	14.1	11.5	12.6	13.7	14.8	15.9	16.2
100°	53.9	44.7	35.3	26.1	16.9	12.7	13.9	15.1	16.2	17.3	17.9
102.5°	70.0	68.1	66.1	64.2	62.2	56.4	46.8	37.1	27.5	17.8	18.6
105°	92.7	94.6	96.7	98.8	100.8	92.6	74.1	55.6	37.0	18.6	19.3
107.5°	118.4	120.1	121.7	123.4	125.0	114.7	92.6	70.4	48.2	26.0	25.3
110°	135.0	136.4	137.9	139.3	140.7	131.6	112.1	92.5	72.9	53.3	46.6



TEST NUMBER: P331708-830

CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	150.6	151.8	153.2	154.4	155.6	153.8	149.0	144.2	139.3	134.5	109.8
115°	175.2	176.3	177.6	178.7	179.8	181.3	182.9	184.6	186.3	188.0	156.7
117.5°	197.3	198.5	199.8	201.1	202.4	203.6	204.8	205.9	207.1	208.3	200.7
120°	213.3	214.3	215.4	216.4	217.4	218.5	219.7	220.9	222.2	223.4	224.2
122.5°	227.0	228.1	229.1	230.2	231.3	232.4	233.8	235.1	236.5	237.8	238.3
125°	247.8	248.6	249.5	250.4	251.3	252.4	253.6	255.0	256.2	257.5	258.0
127.5°	266.6	267.6	268.5	269.6	270.5	271.5	272.4	273.4	274.4	275.3	276.0
130°	278.5	279.7	280.7	281.8	282.9	283.8	284.6	285.3	286.1	286.8	287.5
132.5°	290.8	291.6	292.6	293.5	294.5	295.2	296.0	296.7	297.5	298.2	298.9
135°	306.6	307.6	308.8	309.8	310.9	311.8	312.4	313.0	313.6	314.2	314.9
137.5°	322.6	323.4	324.1	324.9	325.6	326.4	327.1	327.7	328.5	329.1	329.8
140°	333.1	333.7	334.1	334.7	335.3	335.9	336.7	337.4	338.2	338.8	339.5
142.5°	341.9	342.3	342.8	343.4	343.8	344.5	345.3	346.2	347.0	347.9	348.5
145°	355.6	355.6	355.5	355.4	355.3	355.9	357.0	358.3	359.4	360.5	361.0
147.5°	367.7	367.4	367.1	366.8	366.6	367.0	368.2	369.4	370.5	371.6	371.9
150°	375.4	374.9	374.5	374.0	373.5	373.9	374.9	376.1	377.1	378.2	378.6
152.5°	382.0	381.5	381.0	380.4	379.9	380.1	381.2	382.2	383.2	384.3	384.7
155°	391.6	391.0	390.4	389.7	389.2	389.3	390.1	390.9	391.7	392.5	392.9
157.5°	399.1	398.6	398.0	397.6	397.0	397.1	397.7	398.2	398.8	399.4	399.8
160°	403.5	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.9
162.5°	407.4	407.0	406.6	406.1	405.8	405.8	406.0	406.4	406.8	407.2	407.6
165°	412.6	412.3	411.8	411.4	411.0	410.9	411.1	411.3	411.5	411.7	412.2
167.5°	416.5	416.1	415.8	415.3	414.9	414.8	415.0	415.2	415.4	415.6	416.0
170°	418.8	418.3	417.9	417.5	417.1	417.0	417.1	417.3	417.4	417.5	418.0
172.5°	420.2	419.8	419.3	419.0	418.6	418.4	418.6	418.7	418.9	419.0	419.4
175°	422.1	421.6	421.1	420.7	420.2	420.0	420.2	420.3	420.5	420.6	421.0
177.5°	422.4	422.0	421.6	421.2	420.8	420.8	420.8	420.8	420.8	420.9	421.3
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331708-830

CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1375.5	1377.7	1379.9	1380.8	1380.4	1379.9	1379.5	1379.0
5°	1364.5	1367.0	1369.5	1370.4	1369.5	1368.7	1367.8	1367.0
7.5°	1342.5	1343.1	1343.9	1343.5	1342.1	1340.7	1339.2	1337.8
10°	1320.3	1319.5	1318.6	1317.4	1315.7	1314.1	1312.4	1310.7
12.5°	1295.0	1293.5	1291.9	1289.9	1287.0	1284.3	1281.5	1278.7
15°	1247.6	1242.4	1237.1	1233.0	1230.3	1227.5	1224.7	1221.9
17.5°	1194.1	1187.8	1181.6	1176.0	1171.2	1166.5	1161.7	1156.9
20°	1156.8	1149.8	1142.8	1136.3	1130.2	1124.1	1117.9	1111.9
22.5°	1115.8	1106.8	1097.9	1091.1	1086.6	1081.9	1077.4	1072.9
25°	1047.8	1036.4	1025.0	1017.2	1013.0	1008.9	1004.8	1000.6
27.5°	983.0	969.7	956.4	946.5	939.9	933.2	926.6	920.0
30°	937.2	923.0	908.8	898.0	890.5	883.0	875.5	868.0
32.5°	891.2	875.0	858.8	847.2	840.2	833.1	826.0	819.0
35°	819.2	801.7	784.2	772.4	766.3	760.2	754.0	747.9
37.5°	749.1	729.8	710.6	697.4	690.4	683.3	676.4	669.4
40°	702.2	682.5	662.7	649.2	642.1	634.8	627.5	620.4
42.5°	654.9	634.4	614.1	600.3	593.3	586.4	579.3	572.3
45°	585.9	566.2	546.4	533.2	526.5	519.9	513.2	506.5
47.5°	518.8	499.2	479.6	466.7	460.7	454.6	448.6	442.5
50°	475.7	456.5	437.3	424.8	419.0	413.1	407.3	401.4
52.5°	435.0	416.5	397.9	386.1	380.6	375.2	369.9	364.5
55°	373.2	356.5	339.8	328.8	323.5	318.2	312.9	307.6
57.5°	316.9	301.6	286.3	276.4	272.0	267.5	263.1	258.6
60°	278.1	263.9	249.7	240.4	235.9	231.5	227.1	222.6
62.5°	244.4	230.9	217.4	209.2	206.6	204.0	201.2	198.6
65°	198.7	189.3	179.8	174.7	173.8	173.1	172.2	171.4
67.5°	160.4	156.1	151.7	149.1	148.3	147.3	146.5	145.6
70°	139.5	136.8	133.9	132.1	130.9	129.8	128.7	127.5
72.5°	121.4	119.0	116.7	115.3	114.5	113.9	113.2	112.5
75°	96.1	94.3	92.3	91.1	90.9	90.6	90.3	90.0
77.5°	72.9	71.7	70.6	69.8	69.4	68.9	68.5	68.1
80°	57.8	56.7	55.6	55.0	55.0	55.0	55.0	55.0
82.5°	43.7	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8
87.5°	9.0	8.8	8.6	8.6	8.6	8.6	8.6	8.7
90°	6.8	7.1	7.4	7.7	7.8	7.9	8.1	8.2
92.5°	7.4	7.6	7.7	7.9	8.0	8.1	8.1	8.2
95°	12.5	12.9	13.2	13.4	13.3	13.2	13.2	13.1
97.5°	16.5	16.7	17.0	17.2	17.2	17.3	17.4	17.5
100°	18.5	19.0	19.5	19.9	20.0	20.2	20.3	20.5
102.5°	19.2	20.0	20.6	21.1	21.3	21.5	21.7	21.9
105°	20.1	20.8	21.6	22.1	22.3	22.6	22.9	23.2
107.5°	24.5	23.8	23.0	22.7	23.0	23.3	23.6	23.8
110°	39.8	33.0	26.2	23.0	23.3	23.6	23.8	24.0



TEST NUMBER: P331708-830

CATALOG NUMBER: SA2XXRDIP-C865D330U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	85.1	60.4	35.7	23.5	23.7	23.8	24.1	24.3
115°	125.4	94.0	62.6	44.5	39.6	34.8	29.9	25.0
117.5°	193.1	185.5	178.0	166.2	150.1	134.1	118.1	102.1
120°	225.0	225.8	226.6	222.4	213.3	204.2	195.0	185.9
122.5°	238.7	239.2	239.7	239.0	237.3	235.5	233.8	232.0
125°	258.4	258.9	259.4	259.8	260.0	260.1	260.3	260.5
127.5°	276.7	277.4	278.1	278.4	278.5	278.5	278.5	278.6
130°	288.2	289.0	289.7	290.1	290.0	289.9	289.9	289.8
132.5°	299.5	300.1	300.8	301.0	301.0	301.0	300.9	300.8
135°	315.6	316.2	316.9	317.2	317.1	316.9	316.8	316.6
137.5°	330.5	331.1	331.8	332.0	331.8	331.6	331.3	331.1
140°	340.1	340.7	341.3	341.5	341.1	340.8	340.4	340.1
142.5°	349.0	349.6	350.2	350.2	349.9	349.6	349.2	348.8
145°	361.5	361.9	362.4	362.5	362.1	361.8	361.5	361.1
147.5°	372.3	372.7	373.1	373.1	372.8	372.5	372.2	371.9
150°	379.0	379.4	379.8	379.8	379.6	379.2	378.8	378.5
152.5°	385.1	385.5	385.9	385.9	385.4	385.0	384.6	384.1
155°	393.3	393.7	394.2	394.1	393.5	393.0	392.5	391.9
157.5°	400.3	400.8	401.1	401.1	400.6	400.1	399.5	399.1
160°	404.4	404.7	405.1	405.1	404.6	404.2	403.7	403.2
162.5°	408.0	408.5	409.0	409.0	408.3	407.7	407.2	406.6
165°	412.6	413.1	413.6	413.6	413.1	412.6	412.2	411.7
167.5°	416.5	417.0	417.5	417.4	416.8	416.1	415.6	414.9
170°	418.5	419.0	419.4	419.3	418.8	418.1	417.5	416.9
172.5°	419.9	420.4	420.8	420.8	420.2	419.6	419.0	418.4
175°	421.5	422.0	422.4	422.4	421.7	421.0	420.3	419.6
177.5°	421.7	422.1	422.4	422.4	421.9	421.4	420.9	420.5
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1

(END OF REPORT)