

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331715-830

Luminaire Tested: **SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331715-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4625.9 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331715-830
CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331715-830

CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	75	70	70	66	63	62	59	56	53	51	49	45
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37	34
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	27
7	62	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22315	22315	22315
5°	22400	22034	22156
10°	22228	21674	21489
15°	21972	21031	20425
20°	21618	20113	19105
25°	21257	19073	17826
30°	20752	18000	16183
35°	20262	16837	14741
40°	19770	15633	13076
45°	19192	14280	11565
50°	18600	12913	10083
55°	17990	11443	8659
60°	17286	9894	7188
65°	16485	8313	6548
70°	15526	6850	6019
75°	14361	6245	5614
80°	12673	5579	5114
85°	9967	4409	4409



TEST NUMBER: P331715-830

CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.4	2.8
10°-20°	355.2	7.7
20°-30°	498.8	10.8
30°-40°	543.9	11.8
40°-50°	500.1	10.8
50°-60°	392.8	8.5
60°-70°	256.1	5.5
70°-80°	132.0	2.9
80°-90°	36.8	0.8
90°-100°	40.4	0.9
100°-110°	125.3	2.7
110°-120°	214.3	4.6
120°-130°	281.8	6.1
130°-140°	316.2	6.8
140°-150°	310.1	6.7
150°-160°	260.1	5.6
160°-170°	172.5	3.7
170°-180°	60.3	1.3
0°-30°	983.3	21.3
0°-40°	1527.2	33.0
0°-60°	2420.1	52.3
0°-90°	2845.0	61.5
90°-120°	380.0	8.2
90°-150°	1288.0	27.8
90°-180°	1781.0	38.5
0°-180°	4625.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1382	1375	1360	1370	1367	131
15°	1314	1299	1258	1235	1222	370
25°	1193	1151	1071	1021	1001	548
35°	1028	962	854	778	748	643
45°	840	754	625	540	506	649
55°	639	539	406	334	308	571
65°	432	330	218	177	171	428
75°	230	145	100	92	90	244
85°	54	29	24	24	24	63
90°	1	7	19	18	18	4
95°	28	33	34	34	33	32
105°	116	117	118	119	119	122
115°	215	218	217	217	215	213
125°	313	317	316	314	314	279
135°	405	410	412	411	410	312
145°	491	495	498	499	497	307
155°	562	563	565	567	566	258
165°	611	611	611	614	612	172
175°	636	634	633	637	634	60
180°	637	637	637	637	637	



TEST NUMBER: P331715-830

CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1387.0	1385.9	1384.8	1383.7	1382.6	1380.8	1378.4	1375.9	1373.5	1371.0	1373.3
5°	1382.1	1380.6	1379.2	1377.8	1376.5	1373.9	1370.4	1366.8	1363.1	1359.5	1362.0
7.5°	1367.7	1366.0	1364.3	1362.6	1360.8	1357.9	1353.7	1349.4	1345.2	1341.0	1341.7
10°	1355.8	1353.8	1351.9	1349.9	1347.9	1344.3	1338.7	1333.1	1327.6	1322.0	1321.2
12.5°	1340.8	1338.3	1336.0	1333.6	1331.2	1326.4	1319.3	1312.2	1305.0	1298.0	1296.5
15°	1314.5	1311.5	1308.3	1305.3	1302.2	1296.0	1286.6	1277.1	1267.6	1258.2	1252.9
17.5°	1282.2	1277.5	1272.9	1268.2	1263.6	1255.2	1243.0	1230.9	1218.8	1206.6	1200.4
20°	1258.2	1252.6	1247.1	1241.5	1236.0	1226.2	1212.3	1198.4	1184.6	1170.6	1163.7
22.5°	1232.2	1226.0	1219.7	1213.5	1207.3	1196.4	1180.6	1165.0	1149.3	1133.6	1124.6
25°	1193.2	1184.3	1175.4	1166.5	1157.6	1144.0	1125.6	1107.3	1088.9	1070.6	1059.2
27.5°	1146.1	1136.4	1126.8	1117.1	1107.5	1092.3	1071.6	1050.9	1030.2	1009.6	996.3
30°	1113.1	1102.6	1092.0	1081.5	1070.9	1054.5	1032.3	1010.0	987.8	965.5	951.4
32.5°	1081.1	1068.7	1056.4	1044.1	1031.7	1014.3	991.6	968.8	946.2	923.5	907.4
35°	1028.0	1013.9	999.8	985.5	971.4	952.1	927.6	903.1	878.7	854.2	836.7
37.5°	975.1	959.5	944.0	928.3	912.8	891.9	865.9	839.8	813.8	787.7	768.4
40°	938.0	921.3	904.7	888.0	871.3	849.5	822.6	795.6	768.6	741.7	721.9
42.5°	900.0	882.4	864.9	847.3	829.7	807.0	779.2	751.3	723.5	695.6	675.2
45°	840.5	821.8	803.2	784.6	766.0	742.1	712.9	683.7	654.5	625.4	605.6
47.5°	782.4	762.7	743.0	723.2	703.5	678.5	648.5	618.3	588.1	558.1	538.5
50°	740.5	720.7	701.0	681.2	661.5	636.3	605.8	575.1	544.6	514.1	494.8
52.5°	699.4	678.7	658.2	637.5	616.9	591.6	561.8	531.8	501.9	472.0	453.5
55°	639.1	617.5	595.8	574.1	552.4	526.5	496.5	466.5	436.5	406.5	389.8
57.5°	577.3	555.1	532.8	510.6	488.4	462.9	433.9	405.1	376.3	347.4	332.2
60°	535.3	513.0	490.9	468.6	446.4	420.9	392.3	363.6	335.1	306.4	292.3
62.5°	494.3	472.0	449.8	427.5	405.3	380.6	353.3	326.0	298.7	271.4	257.9
65°	431.5	409.0	386.4	363.9	341.5	317.6	292.7	267.7	242.6	217.6	208.2
67.5°	371.0	348.6	326.3	303.9	281.5	259.1	236.7	214.1	191.6	169.1	164.8
70°	328.9	307.3	285.6	263.9	242.2	221.8	202.6	183.4	164.3	145.1	142.3
72.5°	288.9	268.2	247.3	226.6	205.8	187.7	172.3	156.8	141.5	126.1	123.8
75°	230.2	210.7	191.2	171.7	152.3	137.9	128.4	118.9	109.5	100.1	98.1
77.5°	172.4	155.2	138.2	121.1	104.1	93.3	88.7	84.2	79.6	75.0	73.9
80°	136.3	122.2	108.0	93.8	79.6	71.2	68.3	65.6	62.8	60.0	58.9
82.5°	103.3	92.3	81.2	70.1	59.1	52.6	50.7	48.8	46.9	45.1	44.4
85°	53.8	48.0	42.1	36.3	30.4	27.1	26.3	25.4	24.6	23.8	23.8
87.5°	16.1	14.6	13.1	11.6	10.2	9.7	10.2	10.7	11.2	11.8	11.5
90°	0.6	2.0	3.4	4.8	6.3	8.3	10.9	13.6	16.2	18.9	18.6
92.5°	9.6	10.7	11.7	12.7	13.8	14.6	15.3	15.8	16.5	17.1	17.2
95°	28.0	29.1	30.3	31.6	32.7	33.5	33.6	33.9	34.1	34.4	34.4
97.5°	51.1	52.1	53.2	54.2	55.2	56.0	56.5	56.9	57.4	57.9	57.9
100°	68.2	69.2	70.1	71.2	72.1	72.8	73.1	73.4	73.8	74.2	74.2
102.5°	86.3	87.1	87.8	88.6	89.4	90.0	90.5	90.9	91.3	91.8	91.9
105°	115.6	115.9	116.3	116.6	117.0	117.3	117.5	117.7	118.0	118.3	118.5
107.5°	145.1	145.5	146.1	146.6	147.1	147.4	147.4	147.4	147.4	147.4	147.5
110°	163.9	164.7	165.3	166.1	166.8	167.1	167.1	167.1	167.1	167.1	167.1



TEST NUMBER: P331715-830

CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	184.5	185.3	186.0	186.7	187.5	187.8	187.7	187.6	187.5	187.4	187.1
115°	215.0	215.7	216.4	217.2	217.8	218.1	217.8	217.6	217.4	217.2	217.1
117.5°	245.3	246.3	247.2	248.2	249.1	249.3	248.6	247.9	247.2	246.6	246.3
120°	265.5	266.5	267.4	268.3	269.4	269.4	268.3	267.4	266.5	265.5	265.5
122.5°	284.0	285.1	286.3	287.5	288.6	288.8	288.1	287.5	286.8	286.2	285.9
125°	312.8	313.9	315.0	316.0	317.1	317.4	317.1	316.8	316.4	316.0	315.7
127.5°	340.8	342.2	343.6	345.0	346.3	346.8	346.4	345.9	345.5	345.1	344.6
130°	358.5	360.1	361.6	363.2	364.7	365.3	365.1	364.9	364.7	364.4	364.2
132.5°	378.2	379.6	380.8	382.1	383.3	384.0	384.1	384.1	384.2	384.2	383.7
135°	404.7	406.0	407.4	408.7	410.0	410.8	410.9	411.2	411.5	411.7	411.6
137.5°	432.5	433.7	434.7	435.8	436.9	437.5	437.9	438.2	438.5	438.8	438.7
140°	449.3	450.4	451.5	452.5	453.6	454.5	455.1	455.6	456.3	456.9	456.9
142.5°	466.6	467.6	468.7	469.8	470.8	471.6	472.0	472.4	472.8	473.2	473.3
145°	491.3	492.1	492.9	493.8	494.6	495.4	496.1	496.8	497.6	498.2	498.3
147.5°	513.3	514.3	515.3	516.3	517.3	518.0	518.5	519.0	519.4	520.0	520.2
150°	528.4	529.0	529.8	530.5	531.2	531.8	532.3	532.7	533.2	533.8	534.0
152.5°	541.7	542.4	543.1	543.8	544.5	545.2	545.7	546.3	546.9	547.5	547.9
155°	561.7	562.0	562.4	562.7	563.1	563.5	563.8	564.2	564.5	564.9	565.5
157.5°	578.7	579.0	579.2	579.5	579.8	579.9	580.1	580.4	580.6	580.8	581.6
160°	589.1	589.3	589.6	589.7	590.0	590.2	590.3	590.4	590.6	590.7	591.4
162.5°	598.5	598.6	598.6	598.7	598.7	598.8	598.9	599.1	599.2	599.3	600.1
165°	611.1	611.0	610.9	610.8	610.7	610.6	610.6	610.6	610.6	610.6	611.4
167.5°	621.6	621.3	620.9	620.6	620.2	620.0	620.0	620.0	619.9	619.9	620.8
170°	627.3	626.9	626.5	626.1	625.8	625.6	625.5	625.3	625.2	625.1	625.9
172.5°	631.1	630.7	630.4	630.0	629.7	629.4	629.3	629.2	629.1	629.0	629.8
175°	635.8	635.5	635.1	634.8	634.4	634.1	633.9	633.7	633.4	633.1	634.0
177.5°	637.8	637.4	637.2	636.9	636.6	636.4	636.2	636.0	635.8	635.7	636.2
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9



TEST NUMBER: P331715-830
 CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1	1382.1
2.5°	1375.5	1377.7	1379.9	1380.8	1380.4	1379.9	1379.5	1379.0
5°	1364.5	1367.0	1369.5	1370.4	1369.5	1368.7	1367.8	1367.0
7.5°	1342.5	1343.1	1343.9	1343.5	1342.1	1340.7	1339.2	1337.8
10°	1320.3	1319.5	1318.6	1317.4	1315.7	1314.1	1312.4	1310.7
12.5°	1295.0	1293.5	1291.9	1289.9	1287.0	1284.3	1281.5	1278.7
15°	1247.6	1242.4	1237.1	1233.0	1230.3	1227.5	1224.7	1221.9
17.5°	1194.1	1187.8	1181.6	1176.0	1171.2	1166.5	1161.7	1156.9
20°	1156.8	1149.8	1142.8	1136.3	1130.2	1124.1	1117.9	1111.9
22.5°	1115.8	1106.8	1097.9	1091.1	1086.6	1081.9	1077.4	1072.9
25°	1047.8	1036.4	1025.0	1017.2	1013.0	1008.9	1004.8	1000.6
27.5°	983.0	969.7	956.4	946.5	939.9	933.2	926.6	920.0
30°	937.2	923.0	908.8	898.0	890.5	883.0	875.5	868.0
32.5°	891.2	875.0	858.8	847.2	840.2	833.1	826.0	819.0
35°	819.2	801.7	784.2	772.4	766.3	760.2	754.0	747.9
37.5°	749.1	729.8	710.6	697.4	690.4	683.3	676.4	669.4
40°	702.2	682.5	662.7	649.2	642.1	634.8	627.5	620.4
42.5°	654.9	634.4	614.1	600.3	593.3	586.4	579.3	572.3
45°	585.9	566.2	546.4	533.2	526.5	519.9	513.2	506.5
47.5°	518.8	499.2	479.6	466.7	460.7	454.6	448.6	442.5
50°	475.7	456.5	437.3	424.8	419.0	413.1	407.3	401.4
52.5°	435.0	416.5	397.9	386.1	380.6	375.2	369.9	364.5
55°	373.2	356.5	339.8	328.8	323.5	318.2	312.9	307.6
57.5°	316.9	301.6	286.3	276.4	272.0	267.5	263.1	258.6
60°	278.1	263.9	249.7	240.4	235.9	231.5	227.1	222.6
62.5°	244.4	230.9	217.4	209.2	206.6	204.0	201.2	198.6
65°	198.7	189.3	179.8	174.7	173.8	173.1	172.2	171.4
67.5°	160.4	156.1	151.7	149.1	148.3	147.3	146.5	145.6
70°	139.5	136.8	133.9	132.1	130.9	129.8	128.7	127.5
72.5°	121.4	119.0	116.7	115.3	114.5	113.9	113.2	112.5
75°	96.1	94.3	92.3	91.1	90.9	90.6	90.3	90.0
77.5°	72.9	71.7	70.6	69.8	69.4	68.9	68.5	68.1
80°	57.8	56.7	55.6	55.0	55.0	55.0	55.0	55.0
82.5°	43.7	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.8	23.8	23.8	23.8	23.8	23.8	23.8	23.8
87.5°	11.2	10.9	10.7	10.6	10.6	10.7	10.7	10.7
90°	18.4	18.1	17.8	17.8	17.9	18.0	18.2	18.3
92.5°	17.2	17.2	17.2	17.3	17.3	17.3	17.4	17.4
95°	34.4	34.4	34.4	34.3	34.0	33.8	33.6	33.4
97.5°	57.9	57.9	57.9	57.8	57.8	57.8	57.8	57.7
100°	74.2	74.2	74.2	74.1	74.0	73.9	73.8	73.6
102.5°	92.0	92.1	92.2	92.2	92.1	91.9	91.8	91.7
105°	118.8	118.9	119.2	119.3	119.3	119.3	119.3	119.3
107.5°	147.6	147.7	147.8	147.5	146.9	146.5	145.9	145.3
110°	167.1	167.1	167.1	167.0	166.6	166.3	165.9	165.5



TEST NUMBER: P331715-830

CATALOG NUMBER: SA2XXRDIP-C865D530U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	186.8	186.5	186.2	186.0	185.7	185.4	185.1	184.9
115°	216.9	216.8	216.7	216.4	216.0	215.7	215.4	215.0
117.5°	246.0	245.7	245.4	245.2	244.8	244.4	244.0	243.6
120°	265.5	265.5	265.5	265.3	264.9	264.7	264.3	263.9
122.5°	285.6	285.3	285.0	284.7	284.5	284.2	284.0	283.7
125°	315.3	315.0	314.6	314.3	314.2	314.1	314.0	313.9
127.5°	344.2	343.7	343.4	342.9	342.5	342.1	341.8	341.4
130°	363.9	363.7	363.4	363.1	362.6	362.1	361.7	361.2
132.5°	383.1	382.6	382.1	381.6	381.3	380.9	380.5	380.1
135°	411.5	411.3	411.2	410.9	410.7	410.3	409.9	409.5
137.5°	438.6	438.5	438.4	438.1	437.6	437.2	436.7	436.2
140°	456.9	456.9	456.9	456.7	456.1	455.6	455.2	454.7
142.5°	473.3	473.4	473.5	473.3	472.9	472.4	471.9	471.5
145°	498.5	498.6	498.7	498.5	498.0	497.6	497.1	496.6
147.5°	520.5	520.8	521.0	520.9	520.5	520.0	519.5	519.1
150°	534.4	534.8	535.2	535.2	534.8	534.4	534.0	533.8
152.5°	548.4	548.8	549.3	549.3	548.8	548.4	547.9	547.5
155°	566.1	566.7	567.3	567.4	567.0	566.7	566.3	566.0
157.5°	582.4	583.2	584.1	584.2	583.6	583.1	582.5	581.8
160°	592.1	592.9	593.5	593.7	593.2	592.8	592.2	591.7
162.5°	600.9	601.7	602.6	602.7	602.1	601.5	601.0	600.4
165°	612.3	613.1	613.9	614.1	613.4	612.8	612.3	611.6
167.5°	621.6	622.5	623.3	623.4	622.7	622.2	621.5	620.9
170°	626.8	627.6	628.4	628.5	627.7	627.1	626.3	625.7
172.5°	630.7	631.5	632.3	632.4	631.7	630.9	630.2	629.5
175°	634.8	635.7	636.5	636.6	635.8	635.1	634.4	633.7
177.5°	636.8	637.3	637.9	637.9	637.3	636.8	636.2	635.7
180°	636.9	636.9	636.9	636.9	636.9	636.9	636.9	636.9

(END OF REPORT)