

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331337-935

Luminaire Tested: **SA2XXDIP-C675D330U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331337-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3335.0 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331337-935  
CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331337-935

CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR	0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	74	74	70																			
	1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63	63	63	63	63	63	63	63	63	59																			
	2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53	53	53	53	53	53	53	53	53	49																			
	3	85	75	68	61	80	71	64	59	64	59	54	57	53	50	51	48	45	45	45	45	45	45	45	45	45	42																			
	4	78	67	58	52	73	63	56	50	57	51	46	51	46	43	46	42	39	39	39	39	39	39	39	39	39	36																			
	5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	34	34	34	34	34	34	34	34	31																			
	6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	30	30	30	30	30	30	30	30	27																			
	7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	27	27	27	27	27	27	27	27	24																			
	8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	24	24	24	24	24	24	24	24	22																			
	9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22	22	22	22	22	22	22	22	22	20																			
	10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	20	20	20	20	20	20	20	20	18																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331337-935

CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.0	2.6
10°-20°	241.9	7.3
20°-30°	355.5	10.7
30°-40°	412.9	12.4
40°-50°	412.5	12.4
50°-60°	359.7	10.8
60°-70°	266.0	8.0
70°-80°	150.6	4.5
80°-90°	41.9	1.3
90°-100°	22.8	0.7
100°-110°	70.9	2.1
110°-120°	121.3	3.6
120°-130°	159.5	4.8
130°-140°	179.0	5.4
140°-150°	175.5	5.3
150°-160°	147.2	4.4
160°-170°	97.6	2.9
170°-180°	34.1	1.0
0°-30°	683.3	20.5
0°-40°	1096.3	32.9
0°-60°	1868.5	56.0
0°-90°	2327.1	69.8
90°-120°	215.0	6.4
90°-150°	729.0	21.9
90°-180°	1008.0	30.2
0°-180°	3335.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	0	4	11	10	10	3
95°	16	19	20	19	19	18
105°	65	66	67	68	68	69
115°	122	123	123	123	122	120
125°	177	180	179	178	178	158
135°	229	232	233	233	232	177
145°	278	280	282	282	281	174
155°	318	319	320	321	320	146
165°	346	346	346	347	346	98
175°	360	359	358	360	359	34
180°	360	360	360	360	360	



TEST NUMBER: P331337-935

CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.7	12.6	12.4	12.2	12.1	12.1	12.1	12.0	12.0	12.0	11.5
90°	0.3	1.1	1.9	2.8	3.5	4.7	6.2	7.7	9.1	10.7	10.5
92.5°	5.4	6.0	6.6	7.2	7.8	8.3	8.6	9.0	9.3	9.6	9.7
95°	15.8	16.5	17.1	17.8	18.5	18.9	19.0	19.2	19.4	19.5	19.5
97.5°	28.9	29.5	30.0	30.7	31.3	31.7	31.9	32.2	32.5	32.7	32.7
100°	38.7	39.2	39.7	40.3	40.8	41.2	41.3	41.6	41.8	42.0	42.0
102.5°	48.8	49.2	49.7	50.1	50.5	51.0	51.1	51.4	51.7	51.9	52.0
105°	65.4	65.6	65.8	66.0	66.2	66.4	66.6	66.6	66.8	66.9	67.1
107.5°	82.1	82.4	82.7	83.0	83.3	83.4	83.4	83.4	83.4	83.4	83.4
110°	92.8	93.2	93.6	94.0	94.4	94.6	94.6	94.6	94.6	94.6	94.6



TEST NUMBER: P331337-935

CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.4	104.9	105.3	105.6	106.1	106.2	106.2	106.2	106.1	106.1	105.9
115°	121.7	122.1	122.5	122.9	123.3	123.5	123.3	123.1	123.0	122.9	122.9
117.5°	138.8	139.4	139.9	140.4	141.0	141.1	140.7	140.3	139.9	139.6	139.4
120°	150.2	150.8	151.4	151.9	152.4	152.4	151.9	151.4	150.8	150.2	150.2
122.5°	160.7	161.4	162.0	162.6	163.3	163.5	163.1	162.7	162.3	162.0	161.8
125°	177.0	177.6	178.2	178.8	179.4	179.7	179.4	179.3	179.1	178.8	178.7
127.5°	193.0	193.7	194.5	195.2	196.0	196.2	196.0	195.8	195.5	195.3	195.0
130°	202.9	203.8	204.7	205.5	206.4	206.8	206.6	206.6	206.4	206.2	206.1
132.5°	214.1	214.8	215.5	216.2	217.0	217.3	217.3	217.4	217.4	217.4	217.1
135°	229.0	229.8	230.6	231.3	232.0	232.5	232.6	232.7	232.9	233.0	232.9
137.5°	244.8	245.4	246.0	246.7	247.3	247.6	247.8	248.0	248.1	248.3	248.3
140°	254.3	254.9	255.5	256.1	256.8	257.2	257.5	257.9	258.2	258.6	258.6
142.5°	264.1	264.7	265.3	265.9	266.5	266.9	267.1	267.3	267.6	267.8	267.9
145°	278.0	278.5	279.0	279.5	279.9	280.3	280.8	281.2	281.5	282.0	282.1
147.5°	290.5	291.1	291.6	292.2	292.7	293.2	293.4	293.8	294.0	294.3	294.5
150°	299.0	299.5	299.8	300.2	300.7	301.0	301.3	301.5	301.8	302.0	302.3
152.5°	306.6	306.9	307.4	307.8	308.2	308.6	308.8	309.2	309.5	309.9	310.1
155°	317.9	318.1	318.3	318.5	318.7	318.9	319.1	319.3	319.5	319.7	320.0
157.5°	327.5	327.7	327.8	328.0	328.1	328.2	328.4	328.5	328.6	328.7	329.2
160°	333.4	333.6	333.6	333.8	333.9	334.1	334.1	334.2	334.2	334.3	334.7
162.5°	338.7	338.8	338.8	338.8	338.9	338.9	339.0	339.1	339.1	339.1	339.7
165°	345.9	345.8	345.7	345.7	345.6	345.5	345.5	345.5	345.5	345.5	346.0
167.5°	351.8	351.6	351.5	351.2	351.0	350.9	350.9	350.9	350.9	350.9	351.3
170°	355.0	354.8	354.6	354.4	354.2	354.0	354.0	353.9	353.9	353.8	354.2
172.5°	357.1	357.0	356.8	356.5	356.4	356.2	356.2	356.1	356.0	355.9	356.5
175°	359.9	359.6	359.5	359.2	359.0	358.9	358.8	358.6	358.4	358.3	358.8
177.5°	360.9	360.8	360.6	360.5	360.3	360.2	360.1	360.0	359.8	359.7	360.1
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5



TEST NUMBER: P331337-935

CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	11.0	10.5	10.0	9.6	9.6	9.4	9.2	9.1
90°	10.4	10.2	10.1	10.1	10.2	10.2	10.2	10.3
92.5°	9.7	9.7	9.8	9.8	9.8	9.8	9.8	9.8
95°	19.5	19.5	19.5	19.4	19.3	19.1	19.0	18.9
97.5°	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.6
100°	42.0	42.0	42.0	41.9	41.8	41.8	41.8	41.7
102.5°	52.1	52.1	52.2	52.2	52.1	52.0	52.0	51.9
105°	67.2	67.3	67.5	67.5	67.5	67.5	67.5	67.5
107.5°	83.5	83.6	83.6	83.5	83.2	82.9	82.6	82.2
110°	94.6	94.6	94.6	94.5	94.3	94.1	93.9	93.7





TEST NUMBER: P331337-935

CATALOG NUMBER: SA2XXDIP-C675D330U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	105.7	105.6	105.4	105.2	105.1	105.0	104.8	104.6
115°	122.8	122.7	122.6	122.5	122.3	122.1	121.9	121.7
117.5°	139.2	139.1	138.9	138.7	138.5	138.4	138.1	137.9
120°	150.2	150.2	150.2	150.2	150.0	149.7	149.6	149.4
122.5°	161.6	161.4	161.3	161.2	161.0	160.8	160.7	160.6
125°	178.5	178.2	178.1	177.9	177.9	177.8	177.7	177.6
127.5°	194.8	194.6	194.3	194.1	193.9	193.6	193.5	193.2
130°	206.0	205.9	205.7	205.5	205.3	204.9	204.7	204.4
132.5°	216.8	216.5	216.3	216.0	215.8	215.6	215.3	215.2
135°	232.9	232.8	232.7	232.6	232.4	232.2	232.0	231.8
137.5°	248.2	248.1	248.1	248.0	247.7	247.5	247.2	246.8
140°	258.6	258.6	258.6	258.4	258.1	257.9	257.6	257.4
142.5°	267.9	267.9	268.0	267.9	267.7	267.3	267.1	266.8
145°	282.1	282.1	282.2	282.1	281.9	281.6	281.4	281.0
147.5°	294.5	294.7	294.9	294.8	294.5	294.3	294.0	293.8
150°	302.5	302.6	302.9	302.9	302.6	302.5	302.3	302.0
152.5°	310.4	310.6	310.9	310.9	310.6	310.4	310.1	309.9
155°	320.4	320.7	321.1	321.2	320.9	320.7	320.6	320.3
157.5°	329.6	330.1	330.5	330.6	330.3	329.9	329.7	329.3
160°	335.1	335.5	336.0	336.0	335.7	335.4	335.2	334.9
162.5°	340.1	340.5	341.0	341.0	340.8	340.4	340.1	339.8
165°	346.5	347.0	347.4	347.5	347.2	346.8	346.5	346.2
167.5°	351.8	352.2	352.8	352.8	352.5	352.1	351.7	351.4
170°	354.7	355.2	355.7	355.7	355.3	354.9	354.5	354.0
172.5°	356.9	357.4	357.8	357.9	357.5	357.1	356.7	356.3
175°	359.3	359.7	360.2	360.2	359.9	359.5	359.0	358.6
177.5°	360.4	360.7	361.0	361.0	360.7	360.4	360.1	359.7
180°	360.5	360.5	360.5	360.5	360.5	360.5	360.5	360.5

(END OF REPORT)