

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331462-930

Luminaire Tested: **SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331462-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6819.1 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331462-930
CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331462-930

CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331462-930

CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	1.8
10°-20°	343.8	5.0
20°-30°	505.4	7.4
30°-40°	587.0	8.6
40°-50°	586.4	8.6
50°-60°	511.4	7.5
60°-70°	378.1	5.5
70°-80°	214.2	3.1
80°-90°	60.5	0.9
90°-100°	40.0	0.6
100°-110°	146.5	2.1
110°-120°	391.7	5.7
120°-130°	646.5	9.5
130°-140°	687.6	10.1
140°-150°	639.1	9.4
150°-160°	513.8	7.5
160°-170°	331.1	4.9
170°-180°	114.0	1.7
0°-30°	971.4	14.2
0°-40°	1558.4	22.9
0°-60°	2656.1	39.0
0°-90°	3308.9	48.5
90°-120°	578.1	8.5
90°-150°	2551.3	37.4
90°-180°	3510.0	51.5
0°-180°	6819.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	10	17	22	23	5
95°	56	30	34	38	37	69
105°	264	275	53	62	66	282
115°	498	513	535	152	71	491
125°	705	716	732	738	741	628
135°	872	885	894	902	900	673
145°	1012	1011	1025	1031	1027	632
155°	1114	1107	1116	1121	1115	513
165°	1174	1169	1171	1176	1171	331
175°	1200	1195	1196	1201	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331462-930

CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.2	18.2	18.1	18.1	18.1	18.0	17.9	17.8	17.6	17.4	17.0
90°	0.9	3.0	5.1	7.3	9.4	11.2	12.7	14.3	15.8	17.4	18.3
92.5°	17.5	17.3	17.1	17.0	16.7	17.0	17.8	18.6	19.3	20.1	20.6
95°	56.3	50.0	43.6	37.3	30.9	28.4	29.8	31.1	32.4	33.8	34.7
97.5°	111.8	93.9	76.0	58.0	40.2	32.8	35.9	39.0	42.2	45.2	46.0
100°	153.4	127.0	100.6	74.3	47.9	36.3	39.5	42.9	46.1	49.4	51.0
102.5°	199.2	193.6	188.0	182.4	176.8	160.4	133.0	105.6	78.2	50.8	52.8
105°	263.5	269.3	275.0	280.8	286.6	263.2	210.6	158.0	105.4	52.8	55.0
107.5°	336.8	341.4	346.1	350.7	355.5	326.3	263.2	200.2	137.1	74.0	71.8
110°	383.9	388.0	392.1	396.1	400.1	374.3	318.6	263.0	207.3	151.6	132.4



TEST NUMBER: P331462-930

CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.4	431.9	435.5	439.0	442.6	437.6	423.8	410.1	396.3	382.5	312.3
115°	498.4	501.7	504.9	508.2	511.4	515.5	520.3	525.1	529.9	534.8	445.6
117.5°	560.9	564.6	568.3	571.9	575.6	579.0	582.4	585.7	589.0	592.3	570.7
120°	606.7	609.6	612.5	615.4	618.2	621.4	624.9	628.4	631.9	635.3	637.6
122.5°	645.6	648.6	651.6	654.7	657.7	661.1	664.9	668.6	672.5	676.2	677.6
125°	704.7	707.1	709.6	712.2	714.6	717.7	721.4	725.0	728.7	732.4	733.7
127.5°	758.2	761.0	763.8	766.5	769.3	772.0	774.8	777.5	780.2	783.0	785.0
130°	792.1	795.2	798.3	801.4	804.5	807.1	809.2	811.3	813.4	815.5	817.7
132.5°	826.8	829.5	832.1	834.7	837.3	839.7	841.8	843.9	846.0	848.2	849.9
135°	871.9	875.0	878.1	881.2	884.2	886.6	888.4	890.1	891.9	893.6	895.5
137.5°	917.5	919.7	921.8	924.0	926.1	928.1	930.2	932.1	934.1	936.0	937.9
140°	947.3	948.8	950.4	951.9	953.5	955.3	957.4	959.5	961.6	963.8	965.5
142.5°	972.2	973.6	975.0	976.4	977.8	979.7	982.1	984.6	987.0	989.4	991.0
145°	1011.5	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6
147.5°	1045.6	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9
150°	1067.8	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8
152.5°	1086.5	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1
155°	1113.7	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4
157.5°	1135.1	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0
160°	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7
162.5°	1158.6	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2
165°	1173.5	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2
167.5°	1184.6	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2
170°	1190.8	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7
172.5°	1195.0	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9
175°	1200.4	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4
177.5°	1201.3	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331462-930

CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	16.6	16.1	15.6	15.2	15.1	15.0	14.8	14.7
90°	19.2	20.2	21.2	21.9	22.3	22.7	23.0	23.4
92.5°	21.1	21.6	22.1	22.5	22.7	22.9	23.2	23.4
95°	35.7	36.7	37.7	38.1	37.8	37.7	37.4	37.3
97.5°	46.8	47.5	48.3	48.8	49.1	49.3	49.5	49.7
100°	52.5	54.1	55.6	56.5	56.9	57.3	57.7	58.0
102.5°	54.8	56.8	58.8	60.1	60.6	61.1	61.7	62.2
105°	57.1	59.2	61.3	62.8	63.6	64.3	65.1	65.9
107.5°	69.7	67.5	65.4	64.7	65.5	66.2	67.0	67.8
110°	113.2	93.9	74.6	65.4	66.1	66.9	67.7	68.5



TEST NUMBER: P331462-930

CATALOG NUMBER: SA2XXDIP-C1005D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	242.1	171.8	101.5	66.7	67.3	67.9	68.6	69.1
115°	356.4	267.3	178.1	126.5	112.7	98.8	85.0	71.1
117.5°	549.2	527.6	506.1	472.5	426.9	381.3	335.7	290.2
120°	639.9	642.2	644.6	632.7	606.7	580.7	554.6	528.7
122.5°	679.0	680.4	681.8	679.9	674.9	669.8	664.8	659.7
125°	735.1	736.4	737.8	738.7	739.3	739.9	740.5	741.0
127.5°	786.9	788.9	790.8	791.9	792.0	792.1	792.2	792.3
130°	819.8	821.9	824.0	825.0	824.8	824.6	824.4	824.3
132.5°	851.7	853.6	855.4	856.2	856.0	855.8	855.7	855.4
135°	897.4	899.4	901.2	902.0	901.6	901.2	900.9	900.5
137.5°	939.8	941.7	943.5	944.2	943.5	942.9	942.2	941.6
140°	967.3	969.0	970.7	971.1	970.1	969.1	968.2	967.3
142.5°	992.5	994.2	995.7	996.1	995.1	994.1	993.2	992.2
145°	1028.0	1029.3	1030.7	1030.9	1030.0	1029.0	1028.0	1027.0
147.5°	1058.8	1059.9	1060.9	1060.9	1060.1	1059.3	1058.5	1057.7
150°	1077.9	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1095.2	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1118.6	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1138.3	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1149.8	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1160.5	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1184.5	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1190.1	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1194.3	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1198.7	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1199.2	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)