

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331427-930

Luminaire Tested: **SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331427-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4261.8 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331427-930
CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331427-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46
4	79	68	60	53	75	65	57	52	60	53	49	55	50	46	50	46	43	40
5	73	61	52	46	69	58	50	45	54	47	42	49	44	40	45	41	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	37	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	33	28	37	31	26	34	29	25	32	27	24	22
10	51	38	31	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331427-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	2.9
10°-20°	343.8	8.1
20°-30°	505.4	11.9
30°-40°	587.0	13.8
40°-50°	586.4	13.8
50°-60°	511.4	12.0
60°-70°	378.1	8.9
70°-80°	214.2	5.0
80°-90°	59.0	1.4
90°-100°	21.6	0.5
100°-110°	67.2	1.6
110°-120°	114.8	2.7
120°-130°	151.0	3.5
130°-140°	169.5	4.0
140°-150°	166.2	3.9
150°-160°	139.4	3.3
160°-170°	92.4	2.2
170°-180°	32.3	0.8
0°-30°	971.4	22.8
0°-40°	1558.4	36.6
0°-60°	2656.1	62.3
0°-90°	3307.3	77.6
90°-120°	203.6	4.8
90°-150°	690.3	16.2
90°-180°	954.0	22.4
0°-180°	4261.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	4	10	10	10	3
95°	15	18	18	18	18	17
105°	62	63	63	64	64	65
115°	115	117	116	116	115	114
125°	168	170	169	168	168	150
135°	217	220	221	220	220	168
145°	263	265	267	267	266	164
155°	301	302	303	304	303	138
165°	328	327	327	329	328	92
175°	341	340	339	341	340	32
180°	341	341	341	341	341	



TEST NUMBER: P331427-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.0	17.8	17.4	17.2	16.9	16.6	16.5	16.3	16.1	16.0	15.3
90°	0.3	1.1	1.8	2.6	3.3	4.5	5.9	7.3	8.6	10.1	9.9
92.5°	5.1	5.7	6.3	6.8	7.4	7.8	8.2	8.5	8.8	9.1	9.2
95°	15.0	15.7	16.2	16.9	17.5	17.9	18.0	18.2	18.3	18.4	18.4
97.5°	27.4	28.0	28.5	29.0	29.6	30.0	30.2	30.5	30.7	31.0	31.0
100°	36.6	37.1	37.6	38.2	38.6	39.0	39.1	39.4	39.5	39.8	39.8
102.5°	46.2	46.6	47.0	47.5	47.9	48.3	48.4	48.7	48.9	49.2	49.2
105°	62.0	62.1	62.3	62.5	62.7	62.9	63.0	63.1	63.3	63.3	63.5
107.5°	77.7	78.0	78.3	78.6	78.8	79.0	79.0	79.0	79.0	79.0	79.0
110°	87.9	88.2	88.6	89.0	89.4	89.6	89.6	89.6	89.6	89.6	89.6



TEST NUMBER: P331427-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.9	99.3	99.7	100.0	100.4	100.6	100.5	100.5	100.4	100.4	100.3
115°	115.2	115.6	116.0	116.3	116.8	116.9	116.8	116.6	116.5	116.3	116.3
117.5°	131.4	132.0	132.5	133.0	133.5	133.6	133.2	132.9	132.5	132.2	132.0
120°	142.3	142.8	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3	142.3
122.5°	152.2	152.8	153.4	154.0	154.7	154.8	154.4	154.1	153.7	153.4	153.2
125°	167.6	168.2	168.8	169.3	169.9	170.2	169.9	169.7	169.6	169.3	169.2
127.5°	182.7	183.4	184.2	184.8	185.6	185.8	185.6	185.4	185.2	184.9	184.7
130°	192.2	193.0	193.8	194.6	195.4	195.8	195.7	195.6	195.4	195.3	195.2
132.5°	202.8	203.4	204.1	204.7	205.5	205.8	205.8	205.9	205.9	205.9	205.6
135°	216.9	217.6	218.3	219.0	219.7	220.1	220.3	220.4	220.5	220.6	220.5
137.5°	231.8	232.4	232.9	233.6	234.2	234.5	234.6	234.8	235.0	235.1	235.1
140°	240.8	241.4	242.0	242.6	243.1	243.5	243.9	244.2	244.5	244.8	244.8
142.5°	250.1	250.6	251.2	251.8	252.3	252.7	252.9	253.2	253.4	253.6	253.6
145°	263.3	263.7	264.2	264.6	265.1	265.5	265.9	266.3	266.6	267.0	267.1
147.5°	275.1	275.7	276.1	276.7	277.2	277.6	277.9	278.2	278.4	278.7	278.8
150°	283.2	283.6	283.9	284.3	284.7	285.0	285.3	285.5	285.8	286.0	286.3
152.5°	290.3	290.7	291.1	291.5	291.8	292.2	292.4	292.8	293.1	293.4	293.7
155°	301.0	301.2	301.4	301.6	301.7	302.0	302.1	302.3	302.6	302.7	303.0
157.5°	310.1	310.3	310.4	310.5	310.7	310.8	311.0	311.0	311.1	311.3	311.7
160°	315.7	315.8	315.9	316.1	316.2	316.3	316.3	316.4	316.5	316.6	316.9
162.5°	320.7	320.8	320.8	320.8	320.9	320.9	321.0	321.1	321.1	321.1	321.6
165°	327.5	327.4	327.3	327.3	327.3	327.2	327.2	327.2	327.2	327.2	327.7
167.5°	333.1	333.0	332.8	332.6	332.4	332.3	332.2	332.2	332.2	332.2	332.6
170°	336.1	336.0	335.7	335.6	335.4	335.3	335.2	335.1	335.1	335.0	335.4
172.5°	338.2	338.0	337.9	337.6	337.5	337.3	337.3	337.2	337.1	337.0	337.5
175°	340.8	340.6	340.4	340.1	340.0	339.8	339.7	339.6	339.4	339.3	339.7
177.5°	341.8	341.6	341.4	341.4	341.2	341.0	341.0	340.9	340.7	340.6	341.0
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331427-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	14.6	13.9	13.2	12.8	12.6	12.4	12.1	12.0
90°	9.9	9.7	9.5	9.5	9.6	9.7	9.7	9.8
92.5°	9.2	9.2	9.3	9.3	9.3	9.3	9.3	9.3
95°	18.4	18.4	18.4	18.3	18.3	18.1	18.0	17.9
97.5°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.9
100°	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.5
102.5°	49.3	49.3	49.4	49.4	49.3	49.2	49.2	49.2
105°	63.6	63.8	63.9	63.9	63.9	63.9	63.9	63.9
107.5°	79.1	79.2	79.2	79.1	78.8	78.5	78.2	77.9
110°	89.6	89.6	89.6	89.5	89.3	89.1	88.9	88.7



TEST NUMBER: P331427-930

CATALOG NUMBER: SA2XXDIP-C1005D330U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	100.1	100.0	99.8	99.6	99.5	99.4	99.2	99.1
115°	116.3	116.2	116.1	116.0	115.8	115.6	115.4	115.2
117.5°	131.8	131.7	131.5	131.3	131.2	131.0	130.8	130.6
120°	142.3	142.3	142.3	142.2	142.0	141.8	141.6	141.5
122.5°	153.0	152.9	152.7	152.6	152.5	152.3	152.1	152.1
125°	169.0	168.8	168.6	168.4	168.4	168.4	168.3	168.2
127.5°	184.5	184.3	184.0	183.8	183.6	183.4	183.2	183.0
130°	195.0	194.9	194.8	194.6	194.4	194.0	193.8	193.6
132.5°	205.3	205.0	204.8	204.6	204.3	204.2	203.9	203.7
135°	220.5	220.5	220.4	220.3	220.0	219.9	219.7	219.5
137.5°	235.1	235.0	235.0	234.8	234.6	234.3	234.1	233.7
140°	244.8	244.8	244.8	244.7	244.4	244.2	243.9	243.7
142.5°	253.7	253.7	253.8	253.7	253.5	253.2	252.9	252.7
145°	267.2	267.2	267.3	267.2	266.9	266.7	266.4	266.1
147.5°	278.9	279.1	279.2	279.2	278.9	278.7	278.4	278.2
150°	286.4	286.6	286.8	286.8	286.6	286.4	286.3	286.0
152.5°	293.9	294.2	294.4	294.4	294.2	293.9	293.7	293.4
155°	303.4	303.7	304.0	304.1	303.9	303.7	303.5	303.3
157.5°	312.1	312.6	313.0	313.1	312.7	312.4	312.2	311.9
160°	317.3	317.7	318.1	318.1	317.9	317.6	317.4	317.2
162.5°	322.0	322.5	322.9	322.9	322.7	322.4	322.0	321.7
165°	328.1	328.6	329.0	329.1	328.7	328.4	328.1	327.8
167.5°	333.1	333.5	334.0	334.1	333.8	333.4	333.0	332.7
170°	335.9	336.3	336.8	336.8	336.5	336.1	335.7	335.3
172.5°	337.9	338.4	338.8	338.9	338.5	338.1	337.8	337.4
175°	340.2	340.6	341.1	341.1	340.8	340.4	340.0	339.6
177.5°	341.3	341.5	341.9	341.9	341.5	341.3	341.0	340.6
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4

(END OF REPORT)