

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331435-930

Luminaire Tested: **SA2XXDIP-C1005D530U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331435-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5030.6 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.2	2.4
10°-20°	343.8	6.8
20°-30°	505.4	10.0
30°-40°	587.0	11.7
40°-50°	586.4	11.7
50°-60°	511.4	10.2
60°-70°	378.1	7.5
70°-80°	214.2	4.3
80°-90°	59.0	1.2
90°-100°	19.6	0.4
100°-110°	71.9	1.4
110°-120°	192.3	3.8
120°-130°	317.4	6.3
130°-140°	337.5	6.7
140°-150°	313.7	6.2
150°-160°	252.2	5.0
160°-170°	162.5	3.2
170°-180°	55.9	1.1
0°-30°	971.4	19.3
0°-40°	1558.4	31.0
0°-60°	2656.1	52.8
0°-90°	3307.4	65.7
90°-120°	283.8	5.6
90°-150°	1252.5	24.9
90°-180°	1723.0	34.3
0°-180°	5030.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	5	8	11	12	4
95°	28	15	17	19	18	34
105°	129	135	26	30	32	138
115°	245	252	262	75	35	241
125°	346	352	360	362	364	308
135°	428	435	439	443	442	330
145°	496	497	503	506	504	310
155°	547	543	548	550	547	252
165°	576	574	575	578	575	163
175°	589	586	587	590	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.1	17.9	17.6	17.4	17.1	16.9	16.6	16.3	16.0	15.7	15.2
90°	0.4	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1
95°	27.6	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0
97.5°	54.9	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6
100°	75.3	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0
102.5°	97.8	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9
105°	129.3	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0
107.5°	165.3	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3
110°	188.5	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0



TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3
115°	244.7	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7
117.5°	275.4	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2
120°	297.8	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0
122.5°	316.9	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6
125°	345.9	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2
127.5°	372.2	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3
130°	388.9	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5
132.5°	405.9	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3
135°	428.0	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6
137.5°	450.5	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5
140°	465.0	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0
142.5°	477.3	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5
145°	496.5	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0
147.5°	513.3	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3
150°	524.2	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6
152.5°	533.4	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1
155°	546.7	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6
157.5°	557.2	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2
160°	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9
162.5°	568.8	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1
165°	576.1	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5
167.5°	581.6	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8
170°	584.6	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6
172.5°	586.7	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6
175°	589.3	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8
177.5°	589.7	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	14.5	13.9	13.4	13.0	12.9	12.6	12.5	12.3
90°	9.5	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.4	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	17.5	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.0	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	25.8	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	26.9	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	28.0	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	34.2	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	55.5	46.1	36.6	32.1	32.4	32.9	33.3	33.6





TEST NUMBER: P331435-930

CATALOG NUMBER: SA2XXDIP-C1005D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.8	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	175.0	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	269.6	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	314.1	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	333.3	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	360.9	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	386.3	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	402.4	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	418.2	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	440.6	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	461.4	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	474.8	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	487.3	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	504.7	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	519.8	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.1	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	537.7	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.2	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	558.8	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	564.4	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	569.7	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	581.5	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.2	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.3	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	588.5	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	588.7	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)