

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331279-930

Luminaire Tested: **SA2XXDIP-C290D1080U930-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331279-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4488.1 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331279-930
CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331279-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	90	86	82	78	79	76	73	70	57	55	53	40	38	37	24	23	22	15				
2	82	75	69	64	72	66	61	57	50	46	43	34	32	31	21	19	18	12				
3	75	65	58	53	65	58	52	47	43	39	36	30	28	25	18	17	15	10				
4	68	58	50	44	60	51	44	39	38	34	30	27	24	22	16	14	13	8				
5	62	51	43	37	55	45	38	33	34	29	26	24	21	18	14	13	11	7				
6	57	45	38	32	50	40	34	29	31	26	22	21	18	16	13	11	10	6				
7	53	41	33	28	46	36	30	25	27	23	19	19	16	14	12	10	9	6				
8	49	37	29	24	43	33	26	22	25	20	17	18	14	12	11	9	8	5				
9	45	33	26	21	40	30	23	19	23	18	15	16	13	11	10	8	7	4				
10	42	30	23	19	37	27	21	17	21	16	13	15	12	10	9	7	6	4				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4127	4127	4127
5°	4146	3973	3957
10°	4121	3855	3812
15°	4063	3730	3659
20°	3992	3597	3511
25°	3922	3468	3376
30°	3821	3336	3241
35°	3720	3209	3148
40°	3615	3101	3051
45°	3512	3004	2971
50°	3404	2917	2891
55°	3289	2822	2810
60°	3151	2723	2724
65°	3006	2608	2622
70°	2844	2485	2512
75°	2639	2365	2410
80°	2312	2240	2305
85°	2005	2134	2226



TEST NUMBER: P331279-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.2	0.5
10°-20°	69.4	1.5
20°-30°	105.2	2.3
30°-40°	128.2	2.9
40°-50°	137.9	3.1
50°-60°	133.9	3.0
60°-70°	116.9	2.6
70°-80°	90.0	2.0
80°-90°	63.4	1.4
90°-100°	81.6	1.8
100°-110°	176.9	3.9
110°-120°	411.7	9.2
120°-130°	657.7	14.7
130°-140°	692.3	15.4
140°-150°	639.9	14.3
150°-160°	513.8	11.4
160°-170°	331.1	7.4
170°-180°	114.0	2.5
0°-30°	198.9	4.4
0°-40°	327.1	7.3
0°-60°	598.8	13.3
0°-90°	869.1	19.4
90°-120°	670.2	14.9
90°-150°	2660.1	59.3
90°-180°	3619.0	80.6
0°-180°	4488.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	256	256	256	256	256	
5°	256	255	253	255	255	24
15°	244	245	245	248	248	69
25°	222	225	228	232	234	102
35°	192	198	205	213	216	120
45°	157	167	180	191	195	121
55°	120	134	153	166	171	108
65°	82	101	122	137	142	82
75°	46	66	90	105	111	48
85°	13	36	60	75	81	14
90°	5	36	66	85	92	5
95°	59	50	76	94	98	71
105°	265	288	85	106	115	284
115°	500	520	557	185	108	492
125°	705	718	745	760	767	629
135°	872	886	898	913	915	674
145°	1012	1011	1025	1033	1031	633
155°	1114	1107	1116	1121	1115	513
165°	1174	1169	1171	1176	1171	331
175°	1200	1195	1196	1201	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331279-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	255.6	255.6	255.6	255.6	255.6	255.6	255.6	255.6	255.6	255.6	255.6
2.5°	257.1	256.8	256.7	256.4	256.2	255.9	255.4	255.0	254.5	254.0	254.4
5°	256.3	256.1	255.8	255.6	255.3	254.9	254.5	254.0	253.5	253.0	253.5
7.5°	254.0	253.8	253.6	253.5	253.3	253.1	252.7	252.3	251.9	251.5	252.2
10°	252.3	252.1	251.9	251.8	251.6	251.4	251.1	250.9	250.6	250.4	251.0
12.5°	249.2	249.3	249.3	249.4	249.4	249.3	249.2	249.0	248.7	248.6	249.2
15°	244.4	244.6	244.8	244.9	245.1	245.2	245.2	245.2	245.2	245.2	245.9
17.5°	238.2	238.6	238.9	239.3	239.6	239.9	240.2	240.4	240.7	241.0	241.7
20°	234.1	234.5	234.9	235.3	235.7	236.1	236.4	236.8	237.1	237.4	238.3
22.5°	229.7	230.1	230.6	231.1	231.5	232.0	232.4	232.9	233.4	233.8	234.7
25°	222.3	222.8	223.4	224.0	224.5	225.2	225.9	226.7	227.4	228.1	229.1
27.5°	213.4	214.3	215.2	216.1	217.1	218.0	218.8	219.7	220.6	221.5	222.7
30°	207.4	208.5	209.5	210.6	211.7	212.8	213.9	214.9	216.0	217.0	218.3
32.5°	200.9	202.1	203.3	204.5	205.7	206.9	208.2	209.5	210.8	212.0	213.5
35°	191.5	192.9	194.3	195.7	197.1	198.5	200.2	201.7	203.3	204.8	206.6
37.5°	181.2	182.9	184.5	186.1	187.7	189.6	191.6	193.6	195.6	197.6	199.7
40°	174.5	176.3	178.1	179.9	181.6	183.7	185.9	188.2	190.4	192.6	194.7
42.5°	168.0	169.7	171.5	173.3	175.2	177.3	179.9	182.5	185.0	187.5	189.9
45°	157.0	159.2	161.5	163.7	165.9	168.4	171.4	174.2	177.1	180.0	182.5
47.5°	146.3	148.7	151.2	153.5	156.0	158.9	162.2	165.6	169.0	172.4	175.0
50°	138.9	141.5	144.0	146.5	149.1	152.2	156.0	159.6	163.3	167.1	169.8
52.5°	131.8	134.4	137.1	139.8	142.5	145.8	149.7	153.6	157.5	161.4	164.3
55°	120.3	123.4	126.3	129.2	132.2	135.8	140.1	144.4	148.7	153.0	156.0
57.5°	109.1	112.4	115.8	119.1	122.5	126.3	130.7	135.0	139.4	143.8	147.0
60°	101.1	104.7	108.2	111.7	115.3	119.4	124.1	128.7	133.5	138.1	141.3
62.5°	94.0	97.7	101.3	105.0	108.7	112.8	117.6	122.2	126.9	131.7	134.9
65°	82.2	86.3	90.3	94.3	98.3	102.8	107.6	112.5	117.4	122.2	125.6
67.5°	71.4	75.7	79.8	84.1	88.3	92.9	97.8	102.8	107.8	112.8	116.2
70°	63.7	68.0	72.2	76.6	80.8	85.5	90.6	95.7	100.9	105.9	109.5
72.5°	56.6	61.0	65.4	69.8	74.3	79.0	84.2	89.4	94.6	99.7	103.2
75°	45.6	50.1	54.8	59.4	64.0	68.9	74.2	79.5	84.7	90.0	93.5
77.5°	34.9	39.7	44.5	49.3	54.2	59.3	64.7	70.0	75.3	80.6	84.2
80°	27.8	32.8	37.8	42.8	47.9	53.1	58.4	63.8	69.1	74.4	77.9
82.5°	21.9	26.8	31.8	36.7	41.7	46.9	52.3	57.7	63.1	68.5	72.0
85°	13.4	18.4	23.6	28.6	33.8	38.9	44.2	49.5	54.7	60.0	63.4
87.5°	7.4	12.8	18.1	23.4	28.8	34.2	39.8	45.3	51.0	56.5	60.1
90°	4.6	11.5	18.3	25.3	32.1	39.0	45.8	52.6	59.4	66.2	70.4
92.5°	21.0	25.2	29.4	33.7	37.9	43.0	48.8	54.6	60.5	66.4	70.0
95°	59.3	56.8	54.3	51.9	49.3	51.3	57.6	63.8	70.1	76.4	80.5
97.5°	114.4	100.0	85.4	71.0	56.5	53.2	61.1	68.9	76.8	84.6	88.5
100°	156.0	132.6	109.3	86.0	62.6	54.9	62.8	70.7	78.6	86.4	91.0
102.5°	201.5	198.7	195.8	193.1	190.2	177.4	154.5	131.6	108.7	85.8	90.7
105°	265.3	273.5	281.7	289.8	298.0	277.9	229.6	181.3	133.1	84.7	89.7
107.5°	338.6	345.1	351.7	358.3	364.8	338.7	279.7	220.8	161.8	102.8	103.5
110°	385.4	391.1	396.8	402.5	408.2	385.2	333.6	281.9	230.3	178.7	162.1



TEST NUMBER: P331279-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	429.8	434.8	439.8	444.7	449.6	447.2	437.2	427.4	417.4	407.5	339.9
115°	499.9	504.0	508.2	512.3	516.6	522.9	531.4	540.0	548.5	557.0	470.3
117.5°	562.1	566.3	570.5	574.8	579.0	584.6	591.3	598.0	604.8	611.5	592.3
120°	607.8	611.0	614.2	617.4	620.7	625.7	632.4	639.2	646.0	652.7	657.3
122.5°	646.6	649.8	653.0	656.2	659.3	664.4	671.2	678.1	684.9	691.9	695.5
125°	705.4	707.8	710.4	712.9	715.3	719.7	726.1	732.4	738.7	744.9	748.5
127.5°	759.0	761.7	764.3	767.0	769.7	773.5	778.4	783.2	788.1	792.9	796.9
130°	792.9	795.9	798.9	801.9	804.9	808.3	812.2	816.0	819.9	823.7	827.8
132.5°	827.6	830.1	832.7	835.2	837.7	840.7	844.2	847.6	851.1	854.5	858.3
135°	872.3	875.4	878.4	881.5	884.6	887.5	890.0	892.5	895.1	897.6	901.3
137.5°	917.9	920.0	922.1	924.3	926.4	928.6	931.0	933.3	935.6	937.9	941.3
140°	947.7	949.2	950.6	952.0	953.5	955.4	957.7	959.9	962.2	964.5	967.6
142.5°	972.7	974.0	975.3	976.6	977.9	979.7	982.2	984.6	987.1	989.6	992.2
145°	1011.5	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1027.1
147.5°	1045.6	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9
150°	1067.8	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8
152.5°	1086.5	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1
155°	1113.7	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4
157.5°	1135.1	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0
160°	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7
162.5°	1158.6	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2
165°	1173.5	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2
167.5°	1184.6	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2
170°	1190.8	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7
172.5°	1195.0	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9
175°	1200.4	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4
177.5°	1201.3	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331279-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	255.6	255.6	255.6	255.6	255.6	255.6	255.6	255.6
2.5°	254.7	255.0	255.4	255.5	255.4	255.2	255.1	254.9
5°	254.0	254.5	254.9	255.1	255.0	254.9	254.9	254.8
7.5°	252.7	253.3	254.0	254.2	254.1	254.0	254.0	253.9
10°	251.7	252.3	253.0	253.3	253.2	253.2	253.1	253.0
12.5°	249.9	250.5	251.2	251.5	251.4	251.4	251.3	251.2
15°	246.6	247.4	248.2	248.5	248.4	248.3	248.3	248.2
17.5°	242.6	243.3	244.0	244.4	244.4	244.4	244.4	244.4
20°	239.2	240.1	241.0	241.5	241.5	241.5	241.5	241.5
22.5°	235.7	236.6	237.5	238.0	238.1	238.2	238.4	238.6
25°	230.2	231.1	232.1	232.7	232.9	233.2	233.4	233.7
27.5°	224.0	225.3	226.5	227.2	227.4	227.6	227.7	228.0
30°	219.6	221.0	222.3	223.1	223.3	223.6	223.8	224.0
32.5°	215.0	216.5	218.1	219.1	219.5	220.0	220.4	220.8
35°	208.5	210.3	212.1	213.3	213.9	214.4	215.0	215.6
37.5°	201.6	203.7	205.7	207.0	207.6	208.2	208.8	209.4
40°	196.9	199.0	201.1	202.6	203.3	204.1	204.8	205.5
42.5°	192.2	194.5	196.9	198.4	199.2	199.9	200.6	201.4
45°	185.1	187.7	190.2	191.9	192.7	193.6	194.4	195.2
47.5°	177.7	180.3	183.0	184.8	185.7	186.6	187.5	188.4
50°	172.6	175.5	178.2	180.1	181.0	181.9	182.8	183.7
52.5°	167.1	170.0	172.8	174.8	175.8	176.8	177.7	178.6
55°	158.9	161.8	164.9	166.8	167.9	169.0	170.1	171.1
57.5°	150.2	153.4	156.5	158.7	159.8	160.9	161.9	163.1
60°	144.4	147.6	150.7	152.8	153.9	155.1	156.3	157.4
62.5°	138.3	141.6	145.0	147.2	148.2	149.3	150.4	151.5
65°	129.0	132.3	135.7	137.9	139.0	140.1	141.1	142.2
67.5°	119.5	122.9	126.4	128.7	129.7	130.9	132.0	133.1
70°	113.0	116.5	120.1	122.4	123.4	124.3	125.3	126.3
72.5°	106.6	110.1	113.6	115.9	117.1	118.3	119.5	120.7
75°	97.1	100.6	104.2	106.5	107.5	108.6	109.7	110.7
77.5°	87.7	91.2	94.7	97.1	98.2	99.4	100.5	101.7
80°	81.4	84.8	88.3	90.6	91.7	92.9	94.0	95.1
82.5°	75.4	78.9	82.3	84.6	85.7	86.8	87.9	88.9
85°	66.9	70.4	73.9	76.1	77.3	78.4	79.6	80.7
87.5°	63.6	67.2	70.7	73.1	74.2	75.3	76.5	77.5
90°	74.8	79.0	83.2	86.1	87.4	88.8	90.2	91.6
92.5°	73.8	77.5	81.2	83.7	85.0	86.2	87.4	88.6
95°	84.5	88.7	92.8	95.2	96.0	96.8	97.6	98.4
97.5°	92.3	96.1	99.9	102.4	103.6	104.8	106.0	107.2
100°	95.6	100.2	104.8	107.7	109.0	110.3	111.6	112.9
102.5°	95.7	100.7	105.7	108.9	110.3	111.8	113.2	114.7
105°	94.7	99.7	104.7	108.0	109.7	111.4	113.1	114.8
107.5°	104.0	104.7	105.3	106.4	108.1	109.7	111.5	113.1
110°	145.4	128.8	112.2	104.8	106.4	108.1	109.7	111.5



TEST NUMBER: P331279-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	272.3	204.6	137.1	104.0	105.5	107.0	108.5	110.1
115°	383.6	296.9	210.2	160.3	147.3	134.4	121.4	108.5
117.5°	573.2	554.1	534.9	503.0	458.3	413.5	368.8	324.1
120°	661.9	666.5	671.2	660.9	635.9	610.7	585.6	560.5
122.5°	699.1	702.7	706.3	706.0	701.7	697.5	693.2	688.9
125°	752.1	755.7	759.2	761.7	763.0	764.3	765.6	767.0
127.5°	801.0	804.9	808.9	811.4	812.2	813.0	813.8	814.7
130°	831.9	836.0	840.1	842.4	842.9	843.3	843.8	844.2
132.5°	861.9	865.7	869.4	871.5	872.0	872.5	872.9	873.3
135°	905.0	908.6	912.2	914.2	914.5	914.8	915.0	915.3
137.5°	944.8	948.2	951.5	953.2	953.2	953.0	952.9	952.8
140°	970.6	973.6	976.7	978.0	977.5	977.1	976.6	976.2
142.5°	994.8	997.4	1000.1	1001.2	1000.6	1000.0	999.6	999.0
145°	1029.0	1030.9	1032.7	1033.3	1032.7	1032.3	1031.7	1031.1
147.5°	1059.0	1060.1	1061.1	1061.4	1060.7	1060.1	1059.5	1058.9
150°	1077.9	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1095.2	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1118.6	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1138.3	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1149.8	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1160.5	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1184.5	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1190.1	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1194.3	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1198.7	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1199.2	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)