

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331282-930

Luminaire Tested: **SA2XXDIP-C290D1080U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331282-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4493.1 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331282-930
CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331282-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22																												
1	91	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	25	18																												
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	23	22	21	15																												
3	76	67	60	54	67	59	54	49	46	42	38	33	30	28	21	19	18	13																												
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11																												
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10																												
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9																												
7	54	42	35	29	47	38	31	26	29	24	21	21	18	16	14	12	11	8																												
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7																												
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	8	6																												
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331282-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	0.8
10°-20°	101.9	2.3
20°-30°	149.8	3.3
30°-40°	174.0	3.9
40°-50°	173.8	3.9
50°-60°	151.6	3.4
60°-70°	112.1	2.5
70°-80°	63.5	1.4
80°-90°	20.0	0.4
90°-100°	40.0	0.9
100°-110°	146.5	3.3
110°-120°	391.7	8.7
120°-130°	646.5	14.4
130°-140°	687.6	15.3
140°-150°	639.1	14.2
150°-160°	513.8	11.4
160°-170°	331.1	7.4
170°-180°	114.0	2.5
0°-30°	287.9	6.4
0°-40°	461.9	10.3
0°-60°	787.3	17.5
0°-90°	982.9	21.9
90°-120°	578.1	12.9
90°-150°	2551.3	56.8
90°-180°	3510.0	78.1
0°-180°	4493.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	1	10	17	22	23	3
95°	56	30	34	38	37	69
105°	264	275	53	62	66	282
115°	498	513	535	152	71	491
125°	705	716	732	738	741	628
135°	872	885	894	902	900	673
145°	1012	1011	1025	1031	1027	632
155°	1114	1107	1116	1121	1115	513
165°	1174	1169	1171	1176	1171	331
175°	1200	1195	1196	1201	1193	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331282-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	5.8	6.1	6.4	6.7	6.9	7.1	7.3	7.4	7.6	7.6
90°	0.9	3.0	5.1	7.3	9.4	11.2	12.7	14.3	15.8	17.4	18.3
92.5°	17.5	17.3	17.1	17.0	16.7	17.0	17.8	18.6	19.3	20.1	20.6
95°	56.3	50.0	43.6	37.3	30.9	28.4	29.8	31.1	32.4	33.8	34.7
97.5°	111.8	93.9	76.0	58.0	40.2	32.8	35.9	39.0	42.2	45.2	46.0
100°	153.4	127.0	100.6	74.3	47.9	36.3	39.5	42.9	46.1	49.4	51.0
102.5°	199.2	193.6	188.0	182.4	176.8	160.4	133.0	105.6	78.2	50.8	52.8
105°	263.5	269.3	275.0	280.8	286.6	263.2	210.6	158.0	105.4	52.8	55.0
107.5°	336.8	341.4	346.1	350.7	355.5	326.3	263.2	200.2	137.1	74.0	71.8
110°	383.9	388.0	392.1	396.1	400.1	374.3	318.6	263.0	207.3	151.6	132.4



TEST NUMBER: P331282-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	428.4	431.9	435.5	439.0	442.6	437.6	423.8	410.1	396.3	382.5	312.3
115°	498.4	501.7	504.9	508.2	511.4	515.5	520.3	525.1	529.9	534.8	445.6
117.5°	560.9	564.6	568.3	571.9	575.6	579.0	582.4	585.7	589.0	592.3	570.7
120°	606.7	609.6	612.5	615.4	618.2	621.4	624.9	628.4	631.9	635.3	637.6
122.5°	645.6	648.6	651.6	654.7	657.7	661.1	664.9	668.6	672.5	676.2	677.6
125°	704.7	707.1	709.6	712.2	714.6	717.7	721.4	725.0	728.7	732.4	733.7
127.5°	758.2	761.0	763.8	766.5	769.3	772.0	774.8	777.5	780.2	783.0	785.0
130°	792.1	795.2	798.3	801.4	804.5	807.1	809.2	811.3	813.4	815.5	817.7
132.5°	826.8	829.5	832.1	834.7	837.3	839.7	841.8	843.9	846.0	848.2	849.9
135°	871.9	875.0	878.1	881.2	884.2	886.6	888.4	890.1	891.9	893.6	895.5
137.5°	917.5	919.7	921.8	924.0	926.1	928.1	930.2	932.1	934.1	936.0	937.9
140°	947.3	948.8	950.4	951.9	953.5	955.3	957.4	959.5	961.6	963.8	965.5
142.5°	972.2	973.6	975.0	976.4	977.8	979.7	982.1	984.6	987.0	989.4	991.0
145°	1011.5	1011.2	1011.1	1010.9	1010.6	1012.2	1015.5	1018.7	1022.1	1025.3	1026.6
147.5°	1045.6	1044.9	1044.2	1043.4	1042.7	1043.9	1047.2	1050.4	1053.6	1056.9	1057.9
150°	1067.8	1066.4	1065.1	1063.7	1062.4	1063.2	1066.3	1069.4	1072.5	1075.5	1076.8
152.5°	1086.5	1085.0	1083.5	1082.0	1080.5	1081.2	1084.1	1087.0	1090.0	1092.9	1094.1
155°	1113.7	1112.0	1110.3	1108.5	1106.8	1107.1	1109.4	1111.7	1114.0	1116.3	1117.4
157.5°	1135.1	1133.6	1132.1	1130.7	1129.2	1129.3	1130.9	1132.5	1134.1	1135.7	1137.0
160°	1147.5	1146.4	1145.2	1144.0	1142.9	1142.9	1144.0	1145.2	1146.4	1147.5	1148.7
162.5°	1158.6	1157.5	1156.3	1155.1	1154.0	1153.9	1154.9	1155.9	1156.9	1157.9	1159.2
165°	1173.5	1172.3	1171.2	1170.0	1168.9	1168.6	1169.1	1169.8	1170.4	1170.9	1172.2
167.5°	1184.6	1183.5	1182.3	1181.1	1180.0	1179.7	1180.2	1180.7	1181.3	1181.9	1183.2
170°	1190.8	1189.7	1188.5	1187.4	1186.3	1185.9	1186.3	1186.6	1187.0	1187.4	1188.7
172.5°	1195.0	1193.8	1192.7	1191.6	1190.4	1190.0	1190.4	1190.7	1191.2	1191.6	1192.9
175°	1200.4	1199.1	1197.7	1196.4	1195.0	1194.5	1194.9	1195.3	1195.6	1196.0	1197.4
177.5°	1201.3	1200.2	1199.1	1198.0	1196.9	1196.5	1196.6	1196.8	1196.9	1197.1	1198.2
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8



TEST NUMBER: P331282-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.7	7.7
90°	19.2	20.2	21.2	21.9	22.3	22.7	23.0	23.4
92.5°	21.1	21.6	22.1	22.5	22.7	22.9	23.2	23.4
95°	35.7	36.7	37.7	38.1	37.8	37.7	37.4	37.3
97.5°	46.8	47.5	48.3	48.8	49.1	49.3	49.5	49.7
100°	52.5	54.1	55.6	56.5	56.9	57.3	57.7	58.0
102.5°	54.8	56.8	58.8	60.1	60.6	61.1	61.7	62.2
105°	57.1	59.2	61.3	62.8	63.6	64.3	65.1	65.9
107.5°	69.7	67.5	65.4	64.7	65.5	66.2	67.0	67.8
110°	113.2	93.9	74.6	65.4	66.1	66.9	67.7	68.5



TEST NUMBER: P331282-930

CATALOG NUMBER: SA2XXDIP-C290D1080U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	242.1	171.8	101.5	66.7	67.3	67.9	68.6	69.1
115°	356.4	267.3	178.1	126.5	112.7	98.8	85.0	71.1
117.5°	549.2	527.6	506.1	472.5	426.9	381.3	335.7	290.2
120°	639.9	642.2	644.6	632.7	606.7	580.7	554.6	528.7
122.5°	679.0	680.4	681.8	679.9	674.9	669.8	664.8	659.7
125°	735.1	736.4	737.8	738.7	739.3	739.9	740.5	741.0
127.5°	786.9	788.9	790.8	791.9	792.0	792.1	792.2	792.3
130°	819.8	821.9	824.0	825.0	824.8	824.6	824.4	824.3
132.5°	851.7	853.6	855.4	856.2	856.0	855.8	855.7	855.4
135°	897.4	899.4	901.2	902.0	901.6	901.2	900.9	900.5
137.5°	939.8	941.7	943.5	944.2	943.5	942.9	942.2	941.6
140°	967.3	969.0	970.7	971.1	970.1	969.1	968.2	967.3
142.5°	992.5	994.2	995.7	996.1	995.1	994.1	993.2	992.2
145°	1028.0	1029.3	1030.7	1030.9	1030.0	1029.0	1028.0	1027.0
147.5°	1058.8	1059.9	1060.9	1060.9	1060.1	1059.3	1058.5	1057.7
150°	1077.9	1079.0	1080.2	1080.3	1079.3	1078.4	1077.4	1076.4
152.5°	1095.2	1096.4	1097.6	1097.5	1096.2	1094.9	1093.6	1092.4
155°	1118.6	1119.8	1121.0	1120.7	1119.2	1117.7	1116.1	1114.6
157.5°	1138.3	1139.6	1140.9	1140.8	1139.4	1137.8	1136.4	1134.8
160°	1149.8	1151.0	1152.1	1152.0	1150.7	1149.3	1148.0	1146.6
162.5°	1160.5	1161.8	1163.2	1162.9	1161.3	1159.7	1158.0	1156.3
165°	1173.6	1174.9	1176.3	1176.3	1174.9	1173.6	1172.2	1170.9
167.5°	1184.5	1185.9	1187.2	1187.0	1185.3	1183.6	1181.9	1180.1
170°	1190.1	1191.4	1192.8	1192.5	1190.8	1189.1	1187.4	1185.6
172.5°	1194.3	1195.6	1196.9	1196.8	1195.0	1193.3	1191.6	1189.8
175°	1198.7	1200.1	1201.4	1201.2	1199.2	1197.3	1195.4	1193.4
177.5°	1199.2	1200.3	1201.4	1201.3	1199.9	1198.5	1197.1	1195.7
180°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8

(END OF REPORT)