

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331759-935

Luminaire Tested: **SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331759-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6991.7 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.0	2.6
10°-20°	501.6	7.2
20°-30°	646.3	9.2
30°-40°	614.2	8.8
40°-50°	526.2	7.5
50°-60°	400.7	5.7
60°-70°	253.3	3.6
70°-80°	126.5	1.8
80°-90°	36.1	0.5
90°-100°	42.2	0.6
100°-110°	154.7	2.2
110°-120°	413.6	5.9
120°-130°	682.8	9.8
130°-140°	726.1	10.4
140°-150°	674.9	9.7
150°-160°	542.6	7.8
160°-170°	349.7	5.0
170°-180°	120.4	1.7
0°-30°	1327.9	19.0
0°-40°	1942.1	27.8
0°-60°	2869.0	41.0
0°-90°	3284.8	47.0
90°-120°	610.5	8.7
90°-150°	2694.3	38.5
90°-180°	3707.0	53.0
0°-180°	6991.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	25	1	25	1	25	12
95°	39	60	39	60	39	37
105°	70	278	70	278	70	72
115°	75	526	75	526	75	188
125°	783	744	783	744	783	677
135°	951	921	951	921	951	733
145°	1085	1068	1085	1068	1085	678
155°	1177	1176	1177	1176	1177	543
165°	1237	1239	1237	1239	1237	349
175°	1260	1268	1260	1268	1260	120
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	13.3	13.9	13.8	13.7	13.6	13.4	13.3	13.6	12.8	13.2	12.3
90°	24.7	24.3	23.9	23.5	23.1	22.4	21.4	20.3	19.3	18.3	16.7
92.5°	24.7	24.5	24.2	24.0	23.8	23.3	22.8	22.3	21.8	21.3	20.4
95°	39.3	39.5	39.8	40.0	40.2	39.8	38.7	37.7	36.7	35.7	34.3
97.5°	52.5	52.3	52.1	51.8	51.6	51.1	50.2	49.4	48.6	47.8	44.5
100°	61.3	61.0	60.5	60.1	59.7	58.7	57.1	55.4	53.8	52.2	48.7
102.5°	65.7	65.2	64.6	64.0	63.5	62.1	60.0	57.9	55.8	53.6	48.6
105°	69.6	68.7	67.9	67.2	66.3	64.7	62.5	60.3	58.0	55.8	48.7
107.5°	71.5	70.8	69.9	69.1	68.4	69.1	71.3	73.6	75.9	78.2	144.7
110°	72.3	71.5	70.7	69.8	69.1	78.8	99.2	119.5	139.8	160.1	219.0



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.0	72.4	71.7	71.1	70.4	107.2	181.4	255.6	329.8	404.0	418.5
115°	75.1	89.7	104.4	119.0	133.6	188.0	282.2	376.3	470.5	564.7	559.6
117.5°	306.4	354.6	402.7	450.8	498.9	534.4	557.2	580.0	602.7	625.5	622.0
120°	558.4	585.7	613.2	640.7	668.1	680.7	678.2	675.8	673.3	670.9	667.3
122.5°	696.7	702.1	707.4	712.7	718.0	720.0	718.5	717.0	715.6	714.1	710.2
125°	782.6	782.0	781.4	780.8	780.2	779.1	777.7	776.3	774.8	773.4	769.6
127.5°	836.7	836.6	836.5	836.4	836.3	835.2	833.1	831.0	829.0	826.9	824.0
130°	870.5	870.6	870.8	871.1	871.2	870.2	868.0	865.7	863.5	861.3	859.0
132.5°	903.4	903.6	903.8	904.0	904.2	903.4	901.5	899.5	897.6	895.7	893.5
135°	951.0	951.4	951.7	952.2	952.6	951.7	949.8	947.7	945.7	943.7	941.8
137.5°	994.4	995.1	995.7	996.4	997.1	996.4	994.5	992.5	990.5	988.5	986.4
140°	1021.5	1022.4	1023.5	1024.5	1025.5	1025.1	1023.3	1021.5	1019.6	1017.8	1015.5
142.5°	1047.8	1048.9	1049.8	1050.9	1051.9	1051.5	1049.9	1048.2	1046.5	1044.9	1042.3
145°	1084.6	1085.6	1086.7	1087.7	1088.6	1088.5	1087.0	1085.6	1084.2	1082.8	1079.3
147.5°	1117.0	1117.8	1118.7	1119.6	1120.4	1120.3	1119.3	1118.2	1117.1	1116.1	1112.7
150°	1136.8	1137.8	1138.8	1139.8	1140.8	1140.7	1139.5	1138.3	1137.1	1135.8	1132.6
152.5°	1153.7	1154.9	1156.3	1157.6	1159.0	1159.1	1157.9	1156.6	1155.4	1154.2	1151.1
155°	1177.1	1178.7	1180.3	1181.9	1183.5	1183.8	1182.6	1181.3	1180.1	1178.9	1176.5
157.5°	1198.4	1200.1	1201.6	1203.2	1204.8	1204.9	1203.5	1202.1	1200.8	1199.4	1197.7
160°	1210.9	1212.4	1213.8	1215.2	1216.6	1216.7	1215.5	1214.3	1213.1	1211.9	1210.7
162.5°	1221.2	1222.9	1224.7	1226.4	1228.1	1228.4	1226.9	1225.5	1224.2	1222.8	1221.8
165°	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6	1236.0
167.5°	1246.2	1248.1	1249.9	1251.7	1253.5	1253.8	1252.3	1250.9	1249.5	1248.1	1247.5
170°	1252.1	1254.0	1255.8	1257.6	1259.4	1259.6	1258.2	1256.8	1255.3	1254.0	1253.5
172.5°	1256.5	1258.4	1260.2	1262.0	1263.9	1264.0	1262.6	1261.2	1259.7	1258.4	1257.9
175°	1260.3	1262.4	1264.4	1266.4	1268.5	1268.8	1267.4	1265.9	1264.6	1263.1	1262.7
177.5°	1262.7	1264.2	1265.7	1267.1	1268.6	1268.8	1267.6	1266.4	1265.3	1264.2	1264.0
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	12.0	12.2	11.9	10.9	11.0	11.1	13.3	15.5	13.9	12.7	12.1
90°	15.1	13.4	11.8	9.9	7.7	5.4	3.2	0.9	3.2	5.4	7.7
92.5°	19.6	18.8	18.0	17.7	17.9	18.1	18.3	18.5	18.3	18.1	17.9
95°	32.9	31.4	30.0	32.6	39.3	46.1	52.8	59.5	52.8	46.1	39.3
97.5°	41.2	37.9	34.6	42.4	61.3	80.2	99.2	118.0	99.2	80.2	61.3
100°	45.3	41.8	38.3	50.5	78.4	106.2	134.1	162.0	134.1	106.2	78.4
102.5°	111.5	140.4	169.4	186.8	192.6	198.5	204.4	210.3	204.4	198.5	192.6
105°	166.9	222.4	277.9	302.6	296.5	290.4	284.4	278.3	284.4	290.4	296.5
107.5°	211.4	277.9	344.6	375.4	370.4	365.5	360.6	355.7	360.6	365.5	370.4
110°	277.8	336.5	395.3	422.6	418.3	414.1	409.7	405.4	409.7	414.1	418.3





TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	433.1	447.5	462.1	467.4	463.6	459.9	456.2	452.4	456.2	459.9	463.6
115°	554.6	549.5	544.4	540.1	536.7	533.2	529.8	526.3	529.8	533.2	536.7
117.5°	618.5	615.0	611.5	607.9	604.0	600.1	596.2	592.4	596.2	600.1	604.0
120°	663.6	660.0	656.3	652.9	649.9	646.8	643.8	640.7	643.8	646.8	649.9
122.5°	706.1	702.1	698.2	694.6	691.4	688.1	684.9	681.7	684.9	688.1	691.4
125°	765.7	761.8	757.9	754.7	752.1	749.4	746.7	744.2	746.7	749.4	752.1
127.5°	821.0	818.2	815.3	812.4	809.5	806.6	803.7	800.7	803.7	806.6	809.5
130°	856.8	854.5	852.3	849.5	846.4	843.1	839.8	836.5	839.8	843.1	846.4
132.5°	891.2	889.0	886.7	884.2	881.5	878.7	876.0	873.1	876.0	878.7	881.5
135°	940.0	938.1	936.3	933.8	930.6	927.3	924.0	920.8	924.0	927.3	930.6
137.5°	984.4	982.3	980.2	978.0	975.8	973.4	971.2	968.9	971.2	973.4	975.8
140°	1013.3	1011.1	1008.8	1006.9	1005.3	1003.7	1002.0	1000.4	1002.0	1003.7	1005.3
142.5°	1039.7	1037.2	1034.7	1032.6	1031.1	1029.7	1028.2	1026.7	1028.2	1029.7	1031.1
145°	1075.8	1072.4	1068.9	1067.3	1067.6	1067.7	1067.9	1068.2	1067.9	1067.7	1067.6
147.5°	1109.2	1105.9	1102.4	1101.1	1101.9	1102.7	1103.5	1104.2	1103.5	1102.7	1101.9
150°	1129.4	1126.1	1122.8	1122.0	1123.3	1124.8	1126.2	1127.7	1126.2	1124.8	1123.3
152.5°	1148.0	1144.9	1141.8	1141.1	1142.6	1144.2	1145.8	1147.4	1145.8	1144.2	1142.6
155°	1174.0	1171.6	1169.2	1168.8	1170.6	1172.5	1174.3	1176.1	1174.3	1172.5	1170.6
157.5°	1195.9	1194.3	1192.6	1192.5	1194.0	1195.6	1197.1	1198.7	1197.1	1195.6	1194.0
160°	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1210.7	1209.4	1208.2
162.5°	1220.7	1219.6	1218.6	1218.7	1219.9	1221.1	1222.4	1223.6	1222.4	1221.1	1219.9
165°	1235.4	1234.7	1234.1	1234.4	1235.6	1236.8	1238.0	1239.3	1238.0	1236.8	1235.6
167.5°	1246.9	1246.4	1245.8	1246.1	1247.3	1248.5	1249.8	1251.0	1249.8	1248.5	1247.3
170°	1253.1	1252.8	1252.3	1252.8	1254.0	1255.2	1256.4	1257.6	1256.4	1255.2	1254.0
172.5°	1257.5	1257.1	1256.7	1257.1	1258.4	1259.6	1260.8	1262.0	1260.8	1259.6	1258.4
175°	1262.3	1261.9	1261.5	1262.0	1263.4	1264.8	1266.3	1267.7	1266.3	1264.8	1263.4
177.5°	1263.9	1263.7	1263.5	1264.0	1265.2	1266.3	1267.5	1268.6	1267.5	1266.3	1265.2
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	12.0	11.9	11.1	11.5	11.8	11.5	11.8	11.5	11.6	11.9	11.5
90°	9.9	11.8	13.4	15.1	16.7	18.3	19.3	20.3	21.4	22.4	23.1
92.5°	17.7	18.0	18.8	19.6	20.4	21.3	21.8	22.3	22.8	23.3	23.8
95°	32.6	30.0	31.4	32.9	34.3	35.7	36.7	37.7	38.7	39.8	40.2
97.5°	42.4	34.6	37.9	41.2	44.5	47.8	48.6	49.4	50.2	51.1	51.6
100°	50.5	38.3	41.8	45.3	48.7	52.2	53.8	55.4	57.1	58.7	59.7
102.5°	186.8	169.4	140.4	111.5	82.6	53.6	55.8	57.9	60.0	62.1	63.5
105°	302.6	277.9	222.4	166.9	111.3	55.8	58.0	60.3	62.5	64.7	66.3
107.5°	375.4	344.6	277.9	211.4	144.7	78.2	75.9	73.6	71.3	69.1	68.4
110°	422.6	395.3	336.5	277.8	219.0	160.1	139.8	119.5	99.2	78.8	69.1



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	467.4	462.1	447.5	433.1	418.5	404.0	329.8	255.6	181.4	107.2	70.4
115°	540.1	544.4	549.5	554.6	559.6	564.7	470.5	376.3	282.2	188.0	133.6
117.5°	607.9	611.5	615.0	618.5	622.0	625.5	602.7	580.0	557.2	534.4	498.9
120°	652.9	656.3	660.0	663.6	667.3	670.9	673.3	675.8	678.2	680.7	668.1
122.5°	694.6	698.2	702.1	706.1	710.2	714.1	715.6	717.0	718.5	720.0	718.0
125°	754.7	757.9	761.8	765.7	769.6	773.4	774.8	776.3	777.7	779.1	780.2
127.5°	812.4	815.3	818.2	821.0	824.0	826.9	829.0	831.0	833.1	835.2	836.3
130°	849.5	852.3	854.5	856.8	859.0	861.3	863.5	865.7	868.0	870.2	871.2
132.5°	884.2	886.7	889.0	891.2	893.5	895.7	897.6	899.5	901.5	903.4	904.2
135°	933.8	936.3	938.1	940.0	941.8	943.7	945.7	947.7	949.8	951.7	952.6
137.5°	978.0	980.2	982.3	984.4	986.4	988.5	990.5	992.5	994.5	996.4	997.1
140°	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6	1021.5	1023.3	1025.1	1025.5
142.5°	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5	1048.2	1049.9	1051.5	1051.9
145°	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2	1085.6	1087.0	1088.5	1088.6
147.5°	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1	1118.2	1119.3	1120.3	1120.4
150°	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1	1138.3	1139.5	1140.7	1140.8
152.5°	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4	1156.6	1157.9	1159.1	1159.0
155°	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1	1181.3	1182.6	1183.8	1183.5
157.5°	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8	1202.1	1203.5	1204.9	1204.8
160°	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1	1214.3	1215.5	1216.7	1216.6
162.5°	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2	1225.5	1226.9	1228.4	1228.1
165°	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3
167.5°	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5	1250.9	1252.3	1253.8	1253.5
170°	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3	1256.8	1258.2	1259.6	1259.4
172.5°	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7	1261.2	1262.6	1264.0	1263.9
175°	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6	1265.9	1267.4	1268.8	1268.5
177.5°	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3	1266.4	1267.6	1268.8	1268.6
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	11.5	11.1	11.7	11.3	11.7	11.1	11.5	11.5	11.9	11.6	11.5
90°	23.5	23.9	24.3	24.7	24.3	23.9	23.5	23.1	22.4	21.4	20.3
92.5°	24.0	24.2	24.5	24.7	24.5	24.2	24.0	23.8	23.3	22.8	22.3
95°	40.0	39.8	39.5	39.3	39.5	39.8	40.0	40.2	39.8	38.7	37.7
97.5°	51.8	52.1	52.3	52.5	52.3	52.1	51.8	51.6	51.1	50.2	49.4
100°	60.1	60.5	61.0	61.3	61.0	60.5	60.1	59.7	58.7	57.1	55.4
102.5°	64.0	64.6	65.2	65.7	65.2	64.6	64.0	63.5	62.1	60.0	57.9
105°	67.2	67.9	68.7	69.6	68.7	67.9	67.2	66.3	64.7	62.5	60.3
107.5°	69.1	69.9	70.8	71.5	70.8	69.9	69.1	68.4	69.1	71.3	73.6
110°	69.8	70.7	71.5	72.3	71.5	70.7	69.8	69.1	78.8	99.2	119.5



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.1	71.7	72.4	73.0	72.4	71.7	71.1	70.4	107.2	181.4	255.6
115°	119.0	104.4	89.7	75.1	89.7	104.4	119.0	133.6	188.0	282.2	376.3
117.5°	450.8	402.7	354.6	306.4	354.6	402.7	450.8	498.9	534.4	557.2	580.0
120°	640.7	613.2	585.7	558.4	585.7	613.2	640.7	668.1	680.7	678.2	675.8
122.5°	712.7	707.4	702.1	696.7	702.1	707.4	712.7	718.0	720.0	718.5	717.0
125°	780.8	781.4	782.0	782.6	782.0	781.4	780.8	780.2	779.1	777.7	776.3
127.5°	836.4	836.5	836.6	836.7	836.6	836.5	836.4	836.3	835.2	833.1	831.0
130°	871.1	870.8	870.6	870.5	870.6	870.8	871.1	871.2	870.2	868.0	865.7
132.5°	904.0	903.8	903.6	903.4	903.6	903.8	904.0	904.2	903.4	901.5	899.5
135°	952.2	951.7	951.4	951.0	951.4	951.7	952.2	952.6	951.7	949.8	947.7
137.5°	996.4	995.7	995.1	994.4	995.1	995.7	996.4	997.1	996.4	994.5	992.5
140°	1024.5	1023.5	1022.4	1021.5	1022.4	1023.5	1024.5	1025.5	1025.1	1023.3	1021.5
142.5°	1050.9	1049.8	1048.9	1047.8	1048.9	1049.8	1050.9	1051.9	1051.5	1049.9	1048.2
145°	1087.7	1086.7	1085.6	1084.6	1085.6	1086.7	1087.7	1088.6	1088.5	1087.0	1085.6
147.5°	1119.6	1118.7	1117.8	1117.0	1117.8	1118.7	1119.6	1120.4	1120.3	1119.3	1118.2
150°	1139.8	1138.8	1137.8	1136.8	1137.8	1138.8	1139.8	1140.8	1140.7	1139.5	1138.3
152.5°	1157.6	1156.3	1154.9	1153.7	1154.9	1156.3	1157.6	1159.0	1159.1	1157.9	1156.6
155°	1181.9	1180.3	1178.7	1177.1	1178.7	1180.3	1181.9	1183.5	1183.8	1182.6	1181.3
157.5°	1203.2	1201.6	1200.1	1198.4	1200.1	1201.6	1203.2	1204.8	1204.9	1203.5	1202.1
160°	1215.2	1213.8	1212.4	1210.9	1212.4	1213.8	1215.2	1216.6	1216.7	1215.5	1214.3
162.5°	1226.4	1224.7	1222.9	1221.2	1222.9	1224.7	1226.4	1228.1	1228.4	1226.9	1225.5
165°	1240.8	1239.4	1237.9	1236.6	1237.9	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4
167.5°	1251.7	1249.9	1248.1	1246.2	1248.1	1249.9	1251.7	1253.5	1253.8	1252.3	1250.9
170°	1257.6	1255.8	1254.0	1252.1	1254.0	1255.8	1257.6	1259.4	1259.6	1258.2	1256.8
172.5°	1262.0	1260.2	1258.4	1256.5	1258.4	1260.2	1262.0	1263.9	1264.0	1262.6	1261.2
175°	1266.4	1264.4	1262.4	1260.3	1262.4	1264.4	1266.4	1268.5	1268.8	1267.4	1265.9
177.5°	1267.1	1265.7	1264.2	1262.7	1264.2	1265.7	1267.1	1268.6	1268.8	1267.6	1266.4
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	11.8	11.5	11.8	11.5	11.1	11.9	12.0	12.1	12.7	13.9	15.5
90°	19.3	18.3	16.7	15.1	13.4	11.8	9.9	7.7	5.4	3.2	0.9
92.5°	21.8	21.3	20.4	19.6	18.8	18.0	17.7	17.9	18.1	18.3	18.5
95°	36.7	35.7	34.3	32.9	31.4	30.0	32.6	39.3	46.1	52.8	59.5
97.5°	48.6	47.8	44.5	41.2	37.9	34.6	42.4	61.3	80.2	99.2	118.0
100°	53.8	52.2	48.7	45.3	41.8	38.3	50.5	78.4	106.2	134.1	162.0
102.5°	55.8	53.6	82.6	111.5	140.4	169.4	186.8	192.6	198.5	204.4	210.3
105°	58.0	55.8	111.3	166.9	222.4	277.9	302.6	296.5	290.4	284.4	278.3
107.5°	75.9	78.2	144.7	211.4	277.9	344.6	375.4	370.4	365.5	360.6	355.7
110°	139.8	160.1	219.0	277.8	336.5	395.3	422.6	418.3	414.1	409.7	405.4



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.8	404.0	418.5	433.1	447.5	462.1	467.4	463.6	459.9	456.2	452.4
115°	470.5	564.7	559.6	554.6	549.5	544.4	540.1	536.7	533.2	529.8	526.3
117.5°	602.7	625.5	622.0	618.5	615.0	611.5	607.9	604.0	600.1	596.2	592.4
120°	673.3	670.9	667.3	663.6	660.0	656.3	652.9	649.9	646.8	643.8	640.7
122.5°	715.6	714.1	710.2	706.1	702.1	698.2	694.6	691.4	688.1	684.9	681.7
125°	774.8	773.4	769.6	765.7	761.8	757.9	754.7	752.1	749.4	746.7	744.2
127.5°	829.0	826.9	824.0	821.0	818.2	815.3	812.4	809.5	806.6	803.7	800.7
130°	863.5	861.3	859.0	856.8	854.5	852.3	849.5	846.4	843.1	839.8	836.5
132.5°	897.6	895.7	893.5	891.2	889.0	886.7	884.2	881.5	878.7	876.0	873.1
135°	945.7	943.7	941.8	940.0	938.1	936.3	933.8	930.6	927.3	924.0	920.8
137.5°	990.5	988.5	986.4	984.4	982.3	980.2	978.0	975.8	973.4	971.2	968.9
140°	1019.6	1017.8	1015.5	1013.3	1011.1	1008.8	1006.9	1005.3	1003.7	1002.0	1000.4
142.5°	1046.5	1044.9	1042.3	1039.7	1037.2	1034.7	1032.6	1031.1	1029.7	1028.2	1026.7
145°	1084.2	1082.8	1079.3	1075.8	1072.4	1068.9	1067.3	1067.6	1067.7	1067.9	1068.2
147.5°	1117.1	1116.1	1112.7	1109.2	1105.9	1102.4	1101.1	1101.9	1102.7	1103.5	1104.2
150°	1137.1	1135.8	1132.6	1129.4	1126.1	1122.8	1122.0	1123.3	1124.8	1126.2	1127.7
152.5°	1155.4	1154.2	1151.1	1148.0	1144.9	1141.8	1141.1	1142.6	1144.2	1145.8	1147.4
155°	1180.1	1178.9	1176.5	1174.0	1171.6	1169.2	1168.8	1170.6	1172.5	1174.3	1176.1
157.5°	1200.8	1199.4	1197.7	1195.9	1194.3	1192.6	1192.5	1194.0	1195.6	1197.1	1198.7
160°	1213.1	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9
162.5°	1224.2	1222.8	1221.8	1220.7	1219.6	1218.6	1218.7	1219.9	1221.1	1222.4	1223.6
165°	1237.9	1236.6	1236.0	1235.4	1234.7	1234.1	1234.4	1235.6	1236.8	1238.0	1239.3
167.5°	1249.5	1248.1	1247.5	1246.9	1246.4	1245.8	1246.1	1247.3	1248.5	1249.8	1251.0
170°	1255.3	1254.0	1253.5	1253.1	1252.8	1252.3	1252.8	1254.0	1255.2	1256.4	1257.6
172.5°	1259.7	1258.4	1257.9	1257.5	1257.1	1256.7	1257.1	1258.4	1259.6	1260.8	1262.0
175°	1264.6	1263.1	1262.7	1262.3	1261.9	1261.5	1262.0	1263.4	1264.8	1266.3	1267.7
177.5°	1265.3	1264.2	1264.0	1263.9	1263.7	1263.5	1264.0	1265.2	1266.3	1267.5	1268.6
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.3	11.1	11.0	10.9	11.9	12.2	12.0	12.3	13.2	12.8	13.6
90°	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3	20.3
92.5°	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8	22.3
95°	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7	37.7
97.5°	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6	49.4
100°	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8	55.4
102.5°	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8	57.9
105°	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0	60.3
107.5°	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9	73.6
110°	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8	119.5





TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8	255.6
115°	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5	376.3
117.5°	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7	580.0
120°	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3	675.8
122.5°	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6	717.0
125°	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8	776.3
127.5°	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0	831.0
130°	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5	865.7
132.5°	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6	899.5
135°	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7	947.7
137.5°	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5	992.5
140°	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6	1021.5
142.5°	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5	1048.2
145°	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2	1085.6
147.5°	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1	1118.2
150°	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1	1138.3
152.5°	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4	1156.6
155°	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1	1181.3
157.5°	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8	1202.1
160°	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1	1214.3
162.5°	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2	1225.5
165°	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9	1239.4
167.5°	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5	1250.9
170°	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3	1256.8
172.5°	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7	1261.2
175°	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6	1265.9
177.5°	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3	1266.4
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	13.3	13.4	13.6	13.7	13.8	13.9	13.3
90°	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	99.2	78.8	69.1	69.8	70.7	71.5	72.3



TEST NUMBER: P331759-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)