

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331246-930

Luminaire Tested: **SA2XXDIP-C290D330U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331246-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D330U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2048.5 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331246-930
CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331246-930

CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48	48	48	48	48	48	48																
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46	40	40	40	40	40	40	40	40	40	40	40	40	40																
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39	34	34	34	34	34	34	34	34	34	34	34	34	34																
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33	29	29	29	29	29	29	29	29	29	29	29	29	29																
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25	25	25	25	25	25	25	25	25	25	25	25	25	25															
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21	21	21	21	21	21	21	21	21	21	21	21	21	21															
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19	19	19	19	19	19	19	19	19	19	19	19															
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17	17	17	17	17	17	17	17	17	17	17	17	17	17															
8	54	41	34	28	49	38	32	27	33	27	24	28	23	20	23	20	17	15	15	15	15	15	15	15	15	15	15	15	15	15	15															
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13	13	13	13	13	13	13	13	13	13	13	13	13	13															
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12	12	12	12	12	12	12	12	12	12	12	12	12	12															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331246-930

CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	1.8
10°-20°	101.9	5.0
20°-30°	149.8	7.3
30°-40°	174.0	8.5
40°-50°	173.8	8.5
50°-60°	151.6	7.4
60°-70°	112.1	5.5
70°-80°	63.5	3.1
80°-90°	18.0	0.9
90°-100°	12.1	0.6
100°-110°	44.6	2.2
110°-120°	119.1	5.8
120°-130°	196.6	9.6
130°-140°	209.1	10.2
140°-150°	194.4	9.5
150°-160°	156.3	7.6
160°-170°	100.7	4.9
170°-180°	34.7	1.7
0°-30°	287.9	14.1
0°-40°	461.9	22.6
0°-60°	787.3	38.4
0°-90°	980.9	47.9
90°-120°	175.8	8.6
90°-150°	776.0	37.9
90°-180°	1068.0	52.1
0°-180°	2048.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	0	3	5	7	7	2
95°	17	9	10	12	11	21
105°	80	84	16	19	20	86
115°	152	156	163	46	22	149
125°	214	218	223	225	225	191
135°	265	269	272	274	274	205
145°	308	308	312	314	312	192
155°	339	337	340	341	339	156
165°	357	356	356	358	356	101
175°	365	363	364	365	363	35
180°	364	364	364	364	364	



TEST NUMBER: P331246-930

CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.3	5.3	5.2	5.2	5.1
90°	0.2	0.9	1.5	2.2	2.9	3.4	3.8	4.3	4.8	5.3	5.5
92.5°	5.3	5.3	5.2	5.1	5.1	5.2	5.4	5.6	5.9	6.1	6.3
95°	17.1	15.2	13.3	11.3	9.4	8.6	9.0	9.5	9.9	10.3	10.6
97.5°	34.0	28.5	23.1	17.7	12.2	9.9	10.9	11.8	12.8	13.8	14.0
100°	46.6	38.6	30.6	22.6	14.6	11.0	12.1	13.0	14.0	15.0	15.5
102.5°	60.6	58.9	57.2	55.5	53.8	48.8	40.4	32.1	23.8	15.4	16.1
105°	80.1	81.9	83.6	85.4	87.2	80.1	64.1	48.1	32.0	16.1	16.7
107.5°	102.4	103.9	105.3	106.7	108.1	99.2	80.1	60.9	41.7	22.5	21.9
110°	116.8	118.0	119.3	120.5	121.7	113.8	96.9	80.0	63.0	46.1	40.3



TEST NUMBER: P331246-930

CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	131.3	132.5	133.5	134.6	133.1	128.9	124.7	120.5	116.3	95.0
115°	151.6	152.5	153.6	154.6	155.6	156.8	158.2	159.7	161.2	162.7	135.5
117.5°	170.6	171.7	172.8	174.0	175.0	176.1	177.2	178.1	179.1	180.2	173.6
120°	184.5	185.4	186.3	187.2	188.0	189.0	190.0	191.1	192.2	193.2	194.0
122.5°	196.3	197.3	198.2	199.1	200.1	201.1	202.2	203.3	204.6	205.7	206.1
125°	214.3	215.1	215.8	216.6	217.4	218.3	219.4	220.5	221.6	222.7	223.1
127.5°	230.6	231.5	232.3	233.2	234.0	234.8	235.6	236.5	237.3	238.1	238.7
130°	240.9	241.9	242.8	243.8	244.7	245.5	246.1	246.8	247.4	248.1	248.7
132.5°	251.5	252.3	253.1	253.9	254.7	255.4	256.0	256.7	257.3	258.0	258.5
135°	265.2	266.1	267.1	268.0	269.0	269.7	270.2	270.8	271.3	271.8	272.4
137.5°	279.1	279.7	280.4	281.0	281.7	282.3	282.9	283.5	284.1	284.7	285.3
140°	288.1	288.6	289.0	289.5	290.0	290.6	291.2	291.9	292.5	293.1	293.7
142.5°	295.7	296.1	296.5	297.0	297.4	298.0	298.7	299.5	300.2	300.9	301.4
145°	307.6	307.6	307.5	307.4	307.4	307.9	308.8	309.9	310.9	311.9	312.3
147.5°	318.0	317.8	317.6	317.3	317.2	317.5	318.5	319.5	320.5	321.5	321.7
150°	324.7	324.3	323.9	323.5	323.1	323.4	324.3	325.3	326.2	327.2	327.5
152.5°	330.4	330.0	329.5	329.1	328.6	328.8	329.7	330.6	331.5	332.4	332.7
155°	338.8	338.2	337.7	337.1	336.6	336.7	337.5	338.1	338.8	339.5	339.9
157.5°	345.2	344.8	344.3	343.9	343.4	343.5	344.0	344.5	345.0	345.4	345.8
160°	349.0	348.7	348.3	348.0	347.6	347.6	348.0	348.3	348.7	349.0	349.4
162.5°	352.4	352.0	351.7	351.3	351.0	351.0	351.2	351.6	351.9	352.2	352.6
165°	356.9	356.6	356.2	355.9	355.6	355.5	355.6	355.8	356.0	356.1	356.5
167.5°	360.3	360.0	359.6	359.2	358.9	358.8	359.0	359.1	359.3	359.5	359.9
170°	362.2	361.8	361.5	361.2	360.8	360.7	360.8	360.9	361.0	361.2	361.6
172.5°	363.5	363.1	362.7	362.4	362.1	361.9	362.1	362.2	362.3	362.4	362.8
175°	365.1	364.7	364.3	363.9	363.5	363.3	363.5	363.5	363.7	363.8	364.2
177.5°	365.3	365.0	364.7	364.4	364.0	363.9	363.9	364.0	364.0	364.1	364.4
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3



TEST NUMBER: P331246-930

CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	4.9	4.8	4.6	4.6	4.5	4.5	4.4	4.4
90°	5.9	6.1	6.4	6.7	6.8	6.8	7.0	7.1
92.5°	6.4	6.6	6.7	6.8	6.9	7.0	7.0	7.1
95°	10.8	11.2	11.4	11.6	11.5	11.4	11.4	11.3
97.5°	14.3	14.4	14.7	14.8	14.9	15.0	15.1	15.2
100°	16.0	16.5	16.9	17.2	17.3	17.4	17.5	17.7
102.5°	16.6	17.3	17.9	18.3	18.4	18.6	18.8	18.9
105°	17.4	18.0	18.7	19.1	19.3	19.6	19.8	20.1
107.5°	21.2	20.5	19.9	19.6	19.9	20.1	20.4	20.6
110°	34.4	28.5	22.7	19.9	20.1	20.4	20.6	20.8



TEST NUMBER: P331246-930

CATALOG NUMBER: SA2XXDIP-C290D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	73.6	52.3	30.9	20.3	20.5	20.6	20.9	21.0
115°	108.4	81.3	54.1	38.5	34.2	30.1	25.8	21.6
117.5°	167.1	160.5	153.9	143.7	129.9	116.0	102.2	88.3
120°	194.6	195.3	196.0	192.4	184.5	176.6	168.7	160.8
122.5°	206.5	206.9	207.3	206.8	205.3	203.7	202.2	200.6
125°	223.6	224.0	224.4	224.7	224.9	225.0	225.2	225.3
127.5°	239.4	239.9	240.5	240.8	240.9	240.9	240.9	241.0
130°	249.3	250.0	250.6	250.9	250.9	250.8	250.8	250.7
132.5°	259.1	259.6	260.2	260.4	260.3	260.3	260.2	260.2
135°	273.0	273.5	274.1	274.3	274.3	274.1	274.0	273.9
137.5°	285.8	286.4	287.0	287.1	287.0	286.8	286.6	286.4
140°	294.2	294.7	295.2	295.4	295.1	294.8	294.5	294.2
142.5°	301.9	302.4	302.9	303.0	302.6	302.4	302.1	301.7
145°	312.7	313.1	313.5	313.6	313.2	313.0	312.7	312.3
147.5°	322.0	322.4	322.7	322.7	322.5	322.2	322.0	321.7
150°	327.8	328.2	328.6	328.6	328.3	328.0	327.7	327.4
152.5°	333.1	333.5	333.8	333.8	333.4	333.0	332.6	332.2
155°	340.2	340.6	341.0	340.9	340.4	340.0	339.5	339.0
157.5°	346.3	346.7	347.0	347.0	346.5	346.1	345.6	345.2
160°	349.8	350.1	350.4	350.4	350.0	349.6	349.2	348.8
162.5°	352.9	353.4	353.8	353.8	353.2	352.7	352.2	351.7
165°	356.9	357.3	357.8	357.8	357.3	356.9	356.5	356.1
167.5°	360.3	360.7	361.1	361.0	360.5	360.0	359.5	358.9
170°	362.0	362.4	362.8	362.7	362.2	361.7	361.2	360.6
172.5°	363.2	363.6	364.0	364.0	363.5	363.0	362.4	361.9
175°	364.6	365.0	365.4	365.3	364.8	364.2	363.5	363.0
177.5°	364.8	365.1	365.4	365.3	364.9	364.5	364.1	363.7
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3

(END OF REPORT)