

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331760-935

Luminaire Tested: **SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331760-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6600.3 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331760-935
CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	91	88	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	78	73	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	74	67	62	76	69	63	58	59	54	51	50	46	44	41	39	37	33
4	76	66	59	53	70	62	55	50	53	48	44	45	41	38	37	35	33	29
5	70	59	52	46	65	55	49	44	48	43	39	41	37	34	34	31	29	26
6	65	54	46	40	60	50	43	38	43	38	34	37	33	30	31	28	26	23
7	61	49	41	36	56	46	39	34	40	34	31	34	30	27	29	26	24	21
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	27	24	21	19
9	53	41	34	29	49	38	32	28	34	29	25	29	25	22	25	22	20	18
10	49	38	31	26	46	36	29	25	31	26	23	27	23	20	23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	2.7
10°-20°	501.6	7.6
20°-30°	646.3	9.8
30°-40°	614.2	9.3
40°-50°	526.2	8.0
50°-60°	400.7	6.1
60°-70°	253.3	3.8
70°-80°	126.5	1.9
80°-90°	37.7	0.6
90°-100°	75.1	1.1
100°-110°	233.2	3.5
110°-120°	398.7	6.0
120°-130°	524.3	7.9
130°-140°	588.5	8.9
140°-150°	577.0	8.7
150°-160°	484.0	7.3
160°-170°	321.0	4.9
170°-180°	112.2	1.7
0°-30°	1327.9	20.1
0°-40°	1942.1	29.4
0°-60°	2869.0	43.5
0°-90°	3286.4	49.8
90°-120°	707.0	10.7
90°-150°	2396.8	36.3
90°-180°	3314.0	50.2
0°-180°	6600.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	34	1	34	1	34	16
95°	62	52	62	52	62	69
105°	222	215	222	215	222	234
115°	400	400	400	400	400	395
125°	584	582	584	582	584	521
135°	762	753	762	753	762	587
145°	924	914	924	914	924	577
155°	1053	1045	1053	1045	1053	485
165°	1138	1137	1138	1137	1138	321
175°	1179	1183	1179	1183	1179	112
180°	1185	1185	1185	1185	1185	



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	15.2	15.8	15.7	15.7	15.6	15.6	15.7	16.4	15.8	16.5	15.0
90°	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1	34.5	35.0	30.1
92.5°	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9	31.9	31.8	30.7
95°	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0	64.0	64.0	63.5
97.5°	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6	107.6	107.6	106.8
100°	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0	138.0	138.0	137.3
102.5°	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2	171.0	170.8	170.0
105°	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9	220.5	220.0	219.6
107.5°	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6	274.4	274.2	274.2
110°	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6	348.1	348.6	348.8
115°	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6	403.8	404.1	404.5
117.5°	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8	458.3	458.8	460.1
120°	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0	494.0	494.0	495.8
122.5°	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4	531.9	532.4	533.7
125°	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8	587.4	588.1	588.8
127.5°	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5	641.3	642.0	642.9
130°	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2	677.6	678.1	678.6
132.5°	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9	713.9	714.9	714.8
135°	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7	765.9	766.1	765.7
137.5°	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1	816.3	816.5	815.9
140°	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1	850.1	850.1	849.0
142.5°	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9	880.7	880.5	879.8
145°	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6	927.3	927.1	925.7
147.5°	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5	968.0	967.5	966.6
150°	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5	993.8	993.2	992.2
152.5°	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7	1017.7
155°	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3	1052.2	1051.1	1050.5
157.5°	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7	1082.3	1080.7	1080.3
160°	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8	1100.4	1099.2	1098.9
162.5°	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2	1116.6	1115.2	1114.9
165°	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3	1137.7	1136.2	1136.2
167.5°	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7	1155.1	1153.6	1153.6
170°	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2	1164.7	1163.1	1163.4
172.5°	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5	1171.9	1170.4	1170.5
175°	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3	1179.7	1178.1	1178.6
177.5°	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8	1183.1
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	14.0	13.6	12.6	11.3	11.3	11.3	13.4	15.5	13.9	12.9	12.4
90°	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0	3.7	6.4	9.0
92.5°	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8	19.7	21.7	23.7
95°	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0	54.2	56.5	58.6
97.5°	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1	96.9	98.9	100.9
100°	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0	128.8	130.6	132.3
102.5°	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7	162.0	163.5	164.9
105°	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0	215.7	216.4	217.1
107.5°	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8	270.8	271.8	272.8
110°	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1	306.3	307.7	309.0



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5	344.7	346.1	347.4
115°	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0	401.4	402.7	404.1
117.5°	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4	458.2	460.0	461.8
120°	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	495.8	497.7	499.4
122.5°	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5	530.6	532.7	534.9
125°	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0	584.1	586.1	588.1
127.5°	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3	636.8	639.4	641.9
130°	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1	669.9	672.9	675.7
132.5°	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9	706.3	708.6	710.9
135°	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1	755.5	758.0	760.4
137.5°	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9	806.9	808.9	810.9
140°	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1	838.1	840.1	842.1
142.5°	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1	870.1	872.1	874.1
145°	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1	915.7	917.2	918.8
147.5°	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1	957.0	958.8	960.7
150°	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1	984.5	985.8	987.1
152.5°	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9	1009.3	1010.6	1011.9
155°	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2	1045.8	1046.5	1047.1
157.5°	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9	1077.4	1077.8	1078.2
160°	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1	1096.6	1097.0	1097.4
162.5°	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7	1113.8	1113.9	1114.0
165°	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1	1137.0	1136.7	1136.4
167.5°	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8	1156.1	1155.4	1154.8
170°	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2	1166.5	1165.8	1165.1
172.5°	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3	1173.7	1173.0	1172.3
175°	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2	1182.5	1181.8	1181.1
177.5°	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7	1186.2	1185.7	1185.2
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	12.4	12.6	12.5	13.5	14.5	14.9	14.8	14.2	14.1	14.0	13.5
90°	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1	33.7	33.2	33.1
92.5°	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9	32.0	32.2	32.2
95°	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0	64.0	64.0	63.8
97.5°	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6	107.6	107.6	107.6
100°	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0	138.0	138.0	137.9
102.5°	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2	171.3	171.5	171.5
105°	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9	221.4	221.8	222.1
107.5°	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6	274.7	274.9	274.5
110°	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	311.1	310.7



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6	347.1	346.6	346.0
115°	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6	403.4	403.1	402.7
117.5°	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8	457.3	456.8	456.2
120°	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0	494.0	494.0	493.7
122.5°	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4	530.9	530.3	529.9
125°	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8	586.1	585.4	585.0
127.5°	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5	639.6	638.9	638.1
130°	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2	676.7	676.3	675.6
132.5°	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9	712.0	711.0	710.2
135°	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7	765.4	765.2	764.7
137.5°	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1	816.0	815.8	815.3
140°	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1	850.1	850.1	849.6
142.5°	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9	881.1	881.2	880.9
145°	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6	927.8	928.0	927.6
147.5°	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5	969.0	969.5	969.3
150°	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5	995.1	995.8	995.8
152.5°	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1
155°	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3	1054.5	1055.6	1055.8
157.5°	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7	1085.3	1086.8	1087.0
160°	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8	1103.1	1104.5	1104.7
162.5°	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2	1119.6	1121.2	1121.4
165°	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3	1140.8	1142.4	1142.5
167.5°	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7	1158.2	1159.8	1159.9
170°	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2	1167.8	1169.3	1169.5
172.5°	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5	1175.0	1176.6	1176.6
175°	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3	1182.8	1184.4	1184.5
177.5°	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331760-935
 CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	13.5	13.1	13.6	13.2	13.6	13.1	13.5	13.5	14.0	14.1	14.2
90°	33.3	33.6	33.8	34.0	33.8	33.6	33.3	33.1	33.2	33.7	34.1
92.5°	32.3	32.3	32.4	32.4	32.4	32.3	32.3	32.2	32.2	32.0	31.9
95°	63.4	62.9	62.4	62.0	62.4	62.9	63.4	63.8	64.0	64.0	64.0
97.5°	107.5	107.5	107.5	107.5	107.5	107.5	107.5	107.6	107.6	107.6	107.6
100°	137.7	137.5	137.2	137.0	137.2	137.5	137.7	137.9	138.0	138.0	138.0
102.5°	171.3	171.1	170.8	170.7	170.8	171.1	171.3	171.5	171.5	171.3	171.2
105°	222.1	222.1	222.1	222.1	222.1	222.1	222.1	222.1	221.8	221.4	220.9
107.5°	273.5	272.5	271.5	270.4	271.5	272.5	273.5	274.5	274.9	274.7	274.6
110°	310.0	309.4	308.7	308.1	308.7	309.4	310.0	310.7	311.1	311.1	311.1



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	345.5	345.0	344.6	344.1	344.6	345.0	345.5	346.0	346.6	347.1	347.6
115°	402.1	401.4	400.7	400.0	400.7	401.4	402.1	402.7	403.1	403.4	403.6
117.5°	455.5	454.8	454.1	453.5	454.1	454.8	455.5	456.2	456.8	457.3	457.8
120°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.7	494.0	494.0	494.0
122.5°	529.3	528.8	528.4	527.9	528.4	528.8	529.3	529.9	530.3	530.9	531.4
125°	584.7	584.5	584.3	584.1	584.3	584.5	584.7	585.0	585.4	586.1	586.8
127.5°	637.4	636.7	636.0	635.2	636.0	636.7	637.4	638.1	638.9	639.6	640.5
130°	674.8	673.8	673.0	672.1	673.0	673.8	674.8	675.6	676.3	676.7	677.2
132.5°	709.5	708.7	708.0	707.3	708.0	708.7	709.5	710.2	711.0	712.0	712.9
135°	764.1	763.4	762.8	762.1	762.8	763.4	764.1	764.7	765.2	765.4	765.7
137.5°	814.3	813.5	812.6	811.7	812.6	813.5	814.3	815.3	815.8	816.0	816.1
140°	848.8	847.9	847.0	846.1	847.0	847.9	848.8	849.6	850.1	850.1	850.1
142.5°	879.9	879.1	878.2	877.3	878.2	879.1	879.9	880.9	881.2	881.1	880.9
145°	926.8	925.9	925.0	924.1	925.0	925.9	926.8	927.6	928.0	927.8	927.6
147.5°	968.5	967.6	966.7	966.0	966.7	967.6	968.5	969.3	969.5	969.0	968.5
150°	995.1	994.5	993.8	993.2	993.8	994.5	995.1	995.8	995.8	995.1	994.5
152.5°	1021.2	1020.5	1019.6	1018.7	1019.6	1020.5	1021.2	1022.1	1022.1	1021.2	1020.5
155°	1055.2	1054.5	1053.8	1053.1	1053.8	1054.5	1055.2	1055.8	1055.6	1054.5	1053.3
157.5°	1085.9	1084.9	1083.8	1082.7	1083.8	1084.9	1085.9	1087.0	1086.8	1085.3	1083.7
160°	1103.8	1102.9	1102.0	1101.1	1102.0	1102.9	1103.8	1104.7	1104.5	1103.1	1101.8
162.5°	1120.3	1119.3	1118.2	1117.1	1118.2	1119.3	1120.3	1121.4	1121.2	1119.6	1118.2
165°	1141.5	1140.4	1139.3	1138.2	1139.3	1140.4	1141.5	1142.5	1142.4	1140.8	1139.3
167.5°	1158.8	1157.6	1156.5	1155.4	1156.5	1157.6	1158.8	1159.9	1159.8	1158.2	1156.7
170°	1168.1	1166.8	1165.4	1164.2	1165.4	1166.8	1168.1	1169.5	1169.3	1167.8	1166.2
172.5°	1175.4	1174.0	1172.7	1171.3	1172.7	1174.0	1175.4	1176.6	1176.6	1175.0	1173.5
175°	1183.2	1181.8	1180.5	1179.1	1180.5	1181.8	1183.2	1184.5	1184.4	1182.8	1181.3
177.5°	1185.9	1184.9	1183.8	1182.8	1183.8	1184.9	1185.9	1187.0	1187.0	1185.9	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	14.8	14.9	14.5	13.5	12.5	12.6	12.4	12.4	12.9	13.9	15.5
90°	34.5	35.0	30.1	25.2	20.3	15.4	11.7	9.0	6.4	3.7	1.0
92.5°	31.9	31.8	30.7	29.5	28.3	27.2	25.7	23.7	21.7	19.7	17.8
95°	64.0	64.0	63.5	63.1	62.7	62.3	60.9	58.6	56.5	54.2	52.0
97.5°	107.6	107.6	106.8	105.9	105.0	104.3	102.8	100.9	98.9	96.9	95.1
100°	138.0	138.0	137.3	136.6	136.0	135.3	134.1	132.3	130.6	128.8	127.0
102.5°	171.0	170.8	170.0	169.1	168.3	167.5	166.3	164.9	163.5	162.0	160.7
105°	220.5	220.0	219.6	219.1	218.7	218.3	217.7	217.1	216.4	215.7	215.0
107.5°	274.4	274.2	274.2	274.2	274.2	274.2	273.7	272.8	271.8	270.8	269.8
110°	311.1	311.1	311.1	311.1	311.1	311.1	310.4	309.0	307.7	306.3	305.1



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	348.1	348.6	348.8	349.0	349.1	349.4	348.8	347.4	346.1	344.7	343.5
115°	403.8	404.1	404.5	404.9	405.4	405.8	405.4	404.1	402.7	401.4	400.0
117.5°	458.3	458.8	460.1	461.3	462.6	463.8	463.6	461.8	460.0	458.2	456.4
120°	494.0	494.0	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0
122.5°	531.9	532.4	533.7	534.9	536.2	537.4	537.0	534.9	532.7	530.6	528.5
125°	587.4	588.1	588.8	589.4	590.0	590.7	590.0	588.1	586.1	584.1	582.0
127.5°	641.3	642.0	642.9	643.7	644.5	645.3	644.4	641.9	639.4	636.8	634.3
130°	677.6	678.1	678.6	679.0	679.4	679.8	678.6	675.7	672.9	669.9	667.1
132.5°	713.9	714.9	714.8	714.7	714.6	714.5	713.3	710.9	708.6	706.3	703.9
135°	765.9	766.1	765.7	765.2	764.7	764.3	762.8	760.4	758.0	755.5	753.1
137.5°	816.3	816.5	815.9	815.4	814.8	814.2	812.9	810.9	808.9	806.9	804.9
140°	850.1	850.1	849.0	847.9	846.8	845.7	844.1	842.1	840.1	838.1	836.1
142.5°	880.7	880.5	879.8	879.0	878.2	877.4	876.1	874.1	872.1	870.1	868.1
145°	927.3	927.1	925.7	924.5	923.1	921.8	920.3	918.8	917.2	915.7	914.1
147.5°	968.0	967.5	966.6	965.8	964.8	964.0	962.6	960.7	958.8	957.0	955.1
150°	993.8	993.2	992.2	991.4	990.5	989.5	988.4	987.1	985.8	984.5	983.1
152.5°	1019.6	1018.7	1017.7	1016.6	1015.5	1014.4	1013.2	1011.9	1010.6	1009.3	1007.9
155°	1052.2	1051.1	1050.5	1049.8	1049.1	1048.4	1047.8	1047.1	1046.5	1045.8	1045.2
157.5°	1082.3	1080.7	1080.3	1080.0	1079.5	1079.1	1078.7	1078.2	1077.8	1077.4	1076.9
160°	1100.4	1099.2	1098.9	1098.7	1098.5	1098.2	1097.9	1097.4	1097.0	1096.6	1096.1
162.5°	1116.6	1115.2	1114.9	1114.7	1114.5	1114.2	1114.1	1114.0	1113.9	1113.8	1113.7
165°	1137.7	1136.2	1136.2	1136.2	1136.2	1136.2	1136.3	1136.4	1136.7	1137.0	1137.1
167.5°	1155.1	1153.6	1153.6	1153.7	1153.7	1153.7	1154.1	1154.8	1155.4	1156.1	1156.8
170°	1164.7	1163.1	1163.4	1163.6	1163.8	1164.1	1164.5	1165.1	1165.8	1166.5	1167.2
172.5°	1171.9	1170.4	1170.5	1170.8	1171.0	1171.2	1171.6	1172.3	1173.0	1173.7	1174.3
175°	1179.7	1178.1	1178.6	1179.1	1179.5	1179.9	1180.5	1181.1	1181.8	1182.5	1183.2
177.5°	1183.8	1182.8	1183.1	1183.4	1183.8	1184.1	1184.6	1185.2	1185.7	1186.2	1186.7
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.4	11.3	11.3	11.3	12.6	13.6	14.0	15.0	16.5	15.8	16.4
90°	3.7	6.4	9.0	11.7	15.4	20.3	25.2	30.1	35.0	34.5	34.1
92.5°	19.7	21.7	23.7	25.7	27.2	28.3	29.5	30.7	31.8	31.9	31.9
95°	54.2	56.5	58.6	60.9	62.3	62.7	63.1	63.5	64.0	64.0	64.0
97.5°	96.9	98.9	100.9	102.8	104.3	105.0	105.9	106.8	107.6	107.6	107.6
100°	128.8	130.6	132.3	134.1	135.3	136.0	136.6	137.3	138.0	138.0	138.0
102.5°	162.0	163.5	164.9	166.3	167.5	168.3	169.1	170.0	170.8	171.0	171.2
105°	215.7	216.4	217.1	217.7	218.3	218.7	219.1	219.6	220.0	220.5	220.9
107.5°	270.8	271.8	272.8	273.7	274.2	274.2	274.2	274.2	274.2	274.4	274.6
110°	306.3	307.7	309.0	310.4	311.1	311.1	311.1	311.1	311.1	311.1	311.1



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.7	346.1	347.4	348.8	349.4	349.1	349.0	348.8	348.6	348.1	347.6
115°	401.4	402.7	404.1	405.4	405.8	405.4	404.9	404.5	404.1	403.8	403.6
117.5°	458.2	460.0	461.8	463.6	463.8	462.6	461.3	460.1	458.8	458.3	457.8
120°	495.8	497.7	499.4	501.2	501.2	499.4	497.7	495.8	494.0	494.0	494.0
122.5°	530.6	532.7	534.9	537.0	537.4	536.2	534.9	533.7	532.4	531.9	531.4
125°	584.1	586.1	588.1	590.0	590.7	590.0	589.4	588.8	588.1	587.4	586.8
127.5°	636.8	639.4	641.9	644.4	645.3	644.5	643.7	642.9	642.0	641.3	640.5
130°	669.9	672.9	675.7	678.6	679.8	679.4	679.0	678.6	678.1	677.6	677.2
132.5°	706.3	708.6	710.9	713.3	714.5	714.6	714.7	714.8	714.9	713.9	712.9
135°	755.5	758.0	760.4	762.8	764.3	764.7	765.2	765.7	766.1	765.9	765.7
137.5°	806.9	808.9	810.9	812.9	814.2	814.8	815.4	815.9	816.5	816.3	816.1
140°	838.1	840.1	842.1	844.1	845.7	846.8	847.9	849.0	850.1	850.1	850.1
142.5°	870.1	872.1	874.1	876.1	877.4	878.2	879.0	879.8	880.5	880.7	880.9
145°	915.7	917.2	918.8	920.3	921.8	923.1	924.5	925.7	927.1	927.3	927.6
147.5°	957.0	958.8	960.7	962.6	964.0	964.8	965.8	966.6	967.5	968.0	968.5
150°	984.5	985.8	987.1	988.4	989.5	990.5	991.4	992.2	993.2	993.8	994.5
152.5°	1009.3	1010.6	1011.9	1013.2	1014.4	1015.5	1016.6	1017.7	1018.7	1019.6	1020.5
155°	1045.8	1046.5	1047.1	1047.8	1048.4	1049.1	1049.8	1050.5	1051.1	1052.2	1053.3
157.5°	1077.4	1077.8	1078.2	1078.7	1079.1	1079.5	1080.0	1080.3	1080.7	1082.3	1083.7
160°	1096.6	1097.0	1097.4	1097.9	1098.2	1098.5	1098.7	1098.9	1099.2	1100.4	1101.8
162.5°	1113.8	1113.9	1114.0	1114.1	1114.2	1114.5	1114.7	1114.9	1115.2	1116.6	1118.2
165°	1137.0	1136.7	1136.4	1136.3	1136.2	1136.2	1136.2	1136.2	1136.2	1137.7	1139.3
167.5°	1156.1	1155.4	1154.8	1154.1	1153.7	1153.7	1153.7	1153.6	1153.6	1155.1	1156.7
170°	1166.5	1165.8	1165.1	1164.5	1164.1	1163.8	1163.6	1163.4	1163.1	1164.7	1166.2
172.5°	1173.7	1173.0	1172.3	1171.6	1171.2	1171.0	1170.8	1170.5	1170.4	1171.9	1173.5
175°	1182.5	1181.8	1181.1	1180.5	1179.9	1179.5	1179.1	1178.6	1178.1	1179.7	1181.3
177.5°	1186.2	1185.7	1185.2	1184.6	1184.1	1183.8	1183.4	1183.1	1182.8	1183.8	1184.9
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	15.7	15.6	15.6	15.7	15.7	15.8	15.2
90°	33.7	33.2	33.1	33.3	33.6	33.8	34.0
92.5°	32.0	32.2	32.2	32.3	32.3	32.4	32.4
95°	64.0	64.0	63.8	63.4	62.9	62.4	62.0
97.5°	107.6	107.6	107.6	107.5	107.5	107.5	107.5
100°	138.0	138.0	137.9	137.7	137.5	137.2	137.0
102.5°	171.3	171.5	171.5	171.3	171.1	170.8	170.7
105°	221.4	221.8	222.1	222.1	222.1	222.1	222.1
107.5°	274.7	274.9	274.5	273.5	272.5	271.5	270.4
110°	311.1	311.1	310.7	310.0	309.4	308.7	308.1



TEST NUMBER: P331760-935

CATALOG NUMBER: SA2XXRDIP-C1005D1080U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.1	346.6	346.0	345.5	345.0	344.6	344.1
115°	403.4	403.1	402.7	402.1	401.4	400.7	400.0
117.5°	457.3	456.8	456.2	455.5	454.8	454.1	453.5
120°	494.0	494.0	493.7	493.1	492.4	491.7	491.0
122.5°	530.9	530.3	529.9	529.3	528.8	528.4	527.9
125°	586.1	585.4	585.0	584.7	584.5	584.3	584.1
127.5°	639.6	638.9	638.1	637.4	636.7	636.0	635.2
130°	676.7	676.3	675.6	674.8	673.8	673.0	672.1
132.5°	712.0	711.0	710.2	709.5	708.7	708.0	707.3
135°	765.4	765.2	764.7	764.1	763.4	762.8	762.1
137.5°	816.0	815.8	815.3	814.3	813.5	812.6	811.7
140°	850.1	850.1	849.6	848.8	847.9	847.0	846.1
142.5°	881.1	881.2	880.9	879.9	879.1	878.2	877.3
145°	927.8	928.0	927.6	926.8	925.9	925.0	924.1
147.5°	969.0	969.5	969.3	968.5	967.6	966.7	966.0
150°	995.1	995.8	995.8	995.1	994.5	993.8	993.2
152.5°	1021.2	1022.1	1022.1	1021.2	1020.5	1019.6	1018.7
155°	1054.5	1055.6	1055.8	1055.2	1054.5	1053.8	1053.1
157.5°	1085.3	1086.8	1087.0	1085.9	1084.9	1083.8	1082.7
160°	1103.1	1104.5	1104.7	1103.8	1102.9	1102.0	1101.1
162.5°	1119.6	1121.2	1121.4	1120.3	1119.3	1118.2	1117.1
165°	1140.8	1142.4	1142.5	1141.5	1140.4	1139.3	1138.2
167.5°	1158.2	1159.8	1159.9	1158.8	1157.6	1156.5	1155.4
170°	1167.8	1169.3	1169.5	1168.1	1166.8	1165.4	1164.2
172.5°	1175.0	1176.6	1176.6	1175.4	1174.0	1172.7	1171.3
175°	1182.8	1184.4	1184.5	1183.2	1181.8	1180.5	1179.1
177.5°	1185.9	1187.0	1187.0	1185.9	1184.9	1183.8	1182.8
180°	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2	1185.2

(END OF REPORT)