

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331740-935

Luminaire Tested: **SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331740-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4101.1 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	104	99	96	92	98	95	91	88	86	83	81	77	75	74	70	68	67	63
2	95	88	82	77	90	84	78	74	76	72	68	69	65	63	62	60	57	54
3	87	78	71	65	83	74	68	62	68	62	58	61	57	54	56	52	50	47
4	80	69	62	56	76	66	59	54	61	55	50	55	51	47	50	46	43	41
5	74	62	54	48	70	60	52	47	55	49	44	50	45	41	46	42	38	36
6	68	56	48	42	65	54	47	41	50	43	39	46	40	36	42	37	34	32
7	64	51	43	38	60	49	42	37	45	39	35	42	36	33	38	34	31	28
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28	26
9	55	43	36	30	53	41	34	30	38	32	28	36	30	27	33	28	25	23
10	52	40	32	28	49	38	32	27	36	30	26	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23541	23541	23541
5°	23631	23246	23376
10°	23451	22866	22673
15°	23181	22188	21549
20°	22807	21220	20155
25°	22425	20122	18805
30°	21895	18990	17074
35°	21378	17763	15554
40°	20858	16493	13793
45°	20247	15066	12202
50°	19623	13622	10638
55°	18978	12073	9137
60°	18235	10440	7585
65°	17391	8772	6907
70°	16386	7227	6354
75°	15147	6588	5926
80°	13371	5895	5393
85°	10504	4650	4650



TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	3.3
10°-20°	374.7	9.1
20°-30°	526.2	12.8
30°-40°	573.8	14.0
40°-50°	527.6	12.9
50°-60°	414.4	10.1
60°-70°	270.2	6.6
70°-80°	139.3	3.4
80°-90°	37.6	0.9
90°-100°	63.3	1.5
100°-110°	214.7	5.2
110°-120°	228.0	5.6
120°-130°	187.7	4.6
130°-140°	150.7	3.7
140°-150°	113.9	2.8
150°-160°	80.1	2.0
160°-170°	47.1	1.1
170°-180°	15.3	0.4
0°-30°	1037.4	25.3
0°-40°	1611.3	39.3
0°-60°	2553.2	62.3
0°-90°	3000.3	73.2
90°-120°	505.9	12.3
90°-150°	958.3	23.4
90°-180°	1101.0	26.8
0°-180°	4101.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1445	1442	138
15°	1387	1371	1327	1303	1289	390
25°	1259	1214	1130	1077	1056	579
35°	1085	1015	901	821	789	678
45°	887	796	660	570	534	684
55°	674	569	429	353	325	602
65°	455	348	230	187	181	451
75°	243	153	106	97	95	257
85°	57	30	25	25	25	67
90°	0	4	10	10	10	3
95°	11	26	119	45	35	11
105°	37	56	225	403	343	39
115°	65	83	189	389	451	65
125°	91	108	181	315	366	81
135°	107	128	179	265	303	83
145°	122	141	178	221	242	77
155°	139	150	173	196	204	64
165°	152	156	166	176	179	43
175°	158	158	159	161	161	15
180°	158	158	158	158	158	



TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1463.4	1462.2	1460.9	1459.8	1458.6	1456.7	1454.1	1451.6	1449.1	1446.5	1448.8
5°	1458.0	1456.6	1455.1	1453.6	1452.2	1449.6	1445.7	1441.9	1438.1	1434.3	1436.9
7.5°	1443.0	1441.2	1439.4	1437.5	1435.7	1432.6	1428.1	1423.7	1419.3	1414.8	1415.6
10°	1430.4	1428.3	1426.2	1424.2	1422.1	1418.2	1412.3	1406.4	1400.6	1394.7	1393.9
12.5°	1414.5	1412.0	1409.5	1407.0	1404.5	1399.4	1391.9	1384.4	1376.9	1369.4	1367.8
15°	1386.8	1383.5	1380.4	1377.1	1373.9	1367.3	1357.4	1347.4	1337.4	1327.4	1321.9
17.5°	1352.7	1347.8	1342.9	1338.0	1333.1	1324.2	1311.4	1298.6	1285.8	1273.1	1266.4
20°	1327.4	1321.5	1315.7	1309.8	1304.0	1293.7	1279.0	1264.4	1249.7	1235.0	1227.7
22.5°	1299.9	1293.4	1286.9	1280.3	1273.7	1262.1	1245.6	1229.1	1212.5	1196.0	1186.5
25°	1258.8	1249.4	1240.0	1230.6	1221.2	1206.9	1187.6	1168.2	1148.8	1129.5	1117.5
27.5°	1209.2	1199.0	1188.8	1178.6	1168.4	1152.4	1130.6	1108.7	1086.9	1065.1	1051.1
30°	1174.4	1163.2	1152.1	1140.9	1129.8	1112.5	1089.0	1065.6	1042.2	1018.6	1003.7
32.5°	1140.6	1127.6	1114.6	1101.6	1088.5	1070.1	1046.1	1022.2	998.2	974.3	957.3
35°	1084.6	1069.7	1054.7	1039.7	1024.8	1004.4	978.6	952.9	927.0	901.2	882.8
37.5°	1028.7	1012.3	995.8	979.4	963.0	941.1	913.5	886.1	858.5	831.0	810.7
40°	989.6	972.1	954.4	936.9	919.3	896.2	867.8	839.4	810.9	782.5	761.6
42.5°	949.5	931.0	912.5	893.9	875.4	851.4	822.1	792.6	763.3	733.9	712.4
45°	886.7	867.0	847.4	827.8	808.1	782.9	752.1	721.3	690.5	659.8	638.9
47.5°	825.4	804.7	783.9	763.0	742.2	715.9	684.2	652.3	620.5	588.8	568.1
50°	781.2	760.3	739.5	718.7	697.8	671.3	639.1	606.8	574.5	542.3	522.1
52.5°	737.9	716.1	694.4	672.6	650.8	624.2	592.6	561.1	529.5	498.0	478.5
55°	674.2	651.4	628.5	605.6	582.8	555.5	523.8	492.1	460.5	428.9	411.2
57.5°	609.1	585.7	562.1	538.7	515.2	488.3	457.9	427.4	397.0	366.5	350.4
60°	564.7	541.3	517.8	494.4	470.9	444.1	413.9	383.7	353.4	323.3	308.3
62.5°	521.5	498.0	474.6	451.1	427.7	401.5	372.7	343.9	315.1	286.4	272.1
65°	455.2	431.4	407.8	384.0	360.2	335.2	308.8	282.4	256.0	229.6	219.6
67.5°	391.3	367.8	344.2	320.6	297.0	273.4	249.7	225.9	202.2	178.4	173.8
70°	347.1	324.2	301.3	278.4	255.5	234.0	213.8	193.6	173.3	153.1	150.2
72.5°	304.8	282.8	261.0	239.0	217.1	197.9	181.8	165.5	149.2	133.0	130.5
75°	242.8	222.2	201.7	181.2	160.7	145.4	135.4	125.5	115.5	105.6	103.5
77.5°	181.8	163.8	145.9	127.9	109.8	98.4	93.6	88.8	83.9	79.2	78.0
80°	143.8	128.9	113.9	98.9	84.0	75.1	72.2	69.2	66.3	63.4	62.2
82.5°	109.0	97.3	85.7	74.0	62.3	55.4	53.5	51.5	49.5	47.5	46.8
85°	56.7	50.5	44.4	38.2	32.1	28.6	27.7	26.9	25.9	25.1	25.1
87.5°	17.0	15.2	13.6	11.9	10.1	9.4	9.6	10.1	10.4	10.5	10.2
90°	0.3	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1
92.5°	3.7	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4
95°	10.7	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4
97.5°	17.3	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5
100°	23.4	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1
102.5°	29.0	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4
105°	37.1	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3
107.5°	45.9	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7
110°	51.7	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9



TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2
115°	65.4	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7
117.5°	74.0	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6
120°	79.4	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7
122.5°	84.6	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5
125°	91.3	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7
127.5°	96.6	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2
130°	99.8	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5
132.5°	102.7	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6
135°	107.1	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5
137.5°	111.2	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6
140°	114.4	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9
142.5°	117.5	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3
145°	122.3	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0
147.5°	127.4	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7
150°	130.8	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7
152.5°	134.2	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0
155°	139.1	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9
157.5°	143.0	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9
160°	145.7	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7
162.5°	148.4	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8
165°	151.5	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5
167.5°	154.0	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4
170°	155.8	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7
172.5°	156.7	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0
175°	157.9	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7
177.5°	158.4	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1451.1	1453.5	1455.9	1456.7	1456.3	1455.9	1455.3	1454.9
5°	1439.6	1442.3	1444.8	1445.7	1444.8	1444.0	1443.1	1442.3
7.5°	1416.3	1417.0	1417.8	1417.5	1415.9	1414.4	1412.9	1411.4
10°	1392.9	1392.1	1391.2	1389.9	1388.1	1386.4	1384.6	1382.9
12.5°	1366.2	1364.6	1363.0	1360.8	1357.9	1355.0	1352.0	1349.1
15°	1316.3	1310.7	1305.1	1300.9	1298.0	1295.0	1292.1	1289.2
17.5°	1259.8	1253.2	1246.6	1240.7	1235.7	1230.6	1225.5	1220.6
20°	1220.4	1213.1	1205.7	1198.9	1192.4	1185.9	1179.5	1173.0
22.5°	1177.2	1167.7	1158.2	1151.1	1146.3	1141.5	1136.7	1131.9
25°	1105.4	1093.5	1081.4	1073.2	1068.8	1064.4	1060.0	1055.6
27.5°	1037.1	1023.0	1009.0	998.5	991.5	984.6	977.6	970.6
30°	988.8	973.8	958.8	947.4	939.5	931.6	923.7	915.8
32.5°	940.2	923.2	906.0	893.8	886.4	878.9	871.4	864.0
35°	864.3	845.8	827.3	814.9	808.4	801.9	795.5	789.1
37.5°	790.3	770.0	749.6	735.7	728.4	721.0	713.6	706.2
40°	740.8	720.0	699.2	685.0	677.3	669.7	662.1	654.4
42.5°	690.9	669.3	647.8	633.4	625.9	618.5	611.2	603.8
45°	618.1	597.3	576.4	562.6	555.5	548.5	541.4	534.4
47.5°	547.3	526.7	505.9	492.4	486.0	479.7	473.2	466.8
50°	501.9	481.6	461.4	448.2	442.0	435.8	429.7	423.5
52.5°	458.9	439.4	419.9	407.3	401.6	395.9	390.2	384.5
55°	393.6	376.1	358.4	346.9	341.3	335.7	330.2	324.6
57.5°	334.3	318.1	302.0	291.6	287.0	282.2	277.6	272.9
60°	293.3	278.4	263.5	253.7	248.9	244.3	239.5	234.9
62.5°	257.9	243.6	229.4	220.8	218.0	215.2	212.3	209.6
65°	209.7	199.7	189.7	184.3	183.4	182.5	181.7	180.8
67.5°	169.3	164.7	160.1	157.3	156.4	155.5	154.5	153.6
70°	147.2	144.3	141.4	139.3	138.1	136.9	135.8	134.6
72.5°	128.1	125.6	123.1	121.6	120.9	120.2	119.4	118.7
75°	101.4	99.4	97.4	96.2	95.9	95.6	95.3	95.0
77.5°	76.8	75.7	74.5	73.6	73.2	72.8	72.2	71.8
80°	61.0	59.8	58.6	58.0	58.0	58.0	58.0	58.0
82.5°	46.1	45.4	44.7	44.3	44.3	44.3	44.3	44.3
85°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
87.5°	9.9	9.6	9.5	9.4	9.4	9.4	9.4	9.4
90°	9.7	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	26.5	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	79.7	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	186.0	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	277.8	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	337.9	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	369.6	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	346.7	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	327.0	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331740-935

CATALOG NUMBER: SA2XXRDIP-C1005D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.0	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	286.9	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	270.2	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	261.9	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	255.4	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	245.8	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	236.3	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	230.3	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	224.5	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	216.3	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	209.8	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	205.6	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	202.2	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	197.4	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	193.7	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	191.1	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	188.4	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	184.7	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	180.4	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	177.6	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	175.0	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	171.0	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	167.1	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	165.2	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.0	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.7	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)