

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331744-935

Luminaire Tested: **SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331744-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4820.2 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331744-935
CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331744-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58	54				
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46				
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43	40				
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38	34				
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	40	36	33	30				
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27				
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24				
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22				
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23541	23541	23541
5°	23631	23246	23376
10°	23451	22866	22673
15°	23181	22188	21549
20°	22807	21220	20155
25°	22425	20122	18805
30°	21895	18990	17074
35°	21378	17763	15554
40°	20858	16493	13793
45°	20247	15066	12202
50°	19623	13622	10638
55°	18978	12073	9137
60°	18235	10440	7585
65°	17391	8772	6907
70°	16386	7227	6354
75°	15147	6588	5926
80°	13371	5895	5393
85°	10504	4650	4650



TEST NUMBER: P331744-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	2.8
10°-20°	374.7	7.8
20°-30°	526.2	10.9
30°-40°	573.8	11.9
40°-50°	527.6	10.9
50°-60°	414.4	8.6
60°-70°	270.2	5.6
70°-80°	139.3	2.9
80°-90°	37.7	0.8
90°-100°	20.7	0.4
100°-110°	76.0	1.6
110°-120°	203.0	4.2
120°-130°	335.2	7.0
130°-140°	356.5	7.4
140°-150°	331.3	6.9
150°-160°	266.4	5.5
160°-170°	171.7	3.6
170°-180°	59.1	1.2
0°-30°	1037.4	21.5
0°-40°	1611.3	33.4
0°-60°	2553.2	53.0
0°-90°	3000.4	62.2
90°-120°	299.7	6.2
90°-150°	1322.7	27.4
90°-180°	1820.0	37.8
0°-180°	4820.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1445	1442	138
15°	1387	1371	1327	1303	1289	390
25°	1259	1214	1130	1077	1056	579
35°	1085	1015	901	821	789	678
45°	887	796	660	570	534	684
55°	674	569	429	353	325	602
65°	455	348	230	187	181	451
75°	243	153	106	97	95	257
85°	57	30	25	25	25	67
90°	0	5	9	11	12	4
95°	29	15	18	20	19	36
105°	137	143	27	32	34	146
115°	258	266	277	79	37	254
125°	365	371	380	383	384	326
135°	452	459	463	468	467	349
145°	524	524	532	534	532	328
155°	577	574	579	581	578	266
165°	608	606	607	610	607	172
175°	622	619	620	623	619	59
180°	621	621	621	621	621	



TEST NUMBER: P331744-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1463.4	1462.2	1460.9	1459.8	1458.6	1456.7	1454.1	1451.6	1449.1	1446.5	1448.8
5°	1458.0	1456.6	1455.1	1453.6	1452.2	1449.6	1445.7	1441.9	1438.1	1434.3	1436.9
7.5°	1443.0	1441.2	1439.4	1437.5	1435.7	1432.6	1428.1	1423.7	1419.3	1414.8	1415.6
10°	1430.4	1428.3	1426.2	1424.2	1422.1	1418.2	1412.3	1406.4	1400.6	1394.7	1393.9
12.5°	1414.5	1412.0	1409.5	1407.0	1404.5	1399.4	1391.9	1384.4	1376.9	1369.4	1367.8
15°	1386.8	1383.5	1380.4	1377.1	1373.9	1367.3	1357.4	1347.4	1337.4	1327.4	1321.9
17.5°	1352.7	1347.8	1342.9	1338.0	1333.1	1324.2	1311.4	1298.6	1285.8	1273.1	1266.4
20°	1327.4	1321.5	1315.7	1309.8	1304.0	1293.7	1279.0	1264.4	1249.7	1235.0	1227.7
22.5°	1299.9	1293.4	1286.9	1280.3	1273.7	1262.1	1245.6	1229.1	1212.5	1196.0	1186.5
25°	1258.8	1249.4	1240.0	1230.6	1221.2	1206.9	1187.6	1168.2	1148.8	1129.5	1117.5
27.5°	1209.2	1199.0	1188.8	1178.6	1168.4	1152.4	1130.6	1108.7	1086.9	1065.1	1051.1
30°	1174.4	1163.2	1152.1	1140.9	1129.8	1112.5	1089.0	1065.6	1042.2	1018.6	1003.7
32.5°	1140.6	1127.6	1114.6	1101.6	1088.5	1070.1	1046.1	1022.2	998.2	974.3	957.3
35°	1084.6	1069.7	1054.7	1039.7	1024.8	1004.4	978.6	952.9	927.0	901.2	882.8
37.5°	1028.7	1012.3	995.8	979.4	963.0	941.1	913.5	886.1	858.5	831.0	810.7
40°	989.6	972.1	954.4	936.9	919.3	896.2	867.8	839.4	810.9	782.5	761.6
42.5°	949.5	931.0	912.5	893.9	875.4	851.4	822.1	792.6	763.3	733.9	712.4
45°	886.7	867.0	847.4	827.8	808.1	782.9	752.1	721.3	690.5	659.8	638.9
47.5°	825.4	804.7	783.9	763.0	742.2	715.9	684.2	652.3	620.5	588.8	568.1
50°	781.2	760.3	739.5	718.7	697.8	671.3	639.1	606.8	574.5	542.3	522.1
52.5°	737.9	716.1	694.4	672.6	650.8	624.2	592.6	561.1	529.5	498.0	478.5
55°	674.2	651.4	628.5	605.6	582.8	555.5	523.8	492.1	460.5	428.9	411.2
57.5°	609.1	585.7	562.1	538.7	515.2	488.3	457.9	427.4	397.0	366.5	350.4
60°	564.7	541.3	517.8	494.4	470.9	444.1	413.9	383.7	353.4	323.3	308.3
62.5°	521.5	498.0	474.6	451.1	427.7	401.5	372.7	343.9	315.1	286.4	272.1
65°	455.2	431.4	407.8	384.0	360.2	335.2	308.8	282.4	256.0	229.6	219.6
67.5°	391.3	367.8	344.2	320.6	297.0	273.4	249.7	225.9	202.2	178.4	173.8
70°	347.1	324.2	301.3	278.4	255.5	234.0	213.8	193.6	173.3	153.1	150.2
72.5°	304.8	282.8	261.0	239.0	217.1	197.9	181.8	165.5	149.2	133.0	130.5
75°	242.8	222.2	201.7	181.2	160.7	145.4	135.4	125.5	115.5	105.6	103.5
77.5°	181.8	163.8	145.9	127.9	109.8	98.4	93.6	88.8	83.9	79.2	78.0
80°	143.8	128.9	113.9	98.9	84.0	75.1	72.2	69.2	66.3	63.4	62.2
82.5°	109.0	97.3	85.7	74.0	62.3	55.4	53.5	51.5	49.5	47.5	46.8
85°	56.7	50.5	44.4	38.2	32.1	28.6	27.7	26.9	25.9	25.1	25.1
87.5°	17.0	15.3	13.7	12.0	10.3	9.6	9.7	9.9	10.1	10.2	10.1
90°	0.4	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5
92.5°	9.0	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7
95°	29.2	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0
97.5°	57.9	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8
100°	79.6	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4
102.5°	103.2	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4
105°	136.6	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5
107.5°	174.6	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3
110°	199.1	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6



TEST NUMBER: P331744-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	222.1	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9
115°	258.4	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0
117.5°	290.8	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9
120°	314.5	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5
122.5°	334.7	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3
125°	365.3	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4
127.5°	393.0	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9
130°	410.7	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0
132.5°	428.7	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7
135°	452.0	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3
137.5°	475.7	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3
140°	491.1	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6
142.5°	504.0	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8
145°	524.3	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3
147.5°	542.1	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5
150°	553.5	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2
152.5°	563.3	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2
155°	577.4	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4
157.5°	588.4	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4
160°	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6
162.5°	600.6	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0
165°	608.4	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8
167.5°	614.2	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4
170°	617.3	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3
172.5°	619.6	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5
175°	622.3	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8
177.5°	622.8	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331744-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1451.1	1453.5	1455.9	1456.7	1456.3	1455.9	1455.3	1454.9
5°	1439.6	1442.3	1444.8	1445.7	1444.8	1444.0	1443.1	1442.3
7.5°	1416.3	1417.0	1417.8	1417.5	1415.9	1414.4	1412.9	1411.4
10°	1392.9	1392.1	1391.2	1389.9	1388.1	1386.4	1384.6	1382.9
12.5°	1366.2	1364.6	1363.0	1360.8	1357.9	1355.0	1352.0	1349.1
15°	1316.3	1310.7	1305.1	1300.9	1298.0	1295.0	1292.1	1289.2
17.5°	1259.8	1253.2	1246.6	1240.7	1235.7	1230.6	1225.5	1220.6
20°	1220.4	1213.1	1205.7	1198.9	1192.4	1185.9	1179.5	1173.0
22.5°	1177.2	1167.7	1158.2	1151.1	1146.3	1141.5	1136.7	1131.9
25°	1105.4	1093.5	1081.4	1073.2	1068.8	1064.4	1060.0	1055.6
27.5°	1037.1	1023.0	1009.0	998.5	991.5	984.6	977.6	970.6
30°	988.8	973.8	958.8	947.4	939.5	931.6	923.7	915.8
32.5°	940.2	923.2	906.0	893.8	886.4	878.9	871.4	864.0
35°	864.3	845.8	827.3	814.9	808.4	801.9	795.5	789.1
37.5°	790.3	770.0	749.6	735.7	728.4	721.0	713.6	706.2
40°	740.8	720.0	699.2	685.0	677.3	669.7	662.1	654.4
42.5°	690.9	669.3	647.8	633.4	625.9	618.5	611.2	603.8
45°	618.1	597.3	576.4	562.6	555.5	548.5	541.4	534.4
47.5°	547.3	526.7	505.9	492.4	486.0	479.7	473.2	466.8
50°	501.9	481.6	461.4	448.2	442.0	435.8	429.7	423.5
52.5°	458.9	439.4	419.9	407.3	401.6	395.9	390.2	384.5
55°	393.6	376.1	358.4	346.9	341.3	335.7	330.2	324.6
57.5°	334.3	318.1	302.0	291.6	287.0	282.2	277.6	272.9
60°	293.3	278.4	263.5	253.7	248.9	244.3	239.5	234.9
62.5°	257.9	243.6	229.4	220.8	218.0	215.2	212.3	209.6
65°	209.7	199.7	189.7	184.3	183.4	182.5	181.7	180.8
67.5°	169.3	164.7	160.1	157.3	156.4	155.5	154.5	153.6
70°	147.2	144.3	141.4	139.3	138.1	136.9	135.8	134.6
72.5°	128.1	125.6	123.1	121.6	120.9	120.2	119.4	118.7
75°	101.4	99.4	97.4	96.2	95.9	95.6	95.3	95.0
77.5°	76.8	75.7	74.5	73.6	73.2	72.8	72.2	71.8
80°	61.0	59.8	58.6	58.0	58.0	58.0	58.0	58.0
82.5°	46.1	45.4	44.7	44.3	44.3	44.3	44.3	44.3
85°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
87.5°	10.0	9.8	9.7	9.6	9.7	9.7	9.8	9.8
90°	10.0	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	10.9	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	18.5	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.3	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	27.2	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	28.4	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	29.6	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	36.2	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	58.6	48.6	38.7	33.9	34.3	34.7	35.1	35.5



TEST NUMBER: P331744-935

CATALOG NUMBER: SA2XXRDIP-C1005D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.4	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	184.8	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	284.7	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	331.7	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.0	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.1	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	407.9	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	425.0	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	441.6	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	465.3	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	487.2	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	501.4	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	514.6	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.0	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.0	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	558.8	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	567.8	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.0	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.1	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.1	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	601.7	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.1	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.0	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.1	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	621.5	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	621.7	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)