

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331264-930

Luminaire Tested: **SA2XXDIP-C290D725U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331264-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3344.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331264-930
CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331264-930

CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21
3	77	68	61	55	69	61	55	51	48	44	41	37	34	31	26	24	22	18
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19	15
5	65	54	46	40	58	48	42	36	38	34	30	29	26	23	21	18	17	13
6	60	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15	11
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	16	13	12	9
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11	8
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331264-930

CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	1.1
10°-20°	101.9	3.0
20°-30°	149.8	4.5
30°-40°	174.0	5.2
40°-50°	173.8	5.2
50°-60°	151.6	4.5
60°-70°	112.1	3.4
70°-80°	63.5	1.9
80°-90°	19.1	0.6
90°-100°	26.9	0.8
100°-110°	98.6	2.9
110°-120°	263.5	7.9
120°-130°	435.0	13.0
130°-140°	462.7	13.8
140°-150°	430.0	12.9
150°-160°	345.7	10.3
160°-170°	222.8	6.7
170°-180°	76.7	2.3
0°-30°	287.9	8.6
0°-40°	461.9	13.8
0°-60°	787.3	23.5
0°-90°	981.9	29.4
90°-120°	389.0	11.6
90°-150°	1716.8	51.3
90°-180°	2362.0	70.6
0°-180°	3344.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	1	7	12	14	16	3
95°	38	20	23	26	25	46
105°	177	185	36	42	44	189
115°	335	346	360	102	48	330
125°	474	482	493	497	499	423
135°	587	596	601	607	606	453
145°	681	681	690	694	691	426
155°	749	745	751	754	750	345
165°	790	786	788	792	788	223
175°	808	804	805	808	803	77
180°	806	806	806	806	806	



TEST NUMBER: P331264-930

CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	5.6	5.8	5.9	6.0	6.2	6.3	6.4	6.4	6.4	6.4
90°	0.6	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3
92.5°	11.7	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9
95°	37.9	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4
97.5°	75.3	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0
100°	103.2	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2
102.5°	134.0	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5
105°	177.3	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0
107.5°	226.7	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3
110°	258.4	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1



TEST NUMBER: P331264-930

CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2
115°	335.3	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9
117.5°	377.5	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1
120°	408.2	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0
122.5°	434.4	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9
125°	474.2	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7
127.5°	510.2	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2
130°	533.0	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2
132.5°	556.4	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9
135°	586.7	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6
137.5°	617.4	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1
140°	637.5	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7
142.5°	654.3	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8
145°	680.6	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9
147.5°	703.6	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8
150°	718.5	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6
152.5°	731.1	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2
155°	749.4	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0
157.5°	763.8	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2
160°	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0
162.5°	779.7	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1
165°	789.7	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8
167.5°	797.1	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1
170°	801.4	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9
172.5°	804.1	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7
175°	807.7	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8
177.5°	808.4	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331264-930

CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	6.4	6.3	6.2	6.2	6.1	6.1	6.1	6.1
90°	13.0	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.2	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.1	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	31.5	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	35.3	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	36.9	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	38.4	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	46.9	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	76.1	63.2	50.2	44.0	44.5	45.0	45.6	46.1



TEST NUMBER: P331264-930

CATALOG NUMBER: SA2XXDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	162.9	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	239.9	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	369.6	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	430.6	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	456.9	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	494.6	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	529.5	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	551.6	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	573.2	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	603.9	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	632.4	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	650.9	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	667.9	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	691.8	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	712.5	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	725.3	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	736.9	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	752.8	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.0	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	773.7	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	780.9	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	797.1	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	800.8	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	803.6	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	806.7	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.0	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)