

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331628-935

Luminaire Tested: **SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331628-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3205.9 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331628-935  
CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	27
2	86	79	73	68	77	71	66	62	57	53	51	43	41	39	31	30	29	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18
5	66	55	48	42	59	50	44	39	41	36	32	31	28	26	23	21	19	16
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17	14
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16	13
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	15	13	11
10	46	34	28	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.4	1.7
10°-20°	148.7	4.6
20°-30°	191.6	6.0
30°-40°	182.1	5.7
40°-50°	156.0	4.9
50°-60°	118.8	3.7
60°-70°	75.1	2.3
70°-80°	37.5	1.2
80°-90°	12.9	0.4
90°-100°	50.5	1.6
100°-110°	157.0	4.9
110°-120°	268.3	8.4
120°-130°	352.8	11.0
130°-140°	396.0	12.4
140°-150°	388.3	12.1
150°-160°	325.7	10.2
160°-170°	216.0	6.7
170°-180°	75.5	2.4
0°-30°	393.6	12.3
0°-40°	575.7	18.0
0°-60°	850.4	26.5
0°-90°	976.0	30.4
90°-120°	475.8	14.8
90°-150°	1612.8	50.3
90°-180°	2230.0	69.6
0°-180°	3205.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	23	1	23	1	23	10
95°	42	35	42	35	42	47
105°	149	145	149	145	149	157
115°	269	269	269	269	269	266
125°	393	392	393	392	393	350
135°	513	507	513	507	513	395
145°	622	615	622	615	622	388
155°	709	703	709	703	709	326
165°	766	765	766	765	766	216
175°	794	796	794	796	794	75
180°	798	798	798	798	798	



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	7.1	7.2	7.1	7.1	7.1	7.1	7.2	7.4	7.3	7.5	6.7
90°	22.9	22.7	22.6	22.5	22.3	22.4	22.6	23.0	23.2	23.6	20.2
92.5°	21.8	21.8	21.8	21.7	21.7	21.6	21.6	21.5	21.4	21.4	20.7
95°	41.8	42.0	42.4	42.6	43.0	43.0	43.0	43.0	43.0	43.0	42.8
97.5°	72.2	72.3	72.3	72.4	72.4	72.4	72.4	72.4	72.4	72.4	71.8
100°	92.2	92.4	92.5	92.6	92.8	92.9	92.9	92.9	92.9	92.9	92.4
102.5°	114.8	114.9	115.1	115.3	115.4	115.5	115.3	115.2	115.0	114.9	114.3
105°	149.4	149.4	149.4	149.4	149.4	149.3	149.0	148.7	148.4	148.1	147.7
107.5°	182.0	182.7	183.4	184.1	184.8	185.0	184.9	184.8	184.7	184.5	184.5
110°	207.2	207.8	208.2	208.6	209.1	209.3	209.3	209.3	209.3	209.3	209.3



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	231.5	231.9	232.1	232.5	232.8	233.2	233.5	233.8	234.3	234.6	234.7
115°	269.2	269.7	270.1	270.5	271.0	271.3	271.5	271.6	271.7	271.9	272.2
117.5°	305.1	305.6	306.0	306.5	306.9	307.3	307.7	308.1	308.4	308.8	309.6
120°	330.5	330.9	331.3	331.7	332.3	332.4	332.4	332.4	332.4	332.4	333.6
122.5°	355.2	355.5	355.9	356.2	356.5	356.9	357.2	357.6	357.9	358.3	359.1
125°	393.0	393.2	393.3	393.5	393.6	393.9	394.3	394.9	395.3	395.7	396.1
127.5°	427.5	428.0	428.4	429.0	429.4	429.9	430.4	431.0	431.5	432.0	432.6
130°	452.3	452.9	453.5	454.0	454.6	455.1	455.4	455.7	456.0	456.3	456.6
132.5°	476.0	476.4	476.9	477.3	477.9	478.5	479.1	479.7	480.4	481.0	481.0
135°	512.8	513.2	513.8	514.2	514.6	514.9	515.1	515.2	515.4	515.5	515.2
137.5°	546.2	546.8	547.4	548.0	548.6	549.0	549.1	549.2	549.3	549.4	549.1
140°	569.4	570.0	570.6	571.2	571.7	572.0	572.0	572.0	572.0	572.0	571.3
142.5°	590.4	591.0	591.5	592.1	592.7	593.0	592.9	592.7	592.6	592.5	592.0
145°	621.8	622.4	623.0	623.6	624.2	624.5	624.3	624.1	624.1	623.9	622.9
147.5°	650.0	650.6	651.1	651.7	652.3	652.4	652.0	651.7	651.3	651.1	650.5
150°	668.3	668.7	669.2	669.6	670.1	670.1	669.6	669.2	668.7	668.3	667.7
152.5°	685.5	686.0	686.6	687.3	687.8	687.8	687.3	686.6	686.0	685.5	684.8
155°	708.7	709.1	709.6	710.0	710.5	710.3	709.6	708.8	708.1	707.3	706.9
157.5°	728.6	729.3	730.0	730.7	731.4	731.3	730.3	729.3	728.2	727.2	726.9
160°	741.0	741.6	742.2	742.8	743.4	743.2	742.4	741.4	740.5	739.6	739.5
162.5°	751.7	752.4	753.2	753.9	754.6	754.5	753.5	752.4	751.4	750.4	750.3
165°	765.9	766.6	767.3	768.1	768.9	768.7	767.7	766.6	765.6	764.5	764.5
167.5°	777.5	778.3	779.0	779.8	780.6	780.4	779.4	778.3	777.3	776.2	776.3
170°	783.3	784.3	785.1	786.1	787.0	786.9	785.8	784.8	783.8	782.6	782.8
172.5°	788.2	789.1	790.0	790.9	791.8	791.7	790.7	789.6	788.6	787.6	787.7
175°	793.5	794.4	795.2	796.2	797.0	796.9	795.9	794.9	793.8	792.8	793.1
177.5°	795.9	796.6	797.3	798.1	798.7	798.7	798.1	797.3	796.6	795.9	796.1
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	6.0	5.5	4.9	4.2	4.0	3.8	4.2	4.6	4.4	4.3	4.3
90°	17.0	13.7	10.4	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	19.8	19.0	18.3	17.2	15.9	14.6	13.3	12.0	13.3	14.6	15.9
95°	42.4	42.2	41.8	41.0	39.5	38.0	36.5	35.0	36.5	38.0	39.5
97.5°	71.3	70.7	70.2	69.2	67.8	66.6	65.3	64.0	65.3	66.6	67.8
100°	92.0	91.5	91.1	90.2	89.0	87.8	86.7	85.5	86.7	87.8	89.0
102.5°	113.8	113.2	112.7	111.9	111.0	110.0	109.0	108.1	109.0	110.0	111.0
105°	147.5	147.1	146.9	146.5	146.0	145.6	145.2	144.7	145.2	145.6	146.0
107.5°	184.5	184.5	184.5	184.2	183.6	182.9	182.3	181.6	182.3	182.9	183.6
110°	209.3	209.3	209.3	208.9	207.9	207.1	206.1	205.3	206.1	207.1	207.9





TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	234.9	235.0	235.1	234.7	233.8	232.9	232.0	231.1	232.0	232.9	233.8
115°	272.5	272.8	273.1	272.8	271.9	271.0	270.1	269.2	270.1	271.0	271.9
117.5°	310.5	311.3	312.1	311.9	310.7	309.5	308.3	307.1	308.3	309.5	310.7
120°	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	333.6	334.8	336.0
122.5°	360.0	360.8	361.6	361.4	359.9	358.5	357.1	355.6	357.1	358.5	359.9
125°	396.6	397.1	397.5	397.1	395.7	394.3	393.0	391.7	393.0	394.3	395.7
127.5°	433.2	433.7	434.2	433.6	432.0	430.2	428.5	426.8	428.5	430.2	432.0
130°	456.8	457.2	457.4	456.7	454.7	452.8	450.8	448.9	450.8	452.8	454.7
132.5°	481.0	480.9	480.8	480.0	478.4	476.8	475.3	473.6	475.3	476.8	478.4
135°	514.9	514.6	514.3	513.3	511.7	510.1	508.4	506.8	508.4	510.1	511.7
137.5°	548.6	548.3	547.9	547.0	545.7	544.3	542.9	541.7	542.9	544.3	545.7
140°	570.6	569.8	569.0	568.0	566.6	565.3	564.0	562.7	564.0	565.3	566.6
142.5°	591.5	591.0	590.5	589.5	588.2	586.9	585.5	584.2	585.5	586.9	588.2
145°	622.1	621.2	620.3	619.3	618.3	617.3	616.1	615.1	616.1	617.3	618.3
147.5°	649.9	649.3	648.7	647.7	646.4	645.2	643.9	642.7	643.9	645.2	646.4
150°	667.1	666.5	665.9	665.1	664.3	663.3	662.5	661.6	662.5	663.3	664.3
152.5°	684.1	683.4	682.6	681.8	681.0	680.0	679.2	678.2	679.2	680.0	681.0
155°	706.5	705.9	705.5	705.1	704.6	704.2	703.7	703.3	703.7	704.2	704.6
157.5°	726.7	726.4	726.2	725.9	725.6	725.3	725.0	724.7	725.0	725.3	725.6
160°	739.3	739.2	739.0	738.8	738.5	738.2	737.9	737.6	737.9	738.2	738.5
162.5°	750.1	749.9	749.8	749.7	749.6	749.6	749.5	749.4	749.5	749.6	749.6
165°	764.5	764.5	764.5	764.6	764.7	764.9	765.1	765.2	765.1	764.9	764.7
167.5°	776.3	776.4	776.4	776.6	777.1	777.5	777.9	778.3	777.9	777.5	777.1
170°	783.0	783.2	783.3	783.6	784.0	784.5	785.0	785.4	785.0	784.5	784.0
172.5°	787.8	788.0	788.2	788.4	788.8	789.4	789.8	790.2	789.8	789.4	788.8
175°	793.4	793.7	794.0	794.4	794.8	795.2	795.7	796.2	795.7	795.2	794.8
177.5°	796.3	796.6	796.9	797.1	797.5	797.9	798.2	798.6	798.2	797.9	797.5
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.6	4.9	5.3	5.9	6.5	7.1	7.0	6.8	6.7	6.6	6.5
90°	7.8	10.4	13.7	17.0	20.2	23.6	23.2	23.0	22.6	22.4	22.3
92.5°	17.2	18.3	19.0	19.8	20.7	21.4	21.4	21.5	21.6	21.6	21.7
95°	41.0	41.8	42.2	42.4	42.8	43.0	43.0	43.0	43.0	43.0	43.0
97.5°	69.2	70.2	70.7	71.3	71.8	72.4	72.4	72.4	72.4	72.4	72.4
100°	90.2	91.1	91.5	92.0	92.4	92.9	92.9	92.9	92.9	92.9	92.8
102.5°	111.9	112.7	113.2	113.8	114.3	114.9	115.0	115.2	115.3	115.5	115.4
105°	146.5	146.9	147.1	147.5	147.7	148.1	148.4	148.7	149.0	149.3	149.4
107.5°	184.2	184.5	184.5	184.5	184.5	184.5	184.7	184.8	184.9	185.0	184.8
110°	208.9	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.3	209.1



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	234.7	235.1	235.0	234.9	234.7	234.6	234.3	233.8	233.5	233.2	232.8
115°	272.8	273.1	272.8	272.5	272.2	271.9	271.7	271.6	271.5	271.3	271.0
117.5°	311.9	312.1	311.3	310.5	309.6	308.8	308.4	308.1	307.7	307.3	306.9
120°	337.3	337.3	336.0	334.8	333.6	332.4	332.4	332.4	332.4	332.4	332.3
122.5°	361.4	361.6	360.8	360.0	359.1	358.3	357.9	357.6	357.2	356.9	356.5
125°	397.1	397.5	397.1	396.6	396.1	395.7	395.3	394.9	394.3	393.9	393.6
127.5°	433.6	434.2	433.7	433.2	432.6	432.0	431.5	431.0	430.4	429.9	429.4
130°	456.7	457.4	457.2	456.8	456.6	456.3	456.0	455.7	455.4	455.1	454.6
132.5°	480.0	480.8	480.9	481.0	481.0	481.0	480.4	479.7	479.1	478.5	477.9
135°	513.3	514.3	514.6	514.9	515.2	515.5	515.4	515.2	515.1	514.9	514.6
137.5°	547.0	547.9	548.3	548.6	549.1	549.4	549.3	549.2	549.1	549.0	548.6
140°	568.0	569.0	569.8	570.6	571.3	572.0	572.0	572.0	572.0	572.0	571.7
142.5°	589.5	590.5	591.0	591.5	592.0	592.5	592.6	592.7	592.9	593.0	592.7
145°	619.3	620.3	621.2	622.1	622.9	623.9	624.1	624.1	624.3	624.5	624.2
147.5°	647.7	648.7	649.3	649.9	650.5	651.1	651.3	651.7	652.0	652.4	652.3
150°	665.1	665.9	666.5	667.1	667.7	668.3	668.7	669.2	669.6	670.1	670.1
152.5°	681.8	682.6	683.4	684.1	684.8	685.5	686.0	686.6	687.3	687.8	687.8
155°	705.1	705.5	705.9	706.5	706.9	707.3	708.1	708.8	709.6	710.3	710.5
157.5°	725.9	726.2	726.4	726.7	726.9	727.2	728.2	729.3	730.3	731.3	731.4
160°	738.8	739.0	739.2	739.3	739.5	739.6	740.5	741.4	742.4	743.2	743.4
162.5°	749.7	749.8	749.9	750.1	750.3	750.4	751.4	752.4	753.5	754.5	754.6
165°	764.6	764.5	764.5	764.5	764.5	764.5	765.6	766.6	767.7	768.7	768.9
167.5°	776.6	776.4	776.4	776.3	776.3	776.2	777.3	778.3	779.4	780.4	780.6
170°	783.6	783.3	783.2	783.0	782.8	782.6	783.8	784.8	785.8	786.9	787.0
172.5°	788.4	788.2	788.0	787.8	787.7	787.6	788.6	789.6	790.7	791.7	791.8
175°	794.4	794.0	793.7	793.4	793.1	792.8	793.8	794.9	795.9	796.9	797.0
177.5°	797.1	796.9	796.6	796.3	796.1	795.9	796.6	797.3	798.1	798.7	798.7
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	6.5	6.4	6.5	6.5	6.5	6.4	6.5	6.5	6.6	6.7	6.8
90°	22.5	22.6	22.7	22.9	22.7	22.6	22.5	22.3	22.4	22.6	23.0
92.5°	21.7	21.8	21.8	21.8	21.8	21.8	21.7	21.7	21.6	21.6	21.5
95°	42.6	42.4	42.0	41.8	42.0	42.4	42.6	43.0	43.0	43.0	43.0
97.5°	72.4	72.3	72.3	72.2	72.3	72.3	72.4	72.4	72.4	72.4	72.4
100°	92.6	92.5	92.4	92.2	92.4	92.5	92.6	92.8	92.9	92.9	92.9
102.5°	115.3	115.1	114.9	114.8	114.9	115.1	115.3	115.4	115.5	115.3	115.2
105°	149.4	149.4	149.4	149.4	149.4	149.4	149.4	149.4	149.3	149.0	148.7
107.5°	184.1	183.4	182.7	182.0	182.7	183.4	184.1	184.8	185.0	184.9	184.8
110°	208.6	208.2	207.8	207.2	207.8	208.2	208.6	209.1	209.3	209.3	209.3



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	232.5	232.1	231.9	231.5	231.9	232.1	232.5	232.8	233.2	233.5	233.8
115°	270.5	270.1	269.7	269.2	269.7	270.1	270.5	271.0	271.3	271.5	271.6
117.5°	306.5	306.0	305.6	305.1	305.6	306.0	306.5	306.9	307.3	307.7	308.1
120°	331.7	331.3	330.9	330.5	330.9	331.3	331.7	332.3	332.4	332.4	332.4
122.5°	356.2	355.9	355.5	355.2	355.5	355.9	356.2	356.5	356.9	357.2	357.6
125°	393.5	393.3	393.2	393.0	393.2	393.3	393.5	393.6	393.9	394.3	394.9
127.5°	429.0	428.4	428.0	427.5	428.0	428.4	429.0	429.4	429.9	430.4	431.0
130°	454.0	453.5	452.9	452.3	452.9	453.5	454.0	454.6	455.1	455.4	455.7
132.5°	477.3	476.9	476.4	476.0	476.4	476.9	477.3	477.9	478.5	479.1	479.7
135°	514.2	513.8	513.2	512.8	513.2	513.8	514.2	514.6	514.9	515.1	515.2
137.5°	548.0	547.4	546.8	546.2	546.8	547.4	548.0	548.6	549.0	549.1	549.2
140°	571.2	570.6	570.0	569.4	570.0	570.6	571.2	571.7	572.0	572.0	572.0
142.5°	592.1	591.5	591.0	590.4	591.0	591.5	592.1	592.7	593.0	592.9	592.7
145°	623.6	623.0	622.4	621.8	622.4	623.0	623.6	624.2	624.5	624.3	624.1
147.5°	651.7	651.1	650.6	650.0	650.6	651.1	651.7	652.3	652.4	652.0	651.7
150°	669.6	669.2	668.7	668.3	668.7	669.2	669.6	670.1	670.1	669.6	669.2
152.5°	687.3	686.6	686.0	685.5	686.0	686.6	687.3	687.8	687.8	687.3	686.6
155°	710.0	709.6	709.1	708.7	709.1	709.6	710.0	710.5	710.3	709.6	708.8
157.5°	730.7	730.0	729.3	728.6	729.3	730.0	730.7	731.4	731.3	730.3	729.3
160°	742.8	742.2	741.6	741.0	741.6	742.2	742.8	743.4	743.2	742.4	741.4
162.5°	753.9	753.2	752.4	751.7	752.4	753.2	753.9	754.6	754.5	753.5	752.4
165°	768.1	767.3	766.6	765.9	766.6	767.3	768.1	768.9	768.7	767.7	766.6
167.5°	779.8	779.0	778.3	777.5	778.3	779.0	779.8	780.6	780.4	779.4	778.3
170°	786.1	785.1	784.3	783.3	784.3	785.1	786.1	787.0	786.9	785.8	784.8
172.5°	790.9	790.0	789.1	788.2	789.1	790.0	790.9	791.8	791.7	790.7	789.6
175°	796.2	795.2	794.4	793.5	794.4	795.2	796.2	797.0	796.9	795.9	794.9
177.5°	798.1	797.3	796.6	795.9	796.6	797.3	798.1	798.7	798.7	798.1	797.3
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	7.0	7.1	6.5	5.9	5.3	4.9	4.6	4.3	4.3	4.4	4.6
90°	23.2	23.6	20.2	17.0	13.7	10.4	7.8	6.0	4.3	2.5	0.7
92.5°	21.4	21.4	20.7	19.8	19.0	18.3	17.2	15.9	14.6	13.3	12.0
95°	43.0	43.0	42.8	42.4	42.2	41.8	41.0	39.5	38.0	36.5	35.0
97.5°	72.4	72.4	71.8	71.3	70.7	70.2	69.2	67.8	66.6	65.3	64.0
100°	92.9	92.9	92.4	92.0	91.5	91.1	90.2	89.0	87.8	86.7	85.5
102.5°	115.0	114.9	114.3	113.8	113.2	112.7	111.9	111.0	110.0	109.0	108.1
105°	148.4	148.1	147.7	147.5	147.1	146.9	146.5	146.0	145.6	145.2	144.7
107.5°	184.7	184.5	184.5	184.5	184.5	184.5	184.2	183.6	182.9	182.3	181.6
110°	209.3	209.3	209.3	209.3	209.3	209.3	208.9	207.9	207.1	206.1	205.3



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	234.3	234.6	234.7	234.9	235.0	235.1	234.7	233.8	232.9	232.0	231.1
115°	271.7	271.9	272.2	272.5	272.8	273.1	272.8	271.9	271.0	270.1	269.2
117.5°	308.4	308.8	309.6	310.5	311.3	312.1	311.9	310.7	309.5	308.3	307.1
120°	332.4	332.4	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4
122.5°	357.9	358.3	359.1	360.0	360.8	361.6	361.4	359.9	358.5	357.1	355.6
125°	395.3	395.7	396.1	396.6	397.1	397.5	397.1	395.7	394.3	393.0	391.7
127.5°	431.5	432.0	432.6	433.2	433.7	434.2	433.6	432.0	430.2	428.5	426.8
130°	456.0	456.3	456.6	456.8	457.2	457.4	456.7	454.7	452.8	450.8	448.9
132.5°	480.4	481.0	481.0	481.0	480.9	480.8	480.0	478.4	476.8	475.3	473.6
135°	515.4	515.5	515.2	514.9	514.6	514.3	513.3	511.7	510.1	508.4	506.8
137.5°	549.3	549.4	549.1	548.6	548.3	547.9	547.0	545.7	544.3	542.9	541.7
140°	572.0	572.0	571.3	570.6	569.8	569.0	568.0	566.6	565.3	564.0	562.7
142.5°	592.6	592.5	592.0	591.5	591.0	590.5	589.5	588.2	586.9	585.5	584.2
145°	624.1	623.9	622.9	622.1	621.2	620.3	619.3	618.3	617.3	616.1	615.1
147.5°	651.3	651.1	650.5	649.9	649.3	648.7	647.7	646.4	645.2	643.9	642.7
150°	668.7	668.3	667.7	667.1	666.5	665.9	665.1	664.3	663.3	662.5	661.6
152.5°	686.0	685.5	684.8	684.1	683.4	682.6	681.8	681.0	680.0	679.2	678.2
155°	708.1	707.3	706.9	706.5	705.9	705.5	705.1	704.6	704.2	703.7	703.3
157.5°	728.2	727.2	726.9	726.7	726.4	726.2	725.9	725.6	725.3	725.0	724.7
160°	740.5	739.6	739.5	739.3	739.2	739.0	738.8	738.5	738.2	737.9	737.6
162.5°	751.4	750.4	750.3	750.1	749.9	749.8	749.7	749.6	749.6	749.5	749.4
165°	765.6	764.5	764.5	764.5	764.5	764.5	764.6	764.7	764.9	765.1	765.2
167.5°	777.3	776.2	776.3	776.3	776.4	776.4	776.6	777.1	777.5	777.9	778.3
170°	783.8	782.6	782.8	783.0	783.2	783.3	783.6	784.0	784.5	785.0	785.4
172.5°	788.6	787.6	787.7	787.8	788.0	788.2	788.4	788.8	789.4	789.8	790.2
175°	793.8	792.8	793.1	793.4	793.7	794.0	794.4	794.8	795.2	795.7	796.2
177.5°	796.6	795.9	796.1	796.3	796.6	796.9	797.1	797.5	797.9	798.2	798.6
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.2	3.8	4.0	4.2	4.9	5.5	6.0	6.7	7.5	7.3	7.4
90°	2.5	4.3	6.0	7.8	10.4	13.7	17.0	20.2	23.6	23.2	23.0
92.5°	13.3	14.6	15.9	17.2	18.3	19.0	19.8	20.7	21.4	21.4	21.5
95°	36.5	38.0	39.5	41.0	41.8	42.2	42.4	42.8	43.0	43.0	43.0
97.5°	65.3	66.6	67.8	69.2	70.2	70.7	71.3	71.8	72.4	72.4	72.4
100°	86.7	87.8	89.0	90.2	91.1	91.5	92.0	92.4	92.9	92.9	92.9
102.5°	109.0	110.0	111.0	111.9	112.7	113.2	113.8	114.3	114.9	115.0	115.2
105°	145.2	145.6	146.0	146.5	146.9	147.1	147.5	147.7	148.1	148.4	148.7
107.5°	182.3	182.9	183.6	184.2	184.5	184.5	184.5	184.5	184.5	184.7	184.8
110°	206.1	207.1	207.9	208.9	209.3	209.3	209.3	209.3	209.3	209.3	209.3





TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	232.0	232.9	233.8	234.7	235.1	235.0	234.9	234.7	234.6	234.3	233.8
115°	270.1	271.0	271.9	272.8	273.1	272.8	272.5	272.2	271.9	271.7	271.6
117.5°	308.3	309.5	310.7	311.9	312.1	311.3	310.5	309.6	308.8	308.4	308.1
120°	333.6	334.8	336.0	337.3	337.3	336.0	334.8	333.6	332.4	332.4	332.4
122.5°	357.1	358.5	359.9	361.4	361.6	360.8	360.0	359.1	358.3	357.9	357.6
125°	393.0	394.3	395.7	397.1	397.5	397.1	396.6	396.1	395.7	395.3	394.9
127.5°	428.5	430.2	432.0	433.6	434.2	433.7	433.2	432.6	432.0	431.5	431.0
130°	450.8	452.8	454.7	456.7	457.4	457.2	456.8	456.6	456.3	456.0	455.7
132.5°	475.3	476.8	478.4	480.0	480.8	480.9	481.0	481.0	481.0	480.4	479.7
135°	508.4	510.1	511.7	513.3	514.3	514.6	514.9	515.2	515.5	515.4	515.2
137.5°	542.9	544.3	545.7	547.0	547.9	548.3	548.6	549.1	549.4	549.3	549.2
140°	564.0	565.3	566.6	568.0	569.0	569.8	570.6	571.3	572.0	572.0	572.0
142.5°	585.5	586.9	588.2	589.5	590.5	591.0	591.5	592.0	592.5	592.6	592.7
145°	616.1	617.3	618.3	619.3	620.3	621.2	622.1	622.9	623.9	624.1	624.1
147.5°	643.9	645.2	646.4	647.7	648.7	649.3	649.9	650.5	651.1	651.3	651.7
150°	662.5	663.3	664.3	665.1	665.9	666.5	667.1	667.7	668.3	668.7	669.2
152.5°	679.2	680.0	681.0	681.8	682.6	683.4	684.1	684.8	685.5	686.0	686.6
155°	703.7	704.2	704.6	705.1	705.5	705.9	706.5	706.9	707.3	708.1	708.8
157.5°	725.0	725.3	725.6	725.9	726.2	726.4	726.7	726.9	727.2	728.2	729.3
160°	737.9	738.2	738.5	738.8	739.0	739.2	739.3	739.5	739.6	740.5	741.4
162.5°	749.5	749.6	749.6	749.7	749.8	749.9	750.1	750.3	750.4	751.4	752.4
165°	765.1	764.9	764.7	764.6	764.5	764.5	764.5	764.5	764.5	765.6	766.6
167.5°	777.9	777.5	777.1	776.6	776.4	776.4	776.3	776.3	776.2	777.3	778.3
170°	785.0	784.5	784.0	783.6	783.3	783.2	783.0	782.8	782.6	783.8	784.8
172.5°	789.8	789.4	788.8	788.4	788.2	788.0	787.8	787.7	787.6	788.6	789.6
175°	795.7	795.2	794.8	794.4	794.0	793.7	793.4	793.1	792.8	793.8	794.9
177.5°	798.2	797.9	797.5	797.1	796.9	796.6	796.3	796.1	795.9	796.6	797.3
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5	797.5



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	7.2	7.1	7.1	7.1	7.1	7.2	7.1
90°	22.6	22.4	22.3	22.5	22.6	22.7	22.9
92.5°	21.6	21.6	21.7	21.7	21.8	21.8	21.8
95°	43.0	43.0	43.0	42.6	42.4	42.0	41.8
97.5°	72.4	72.4	72.4	72.4	72.3	72.3	72.2
100°	92.9	92.9	92.8	92.6	92.5	92.4	92.2
102.5°	115.3	115.5	115.4	115.3	115.1	114.9	114.8
105°	149.0	149.3	149.4	149.4	149.4	149.4	149.4
107.5°	184.9	185.0	184.8	184.1	183.4	182.7	182.0
110°	209.3	209.3	209.1	208.6	208.2	207.8	207.2



TEST NUMBER: P331628-935

CATALOG NUMBER: SA2XXRDIP-C290D725U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	233.5	233.2	232.8	232.5	232.1	231.9	231.5
115°	271.5	271.3	271.0	270.5	270.1	269.7	269.2
117.5°	307.7	307.3	306.9	306.5	306.0	305.6	305.1
120°	332.4	332.4	332.3	331.7	331.3	330.9	330.5
122.5°	357.2	356.9	356.5	356.2	355.9	355.5	355.2
125°	394.3	393.9	393.6	393.5	393.3	393.2	393.0
127.5°	430.4	429.9	429.4	429.0	428.4	428.0	427.5
130°	455.4	455.1	454.6	454.0	453.5	452.9	452.3
132.5°	479.1	478.5	477.9	477.3	476.9	476.4	476.0
135°	515.1	514.9	514.6	514.2	513.8	513.2	512.8
137.5°	549.1	549.0	548.6	548.0	547.4	546.8	546.2
140°	572.0	572.0	571.7	571.2	570.6	570.0	569.4
142.5°	592.9	593.0	592.7	592.1	591.5	591.0	590.4
145°	624.3	624.5	624.2	623.6	623.0	622.4	621.8
147.5°	652.0	652.4	652.3	651.7	651.1	650.6	650.0
150°	669.6	670.1	670.1	669.6	669.2	668.7	668.3
152.5°	687.3	687.8	687.8	687.3	686.6	686.0	685.5
155°	709.6	710.3	710.5	710.0	709.6	709.1	708.7
157.5°	730.3	731.3	731.4	730.7	730.0	729.3	728.6
160°	742.4	743.2	743.4	742.8	742.2	741.6	741.0
162.5°	753.5	754.5	754.6	753.9	753.2	752.4	751.7
165°	767.7	768.7	768.9	768.1	767.3	766.6	765.9
167.5°	779.4	780.4	780.6	779.8	779.0	778.3	777.5
170°	785.8	786.9	787.0	786.1	785.1	784.3	783.3
172.5°	790.7	791.7	791.8	790.9	790.0	789.1	788.2
175°	795.9	796.9	797.0	796.2	795.2	794.4	793.5
177.5°	798.1	798.7	798.7	798.1	797.3	796.6	795.9
180°	797.5	797.5	797.5	797.5	797.5	797.5	797.5

(END OF REPORT)