

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331637-935

Luminaire Tested: **SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331637-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3740.1 lumens  
Efficiency: N/A  
Efficacy: 100.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331637-935  
CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331637-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	20
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23	18
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	26	20	19	18	13
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	10
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331637-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.5	1.1
10°-20°	111.1	3.0
20°-30°	156.0	4.2
30°-40°	170.1	4.5
40°-50°	156.4	4.2
50°-60°	122.8	3.3
60°-70°	80.1	2.1
70°-80°	41.3	1.1
80°-90°	14.8	0.4
90°-100°	64.5	1.7
100°-110°	200.4	5.4
110°-120°	342.5	9.2
120°-130°	450.4	12.0
130°-140°	505.6	13.5
140°-150°	495.7	13.3
150°-160°	415.8	11.1
160°-170°	275.8	7.4
170°-180°	96.4	2.6
0°-30°	307.5	8.2
0°-40°	477.6	12.8
0°-60°	756.8	20.2
0°-90°	893.0	23.9
90°-120°	607.4	16.2
90°-150°	2059.1	55.1
90°-180°	2847.0	76.1
0°-180°	3740.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	1	12	30	28	29	3
95°	45	53	55	55	53	51
105°	185	187	189	191	191	195
115°	344	348	347	346	344	340
125°	500	507	505	503	502	447
135°	647	656	658	657	655	500
145°	785	791	796	797	794	490
155°	898	900	903	907	905	413
165°	977	976	976	982	978	275
175°	1016	1014	1012	1018	1013	97
180°	1018	1018	1018	1018	1018	



TEST NUMBER: P331637-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.2	5.1	5.0	4.9	4.8	5.2	6.0	6.8	7.7	8.5	8.4
90°	0.9	3.2	5.4	7.7	10.0	13.3	17.5	21.7	25.8	30.0	29.7
92.5°	15.3	17.0	18.7	20.3	22.0	23.3	24.4	25.3	26.3	27.3	27.4
95°	44.7	46.6	48.5	50.4	52.3	53.5	53.8	54.2	54.6	55.0	55.0
97.5°	81.6	83.3	85.0	86.7	88.3	89.5	90.3	91.0	91.7	92.5	92.5
100°	109.1	110.6	112.2	113.7	115.2	116.3	116.8	117.4	118.0	118.6	118.6
102.5°	138.0	139.2	140.4	141.6	142.8	143.9	144.6	145.3	146.0	146.8	146.9
105°	184.8	185.3	185.9	186.5	187.0	187.5	187.9	188.3	188.6	189.0	189.4
107.5°	231.8	232.6	233.5	234.4	235.2	235.6	235.6	235.6	235.6	235.6	235.7
110°	262.1	263.2	264.3	265.5	266.7	267.3	267.3	267.3	267.3	267.3	267.3



TEST NUMBER: P331637-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	295.1	296.2	297.4	298.5	299.6	300.1	300.0	299.8	299.7	299.5	299.1
115°	343.7	344.8	345.9	347.2	348.3	348.6	348.3	347.9	347.5	347.2	347.0
117.5°	392.2	393.6	395.2	396.7	398.3	398.5	397.4	396.3	395.3	394.3	393.7
120°	424.5	426.0	427.5	429.0	430.6	430.6	429.0	427.5	426.0	424.5	424.5
122.5°	454.0	455.8	457.7	459.5	461.3	461.8	460.6	459.6	458.6	457.4	457.0
125°	500.1	501.8	503.5	505.2	507.0	507.6	507.0	506.4	505.8	505.2	504.6
127.5°	544.9	547.1	549.3	551.5	553.6	554.4	553.7	553.0	552.3	551.6	551.0
130°	573.1	575.6	578.1	580.6	583.1	584.1	583.7	583.3	583.0	582.6	582.2
132.5°	604.8	606.7	608.8	610.8	612.9	613.9	614.0	614.1	614.1	614.2	613.4
135°	647.0	649.1	651.2	653.3	655.4	656.7	657.0	657.4	657.8	658.1	658.0
137.5°	691.6	693.2	694.9	696.6	698.4	699.5	700.0	700.5	701.0	701.5	701.4
140°	718.3	720.1	721.8	723.5	725.2	726.5	727.5	728.4	729.4	730.4	730.4
142.5°	745.8	747.5	749.2	751.0	752.7	753.9	754.5	755.2	755.8	756.5	756.6
145°	785.3	786.7	788.0	789.4	790.7	791.9	793.1	794.2	795.4	796.5	796.7
147.5°	820.5	822.2	823.8	825.4	827.0	828.2	829.0	829.7	830.4	831.2	831.6
150°	844.6	845.8	846.9	848.1	849.2	850.2	850.9	851.7	852.5	853.3	853.8
152.5°	865.9	867.1	868.2	869.4	870.6	871.6	872.5	873.4	874.3	875.2	876.0
155°	897.9	898.5	899.1	899.7	900.2	900.8	901.4	901.9	902.5	903.0	904.0
157.5°	925.2	925.6	926.0	926.3	926.8	927.1	927.5	927.8	928.2	928.5	929.8
160°	941.8	942.1	942.5	942.9	943.2	943.6	943.7	943.9	944.1	944.3	945.5
162.5°	956.8	956.9	957.0	957.1	957.2	957.3	957.5	957.7	957.9	958.0	959.3
165°	977.0	976.8	976.5	976.4	976.2	976.1	976.1	976.1	976.1	976.1	977.4
167.5°	993.8	993.2	992.6	992.0	991.5	991.2	991.2	991.1	991.1	991.0	992.4
170°	1002.7	1002.1	1001.6	1001.0	1000.4	1000.1	999.9	999.7	999.4	999.3	1000.7
172.5°	1008.9	1008.3	1007.8	1007.2	1006.6	1006.3	1006.1	1005.8	1005.6	1005.5	1006.9
175°	1016.5	1015.9	1015.3	1014.8	1014.2	1013.7	1013.3	1013.0	1012.5	1012.2	1013.5
177.5°	1019.6	1019.1	1018.6	1018.2	1017.7	1017.4	1017.0	1016.8	1016.4	1016.2	1017.0
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2



TEST NUMBER: P331637-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	8.3	8.1	7.9	7.9	7.9	7.9	8.0	8.0
90°	29.3	28.9	28.6	28.4	28.7	28.8	29.0	29.2
92.5°	27.5	27.6	27.6	27.7	27.7	27.7	27.8	27.8
95°	55.0	55.0	55.0	54.8	54.4	54.1	53.6	53.3
97.5°	92.5	92.5	92.5	92.5	92.4	92.4	92.3	92.3
100°	118.6	118.6	118.6	118.5	118.3	118.1	117.9	117.7
102.5°	147.1	147.2	147.4	147.3	147.1	147.0	146.8	146.6
105°	189.8	190.2	190.5	190.7	190.7	190.7	190.7	190.7
107.5°	235.9	236.1	236.2	235.8	235.0	234.1	233.2	232.3
110°	267.3	267.3	267.3	266.9	266.4	265.8	265.2	264.7





TEST NUMBER: P331637-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	298.6	298.2	297.7	297.2	296.9	296.4	296.0	295.6
115°	346.7	346.6	346.4	345.9	345.4	344.8	344.2	343.7
117.5°	393.3	392.9	392.4	391.8	391.3	390.7	390.1	389.6
120°	424.5	424.5	424.5	424.2	423.6	423.0	422.5	421.9
122.5°	456.5	456.1	455.6	455.2	454.8	454.3	453.9	453.5
125°	504.1	503.5	502.9	502.6	502.4	502.1	502.0	501.8
127.5°	550.3	549.6	548.9	548.2	547.6	547.0	546.4	545.8
130°	581.8	581.4	581.0	580.5	579.7	578.9	578.2	577.4
132.5°	612.5	611.7	610.8	610.1	609.5	608.9	608.3	607.7
135°	657.8	657.6	657.4	657.0	656.4	655.9	655.3	654.7
137.5°	701.2	701.0	700.9	700.4	699.6	698.9	698.1	697.3
140°	730.4	730.4	730.4	730.0	729.2	728.4	727.7	726.9
142.5°	756.8	756.9	757.1	756.8	756.0	755.3	754.5	753.7
145°	796.9	797.1	797.3	797.0	796.3	795.5	794.7	793.9
147.5°	832.1	832.5	832.9	832.8	832.1	831.3	830.6	829.8
150°	854.4	855.0	855.5	855.5	855.0	854.4	853.8	853.3
152.5°	876.7	877.4	878.1	878.1	877.4	876.7	876.0	875.2
155°	905.0	905.9	906.9	907.1	906.5	905.9	905.3	904.7
157.5°	931.1	932.4	933.7	933.8	933.0	932.0	931.1	930.2
160°	946.6	947.7	948.9	949.1	948.3	947.5	946.8	946.0
162.5°	960.6	961.9	963.2	963.5	962.5	961.6	960.7	959.8
165°	978.8	980.1	981.5	981.6	980.7	979.7	978.8	977.8
167.5°	993.7	995.1	996.3	996.5	995.6	994.5	993.6	992.6
170°	1001.9	1003.3	1004.6	1004.7	1003.6	1002.5	1001.3	1000.1
172.5°	1008.1	1009.5	1010.8	1010.9	1009.8	1008.7	1007.5	1006.3
175°	1014.9	1016.2	1017.5	1017.6	1016.5	1015.3	1014.2	1013.1
177.5°	1018.0	1018.9	1019.8	1019.8	1018.9	1018.0	1017.0	1016.2
180°	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2	1018.2

(END OF REPORT)