

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331309-930

Luminaire Tested: **SA2XXDIP-C485D725U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331309-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3975.1 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34				34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29				29
3	79	70	63	57	72	64	58	53	53	48	45	42	39	36	33	31	29	24				24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21				21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18				18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16				16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14				14
8	53	40	33	28	48	37	30	26	31	26	22	25	21	19	20	17	15	13				13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11				11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	1.5
10°-20°	167.6	4.2
20°-30°	246.3	6.2
30°-40°	286.1	7.2
40°-50°	285.8	7.2
50°-60°	249.2	6.3
60°-70°	184.3	4.6
70°-80°	104.4	2.6
80°-90°	30.0	0.8
90°-100°	26.9	0.7
100°-110°	98.6	2.5
110°-120°	263.5	6.6
120°-130°	435.0	10.9
130°-140°	462.7	11.6
140°-150°	430.0	10.8
150°-160°	345.7	8.7
160°-170°	222.8	5.6
170°-180°	76.7	1.9
0°-30°	473.4	11.9
0°-40°	759.4	19.1
0°-60°	1294.4	32.6
0°-90°	1613.1	40.6
90°-120°	389.0	9.8
90°-150°	1716.8	43.2
90°-180°	2362.0	59.4
0°-180°	3975.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	1	7	12	14	16	3
95°	38	20	23	26	25	46
105°	177	185	36	42	44	189
115°	335	346	360	102	48	330
125°	474	482	493	497	499	423
135°	587	596	601	607	606	453
145°	681	681	690	694	691	426
155°	749	745	751	754	750	345
165°	790	786	788	792	788	223
175°	808	804	805	808	803	77
180°	806	806	806	806	806	



TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	8.9	9.0	9.0	9.1	9.1	9.2	9.2	9.1	9.1	9.1	9.0
90°	0.6	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3
92.5°	11.7	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9
95°	37.9	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4
97.5°	75.3	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0
100°	103.2	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2
102.5°	134.0	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5
105°	177.3	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0
107.5°	226.7	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3
110°	258.4	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1



TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2
115°	335.3	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9
117.5°	377.5	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1
120°	408.2	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0
122.5°	434.4	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9
125°	474.2	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7
127.5°	510.2	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2
130°	533.0	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2
132.5°	556.4	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9
135°	586.7	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6
137.5°	617.4	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1
140°	637.5	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7
142.5°	654.3	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8
145°	680.6	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9
147.5°	703.6	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8
150°	718.5	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6
152.5°	731.1	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2
155°	749.4	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0
157.5°	763.8	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2
160°	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0
162.5°	779.7	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1
165°	789.7	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8
167.5°	797.1	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1
170°	801.4	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9
172.5°	804.1	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7
175°	807.7	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8
177.5°	808.4	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	8.7	8.6	8.4	8.2	8.2	8.2	8.1	8.0
90°	13.0	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.2	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.1	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	31.5	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	35.3	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	36.9	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	38.4	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	46.9	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	76.1	63.2	50.2	44.0	44.5	45.0	45.6	46.1



TEST NUMBER: P331309-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	162.9	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	239.9	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	369.6	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	430.6	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	456.9	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	494.6	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	529.5	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	551.6	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	573.2	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	603.9	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	632.4	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	650.9	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	667.9	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	691.8	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	712.5	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	725.3	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	736.9	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	752.8	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.0	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	773.7	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	780.9	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	797.1	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	800.8	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	803.6	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	806.7	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.0	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)