

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331638-935

Luminaire Tested: **SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331638-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4002.3 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331638-935  
CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331638-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26	19
2	84	77	71	66	74	68	64	59	52	49	47	38	36	34	24	23	22	16
3	76	68	61	55	68	60	54	50	46	42	39	34	31	29	22	20	19	14
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	19	20	17	15	13	12	10	8
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331638-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.5	1.0
10°-20°	111.1	2.8
20°-30°	156.0	3.9
30°-40°	170.1	4.2
40°-50°	156.4	3.9
50°-60°	122.8	3.1
60°-70°	80.1	2.0
70°-80°	41.3	1.0
80°-90°	14.7	0.4
90°-100°	178.7	4.5
100°-110°	606.3	15.1
110°-120°	644.1	16.1
120°-130°	530.2	13.2
130°-140°	425.8	10.6
140°-150°	321.8	8.0
150°-160°	226.1	5.6
160°-170°	133.1	3.3
170°-180°	43.3	1.1
0°-30°	307.5	7.7
0°-40°	477.6	11.9
0°-60°	756.8	18.9
0°-90°	892.9	22.3
90°-120°	1429.1	35.7
90°-150°	2706.8	67.6
90°-180°	3109.0	77.7
0°-180°	4002.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	1	12	29	28	28	2
95°	30	74	337	127	98	32
105°	105	158	637	1138	968	111
115°	185	233	533	1100	1274	183
125°	258	305	512	891	1034	229
135°	302	361	506	748	857	234
145°	345	397	504	625	684	217
155°	393	424	489	553	575	181
165°	428	441	468	497	504	121
175°	446	446	450	456	455	42
180°	447	447	447	447	447	



TEST NUMBER: P331638-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.2	5.2	5.3	5.1	4.8	5.1	5.9	7.1	8.2	8.4	8.1
90°	0.9	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3
92.5°	10.5	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4
95°	30.0	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7
97.5°	49.0	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2
100°	66.1	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6
102.5°	82.0	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8
105°	104.9	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3
107.5°	129.6	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9
110°	146.1	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4



TEST NUMBER: P331638-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.2	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5
115°	184.8	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6
117.5°	209.1	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7
120°	224.3	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0
122.5°	238.8	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3
125°	257.8	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6
127.5°	272.9	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2
130°	281.9	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9
132.5°	290.1	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6
135°	302.5	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1
137.5°	314.2	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0
140°	323.1	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3
142.5°	332.0	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4
145°	345.4	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1
147.5°	359.9	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5
150°	369.5	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0
152.5°	379.1	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2
155°	392.7	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2
157.5°	404.1	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9
160°	411.6	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7
162.5°	419.1	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2
165°	427.9	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0
167.5°	435.1	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1
170°	440.0	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3
172.5°	442.7	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5
175°	446.0	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2
177.5°	447.5	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331638-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	7.8	7.5	7.7	7.8	7.8	7.8	7.8	7.8
90°	27.5	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	74.9	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	225.2	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	525.4	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	784.5	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	954.3	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1044.0	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	979.5	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	923.8	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2





TEST NUMBER: P331638-935

CATALOG NUMBER: SA2XXRDIP-C290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.9	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	810.3	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	763.2	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	739.9	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	721.3	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	694.3	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	667.7	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	650.5	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	634.0	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	611.0	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	592.5	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	580.9	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	571.3	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	557.7	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	547.2	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	539.7	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	532.1	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	521.6	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	509.4	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	501.8	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	494.3	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	482.9	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	472.1	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	466.6	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	460.4	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	453.7	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)