

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331310-930

Luminaire Tested: **SA2XXDIP-C485D725U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331310-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3725.7 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	1.6
10°-20°	167.6	4.5
20°-30°	246.3	6.6
30°-40°	286.1	7.7
40°-50°	285.8	7.7
50°-60°	249.2	6.7
60°-70°	184.3	4.9
70°-80°	104.4	2.8
80°-90°	31.1	0.8
90°-100°	47.9	1.3
100°-110°	148.6	4.0
110°-120°	254.0	6.8
120°-130°	334.1	9.0
130°-140°	375.0	10.1
140°-150°	367.7	9.9
150°-160°	308.4	8.3
160°-170°	204.5	5.5
170°-180°	71.5	1.9
0°-30°	473.4	12.7
0°-40°	759.4	20.4
0°-60°	1294.4	34.7
0°-90°	1614.1	43.3
90°-120°	450.5	12.1
90°-150°	1527.2	41.0
90°-180°	2112.0	56.7
0°-180°	3725.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	1	9	22	21	22	3
95°	33	39	41	41	40	38
105°	137	139	140	141	142	145
115°	255	258	258	257	255	252
125°	371	376	375	373	372	331
135°	480	487	488	487	486	371
145°	582	587	591	591	589	364
155°	666	668	670	673	671	306
165°	725	724	724	728	725	204
175°	754	752	751	755	751	72
180°	755	755	755	755	755	



TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	8.9	9.0	9.1	9.3	9.4	9.6	10.0	10.4	10.8	11.3	10.9
90°	0.7	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0
92.5°	11.3	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3
95°	33.1	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8
97.5°	60.6	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6
100°	81.0	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0
102.5°	102.3	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9
105°	137.1	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5
107.5°	171.9	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9
110°	194.4	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.8	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8
115°	254.9	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3
117.5°	290.8	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0
120°	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8
122.5°	336.7	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9
125°	370.9	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3
127.5°	404.1	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6
130°	425.1	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8
132.5°	448.5	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9
135°	479.9	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0
137.5°	512.9	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2
140°	532.8	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7
142.5°	553.2	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2
145°	582.4	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9
147.5°	608.6	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8
150°	626.5	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2
152.5°	642.2	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6
155°	665.9	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5
157.5°	686.2	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6
160°	698.5	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2
162.5°	709.6	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5
165°	724.6	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0
167.5°	737.0	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1
170°	743.7	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2
172.5°	748.3	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7
175°	753.9	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7
177.5°	756.2	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	10.5	10.1	9.8	9.5	9.5	9.4	9.3	9.2
90°	21.8	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.4	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.1	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	140.8	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.2	198.0	197.5	197.1	196.7	196.2



TEST NUMBER: P331310-930

CATALOG NUMBER: SA2XXDIP-C485D725U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.4	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.7	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.6	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.9	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	408.1	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.5	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	454.3	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.9	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	520.1	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.3	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.0	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.1	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.2	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	690.6	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	702.1	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	712.5	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	725.9	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	737.0	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	743.1	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	747.7	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	752.7	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)