

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331373-930

Luminaire Tested: **SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331373-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5344.7 lumens  
Efficiency: N/A  
Efficacy: 93.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331373-930  
CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331373-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	42	41	41	35				
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29				
3	80	70	63	57	72	64	58	53	53	49	45	43	39	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18				
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13				
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331373-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.4	1.5
10°-20°	229.0	4.3
20°-30°	336.6	6.3
30°-40°	391.0	7.3
40°-50°	390.6	7.3
50°-60°	340.6	6.4
60°-70°	251.9	4.7
70°-80°	142.7	2.7
80°-90°	42.8	0.8
90°-100°	71.1	1.3
100°-110°	220.9	4.1
110°-120°	377.5	7.1
120°-130°	496.5	9.3
130°-140°	557.2	10.4
140°-150°	546.4	10.2
150°-160°	458.3	8.6
160°-170°	304.0	5.7
170°-180°	106.2	2.0
0°-30°	647.0	12.1
0°-40°	1038.1	19.4
0°-60°	1769.3	33.1
0°-90°	2206.7	41.3
90°-120°	669.5	12.5
90°-150°	2269.5	42.5
90°-180°	3138.0	58.7
0°-180°	5344.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	1	13	33	31	32	4
95°	49	58	61	60	59	56
105°	204	206	208	210	210	215
115°	379	384	383	382	379	375
125°	551	559	557	554	553	492
135°	713	723	726	724	722	551
145°	866	872	878	879	875	541
155°	990	992	995	1000	997	455
165°	1077	1076	1076	1082	1078	304
175°	1120	1118	1116	1122	1117	106
180°	1122	1122	1122	1122	1122	



TEST NUMBER: P331373-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.4	12.6	12.8	13.0	13.5	14.0	14.7	15.3	16.0	15.4
90°	1.0	3.5	6.0	8.6	11.1	14.6	19.2	23.9	28.5	33.2	32.7
92.5°	16.9	18.7	20.5	22.4	24.3	25.8	26.8	28.0	29.0	30.1	30.2
95°	49.2	51.4	53.5	55.5	57.6	58.9	59.4	59.8	60.2	60.6	60.6
97.5°	90.0	91.8	93.7	95.6	97.3	98.7	99.5	100.3	101.1	101.9	101.9
100°	120.3	122.0	123.7	125.3	127.0	128.2	128.8	129.4	130.0	130.7	130.7
102.5°	152.1	153.4	154.8	156.1	157.5	158.6	159.4	160.1	160.9	161.8	161.9
105°	203.6	204.2	204.9	205.5	206.1	206.7	207.1	207.5	207.9	208.3	208.8
107.5°	255.5	256.4	257.4	258.3	259.2	259.7	259.7	259.7	259.7	259.7	259.8
110°	288.9	290.1	291.4	292.6	293.9	294.6	294.6	294.6	294.6	294.6	294.6



TEST NUMBER: P331373-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.2	326.4	327.8	329.0	330.3	330.8	330.6	330.4	330.3	330.1	329.6
115°	378.8	380.1	381.3	382.6	383.8	384.3	383.8	383.4	383.0	382.6	382.4
117.5°	432.2	433.9	435.6	437.2	439.0	439.2	438.1	436.8	435.7	434.5	434.0
120°	467.8	469.5	471.2	472.9	474.6	474.6	472.9	471.2	469.5	467.8	467.8
122.5°	500.4	502.5	504.4	506.5	508.5	508.9	507.8	506.5	505.4	504.2	503.7
125°	551.1	553.1	555.0	556.8	558.7	559.4	558.7	558.2	557.5	556.8	556.2
127.5°	600.6	603.0	605.4	607.8	610.2	611.1	610.3	609.5	608.8	608.0	607.2
130°	631.7	634.4	637.2	639.8	642.6	643.8	643.4	642.9	642.5	642.1	641.6
132.5°	666.5	668.8	671.0	673.2	675.5	676.6	676.7	676.8	676.9	676.9	676.0
135°	713.1	715.4	717.8	720.1	722.4	723.7	724.1	724.6	725.0	725.5	725.2
137.5°	762.1	764.1	766.0	767.8	769.7	770.9	771.5	772.1	772.6	773.1	773.0
140°	791.7	793.6	795.5	797.4	799.3	800.8	801.8	802.9	804.0	804.9	804.9
142.5°	822.1	823.9	825.8	827.7	829.6	830.9	831.6	832.3	833.1	833.8	834.0
145°	865.6	867.1	868.5	870.0	871.5	872.9	874.1	875.4	876.6	877.9	878.1
147.5°	904.4	906.2	907.9	909.7	911.5	912.8	913.6	914.5	915.3	916.2	916.6
150°	930.9	932.2	933.4	934.7	936.0	937.0	937.9	938.7	939.6	940.4	941.0
152.5°	954.4	955.7	956.9	958.2	959.4	960.6	961.6	962.6	963.7	964.7	965.5
155°	989.7	990.3	990.9	991.6	992.2	992.8	993.4	994.1	994.7	995.3	996.4
157.5°	1019.8	1020.2	1020.6	1021.0	1021.5	1021.8	1022.2	1022.6	1023.0	1023.4	1024.8
160°	1038.0	1038.4	1038.8	1039.2	1039.7	1039.9	1040.2	1040.4	1040.6	1040.8	1042.0
162.5°	1054.6	1054.7	1054.8	1054.8	1055.0	1055.1	1055.3	1055.5	1055.7	1056.0	1057.4
165°	1076.8	1076.6	1076.4	1076.1	1076.0	1075.9	1075.9	1075.9	1075.9	1075.9	1077.3
167.5°	1095.4	1094.7	1094.1	1093.5	1092.8	1092.5	1092.4	1092.4	1092.3	1092.3	1093.8
170°	1105.2	1104.6	1103.9	1103.3	1102.7	1102.3	1102.0	1101.8	1101.6	1101.4	1102.9
172.5°	1112.0	1111.4	1110.8	1110.1	1109.5	1109.1	1108.9	1108.6	1108.4	1108.2	1109.7
175°	1120.4	1119.7	1119.1	1118.4	1117.9	1117.3	1116.9	1116.5	1116.1	1115.6	1117.1
177.5°	1123.7	1123.2	1122.7	1122.3	1121.8	1121.3	1121.0	1120.6	1120.3	1120.0	1121.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3



TEST NUMBER: P331373-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	14.9	14.3	13.9	13.5	13.5	13.3	13.2	13.1
90°	32.3	31.9	31.5	31.4	31.6	31.8	32.0	32.2
92.5°	30.2	30.3	30.5	30.5	30.6	30.6	30.7	30.7
95°	60.6	60.6	60.6	60.4	60.0	59.6	59.1	58.7
97.5°	101.9	101.9	101.9	101.9	101.8	101.8	101.7	101.7
100°	130.7	130.7	130.7	130.6	130.4	130.2	130.0	129.7
102.5°	162.1	162.2	162.4	162.4	162.2	162.0	161.8	161.6
105°	209.2	209.6	210.0	210.3	210.3	210.3	210.3	210.3
107.5°	260.0	260.2	260.3	259.9	259.0	258.0	257.1	256.1
110°	294.6	294.6	294.6	294.2	293.6	292.9	292.3	291.7





TEST NUMBER: P331373-930

CATALOG NUMBER: SA2XXDIP-C675D1080U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.1	328.6	328.2	327.7	327.2	326.7	326.3	325.8
115°	382.2	382.0	381.7	381.3	380.7	380.1	379.4	378.8
117.5°	433.5	433.0	432.5	431.9	431.3	430.6	430.0	429.4
120°	467.8	467.8	467.8	467.5	466.9	466.3	465.6	465.0
122.5°	503.2	502.7	502.1	501.7	501.2	500.8	500.3	499.9
125°	555.6	555.0	554.3	553.9	553.7	553.5	553.3	553.1
127.5°	606.5	605.7	605.0	604.2	603.6	602.9	602.3	601.5
130°	641.2	640.8	640.4	639.8	639.0	638.1	637.2	636.4
132.5°	675.1	674.2	673.3	672.5	671.8	671.1	670.4	669.8
135°	725.0	724.8	724.6	724.1	723.5	722.9	722.3	721.6
137.5°	772.8	772.7	772.5	772.0	771.1	770.3	769.5	768.6
140°	804.9	804.9	804.9	804.5	803.7	802.9	802.0	801.2
142.5°	834.1	834.3	834.5	834.1	833.2	832.4	831.6	830.7
145°	878.3	878.6	878.7	878.4	877.6	876.8	875.9	875.1
147.5°	917.1	917.5	918.0	917.9	917.0	916.2	915.4	914.7
150°	941.7	942.3	943.0	943.0	942.3	941.7	941.0	940.4
152.5°	966.3	967.0	967.8	967.8	967.0	966.3	965.5	964.7
155°	997.4	998.5	999.6	999.7	999.1	998.5	997.8	997.2
157.5°	1026.2	1027.7	1029.1	1029.3	1028.3	1027.3	1026.3	1025.2
160°	1043.3	1044.6	1045.9	1046.0	1045.2	1044.4	1043.5	1042.7
162.5°	1058.8	1060.2	1061.7	1061.8	1060.9	1059.9	1058.8	1057.9
165°	1078.8	1080.3	1081.7	1081.9	1080.9	1079.9	1078.8	1077.7
167.5°	1095.3	1096.7	1098.2	1098.4	1097.3	1096.2	1095.1	1094.1
170°	1104.3	1105.8	1107.3	1107.4	1106.1	1104.9	1103.6	1102.4
172.5°	1111.2	1112.6	1114.1	1114.2	1113.0	1111.7	1110.4	1109.1
175°	1118.6	1120.1	1121.5	1121.6	1120.4	1119.1	1117.9	1116.6
177.5°	1122.0	1123.0	1124.0	1124.0	1123.0	1122.0	1121.0	1120.0
180°	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3	1122.3

(END OF REPORT)