

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331685-935

Luminaire Tested: **SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331685-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3626.8 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331685-935  
CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331685-935

CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	55	53	52	47				
2	91	84	78	73	84	78	73	69	68	64	60	58	55	52	49	47	45	41				
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39	35				
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	31				
5	70	59	51	45	65	55	48	43	48	43	39	42	38	34	36	32	30	27				
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27	24				
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21				
8	56	44	36	31	52	41	35	30	37	31	27	32	27	24	28	24	22	19				
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20	18				
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18	16				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15681	15681	15681
5°	15741	15486	15571
10°	15621	15231	15101
15°	15442	14780	14355
20°	15192	14136	13426
25°	14938	13402	12527
30°	14585	12652	11373
35°	14241	11832	10360
40°	13894	10985	9187
45°	13486	10035	8127
50°	13069	9075	7086
55°	12645	8042	6086
60°	12148	6952	5050
65°	11584	5841	4604
70°	10914	4810	4230
75°	10087	4386	3949
80°	8908	3924	3598
85°	7003	3094	3094



TEST NUMBER: P331685-935

CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.9	2.5
10°-20°	249.6	6.9
20°-30°	350.5	9.7
30°-40°	382.2	10.5
40°-50°	351.5	9.7
50°-60°	276.0	7.6
60°-70°	180.0	5.0
70°-80°	92.8	2.6
80°-90°	26.4	0.7
90°-100°	36.9	1.0
100°-110°	114.5	3.2
110°-120°	195.7	5.4
120°-130°	257.4	7.1
130°-140°	288.9	8.0
140°-150°	283.3	7.8
150°-160°	237.6	6.6
160°-170°	157.6	4.3
170°-180°	55.1	1.5
0°-30°	691.1	19.1
0°-40°	1073.3	29.6
0°-60°	1700.8	46.9
0°-90°	1999.9	55.1
90°-120°	347.1	9.6
90°-150°	1176.6	32.4
90°-180°	1627.0	44.9
0°-180°	3626.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	971	966	956	963	961	92
15°	924	913	884	868	859	260
25°	838	809	752	718	703	385
35°	722	676	600	547	526	452
45°	591	530	440	379	356	456
55°	449	379	286	235	216	401
65°	303	232	153	125	120	300
75°	162	102	70	64	63	171
85°	38	20	17	17	17	45
90°	0	7	17	16	17	3
95°	26	30	31	31	30	29
105°	106	107	108	109	109	112
115°	196	199	198	198	196	194
125°	286	290	289	287	287	255
135°	370	375	376	376	374	285
145°	449	452	455	456	454	280
155°	513	515	516	518	517	236
165°	558	558	558	561	559	157
175°	581	579	578	581	579	55
180°	582	582	582	582	582	



TEST NUMBER: P331685-935

CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	974.7	974.0	973.2	972.4	971.6	970.3	968.6	966.9	965.3	963.5	965.1
5°	971.2	970.3	969.3	968.3	967.3	965.6	963.0	960.5	957.9	955.5	957.2
7.5°	961.2	960.0	958.8	957.6	956.4	954.2	951.3	948.4	945.4	942.5	942.9
10°	952.8	951.4	950.0	948.6	947.3	944.7	940.7	936.9	933.0	929.0	928.5
12.5°	942.2	940.6	938.8	937.2	935.5	932.2	927.2	922.2	917.1	912.1	911.1
15°	923.8	921.6	919.5	917.3	915.2	910.8	904.1	897.5	890.9	884.2	880.5
17.5°	901.1	897.9	894.6	891.2	887.9	882.1	873.6	865.0	856.5	848.0	843.6
20°	884.2	880.3	876.4	872.5	868.6	861.8	852.0	842.2	832.5	822.7	817.8
22.5°	865.9	861.6	857.2	852.8	848.4	840.8	829.7	818.7	807.7	796.7	790.4
25°	838.5	832.2	826.0	819.8	813.6	803.9	791.1	778.2	765.3	752.3	744.3
27.5°	805.5	798.7	791.9	785.1	778.3	767.6	753.1	738.6	724.0	709.5	700.2
30°	782.3	774.8	767.4	760.0	752.6	741.1	725.4	709.8	694.1	678.6	668.6
32.5°	759.7	751.1	742.4	733.7	725.0	712.7	696.8	680.9	665.0	649.0	637.7
35°	722.5	712.6	702.6	692.6	682.7	669.1	651.9	634.7	617.5	600.3	588.0
37.5°	685.3	674.2	663.3	652.4	641.4	626.8	608.6	590.2	571.9	553.5	540.0
40°	659.2	647.5	635.8	624.1	612.3	597.0	578.1	559.1	540.2	521.2	507.4
42.5°	632.5	620.2	607.8	595.5	583.2	567.1	547.6	528.1	508.4	488.9	474.5
45°	590.6	577.6	564.5	551.4	538.3	521.5	501.0	480.5	459.9	439.5	425.6
47.5°	549.8	536.0	522.1	508.2	494.4	476.9	455.7	434.5	413.4	392.2	378.4
50°	520.3	506.4	492.6	478.7	464.9	447.2	425.7	404.2	382.7	361.3	347.8
52.5°	491.5	477.0	462.5	448.1	433.5	415.8	394.8	373.8	352.8	331.7	318.7
55°	449.2	433.9	418.7	403.5	388.2	370.1	349.0	327.9	306.8	285.7	274.0
57.5°	405.7	390.1	374.4	358.9	343.2	325.3	305.0	284.7	264.4	244.2	233.4
60°	376.2	360.6	344.9	329.3	313.7	295.8	275.7	255.5	235.5	215.3	205.3
62.5°	347.3	331.7	316.1	300.5	284.8	267.4	248.3	229.1	209.9	190.7	181.2
65°	303.2	287.4	271.6	255.8	240.0	223.3	205.7	188.1	170.5	152.9	146.3
67.5°	260.7	245.0	229.3	213.6	197.9	182.1	166.3	150.5	134.7	118.8	115.8
70°	231.2	215.9	200.7	185.5	170.2	155.8	142.4	128.9	115.5	101.9	100.0
72.5°	203.0	188.4	173.8	159.2	144.6	131.9	121.1	110.2	99.4	88.6	87.0
75°	161.7	148.1	134.4	120.7	107.0	96.9	90.2	83.6	77.0	70.3	69.0
77.5°	121.1	109.1	97.1	85.2	73.2	65.5	62.3	59.2	56.0	52.8	51.9
80°	95.8	85.8	75.9	66.0	56.0	50.0	48.0	46.1	44.2	42.2	41.4
82.5°	72.6	64.8	57.1	49.2	41.5	36.9	35.6	34.3	33.0	31.7	31.2
85°	37.8	33.7	29.6	25.5	21.4	19.0	18.4	17.9	17.3	16.7	16.7
87.5°	11.4	10.3	9.4	8.4	7.4	7.1	7.7	8.1	8.6	9.0	8.9
90°	0.5	1.8	3.1	4.4	5.8	7.6	10.0	12.4	14.8	17.2	17.0
92.5°	8.8	9.7	10.7	11.6	12.6	13.3	13.9	14.5	15.1	15.6	15.7
95°	25.6	26.6	27.7	28.8	29.9	30.6	30.7	31.0	31.2	31.4	31.4
97.5°	46.7	47.6	48.6	49.5	50.5	51.1	51.6	52.0	52.4	52.9	52.9
100°	62.3	63.2	64.1	65.0	65.9	66.5	66.8	67.1	67.4	67.8	67.8
102.5°	78.9	79.6	80.2	80.9	81.6	82.2	82.7	83.0	83.4	83.9	83.9
105°	105.6	105.9	106.2	106.5	106.9	107.1	107.4	107.5	107.8	108.1	108.2
107.5°	132.5	132.9	133.5	133.9	134.4	134.7	134.7	134.7	134.7	134.7	134.7
110°	149.7	150.4	151.0	151.7	152.4	152.7	152.7	152.7	152.7	152.7	152.7



TEST NUMBER: P331685-935

CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.6	169.3	169.9	170.6	171.3	171.5	171.4	171.3	171.3	171.2	170.9
115°	196.4	197.1	197.7	198.4	199.0	199.2	199.0	198.8	198.5	198.4	198.3
117.5°	224.1	225.0	225.8	226.7	227.6	227.7	227.1	226.4	225.8	225.2	225.0
120°	242.5	243.4	244.3	245.1	246.1	246.1	245.1	244.3	243.4	242.5	242.5
122.5°	259.4	260.5	261.6	262.6	263.6	263.8	263.2	262.6	262.0	261.4	261.1
125°	285.8	286.7	287.7	288.7	289.6	290.0	289.6	289.4	289.0	288.7	288.3
127.5°	311.3	312.6	313.8	315.1	316.3	316.8	316.4	316.0	315.6	315.2	314.8
130°	327.5	328.9	330.3	331.7	333.1	333.7	333.6	333.3	333.1	332.9	332.7
132.5°	345.5	346.7	347.8	349.0	350.2	350.8	350.9	350.9	350.9	350.9	350.5
135°	369.7	370.9	372.1	373.3	374.5	375.2	375.4	375.7	375.9	376.1	376.0
137.5°	395.1	396.1	397.1	398.1	399.1	399.7	400.0	400.3	400.5	400.8	400.7
140°	410.4	411.5	412.4	413.4	414.4	415.2	415.7	416.2	416.8	417.3	417.3
142.5°	426.2	427.1	428.2	429.1	430.1	430.8	431.2	431.5	431.9	432.2	432.3
145°	448.8	449.5	450.3	451.1	451.9	452.5	453.1	453.8	454.5	455.1	455.2
147.5°	468.9	469.8	470.7	471.7	472.5	473.2	473.6	474.1	474.5	475.0	475.2
150°	482.7	483.3	484.0	484.6	485.3	485.8	486.2	486.6	487.1	487.6	487.8
152.5°	494.8	495.5	496.1	496.8	497.4	498.0	498.5	499.0	499.6	500.2	500.5
155°	513.1	513.4	513.8	514.0	514.4	514.7	515.1	515.4	515.7	516.0	516.6
157.5°	528.7	528.9	529.1	529.3	529.6	529.8	529.9	530.2	530.4	530.5	531.3
160°	538.1	538.3	538.6	538.7	539.0	539.2	539.2	539.3	539.5	539.6	540.3
162.5°	546.7	546.8	546.8	546.9	546.9	547.0	547.1	547.3	547.3	547.4	548.2
165°	558.3	558.1	558.0	557.9	557.8	557.8	557.8	557.8	557.8	557.8	558.5
167.5°	567.8	567.6	567.2	566.9	566.5	566.4	566.4	566.4	566.3	566.3	567.1
170°	573.0	572.7	572.3	572.0	571.7	571.4	571.4	571.2	571.1	571.0	571.8
172.5°	576.5	576.2	575.8	575.5	575.2	575.0	574.9	574.8	574.6	574.5	575.3
175°	580.8	580.5	580.1	579.9	579.5	579.3	579.0	578.9	578.6	578.3	579.1
177.5°	582.6	582.3	582.0	581.8	581.5	581.3	581.2	581.0	580.8	580.7	581.2
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331685-935

CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.2	971.2	971.2	971.2	971.2	971.2	971.2	971.2
2.5°	966.6	968.2	969.7	970.3	970.1	969.7	969.5	969.1
5°	958.9	960.7	962.4	963.0	962.4	961.8	961.3	960.7
7.5°	943.4	943.9	944.4	944.2	943.1	942.2	941.2	940.1
10°	927.9	927.3	926.7	925.8	924.6	923.5	922.3	921.1
12.5°	910.1	909.0	907.9	906.5	904.5	902.6	900.6	898.6
15°	876.8	873.1	869.4	866.5	864.6	862.6	860.7	858.8
17.5°	839.2	834.7	830.3	826.5	823.1	819.8	816.4	813.0
20°	813.0	808.0	803.1	798.6	794.3	790.0	785.7	781.4
22.5°	784.1	777.8	771.5	766.8	763.5	760.3	757.2	754.0
25°	736.3	728.3	720.3	714.9	712.0	709.0	706.1	703.2
27.5°	690.8	681.5	672.2	665.1	660.5	655.8	651.2	646.5
30°	658.7	648.7	638.7	631.1	625.8	620.5	615.3	610.0
32.5°	626.3	614.9	603.6	595.4	590.4	585.5	580.5	575.6
35°	575.8	563.4	551.1	542.8	538.5	534.2	529.9	525.6
37.5°	526.4	512.9	499.4	490.1	485.2	480.3	475.4	470.5
40°	493.4	479.6	465.7	456.2	451.2	446.1	441.0	435.9
42.5°	460.2	445.8	431.5	421.9	417.0	412.1	407.2	402.2
45°	411.7	397.9	384.0	374.7	370.1	365.3	360.7	355.9
47.5°	364.6	350.9	337.0	328.0	323.7	319.5	315.2	311.0
50°	334.3	320.8	307.4	298.5	294.5	290.3	286.3	282.1
52.5°	305.7	292.7	279.7	271.3	267.5	263.7	259.9	256.1
55°	262.3	250.5	238.8	231.1	227.4	223.6	219.9	216.2
57.5°	222.7	212.0	201.2	194.2	191.1	188.0	184.9	181.8
60°	195.4	185.5	175.5	168.9	165.8	162.7	159.5	156.4
62.5°	171.8	162.2	152.7	147.1	145.2	143.4	141.5	139.6
65°	139.7	133.0	126.4	122.8	122.2	121.6	121.0	120.5
67.5°	112.7	109.7	106.7	104.8	104.2	103.6	103.0	102.3
70°	98.1	96.1	94.1	92.8	92.0	91.2	90.4	89.6
72.5°	85.3	83.7	82.1	81.0	80.5	80.1	79.6	79.1
75°	67.6	66.2	64.8	64.1	63.9	63.7	63.5	63.3
77.5°	51.1	50.4	49.6	49.1	48.7	48.5	48.1	47.8
80°	40.6	39.9	39.1	38.7	38.7	38.7	38.7	38.7
82.5°	30.7	30.2	29.8	29.5	29.5	29.5	29.5	29.5
85°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	8.7	8.4	8.3	8.2	8.2	8.2	8.3	8.3
90°	16.8	16.5	16.3	16.3	16.4	16.4	16.6	16.7
92.5°	15.7	15.8	15.8	15.8	15.8	15.8	15.9	15.9
95°	31.4	31.4	31.4	31.3	31.1	30.9	30.7	30.5
97.5°	52.9	52.9	52.9	52.8	52.8	52.8	52.8	52.7
100°	67.8	67.8	67.8	67.7	67.6	67.5	67.4	67.2
102.5°	84.0	84.1	84.2	84.2	84.1	83.9	83.9	83.8
105°	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0
107.5°	134.8	134.9	135.0	134.7	134.2	133.8	133.3	132.8
110°	152.7	152.7	152.7	152.6	152.2	151.9	151.5	151.2





TEST NUMBER: P331685-935

CATALOG NUMBER: SA2XXRDIP-C675D530U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.4	170.1	169.9	169.6	169.4	169.1	168.9
115°	198.1	198.0	197.9	197.7	197.3	197.1	196.7	196.4
117.5°	224.7	224.5	224.2	223.9	223.6	223.3	222.9	222.6
120°	242.5	242.5	242.5	242.4	242.0	241.8	241.4	241.1
122.5°	260.9	260.6	260.4	260.1	259.8	259.6	259.4	259.2
125°	288.0	287.7	287.4	287.1	287.1	287.0	286.8	286.7
127.5°	314.4	314.0	313.7	313.2	312.9	312.5	312.2	311.9
130°	332.4	332.3	332.0	331.7	331.2	330.8	330.4	329.9
132.5°	350.0	349.5	349.0	348.6	348.3	347.9	347.6	347.2
135°	375.9	375.7	375.7	375.4	375.1	374.8	374.4	374.1
137.5°	400.6	400.5	400.5	400.2	399.8	399.3	398.9	398.5
140°	417.3	417.3	417.3	417.2	416.6	416.2	415.8	415.3
142.5°	432.4	432.5	432.6	432.4	432.0	431.5	431.1	430.7
145°	455.4	455.5	455.6	455.4	455.0	454.5	454.1	453.7
147.5°	475.4	475.7	476.0	475.9	475.4	475.0	474.6	474.2
150°	488.2	488.5	488.9	488.9	488.5	488.2	487.8	487.6
152.5°	500.9	501.4	501.8	501.8	501.4	500.9	500.5	500.2
155°	517.1	517.6	518.2	518.3	518.0	517.6	517.3	517.0
157.5°	532.0	532.8	533.6	533.6	533.1	532.6	532.1	531.5
160°	540.9	541.6	542.2	542.3	541.9	541.5	541.0	540.5
162.5°	548.9	549.7	550.4	550.5	550.0	549.5	549.0	548.5
165°	559.3	560.1	560.8	560.9	560.3	559.8	559.3	558.7
167.5°	567.8	568.6	569.4	569.5	568.9	568.3	567.7	567.1
170°	572.6	573.3	574.0	574.1	573.4	572.8	572.1	571.5
172.5°	576.1	576.9	577.6	577.6	577.0	576.4	575.7	575.1
175°	579.9	580.7	581.4	581.5	580.8	580.1	579.5	578.9
177.5°	581.7	582.2	582.7	582.7	582.2	581.7	581.2	580.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8

(END OF REPORT)