

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331336-930

Luminaire Tested: **SA2XXDIP-C675D330U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331336-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D330U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3270.7 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331336-930
CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331336-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	64	62	61	57
2	93	85	79	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48
3	85	75	67	61	79	71	64	58	63	58	53	56	52	48	50	46	44	40
4	77	66	58	52	73	63	55	50	56	50	46	50	45	42	44	41	38	35
5	71	59	51	45	67	56	49	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	37	45	39	35	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331336-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	2.5
10°-20°	229.0	7.0
20°-30°	336.6	10.3
30°-40°	391.0	12.0
40°-50°	390.6	11.9
50°-60°	340.6	10.4
60°-70°	251.9	7.7
70°-80°	142.7	4.4
80°-90°	39.3	1.2
90°-100°	12.1	0.4
100°-110°	44.6	1.4
110°-120°	119.1	3.6
120°-130°	196.6	6.0
130°-140°	209.1	6.4
140°-150°	194.4	5.9
150°-160°	156.3	4.8
160°-170°	100.7	3.1
170°-180°	34.7	1.1
0°-30°	647.0	19.8
0°-40°	1038.1	31.7
0°-60°	1769.3	54.1
0°-90°	2203.1	67.4
90°-120°	175.8	5.4
90°-150°	776.0	23.7
90°-180°	1068.0	32.7
0°-180°	3270.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	0	3	5	7	7	2
95°	17	9	10	12	11	21
105°	80	84	16	19	20	86
115°	152	156	163	46	22	149
125°	214	218	223	225	225	191
135°	265	269	272	274	274	205
145°	308	308	312	314	312	192
155°	339	337	340	341	339	156
165°	357	356	356	358	356	101
175°	365	363	364	365	363	35
180°	364	364	364	364	364	



TEST NUMBER: P331336-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	11.9	11.7	11.6	11.3	11.2	11.0	10.8	10.6	10.4	10.0
90°	0.2	0.9	1.5	2.2	2.9	3.4	3.8	4.3	4.8	5.3	5.5
92.5°	5.3	5.3	5.2	5.1	5.1	5.2	5.4	5.6	5.9	6.1	6.3
95°	17.1	15.2	13.3	11.3	9.4	8.6	9.0	9.5	9.9	10.3	10.6
97.5°	34.0	28.5	23.1	17.7	12.2	9.9	10.9	11.8	12.8	13.8	14.0
100°	46.6	38.6	30.6	22.6	14.6	11.0	12.1	13.0	14.0	15.0	15.5
102.5°	60.6	58.9	57.2	55.5	53.8	48.8	40.4	32.1	23.8	15.4	16.1
105°	80.1	81.9	83.6	85.4	87.2	80.1	64.1	48.1	32.0	16.1	16.7
107.5°	102.4	103.9	105.3	106.7	108.1	99.2	80.1	60.9	41.7	22.5	21.9
110°	116.8	118.0	119.3	120.5	121.7	113.8	96.9	80.0	63.0	46.1	40.3



TEST NUMBER: P331336-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.3	131.3	132.5	133.5	134.6	133.1	128.9	124.7	120.5	116.3	95.0
115°	151.6	152.5	153.6	154.6	155.6	156.8	158.2	159.7	161.2	162.7	135.5
117.5°	170.6	171.7	172.8	174.0	175.0	176.1	177.2	178.1	179.1	180.2	173.6
120°	184.5	185.4	186.3	187.2	188.0	189.0	190.0	191.1	192.2	193.2	194.0
122.5°	196.3	197.3	198.2	199.1	200.1	201.1	202.2	203.3	204.6	205.7	206.1
125°	214.3	215.1	215.8	216.6	217.4	218.3	219.4	220.5	221.6	222.7	223.1
127.5°	230.6	231.5	232.3	233.2	234.0	234.8	235.6	236.5	237.3	238.1	238.7
130°	240.9	241.9	242.8	243.8	244.7	245.5	246.1	246.8	247.4	248.1	248.7
132.5°	251.5	252.3	253.1	253.9	254.7	255.4	256.0	256.7	257.3	258.0	258.5
135°	265.2	266.1	267.1	268.0	269.0	269.7	270.2	270.8	271.3	271.8	272.4
137.5°	279.1	279.7	280.4	281.0	281.7	282.3	282.9	283.5	284.1	284.7	285.3
140°	288.1	288.6	289.0	289.5	290.0	290.6	291.2	291.9	292.5	293.1	293.7
142.5°	295.7	296.1	296.5	297.0	297.4	298.0	298.7	299.5	300.2	300.9	301.4
145°	307.6	307.6	307.5	307.4	307.4	307.9	308.8	309.9	310.9	311.9	312.3
147.5°	318.0	317.8	317.6	317.3	317.2	317.5	318.5	319.5	320.5	321.5	321.7
150°	324.7	324.3	323.9	323.5	323.1	323.4	324.3	325.3	326.2	327.2	327.5
152.5°	330.4	330.0	329.5	329.1	328.6	328.8	329.7	330.6	331.5	332.4	332.7
155°	338.8	338.2	337.7	337.1	336.6	336.7	337.5	338.1	338.8	339.5	339.9
157.5°	345.2	344.8	344.3	343.9	343.4	343.5	344.0	344.5	345.0	345.4	345.8
160°	349.0	348.7	348.3	348.0	347.6	347.6	348.0	348.3	348.7	349.0	349.4
162.5°	352.4	352.0	351.7	351.3	351.0	351.0	351.2	351.6	351.9	352.2	352.6
165°	356.9	356.6	356.2	355.9	355.6	355.5	355.6	355.8	356.0	356.1	356.5
167.5°	360.3	360.0	359.6	359.2	358.9	358.8	359.0	359.1	359.3	359.5	359.9
170°	362.2	361.8	361.5	361.2	360.8	360.7	360.8	360.9	361.0	361.2	361.6
172.5°	363.5	363.1	362.7	362.4	362.1	361.9	362.1	362.2	362.3	362.4	362.8
175°	365.1	364.7	364.3	363.9	363.5	363.3	363.5	363.5	363.7	363.8	364.2
177.5°	365.3	365.0	364.7	364.4	364.0	363.9	363.9	364.0	364.0	364.1	364.4
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3



TEST NUMBER: P331336-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	9.6	9.2	8.8	8.6	8.5	8.3	8.2	8.1
90°	5.9	6.1	6.4	6.7	6.8	6.8	7.0	7.1
92.5°	6.4	6.6	6.7	6.8	6.9	7.0	7.0	7.1
95°	10.8	11.2	11.4	11.6	11.5	11.4	11.4	11.3
97.5°	14.3	14.4	14.7	14.8	14.9	15.0	15.1	15.2
100°	16.0	16.5	16.9	17.2	17.3	17.4	17.5	17.7
102.5°	16.6	17.3	17.9	18.3	18.4	18.6	18.8	18.9
105°	17.4	18.0	18.7	19.1	19.3	19.6	19.8	20.1
107.5°	21.2	20.5	19.9	19.6	19.9	20.1	20.4	20.6
110°	34.4	28.5	22.7	19.9	20.1	20.4	20.6	20.8



TEST NUMBER: P331336-930

CATALOG NUMBER: SA2XXDIP-C675D330U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	73.6	52.3	30.9	20.3	20.5	20.6	20.9	21.0
115°	108.4	81.3	54.1	38.5	34.2	30.1	25.8	21.6
117.5°	167.1	160.5	153.9	143.7	129.9	116.0	102.2	88.3
120°	194.6	195.3	196.0	192.4	184.5	176.6	168.7	160.8
122.5°	206.5	206.9	207.3	206.8	205.3	203.7	202.2	200.6
125°	223.6	224.0	224.4	224.7	224.9	225.0	225.2	225.3
127.5°	239.4	239.9	240.5	240.8	240.9	240.9	240.9	241.0
130°	249.3	250.0	250.6	250.9	250.9	250.8	250.8	250.7
132.5°	259.1	259.6	260.2	260.4	260.3	260.3	260.2	260.2
135°	273.0	273.5	274.1	274.3	274.3	274.1	274.0	273.9
137.5°	285.8	286.4	287.0	287.1	287.0	286.8	286.6	286.4
140°	294.2	294.7	295.2	295.4	295.1	294.8	294.5	294.2
142.5°	301.9	302.4	302.9	303.0	302.6	302.4	302.1	301.7
145°	312.7	313.1	313.5	313.6	313.2	313.0	312.7	312.3
147.5°	322.0	322.4	322.7	322.7	322.5	322.2	322.0	321.7
150°	327.8	328.2	328.6	328.6	328.3	328.0	327.7	327.4
152.5°	333.1	333.5	333.8	333.8	333.4	333.0	332.6	332.2
155°	340.2	340.6	341.0	340.9	340.4	340.0	339.5	339.0
157.5°	346.3	346.7	347.0	347.0	346.5	346.1	345.6	345.2
160°	349.8	350.1	350.4	350.4	350.0	349.6	349.2	348.8
162.5°	352.9	353.4	353.8	353.8	353.2	352.7	352.2	351.7
165°	356.9	357.3	357.8	357.8	357.3	356.9	356.5	356.1
167.5°	360.3	360.7	361.1	361.0	360.5	360.0	359.5	358.9
170°	362.0	362.4	362.8	362.7	362.2	361.7	361.2	360.6
172.5°	363.2	363.6	364.0	364.0	363.5	363.0	362.4	361.9
175°	364.6	365.0	365.4	365.3	364.8	364.2	363.5	363.0
177.5°	364.8	365.1	365.4	365.3	364.9	364.5	364.1	363.7
180°	364.3	364.3	364.3	364.3	364.3	364.3	364.3	364.3

(END OF REPORT)