

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331345-930

Luminaire Tested: **SA2XXDIP-C675D530U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331345-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D530U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3926.9 lumens  
Efficiency: N/A  
Efficacy: 97.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331345-930  
CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331345-930

CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47				
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40				
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34				
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29				
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25				
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22				
7	59	47	39	33	55	44	36	31	38	32	28	33	29	25	28	25	22	19				
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	21	18	16				
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331345-930

CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.4	2.1
10°-20°	229.0	5.8
20°-30°	336.6	8.6
30°-40°	391.0	10.0
40°-50°	390.6	9.9
50°-60°	340.6	8.7
60°-70°	251.9	6.4
70°-80°	142.7	3.6
80°-90°	39.8	1.0
90°-100°	19.6	0.5
100°-110°	71.9	1.8
110°-120°	192.3	4.9
120°-130°	317.4	8.1
130°-140°	337.5	8.6
140°-150°	313.7	8.0
150°-160°	252.2	6.4
160°-170°	162.5	4.1
170°-180°	55.9	1.4
0°-30°	647.0	16.5
0°-40°	1038.1	26.4
0°-60°	1769.3	45.1
0°-90°	2203.7	56.1
90°-120°	283.8	7.2
90°-150°	1252.5	31.9
90°-180°	1723.0	43.9
0°-180°	3926.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	0	5	8	11	12	3
95°	28	15	17	19	18	34
105°	129	135	26	30	32	138
115°	245	252	262	75	35	241
125°	346	352	360	362	364	308
135°	428	435	439	443	442	330
145°	496	497	503	506	504	310
155°	547	543	548	550	547	252
165°	576	574	575	578	575	163
175°	589	586	587	590	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331345-930

CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.0	11.9	11.8	11.7	11.6	11.5	11.3	11.2	11.0	10.7
90°	0.4	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1
95°	27.6	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0
97.5°	54.9	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6
100°	75.3	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0
102.5°	97.8	95.1	92.3	89.5	86.8	78.7	65.3	51.9	38.4	24.9	25.9
105°	129.3	132.2	135.0	137.9	140.7	129.2	103.4	77.6	51.8	25.9	27.0
107.5°	165.3	167.6	169.9	172.2	174.5	160.1	129.2	98.2	67.3	36.4	35.3
110°	188.5	190.5	192.5	194.4	196.4	183.8	156.5	129.1	101.7	74.4	65.0



TEST NUMBER: P331345-930

CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3
115°	244.7	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7
117.5°	275.4	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2
120°	297.8	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0
122.5°	316.9	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6
125°	345.9	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2
127.5°	372.2	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3
130°	388.9	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5
132.5°	405.9	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3
135°	428.0	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6
137.5°	450.5	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5
140°	465.0	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0
142.5°	477.3	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5
145°	496.5	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0
147.5°	513.3	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3
150°	524.2	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6
152.5°	533.4	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1
155°	546.7	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6
157.5°	557.2	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2
160°	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9
162.5°	568.8	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1
165°	576.1	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5
167.5°	581.6	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8
170°	584.6	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6
172.5°	586.7	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6
175°	589.3	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8
177.5°	589.7	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331345-930

CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	10.4	9.9	9.6	9.4	9.3	9.2	9.0	9.0
90°	9.5	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.4	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	17.5	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.0	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	25.8	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	26.9	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	28.0	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	34.2	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	55.5	46.1	36.6	32.1	32.4	32.9	33.3	33.6





TEST NUMBER: P331345-930

CATALOG NUMBER: SA2XXDIP-C675D530U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.8	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	175.0	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	269.6	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	314.1	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	333.3	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	360.9	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	386.3	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	402.4	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	418.2	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	440.6	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	461.4	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	474.8	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	487.3	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	504.7	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	519.8	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.1	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	537.7	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.2	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	558.8	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	564.4	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	569.7	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	581.5	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.2	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.3	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	588.5	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	588.7	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)