

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331349-930

Luminaire Tested: **SA2XXDIP-C675D725U930-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331349-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4503.8 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	57	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.1	2.3
10°-20°	299.8	6.7
20°-30°	435.1	9.7
30°-40°	459.2	10.2
40°-50°	406.6	9.0
50°-60°	324.5	7.2
60°-70°	220.5	4.9
70°-80°	113.1	2.5
80°-90°	30.3	0.7
90°-100°	47.9	1.1
100°-110°	148.6	3.3
110°-120°	254.0	5.6
120°-130°	334.1	7.4
130°-140°	375.0	8.3
140°-150°	367.7	8.2
150°-160°	308.4	6.8
160°-170°	204.5	4.5
170°-180°	71.5	1.6
0°-30°	838.1	18.6
0°-40°	1297.3	28.8
0°-60°	2028.3	45.0
0°-90°	2392.2	53.1
90°-120°	450.5	10.0
90°-150°	1527.2	33.9
90°-180°	2112.0	46.9
0°-180°	4503.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	22	1	22	1	22	11
95°	40	33	40	33	40	44
105°	142	137	142	137	142	149
115°	255	255	255	255	255	252
125°	372	371	372	371	372	332
135°	486	480	486	480	486	374
145°	589	582	589	582	589	368
155°	671	666	671	666	671	309
165°	725	725	725	725	725	205
175°	751	754	751	754	751	71
180°	755	755	755	755	755	



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	13.0	13.0	13.3	12.9	12.9	13.2	13.3	13.0	13.4	13.8	13.5
90°	21.7	21.5	21.4	21.3	21.1	21.2	21.4	21.8	22.0	22.3	19.2
92.5°	20.6	20.6	20.6	20.5	20.5	20.5	20.5	20.4	20.3	20.3	19.6
95°	39.5	39.8	40.1	40.4	40.7	40.8	40.8	40.8	40.8	40.8	40.5
97.5°	68.4	68.5	68.5	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.0
100°	87.3	87.5	87.6	87.7	87.9	88.0	88.0	88.0	88.0	88.0	87.5
102.5°	108.7	108.8	109.0	109.2	109.3	109.3	109.2	109.1	108.9	108.8	108.3
105°	141.5	141.5	141.5	141.5	141.5	141.4	141.0	140.8	140.5	140.2	139.9
107.5°	172.4	173.0	173.7	174.3	175.0	175.2	175.0	175.0	174.9	174.7	174.7
110°	196.2	196.7	197.1	197.5	198.0	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.2	219.6	219.8	220.1	220.5	220.8	221.1	221.4	221.8	222.2	222.3
115°	254.9	255.4	255.8	256.2	256.6	256.9	257.1	257.1	257.3	257.5	257.7
117.5°	288.9	289.3	289.8	290.2	290.7	291.0	291.4	291.7	292.0	292.4	293.2
120°	312.9	313.3	313.7	314.1	314.6	314.8	314.8	314.8	314.8	314.8	315.9
122.5°	336.4	336.6	337.0	337.3	337.6	337.9	338.3	338.6	338.9	339.2	340.1
125°	372.2	372.3	372.4	372.6	372.8	373.0	373.4	373.9	374.3	374.7	375.1
127.5°	404.8	405.3	405.7	406.2	406.6	407.1	407.6	408.1	408.6	409.1	409.6
130°	428.3	428.8	429.4	429.9	430.5	431.0	431.2	431.5	431.8	432.1	432.4
132.5°	450.7	451.1	451.6	452.0	452.5	453.1	453.6	454.3	454.9	455.5	455.4
135°	485.6	486.0	486.5	486.9	487.3	487.5	487.7	487.9	488.0	488.1	487.9
137.5°	517.2	517.8	518.4	518.9	519.5	519.8	519.9	520.1	520.2	520.2	519.9
140°	539.2	539.7	540.3	540.9	541.4	541.7	541.7	541.7	541.7	541.7	541.0
142.5°	559.1	559.6	560.1	560.7	561.3	561.5	561.4	561.3	561.2	561.1	560.6
145°	588.8	589.4	590.0	590.5	591.1	591.3	591.2	591.0	590.9	590.8	589.9
147.5°	615.5	616.0	616.5	617.1	617.7	617.8	617.4	617.1	616.8	616.5	616.0
150°	632.8	633.2	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8	632.3
152.5°	649.1	649.6	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1	648.4
155°	671.1	671.5	671.9	672.3	672.8	672.6	671.9	671.2	670.5	669.8	669.4
157.5°	689.9	690.6	691.3	691.9	692.6	692.5	691.5	690.6	689.6	688.6	688.4
160°	701.6	702.2	702.8	703.4	703.9	703.8	703.0	702.1	701.2	700.3	700.3
162.5°	711.8	712.5	713.2	713.9	714.5	714.4	713.5	712.5	711.5	710.5	710.5
165°	725.2	725.9	726.6	727.3	728.1	727.9	726.9	725.9	725.0	723.9	723.9
167.5°	736.2	736.9	737.7	738.4	739.2	739.0	738.0	737.0	736.1	735.0	735.1
170°	741.8	742.7	743.5	744.4	745.2	745.1	744.1	743.1	742.2	741.1	741.3
172.5°	746.4	747.2	748.0	748.9	749.7	749.7	748.7	747.7	746.7	745.8	745.9
175°	751.4	752.2	753.0	753.9	754.7	754.6	753.7	752.7	751.7	750.7	751.0
177.5°	753.7	754.3	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7	753.8
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	13.2	12.6	12.0	12.1	10.8	10.4	8.8	7.4	7.4	7.5	7.2
90°	16.1	13.0	9.9	7.4	5.7	4.1	2.4	0.7	2.4	4.1	5.7
92.5°	18.8	18.0	17.3	16.3	15.1	13.9	12.6	11.3	12.6	13.9	15.1
95°	40.2	39.9	39.6	38.8	37.4	36.0	34.6	33.1	34.6	36.0	37.4
97.5°	67.5	66.9	66.4	65.6	64.2	63.0	61.8	60.6	61.8	63.0	64.2
100°	87.1	86.7	86.3	85.4	84.3	83.2	82.1	81.0	82.1	83.2	84.3
102.5°	107.8	107.2	106.7	106.0	105.1	104.2	103.2	102.3	103.2	104.2	105.1
105°	139.7	139.3	139.1	138.7	138.3	137.9	137.5	137.1	137.5	137.9	138.3
107.5°	174.7	174.7	174.7	174.4	173.8	173.2	172.6	171.9	172.6	173.2	173.8
110°	198.2	198.2	198.2	197.8	196.9	196.1	195.2	194.4	195.2	196.1	196.9





TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.4	222.5	222.6	222.3	221.4	220.5	219.7	218.8	219.7	220.5	221.4
115°	258.0	258.3	258.6	258.3	257.5	256.6	255.8	254.9	255.8	256.6	257.5
117.5°	294.0	294.7	295.5	295.4	294.2	293.1	292.0	290.8	292.0	293.1	294.2
120°	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	315.9	317.1	318.2
122.5°	340.9	341.7	342.4	342.2	340.8	339.5	338.1	336.7	338.1	339.5	340.8
125°	375.5	376.0	376.4	376.0	374.7	373.4	372.2	370.9	372.2	373.4	374.7
127.5°	410.2	410.7	411.2	410.6	409.0	407.4	405.8	404.1	405.8	407.4	409.0
130°	432.6	432.9	433.2	432.4	430.6	428.8	426.9	425.1	426.9	428.8	430.6
132.5°	455.4	455.3	455.3	454.5	453.0	451.5	450.0	448.5	450.0	451.5	453.0
135°	487.5	487.3	487.0	486.1	484.5	483.0	481.4	479.9	481.4	483.0	484.5
137.5°	519.5	519.2	518.8	518.0	516.7	515.4	514.1	512.9	514.1	515.4	516.7
140°	540.3	539.6	538.8	537.9	536.5	535.3	534.0	532.8	534.0	535.3	536.5
142.5°	560.1	559.6	559.1	558.2	557.0	555.7	554.4	553.2	554.4	555.7	557.0
145°	589.1	588.2	587.3	586.4	585.5	584.5	583.4	582.4	583.4	584.5	585.5
147.5°	615.4	614.8	614.2	613.3	612.1	611.0	609.8	608.6	609.8	611.0	612.1
150°	631.7	631.1	630.6	629.8	629.0	628.1	627.3	626.5	627.3	628.1	629.0
152.5°	647.8	647.1	646.4	645.6	644.8	643.9	643.1	642.2	643.1	643.9	644.8
155°	669.0	668.5	668.1	667.6	667.2	666.8	666.3	665.9	666.3	666.8	667.2
157.5°	688.1	687.9	687.6	687.4	687.1	686.8	686.5	686.2	686.5	686.8	687.1
160°	700.1	699.9	699.8	699.6	699.3	699.0	698.7	698.5	698.7	699.0	699.3
162.5°	710.3	710.1	710.0	709.9	709.8	709.8	709.7	709.6	709.7	709.8	709.8
165°	723.9	723.9	723.9	724.0	724.1	724.3	724.5	724.6	724.5	724.3	724.1
167.5°	735.1	735.2	735.2	735.4	735.8	736.2	736.6	737.0	736.6	736.2	735.8
170°	741.4	741.6	741.7	742.0	742.4	742.8	743.3	743.7	743.3	742.8	742.4
172.5°	746.0	746.2	746.3	746.6	747.0	747.5	747.9	748.3	747.9	747.5	747.0
175°	751.3	751.5	751.9	752.2	752.6	753.0	753.5	753.9	753.5	753.0	752.6
177.5°	754.1	754.3	754.6	754.8	755.1	755.5	755.9	756.2	755.9	755.5	755.1
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	7.2	7.3	7.6	8.2	8.5	8.8	8.4	8.3	8.3	7.6	7.6
90°	7.4	9.9	13.0	16.1	19.2	22.3	22.0	21.8	21.4	21.2	21.1
92.5°	16.3	17.3	18.0	18.8	19.6	20.3	20.3	20.4	20.5	20.5	20.5
95°	38.8	39.6	39.9	40.2	40.5	40.8	40.8	40.8	40.8	40.8	40.7
97.5°	65.6	66.4	66.9	67.5	68.0	68.6	68.6	68.6	68.6	68.6	68.6
100°	85.4	86.3	86.7	87.1	87.5	88.0	88.0	88.0	88.0	88.0	87.9
102.5°	106.0	106.7	107.2	107.8	108.3	108.8	108.9	109.1	109.2	109.3	109.3
105°	138.7	139.1	139.3	139.7	139.9	140.2	140.5	140.8	141.0	141.4	141.5
107.5°	174.4	174.7	174.7	174.7	174.7	174.7	174.9	175.0	175.0	175.2	175.0
110°	197.8	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.0



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	222.3	222.6	222.5	222.4	222.3	222.2	221.8	221.4	221.1	220.8	220.5
115°	258.3	258.6	258.3	258.0	257.7	257.5	257.3	257.1	257.1	256.9	256.6
117.5°	295.4	295.5	294.7	294.0	293.2	292.4	292.0	291.7	291.4	291.0	290.7
120°	319.4	319.4	318.2	317.1	315.9	314.8	314.8	314.8	314.8	314.8	314.6
122.5°	342.2	342.4	341.7	340.9	340.1	339.2	338.9	338.6	338.3	337.9	337.6
125°	376.0	376.4	376.0	375.5	375.1	374.7	374.3	373.9	373.4	373.0	372.8
127.5°	410.6	411.2	410.7	410.2	409.6	409.1	408.6	408.1	407.6	407.1	406.6
130°	432.4	433.2	432.9	432.6	432.4	432.1	431.8	431.5	431.2	431.0	430.5
132.5°	454.5	455.3	455.3	455.4	455.4	455.5	454.9	454.3	453.6	453.1	452.5
135°	486.1	487.0	487.3	487.5	487.9	488.1	488.0	487.9	487.7	487.5	487.3
137.5°	518.0	518.8	519.2	519.5	519.9	520.2	520.2	520.1	519.9	519.8	519.5
140°	537.9	538.8	539.6	540.3	541.0	541.7	541.7	541.7	541.7	541.7	541.4
142.5°	558.2	559.1	559.6	560.1	560.6	561.1	561.2	561.3	561.4	561.5	561.3
145°	586.4	587.3	588.2	589.1	589.9	590.8	590.9	591.0	591.2	591.3	591.1
147.5°	613.3	614.2	614.8	615.4	616.0	616.5	616.8	617.1	617.4	617.8	617.7
150°	629.8	630.6	631.1	631.7	632.3	632.8	633.2	633.7	634.1	634.5	634.5
152.5°	645.6	646.4	647.1	647.8	648.4	649.1	649.6	650.2	650.8	651.3	651.3
155°	667.6	668.1	668.5	669.0	669.4	669.8	670.5	671.2	671.9	672.6	672.8
157.5°	687.4	687.6	687.9	688.1	688.4	688.6	689.6	690.6	691.5	692.5	692.6
160°	699.6	699.8	699.9	700.1	700.3	700.3	701.2	702.1	703.0	703.8	703.9
162.5°	709.9	710.0	710.1	710.3	710.5	710.5	711.5	712.5	713.5	714.4	714.5
165°	724.0	723.9	723.9	723.9	723.9	723.9	725.0	725.9	726.9	727.9	728.1
167.5°	735.4	735.2	735.2	735.1	735.1	735.0	736.1	737.0	738.0	739.0	739.2
170°	742.0	741.7	741.6	741.4	741.3	741.1	742.2	743.1	744.1	745.1	745.2
172.5°	746.6	746.3	746.2	746.0	745.9	745.8	746.7	747.7	748.7	749.7	749.7
175°	752.2	751.9	751.5	751.3	751.0	750.7	751.7	752.7	753.7	754.6	754.7
177.5°	754.8	754.6	754.3	754.1	753.8	753.7	754.3	755.0	755.7	756.4	756.4
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	7.6	7.3	7.3	7.0	7.3	7.3	7.6	7.6	7.6	8.3	8.3
90°	21.3	21.4	21.5	21.7	21.5	21.4	21.3	21.1	21.2	21.4	21.8
92.5°	20.5	20.6	20.6	20.6	20.6	20.6	20.5	20.5	20.5	20.5	20.4
95°	40.4	40.1	39.8	39.5	39.8	40.1	40.4	40.7	40.8	40.8	40.8
97.5°	68.6	68.5	68.5	68.4	68.5	68.5	68.6	68.6	68.6	68.6	68.6
100°	87.7	87.6	87.5	87.3	87.5	87.6	87.7	87.9	88.0	88.0	88.0
102.5°	109.2	109.0	108.8	108.7	108.8	109.0	109.2	109.3	109.3	109.2	109.1
105°	141.5	141.5	141.5	141.5	141.5	141.5	141.5	141.5	141.4	141.0	140.8
107.5°	174.3	173.7	173.0	172.4	173.0	173.7	174.3	175.0	175.2	175.0	175.0
110°	197.5	197.1	196.7	196.2	196.7	197.1	197.5	198.0	198.2	198.2	198.2



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	220.1	219.8	219.6	219.2	219.6	219.8	220.1	220.5	220.8	221.1	221.4
115°	256.2	255.8	255.4	254.9	255.4	255.8	256.2	256.6	256.9	257.1	257.1
117.5°	290.2	289.8	289.3	288.9	289.3	289.8	290.2	290.7	291.0	291.4	291.7
120°	314.1	313.7	313.3	312.9	313.3	313.7	314.1	314.6	314.8	314.8	314.8
122.5°	337.3	337.0	336.6	336.4	336.6	337.0	337.3	337.6	337.9	338.3	338.6
125°	372.6	372.4	372.3	372.2	372.3	372.4	372.6	372.8	373.0	373.4	373.9
127.5°	406.2	405.7	405.3	404.8	405.3	405.7	406.2	406.6	407.1	407.6	408.1
130°	429.9	429.4	428.8	428.3	428.8	429.4	429.9	430.5	431.0	431.2	431.5
132.5°	452.0	451.6	451.1	450.7	451.1	451.6	452.0	452.5	453.1	453.6	454.3
135°	486.9	486.5	486.0	485.6	486.0	486.5	486.9	487.3	487.5	487.7	487.9
137.5°	518.9	518.4	517.8	517.2	517.8	518.4	518.9	519.5	519.8	519.9	520.1
140°	540.9	540.3	539.7	539.2	539.7	540.3	540.9	541.4	541.7	541.7	541.7
142.5°	560.7	560.1	559.6	559.1	559.6	560.1	560.7	561.3	561.5	561.4	561.3
145°	590.5	590.0	589.4	588.8	589.4	590.0	590.5	591.1	591.3	591.2	591.0
147.5°	617.1	616.5	616.0	615.5	616.0	616.5	617.1	617.7	617.8	617.4	617.1
150°	634.1	633.7	633.2	632.8	633.2	633.7	634.1	634.5	634.5	634.1	633.7
152.5°	650.8	650.2	649.6	649.1	649.6	650.2	650.8	651.3	651.3	650.8	650.2
155°	672.3	671.9	671.5	671.1	671.5	671.9	672.3	672.8	672.6	671.9	671.2
157.5°	691.9	691.3	690.6	689.9	690.6	691.3	691.9	692.6	692.5	691.5	690.6
160°	703.4	702.8	702.2	701.6	702.2	702.8	703.4	703.9	703.8	703.0	702.1
162.5°	713.9	713.2	712.5	711.8	712.5	713.2	713.9	714.5	714.4	713.5	712.5
165°	727.3	726.6	725.9	725.2	725.9	726.6	727.3	728.1	727.9	726.9	725.9
167.5°	738.4	737.7	736.9	736.2	736.9	737.7	738.4	739.2	739.0	738.0	737.0
170°	744.4	743.5	742.7	741.8	742.7	743.5	744.4	745.2	745.1	744.1	743.1
172.5°	748.9	748.0	747.2	746.4	747.2	748.0	748.9	749.7	749.7	748.7	747.7
175°	753.9	753.0	752.2	751.4	752.2	753.0	753.9	754.7	754.6	753.7	752.7
177.5°	755.7	755.0	754.3	753.7	754.3	755.0	755.7	756.4	756.4	755.7	755.0
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	8.4	8.8	8.5	8.2	7.6	7.3	7.2	7.2	7.5	7.4	7.4
90°	22.0	22.3	19.2	16.1	13.0	9.9	7.4	5.7	4.1	2.4	0.7
92.5°	20.3	20.3	19.6	18.8	18.0	17.3	16.3	15.1	13.9	12.6	11.3
95°	40.8	40.8	40.5	40.2	39.9	39.6	38.8	37.4	36.0	34.6	33.1
97.5°	68.6	68.6	68.0	67.5	66.9	66.4	65.6	64.2	63.0	61.8	60.6
100°	88.0	88.0	87.5	87.1	86.7	86.3	85.4	84.3	83.2	82.1	81.0
102.5°	108.9	108.8	108.3	107.8	107.2	106.7	106.0	105.1	104.2	103.2	102.3
105°	140.5	140.2	139.9	139.7	139.3	139.1	138.7	138.3	137.9	137.5	137.1
107.5°	174.9	174.7	174.7	174.7	174.7	174.7	174.4	173.8	173.2	172.6	171.9
110°	198.2	198.2	198.2	198.2	198.2	198.2	197.8	196.9	196.1	195.2	194.4



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	221.8	222.2	222.3	222.4	222.5	222.6	222.3	221.4	220.5	219.7	218.8
115°	257.3	257.5	257.7	258.0	258.3	258.6	258.3	257.5	256.6	255.8	254.9
117.5°	292.0	292.4	293.2	294.0	294.7	295.5	295.4	294.2	293.1	292.0	290.8
120°	314.8	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8
122.5°	338.9	339.2	340.1	340.9	341.7	342.4	342.2	340.8	339.5	338.1	336.7
125°	374.3	374.7	375.1	375.5	376.0	376.4	376.0	374.7	373.4	372.2	370.9
127.5°	408.6	409.1	409.6	410.2	410.7	411.2	410.6	409.0	407.4	405.8	404.1
130°	431.8	432.1	432.4	432.6	432.9	433.2	432.4	430.6	428.8	426.9	425.1
132.5°	454.9	455.5	455.4	455.4	455.3	455.3	454.5	453.0	451.5	450.0	448.5
135°	488.0	488.1	487.9	487.5	487.3	487.0	486.1	484.5	483.0	481.4	479.9
137.5°	520.2	520.2	519.9	519.5	519.2	518.8	518.0	516.7	515.4	514.1	512.9
140°	541.7	541.7	541.0	540.3	539.6	538.8	537.9	536.5	535.3	534.0	532.8
142.5°	561.2	561.1	560.6	560.1	559.6	559.1	558.2	557.0	555.7	554.4	553.2
145°	590.9	590.8	589.9	589.1	588.2	587.3	586.4	585.5	584.5	583.4	582.4
147.5°	616.8	616.5	616.0	615.4	614.8	614.2	613.3	612.1	611.0	609.8	608.6
150°	633.2	632.8	632.3	631.7	631.1	630.6	629.8	629.0	628.1	627.3	626.5
152.5°	649.6	649.1	648.4	647.8	647.1	646.4	645.6	644.8	643.9	643.1	642.2
155°	670.5	669.8	669.4	669.0	668.5	668.1	667.6	667.2	666.8	666.3	665.9
157.5°	689.6	688.6	688.4	688.1	687.9	687.6	687.4	687.1	686.8	686.5	686.2
160°	701.2	700.3	700.3	700.1	699.9	699.8	699.6	699.3	699.0	698.7	698.5
162.5°	711.5	710.5	710.5	710.3	710.1	710.0	709.9	709.8	709.8	709.7	709.6
165°	725.0	723.9	723.9	723.9	723.9	723.9	724.0	724.1	724.3	724.5	724.6
167.5°	736.1	735.0	735.1	735.1	735.2	735.2	735.4	735.8	736.2	736.6	737.0
170°	742.2	741.1	741.3	741.4	741.6	741.7	742.0	742.4	742.8	743.3	743.7
172.5°	746.7	745.8	745.9	746.0	746.2	746.3	746.6	747.0	747.5	747.9	748.3
175°	751.7	750.7	751.0	751.3	751.5	751.9	752.2	752.6	753.0	753.5	753.9
177.5°	754.3	753.7	753.8	754.1	754.3	754.6	754.8	755.1	755.5	755.9	756.2
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	8.8	10.4	10.8	12.1	12.0	12.6	13.2	13.5	13.8	13.4	13.0
90°	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0	21.8
92.5°	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3	20.4
95°	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8	40.8
97.5°	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6	68.6
100°	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0	88.0
102.5°	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9	109.1
105°	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5	140.8
107.5°	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9	175.0
110°	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2	198.2





TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8	221.4
115°	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3	257.1
117.5°	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0	291.7
120°	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8	314.8
122.5°	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9	338.6
125°	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3	373.9
127.5°	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6	408.1
130°	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8	431.5
132.5°	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9	454.3
135°	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0	487.9
137.5°	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2	520.1
140°	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7	541.7
142.5°	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2	561.3
145°	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9	591.0
147.5°	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8	617.1
150°	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2	633.7
152.5°	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6	650.2
155°	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5	671.2
157.5°	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6	690.6
160°	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2	702.1
162.5°	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5	712.5
165°	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0	725.9
167.5°	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1	737.0
170°	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2	743.1
172.5°	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7	747.7
175°	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7	752.7
177.5°	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3	755.0
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	13.3	13.2	12.9	12.9	13.3	13.0	13.0
90°	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.0	197.5	197.1	196.7	196.2



TEST NUMBER: P331349-930

CATALOG NUMBER: SA2XXDIP-C675D725U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)