

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331364-930

Luminaire Tested: **SA2XXDIP-C675D925U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331364-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4902.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	45	44	43	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	1.7
10°-20°	229.0	4.7
20°-30°	336.6	6.9
30°-40°	391.0	8.0
40°-50°	390.6	8.0
50°-60°	340.6	6.9
60°-70°	251.9	5.1
70°-80°	142.7	2.9
80°-90°	42.2	0.9
90°-100°	61.1	1.2
100°-110°	189.8	3.9
110°-120°	324.3	6.6
120°-130°	426.5	8.7
130°-140°	478.7	9.8
140°-150°	469.4	9.6
150°-160°	393.7	8.0
160°-170°	261.1	5.3
170°-180°	91.3	1.9
0°-30°	647.0	13.2
0°-40°	1038.1	21.2
0°-60°	1769.3	36.1
0°-90°	2206.1	45.0
90°-120°	575.2	11.7
90°-150°	1949.8	39.8
90°-180°	2696.0	55.0
0°-180°	4902.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	1	11	28	27	28	4
95°	42	50	52	52	50	49
105°	175	177	179	180	181	185
115°	326	330	329	328	326	322
125°	474	480	478	476	475	423
135°	613	621	623	622	620	473
145°	744	749	754	755	752	464
155°	850	853	855	859	857	391
165°	925	924	924	929	926	261
175°	962	960	958	964	959	91
180°	964	964	964	964	964	



TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	12.3	12.4	12.6	12.7	13.0	13.5	14.0	14.5	15.0	14.5
90°	0.8	3.0	5.1	7.3	9.5	12.6	16.6	20.5	24.5	28.5	28.1
92.5°	14.5	16.1	17.7	19.2	20.9	22.1	23.1	24.0	24.9	25.8	25.9
95°	42.3	44.1	45.9	47.7	49.6	50.6	51.0	51.4	51.7	52.1	52.1
97.5°	77.3	78.9	80.5	82.1	83.6	84.8	85.5	86.2	86.8	87.6	87.6
100°	103.3	104.8	106.2	107.7	109.1	110.1	110.6	111.2	111.8	112.3	112.3
102.5°	130.7	131.8	133.0	134.1	135.3	136.2	136.9	137.6	138.3	139.0	139.1
105°	175.0	175.5	176.0	176.6	177.1	177.6	177.9	178.3	178.6	179.0	179.4
107.5°	219.5	220.3	221.1	221.9	222.7	223.1	223.1	223.1	223.1	223.1	223.2
110°	248.2	249.2	250.3	251.4	252.5	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.4	280.5	281.6	282.7	283.7	284.2	284.1	283.9	283.8	283.6	283.2
115°	325.5	326.5	327.6	328.7	329.8	330.1	329.8	329.5	329.1	328.7	328.6
117.5°	371.4	372.8	374.2	375.7	377.2	377.3	376.3	375.3	374.3	373.3	372.8
120°	401.9	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	401.9
122.5°	429.9	431.6	433.4	435.1	436.8	437.2	436.2	435.2	434.2	433.2	432.8
125°	473.5	475.2	476.8	478.4	480.0	480.6	480.0	479.5	479.0	478.4	477.8
127.5°	516.0	518.0	520.2	522.2	524.2	525.0	524.3	523.7	523.0	522.4	521.7
130°	542.7	545.0	547.4	549.8	552.1	553.1	552.7	552.4	552.0	551.6	551.3
132.5°	572.7	574.5	576.5	578.4	580.3	581.3	581.4	581.5	581.5	581.6	580.8
135°	612.7	614.7	616.6	618.6	620.6	621.8	622.2	622.5	622.9	623.2	623.1
137.5°	654.8	656.4	658.0	659.7	661.3	662.3	662.8	663.3	663.8	664.2	664.1
140°	680.2	681.8	683.5	685.1	686.7	687.9	688.8	689.7	690.7	691.6	691.6
142.5°	706.2	707.8	709.5	711.1	712.7	713.9	714.4	715.1	715.7	716.3	716.5
145°	743.6	744.9	746.2	747.5	748.7	749.9	751.0	752.0	753.2	754.2	754.4
147.5°	777.0	778.5	780.1	781.5	783.1	784.2	785.0	785.6	786.4	787.1	787.5
150°	799.8	800.9	801.9	803.1	804.1	805.0	805.8	806.5	807.2	808.0	808.5
152.5°	819.9	821.1	822.1	823.2	824.3	825.3	826.1	827.0	827.9	828.8	829.5
155°	850.3	850.8	851.3	851.9	852.4	853.0	853.5	854.0	854.6	855.1	856.1
157.5°	876.1	876.4	876.9	877.2	877.6	877.9	878.2	878.6	878.9	879.2	880.4
160°	891.8	892.1	892.4	892.8	893.2	893.5	893.6	893.8	894.0	894.1	895.3
162.5°	906.0	906.1	906.2	906.3	906.4	906.4	906.7	906.9	907.0	907.2	908.4
165°	925.1	925.0	924.7	924.5	924.4	924.3	924.3	924.3	924.3	924.3	925.5
167.5°	941.0	940.5	940.0	939.4	938.9	938.6	938.6	938.5	938.5	938.4	939.7
170°	949.5	948.9	948.4	947.9	947.3	947.0	946.8	946.6	946.4	946.2	947.5
172.5°	955.4	954.8	954.3	953.7	953.2	952.8	952.7	952.4	952.3	952.1	953.4
175°	962.5	962.0	961.4	960.9	960.3	959.9	959.5	959.2	958.8	958.5	959.7
177.5°	965.5	965.0	964.6	964.2	963.7	963.4	963.0	962.8	962.5	962.2	963.0
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	14.0	13.5	13.0	12.6	12.6	12.4	12.3	12.2
90°	27.7	27.4	27.1	26.9	27.1	27.3	27.5	27.6
92.5°	26.0	26.1	26.2	26.3	26.3	26.3	26.3	26.3
95°	52.1	52.1	52.1	51.9	51.5	51.2	50.8	50.5
97.5°	87.6	87.6	87.6	87.6	87.5	87.5	87.4	87.4
100°	112.3	112.3	112.3	112.2	112.0	111.9	111.6	111.5
102.5°	139.3	139.4	139.6	139.5	139.3	139.2	139.0	138.8
105°	179.7	180.1	180.4	180.6	180.6	180.6	180.6	180.6
107.5°	223.4	223.6	223.6	223.3	222.5	221.7	220.9	220.0
110°	253.1	253.1	253.1	252.7	252.3	251.7	251.1	250.6



TEST NUMBER: P331364-930

CATALOG NUMBER: SA2XXDIP-C675D925U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	282.7	282.3	281.9	281.4	281.1	280.7	280.3	279.9
115°	328.3	328.2	328.0	327.6	327.1	326.5	326.0	325.5
117.5°	372.4	372.0	371.5	371.0	370.6	370.0	369.4	368.9
120°	401.9	401.9	401.9	401.7	401.1	400.6	400.1	399.5
122.5°	432.3	431.9	431.5	431.0	430.6	430.2	429.8	429.4
125°	477.4	476.8	476.2	475.9	475.7	475.5	475.3	475.2
127.5°	521.1	520.4	519.8	519.1	518.5	518.0	517.4	516.8
130°	550.9	550.6	550.2	549.7	548.9	548.2	547.5	546.7
132.5°	580.0	579.2	578.4	577.7	577.2	576.6	576.0	575.4
135°	622.9	622.7	622.5	622.2	621.6	621.1	620.5	620.0
137.5°	664.0	663.8	663.7	663.2	662.5	661.8	661.0	660.3
140°	691.6	691.6	691.6	691.2	690.5	689.7	689.1	688.4
142.5°	716.6	716.7	716.9	716.6	715.9	715.2	714.4	713.7
145°	754.6	754.8	755.0	754.7	754.0	753.3	752.5	751.8
147.5°	787.9	788.3	788.7	788.6	787.9	787.2	786.5	785.8
150°	809.0	809.6	810.1	810.1	809.6	809.0	808.5	808.0
152.5°	830.1	830.8	831.5	831.5	830.8	830.1	829.5	828.8
155°	857.0	857.9	858.8	858.9	858.3	857.9	857.3	856.7
157.5°	881.7	882.9	884.1	884.3	883.5	882.6	881.7	880.8
160°	896.3	897.4	898.5	898.7	898.0	897.2	896.5	895.8
162.5°	909.6	910.9	912.1	912.3	911.4	910.5	909.7	908.8
165°	926.8	928.1	929.4	929.5	928.6	927.7	926.8	925.9
167.5°	940.9	942.2	943.5	943.6	942.7	941.8	940.9	939.9
170°	948.8	950.1	951.3	951.4	950.3	949.3	948.1	947.1
172.5°	954.6	955.9	957.2	957.2	956.2	955.1	954.0	952.9
175°	961.0	962.2	963.5	963.6	962.5	961.4	960.3	959.3
177.5°	963.9	964.8	965.6	965.6	964.8	963.9	963.0	962.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2

(END OF REPORT)